Product data sheet


Subminiature connectors




Product description Bayonet male panel mount connector, Contacts: 4, shielding is not possible, solder, IP40

Area Bayonet series 710
Order number 09 0981 00 04

Illustration





You can find the assembly instructions on the next page.

Technical data

General values

Connector design
Connector locking system
Termination
Wire gauge (mm)
Wire gauge (AWG)
Upper limit temperature
Lower limit temperature
Customs tariff number
Packaging Unit

male panel mount connector Bayonet solder 0.25 mm² 24 85 °C - 40 °C 85369010 50

Electrical values

Rated current (40 °C) 3 A Rated voltage 125 V Rated impulse voltage 1500 V Pollution degree Overvoltage category П Insulating material group Insulation resistance $\geq 10^{10} \, \Omega$ EMC compliance shielding is not possible Degree of protection > 500 Mating cycles Mechanical operation

Material

Contact material CuZn (brass)
Contact plating Au (gold)
Contact body material PA (UL94 V-0)
Housing material PA


Product data sheet

Subminiature connectors



Product description Bayonet male panel mount connector, Contacts: 4, shielding is not possible, solder, IP40

Area Bayonet series 710 Order number 09 0981 00 04



Product data sheet

Subminiature connectors



Product description Bayonet male panel mount connector, Contacts: 4, shielding is not possible, solder, IP40

Area Bayonet series 710
Order number 09 0981 00 04

Security notices

The connector must not be connected or separated under load. Non-observance and incorrect use can result in personal injury.

The connectors are designed for use in plant, control system and electrical equipment. The end user is responsible for checking whether the connectors are suitable for use in other applications.