


Cement Fixed Resistors Axial Leaded

multicomp PRO

**RoHS
Compliant**



Specifications

Rated Power	: 1W, 2W, 3W, 5W, 7W, 10W, 15W, 20W and 25W
Max. Working Voltage	: 500V
Max. Overload Voltage	: 1000V
Rated Ambient Temp.	: +70°C
Operating Temp. Range	: -55°C to +155°C
Resistance Tolerance	: ±5% & ±10%

Power Rating

Resistors shall have a power rating based on continuous full load operation at an ambient temperature of 70°C

Voltage Rating

Resistors shall have a rated direct-current (DC) continuous working voltage or an approximate sine-wave root-mean-square (RMS) alternating-current (AC) continuous working voltage at commercial line frequency and waveform corresponding to the power rating, as determined from the following formula:


$$RCWV = \sqrt{P \times R}$$

RCWV = Rated DC or RMS AC continuous working voltage at commercial-line frequency and waveform (Volt)


P = Power Rating (watt)

R = Nominal Resistance (ohm)

Heat Rise Chart



Derating Curve




Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO

Cement Fixed Resistors Axial Leaded

Construction



List of Material

No.	Subpart Name	Material	Material Generic Name
1	Body	Rod Type Ceramics	Al ₂ O ₃ , SiO ₂
2	End Cap	Tin plated iron surface	Tin: 5%, Iron: 95%
3	Lead	Annealed copper wire	Tin-Plated Copper wire
4	Ceramic Case	Ceramic	Al ₂ O ₃ , SiO ₂
5	Resistance wire Resistance film	Cu-Ni Alloy / Ni-Cr Alloy Metal Oxide Film	Cu-Ni Alloy / Ni-Cr Alloy Metal Oxide Film
6	Filling Materials	Quartz mixed sand	SiO ₂

Characteristic

Characteristics	Limits	Test Methods (JIS C 5201-1)
Dielectric withstanding voltage	No evidence of flashover, mechanical damage, arcing or insulation break down	Resistors shall be clamped in the trough of a 90° metallic V-block and shall be tested at AC potential respectively for 60 +10/ -0 secs.
Temperature coefficient	<20Ω: ± 400 PPM/°C ≥ 20Ω: ± 350 PPM/°C	Natural resistance change per temp. degree centigrade. $\frac{R_2 - R_1}{R_1(t_2 - t_1)} \times 10^6 \text{ (PPM/°C)}$ R ₁ : Resistance value at room temperature (t ₁) R ₂ : Resistance value at room temp. plus 100°C (t ₂)
Short time overload	Resistance change rate is ±(5% + 0.05Ω) Max. with no evidence of mechanical damage	Permanent resistance change after the application of a potential of 2.5 times RCWV for 5 seconds
Terminal strength	No evidence of mechanical damage	Direct load: Resistance to a 2.5 kgs direct load for 10 secs. in the direction of the longitudinal axis of the terminal leads Twist test: Terminal leads shall be bent through 90° at a point of about 6mm from the body of the resistor and shall be rotated through 360° about the original axis of the bent terminal in alternating direction for a total of 3 rotations

Cement Fixed Resistors

Axial Leaded


multicomp PRO

Characteristics	Limits	Test Methods (JIS C 5201-1)															
Solderability	95% coverage Min.	The area covered with a new, smooth clean, shiny and continuous surface free from concentrated pin-holes. Test temp. of solder : 245°C ±5°C Dwell time in solder : 2 to 3 secs.															
Soldering temp. reference	Electrical characteristics shall be satisfied. Without distinct deformation in appearance. (95 % coverage Min.)	The leads immersed into solder bath to 3.2 to 4.8mm. from the body. Permanent resistance change shall be checked. Wave soldering condition: (2 cycles Max.) Pre-heat : 100 ~ 120°C, 30 ±5sec. Suggestion solder temp.: 235 ~ 255°C, 10 sec. (Max.) Peak temp.: 260°C Hand soldering condition: Hand Soldering bit temp. : 380 ±10°C Dwell time in solder : 3 +1/-0 sec.															
Resistance to soldering heat	Resistance change rate is ±(1% + 0.05Ω) Max. with no evidence of mechanical damage	Permanent resistance change when leads immersed to 3.2 to 4.8 mm from the body in 350°C ± 10°C solder for 3 ±0.5 secs.															
Temperature cycling	Resistance change rate is ±(2% + 0.05Ω) Max. with no evidence of mechanical damage	Resistance change after continuous 5 cycles for duty shown below:															
		<table border="1"> <thead> <tr> <th>Step</th> <th>Temperature</th> <th>Time</th> </tr> </thead> <tbody> <tr> <td>1</td> <td>-55°C ±3°C</td> <td>30 mins</td> </tr> <tr> <td>2</td> <td>Room temp.</td> <td>10~15 mins</td> </tr> <tr> <td>3</td> <td>+155°C ±2°C</td> <td>30 mins</td> </tr> <tr> <td>4</td> <td>Room temp.</td> <td>10~15 mins</td> </tr> </tbody> </table>	Step	Temperature	Time	1	-55°C ±3°C	30 mins	2	Room temp.	10~15 mins	3	+155°C ±2°C	30 mins	4	Room temp.	10~15 mins
		Step	Temperature	Time													
		1	-55°C ±3°C	30 mins													
		2	Room temp.	10~15 mins													
3	+155°C ±2°C	30 mins															
4	Room temp.	10~15 mins															
Load life in humidity	Resistance value	ΔR/R															
	Wire-wound	±5%															
	Power film:	<100kΩ ±5% ≥100kΩ ±10%															
		Resistance change after 1,000 hours operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") in a humidity test chamber controlled at 40°C ± 2°C and 90 to 95 % relative humidity															
Load life	Resistance value	ΔR/R															
	Wire-wound	±5%															
	Power film:	<100kΩ ±5% ≥100kΩ ±10%															
		Permanent resistance change after 1,000 hours operating at RCWV with duty cycle of (1.5 hours "on", 0.5 hour "off") at 70°C ±2°C ambient															

Cement Fixed Resistors

Axial Leaded

Diagram



Rating Wattage	W ±1 (mm)	D ±1 (mm)	L ±1 (mm)	d ±0.05 (mm)	H ±5 (mm)	Wire-wound Resistance Range	Power Film Resistance Range
1W	6	6	14	0.7	25	-	30Ω
2W	7	7	18	0.75	28	4.7Ω	100Ω, 3.3KΩ
3W	8	8	22		32	0.15Ω to 0.82Ω	56Ω to 25KΩ
5W	10	9	35		35	0.1Ω to 47Ω	56Ω to 39KΩ
7W			15Ω to 33Ω			-	
10W			0.1Ω to 820Ω			1KΩ to 27KΩ	
15W	12.5	11.5	49			1Ω to 1KΩ	-
20W	14.5	13.5	60			3.3Ω to 100Ω	-
25W			64			0.2Ω to 1.2KΩ	1.5KΩ to 8.2KΩ

Part Number Table

Description	Part Number
Axial Leaded Power Film Resistor, 1W, 30R, ±5%	MCPRW01WJP300B00
Axial Leaded Wire Wound Resistor, 2W, 4.7R, ±5%	MCPRW02WJW47JB00
Axial Leaded Power Film Resistor, 2W, 100R, ±10%	MCPRW02WKP101B00
Axial Leaded Power Film Resistor, 2W, 3.3K, ±10%	MCPRW02WKP332B00
Axial Leaded Wire Wound Resistor, 3W, 0.15R, ±5%	MCPRW03WJW15KB00
Axial Leaded Wire Wound Resistor, 3W, 0.3R, ±5%	MCPRW03WJW30KB00
Axial Leaded Wire Wound Resistor, 3W, 0.68R, ±5%	MCPRW03WJW68KB00
Axial Leaded Wire Wound Resistor, 3W, 0.82R, ±5%	MCPRW03WJW82KB00
Axial Leaded Power Film Resistor, 3W, 56R, ±5%	MCPRW03WJP560B00
Axial Leaded Power Film Resistor, 3W, 560R, ±5%	MCPRW03WJP561B00
Axial Leaded Power Film Resistor, 3W, 25K, ±5%	MCPRW03WJP253B00
Axial Leaded Wire Wound Resistor, 5W, 0.1R, ±5%	MP006022
Axial Leaded Wire Wound Resistor, 5W, 0.12R, ±5%	MP006023
Axial Leaded Wire Wound Resistor, 5W, 0.15R, ±5%	MP006024
Axial Leaded Wire Wound Resistor, 5W, 0.18R, ±5%	MP006025
Axial Leaded Wire Wound Resistor, 5W, 0.2R, ±5%	MP006026
Axial Leaded Wire Wound Resistor, 5W, 0.22R, ±5%	MP006027

Cement Fixed Resistors

Axial Leaded

Description	Part Number
Axial Leaded Wire Wound Resistor, 5W, 0.24R, $\pm 5\%$	MP006028
Axial Leaded Wire Wound Resistor, 5W, 0.27R, $\pm 5\%$	MP006029
Axial Leaded Wire Wound Resistor, 5W, 0.3R, $\pm 5\%$	MP006030
Axial Leaded Wire Wound Resistor, 5W, 0.33R, $\pm 5\%$	MP006031
Axial Leaded Wire Wound Resistor, 5W, 0.36R, $\pm 5\%$	MP006032
Axial Leaded Wire Wound Resistor, 5W, 0.39R, $\pm 5\%$	MP006033
Axial Leaded Wire Wound Resistor, 5W, 0.43R, $\pm 5\%$	MP006034
Axial Leaded Wire Wound Resistor, 5W, 0.47R, $\pm 5\%$	MP006035
Axial Leaded Wire Wound Resistor, 5W, 0.51R, $\pm 5\%$	MP006036
Axial Leaded Wire Wound Resistor, 5W, 0.56R, $\pm 5\%$	MP006037
Axial Leaded Wire Wound Resistor, 5W, 0.62R, $\pm 5\%$	MP006038
Axial Leaded Wire Wound Resistor, 5W, 0.68R, $\pm 5\%$	MP006039
Axial Leaded Wire Wound Resistor, 5W, 0.75R, $\pm 5\%$	MP006040
Axial Leaded Wire Wound Resistor, 5W, 0.82R, $\pm 5\%$	MP006041
Axial Leaded Wire Wound Resistor, 5W, 0.91R, $\pm 5\%$	MP006042
Axial Leaded Wire Wound Resistor, 5W, 1R, $\pm 5\%$	MP006043
Axial Leaded Wire Wound Resistor, 5W, 1.2R, $\pm 5\%$	MP006044
Axial Leaded Wire Wound Resistor, 5W, 1.5R, $\pm 5\%$	MP006045
Axial Leaded Wire Wound Resistor, 5W, 1.8R, $\pm 5\%$	MP006046
Axial Leaded Wire Wound Resistor, 5W, 2R, $\pm 5\%$	MCPRW05WJW20JB00
Axial Leaded Wire Wound Resistor, 5W, 2.2R, $\pm 5\%$	MP006047
Axial Leaded Wire Wound Resistor, 5W, 2.7R, $\pm 5\%$	MP006048
Axial Leaded Wire Wound Resistor, 5W, 3.3R, $\pm 5\%$	MP006049
Axial Leaded Wire Wound Resistor, 5W, 3.9R, $\pm 5\%$	MCPRW05WJW39JB00
Axial Leaded Wire Wound Resistor, 5W, 4.7R, $\pm 5\%$	MP006051
Axial Leaded Wire Wound Resistor, 5W, 5R, $\pm 5\%$	MP006052
Axial Leaded Wire Wound Resistor, 5W, 5.1R, $\pm 5\%$	MP006053
Axial Leaded Wire Wound Resistor, 5W, 5.6R, $\pm 5\%$	MP006054
Axial Leaded Wire Wound Resistor, 5W, 6.8R, $\pm 5\%$	MCPRW05WJW68JB00
Axial Leaded Wire Wound Resistor, 5W, 8.2R, $\pm 5\%$	MP006056
Axial Leaded Wire Wound Resistor, 5W, 10R, $\pm 5\%$	MCPRW05WJW100B00
Axial Leaded Wire Wound Resistor, 5W, 12R, $\pm 5\%$	MP006058
Axial Leaded Wire Wound Resistor, 5W, 15R, $\pm 5\%$	MP006059
Axial Leaded Wire Wound Resistor, 5W, 18R, $\pm 5\%$	MP006060
Axial Leaded Wire Wound Resistor, 5W, 20R, $\pm 5\%$	MCPRW05WJW200B00
Axial Leaded Wire Wound Resistor, 5W, 22R, $\pm 5\%$	MP006061
Axial Leaded Wire Wound Resistor, 5W, 27R, $\pm 5\%$	MCPRW05WJW270B00
Axial Leaded Wire Wound Resistor, 5W, 30R, $\pm 5\%$	MCPRW05WJW300B00

Cement Fixed Resistors

Axial Leaded

multicomp PRO

Description	Part Number
Axial Leaded Wire Wound Resistor, 5W, 33R, $\pm 5\%$	MCPRW05WJW330B00
Axial Leaded Wire Wound Resistor, 5W, 39R, $\pm 5\%$	MP006064
Axial Leaded Wire Wound Resistor, 5W, 47R, $\pm 5\%$	MCPRW05WJW470B00
Axial Leaded Power Film Resistor, 5W, 56R, $\pm 5\%$	MP005990
Axial Leaded Power Film Resistor, 5W, 68R, $\pm 5\%$	MP005991
Axial Leaded Power Film Resistor, 5W, 82R, $\pm 5\%$	MP005992
Axial Leaded Power Film Resistor, 5W, 100R, $\pm 5\%$	MP005993
Axial Leaded Power Film Resistor, 5W, 120R, $\pm 5\%$	MP005994
Axial Leaded Power Film Resistor, 5W, 150R, $\pm 5\%$	MP005995
Axial Leaded Power Film Resistor, 5W, 180R, $\pm 5\%$	MP005996
Axial Leaded Power Film Resistor, 5W, 220R, $\pm 5\%$	MP005997
Axial Leaded Power Film Resistor, 5W, 270R, $\pm 5\%$	MP005998
Axial Leaded Power Film Resistor, 5W, 330R, $\pm 5\%$	MCPRW05WJP331B00
Axial Leaded Power Film Resistor, 5W, 390R, $\pm 5\%$	MP006000
Axial Leaded Power Film Resistor, 5W, 470R, $\pm 5\%$	MP006001
Axial Leaded Power Film Resistor, 5W, 560R, $\pm 5\%$	MP006002
Axial Leaded Power Film Resistor, 5W, 680R, $\pm 5\%$	MP006003
Axial Leaded Power Film Resistor, 5W, 820R, $\pm 5\%$	MP006004
Axial Leaded Power Film Resistor, 5W, 1K, $\pm 5\%$	MP006005
Axial Leaded Power Film Resistor, 5W, 1.2K, $\pm 5\%$	MP006006
Axial Leaded Power Film Resistor, 5W, 1.5K, $\pm 5\%$	MP006007
Axial Leaded Power Film Resistor, 5W, 1.8K, $\pm 5\%$	MP006008
Axial Leaded Power Film Resistor, 5W, 2K, $\pm 5\%$	MCPRW05WJP202B00
Axial Leaded Power Film Resistor, 5W, 2.2K, $\pm 5\%$	MP006009
Axial Leaded Power Film Resistor, 5W, 2.7K, $\pm 5\%$	MP006010
Axial Leaded Power Film Resistor, 5W, 3.3K, $\pm 5\%$	MP006011
Axial Leaded Power Film Resistor, 5W, 3.9K, $\pm 5\%$	MCPRW05WJP392B00
Axial Leaded Power Film Resistor, 5W, 4.7K, $\pm 5\%$	MP006013
Axial Leaded Power Film Resistor, 5W, 5.6K, $\pm 5\%$	MP006014
Axial Leaded Power Film Resistor, 5W, 6.8K, $\pm 5\%$	MP006015
Axial Leaded Power Film Resistor, 5W, 8.2K, $\pm 5\%$	MP006016
Axial Leaded Power Film Resistor, 5W, 8.5K, $\pm 5\%$	MP006017
Axial Leaded Power Film Resistor, 5W, 10K, $\pm 5\%$	MP006018
Axial Leaded Power Film Resistor, 5W, 11K, $\pm 5\%$	MP006019
Axial Leaded Power Film Resistor, 5W, 12K, $\pm 5\%$	MP006020
Axial Leaded Power Film Resistor, 5W, 15K, $\pm 5\%$	MP006021
Axial Leaded Power Film Resistor, 5W, 33K, $\pm 5\%$	MCPRW05WJP333B00
Axial Leaded Power Film Resistor, 5W, 39K, $\pm 5\%$	MCPRW05WJP393B00
Axial Leaded Wire Wound Resistor, 7W, 15R, $\pm 5\%$	MCPRW07WJW150B00

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO

Cement Fixed Resistors

Axial Leaded

multicomp PRO

Description	Part Number
Axial Leaded Wire Wound Resistor, 7W, 20R, $\pm 5\%$	MCPRW07WJW200B00
Axial Leaded Wire Wound Resistor, 7W, 33R, $\pm 5\%$	MCPRW07WJW330B00
Axial Leaded Wire Wound Resistor, 10W, 0.1R, $\pm 5\%$	MP006085
Axial Leaded Wire Wound Resistor, 10W, 0.12R, $\pm 5\%$	MP006086
Axial Leaded Wire Wound Resistor, 10W, 0.15R, $\pm 5\%$	MP006087
Axial Leaded Wire Wound Resistor, 10W, 0.18R, $\pm 5\%$	MP006088
Axial Leaded Wire Wound Resistor, 10W, 0.2R, $\pm 5\%$	MP006089
Axial Leaded Wire Wound Resistor, 10W, 0.22R, $\pm 5\%$	MP006090
Axial Leaded Wire Wound Resistor, 10W, 0.24R, $\pm 5\%$	MP006091
Axial Leaded Wire Wound Resistor, 10W, 0.27R, $\pm 5\%$	MP006092
Axial Leaded Wire Wound Resistor, 10W, 0.3R, $\pm 5\%$	MP006093
Axial Leaded Wire Wound Resistor, 10W, 0.33R, $\pm 5\%$	MP006094
Axial Leaded Wire Wound Resistor, 10W, 0.36R, $\pm 5\%$	MP006095
Axial Leaded Wire Wound Resistor, 10W, 0.39R, $\pm 5\%$	MP006096
Axial Leaded Wire Wound Resistor, 10W, 0.43R, $\pm 5\%$	MP006097
Axial Leaded Wire Wound Resistor, 10W, 0.47R, $\pm 5\%$	MP006098
Axial Leaded Wire Wound Resistor, 10W, 0.51R, $\pm 5\%$	MP006099
Axial Leaded Wire Wound Resistor, 10W, 0.56R, $\pm 5\%$	MP006100
Axial Leaded Wire Wound Resistor, 10W, 0.62R, $\pm 5\%$	MP006101
Axial Leaded Wire Wound Resistor, 10W, 0.68R, $\pm 5\%$	MP006102
Axial Leaded Wire Wound Resistor, 10W, 0.75R, $\pm 5\%$	MP006103
Axial Leaded Wire Wound Resistor, 10W, 0.82R, $\pm 5\%$	MP006104
Axial Leaded Wire Wound Resistor, 10W, 0.91R, $\pm 5\%$	MP006105
Axial Leaded Wire Wound Resistor, 10W, 1R, $\pm 5\%$	MCPRW0AWJW10JB00
Axial Leaded Wire Wound Resistor, 10W, 1.2R, $\pm 5\%$	MP006107
Axial Leaded Wire Wound Resistor, 10W, 1.5R, $\pm 5\%$	MP006108
Axial Leaded Wire Wound Resistor, 10W, 1.8R, $\pm 5\%$	MP006109
Axial Leaded Wire Wound Resistor, 10W, 2R, $\pm 5\%$	MCPRW0AWJW20JB00
Axial Leaded Wire Wound Resistor, 10W, 2.2R, $\pm 5\%$	MP006111
Axial Leaded Wire Wound Resistor, 10W, 2.7R, $\pm 5\%$	MCPRW0AWJW27JB00
Axial Leaded Wire Wound Resistor, 10W, 3R, $\pm 5\%$	MCPRW0AWJW30JB00
Axial Leaded Wire Wound Resistor, 10W, 3.3R, $\pm 5\%$	MP006113
Axial Leaded Wire Wound Resistor, 10W, 3.9R, $\pm 5\%$	MP006114
Axial Leaded Wire Wound Resistor, 10W, 4.7R, $\pm 5\%$	MP006115
Axial Leaded Wire Wound Resistor, 10W, 5.1R, $\pm 5\%$	MP006116
Axial Leaded Wire Wound Resistor, 10W, 5.6R, $\pm 5\%$	MCPRW0AWJW56JB00
Axial Leaded Wire Wound Resistor, 10W, 6.8R, $\pm 5\%$	MP006118
Axial Leaded Wire Wound Resistor, 10W, 7.5R, $\pm 5\%$	MCPRW0AWJW75JB00
Axial Leaded Wire Wound Resistor, 10W, 8.2R, $\pm 5\%$	MP006119

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO

Cement Fixed Resistors

Axial Leaded

multicomp PRO

Description	Part Number
Axial Leaded Wire Wound Resistor, 10W, 10R, $\pm 5\%$	MCPRW0AWJW100B00
Axial Leaded Wire Wound Resistor, 10W, 12R, $\pm 5\%$	MP006121
Axial Leaded Wire Wound Resistor, 10W, 15R, $\pm 5\%$	MP006122
Axial Leaded Wire Wound Resistor, 10W, 18R, $\pm 5\%$	MP006123
Axial Leaded Wire Wound Resistor, 10W, 20R, $\pm 5\%$	MCPRW0AWJW200B00
Axial Leaded Wire Wound Resistor, 10W, 22R, $\pm 5\%$	MP006124
Axial Leaded Wire Wound Resistor, 10W, 27R, $\pm 5\%$	MCPRW0AWJW270B00
Axial Leaded Wire Wound Resistor, 10W, 30R, $\pm 5\%$	MCPRW0AWJW300B00
Axial Leaded Wire Wound Resistor, 10W, 33R, $\pm 5\%$	MP006126
Axial Leaded Wire Wound Resistor, 10W, 39R, $\pm 5\%$	MP006127
Axial Leaded Wire Wound Resistor, 10W, 39R, $\pm 5\%$	MCPRW0AWJW390B00
Axial Leaded Wire Wound Resistor, 10W, 43R, $\pm 5\%$	MCPRW0AWJW430B00
Axial Leaded Wire Wound Resistor, 10W, 47R, $\pm 5\%$	MCPRW0AWJW470B00
Axial Leaded Wire Wound Resistor, 10W, 56R, $\pm 5\%$	MCPRW0AWJW560B00
Axial Leaded Wire Wound Resistor, 10W, 68R, $\pm 5\%$	MCPRW0AWJW680B00
Axial Leaded Wire Wound Resistor, 10W, 75R, $\pm 5\%$	MCPRW0AWJW750B00
Axial Leaded Wire Wound Resistor, 10W, 82R, $\pm 5\%$	MCPRW0AWJW820B00
Axial Leaded Wire Wound Resistor, 10W, 100R, $\pm 5\%$	MP006133
Axial Leaded Wire Wound Resistor, 10W, 120R, $\pm 5\%$	MP006134
Axial Leaded Wire Wound Resistor, 10W, 150R, $\pm 5\%$	MCPRW0AWJW151B00
Axial Leaded Wire Wound Resistor, 10W, 180R, $\pm 5\%$	MP006136
Axial Leaded Wire Wound Resistor, 10W, 220R, $\pm 5\%$	MP006137
Axial Leaded Wire Wound Resistor, 10W, 270R, $\pm 5\%$	MP006138
Axial Leaded Wire Wound Resistor, 10W, 330R, $\pm 5\%$	MP006139
Axial Leaded Wire Wound Resistor, 10W, 390R, $\pm 5\%$	MCPRW0AWJW391B00
Axial Leaded Wire Wound Resistor, 10W, 470R, $\pm 5\%$	MP006141
Axial Leaded Wire Wound Resistor, 10W, 560R, $\pm 5\%$	MP006142
Axial Leaded Wire Wound Resistor, 10W, 680R, $\pm 5\%$	MP006143
Axial Leaded Wire Wound Resistor, 10W, 750R, $\pm 5\%$	MCPRW0AWJW751B00
Axial Leaded Wire Wound Resistor, 10W, 820R, $\pm 5\%$	MCPRW0AWJW821B00
Axial Leaded Power Film Resistor, 10W, 1K, $\pm 5\%$	MCPRW0AWJP102B00
Axial Leaded Power Film Resistor, 10W, 1.2K, $\pm 5\%$	MP006067
Axial Leaded Power Film Resistor, 10W, 1.5K, $\pm 5\%$	MP006068
Axial Leaded Power Film Resistor, 10W, 1.8K, $\pm 5\%$	MP006069
Axial Leaded Power Film Resistor, 10W, 2.2K, $\pm 5\%$	MP006070
Axial Leaded Power Film Resistor, 10W, 2.7K, $\pm 5\%$	MP006071
Axial Leaded Power Film Resistor, 10W, 3.3K, $\pm 5\%$	MP006072
Axial Leaded Power Film Resistor, 10W, 3.9K, $\pm 5\%$	MP006073
Axial Leaded Power Film Resistor, 10W, 4.7K, $\pm 5\%$	MP006074

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO

Cement Fixed Resistors

Axial Leaded

multicomp PRO

Description	Part Number
Axial Leaded Power Film Resistor, 10W, 5.6K, $\pm 5\%$	MP006075
Axial Leaded Power Film Resistor, 10W, 6.8K, $\pm 5\%$	MP006076
Axial Leaded Power Film Resistor, 10W, 8.2K, $\pm 5\%$	MP006077
Axial Leaded Power Film Resistor, 10W, 10K, $\pm 5\%$	MCPRW0AWJP103B00
Axial Leaded Power Film Resistor, 10W, 11K, $\pm 5\%$	MP006079
Axial Leaded Power Film Resistor, 10W, 12K, $\pm 5\%$	MP006080
Axial Leaded Power Film Resistor, 10W, 15K, $\pm 5\%$	MP006081
Axial Leaded Power Film Resistor, 10W, 18K, $\pm 5\%$	MP006082
Axial Leaded Power Film Resistor, 10W, 22K, $\pm 5\%$	MP006083
Axial Leaded Power Film Resistor, 10W, 27K, $\pm 5\%$	MP006084
Axial Leaded Wire Wound Resistor, 15W, 1R, $\pm 5\%$	MCPRW0FWJW10JB00
Axial Leaded Wire Wound Resistor, 15W, 2R, $\pm 5\%$	MCPRW0FWJW20JB00
Axial Leaded Wire Wound Resistor, 15W, 4.7R, $\pm 5\%$	MCPRW0FWJW47JB00
Axial Leaded Wire Wound Resistor, 15W, 10R, $\pm 5\%$	MCPRW0FWJW100B00
Axial Leaded Wire Wound Resistor, 15W, 27R, $\pm 5\%$	MCPRW0FWJW270B00
Axial Leaded Wire Wound Resistor, 15W, 30R, $\pm 5\%$	MCPRW0FWJW300B00
Axial Leaded Wire Wound Resistor, 15W, 47R, $\pm 5\%$	MCPRW0FWJW470B00
Axial Leaded Wire Wound Resistor, 15W, 390R, $\pm 5\%$	MCPRW0FWJW391B00
Axial Leaded Wire Wound Resistor, 15W, 430R, $\pm 5\%$	MCPRW0FWJW431B00
Axial Leaded Wire Wound Resistor, 15W, 1K, $\pm 5\%$	MCPRW0FWJW102B00
Axial Leaded Wire Wound Resistor, 20W, 3.3R, $\pm 5\%$	MCPRW020JW33JB00
Axial Leaded Wire Wound Resistor, 20W, 3.9R, $\pm 5\%$	MCPRW020JW39JB00
Axial Leaded Wire Wound Resistor, 20W, 4.7R, $\pm 5\%$	MCPRW020JW47JB00
Axial Leaded Wire Wound Resistor, 20W, 5.6R, $\pm 5\%$	MCPRW020JW56JB00
Axial Leaded Wire Wound Resistor, 20W, 8.2R, $\pm 5\%$	MCPRW020JW82JB00
Axial Leaded Wire Wound Resistor, 20W, 10R, $\pm 5\%$	MCPRW020JW100B00
Axial Leaded Wire Wound Resistor, 20W, 100R, $\pm 5\%$	MCPRW020JW101B00
Axial Leaded Wire Wound Resistor, 25W, 0.2R, $\pm 5\%$	MP006155
Axial Leaded Wire Wound Resistor, 25W, 0.22R, $\pm 5\%$	MP006156
Axial Leaded Wire Wound Resistor, 25W, 0.24R, $\pm 5\%$	MP006157
Axial Leaded Wire Wound Resistor, 25W, 0.27R, $\pm 5\%$	MP006158
Axial Leaded Wire Wound Resistor, 25W, 0.3R, $\pm 5\%$	MP006159
Axial Leaded Wire Wound Resistor, 25W, 0.33R, $\pm 5\%$	MP006160
Axial Leaded Wire Wound Resistor, 25W, 0.36R, $\pm 5\%$	MP006161
Axial Leaded Wire Wound Resistor, 25W, 0.39R, $\pm 5\%$	MP006162
Axial Leaded Wire Wound Resistor, 25W, 0.43R, $\pm 5\%$	MP006163
Axial Leaded Wire Wound Resistor, 25W, 0.47R, $\pm 5\%$	MP006164
Axial Leaded Wire Wound Resistor, 25W, 0.51R, $\pm 5\%$	MP006165
Axial Leaded Wire Wound Resistor, 25W, 0.56R, $\pm 5\%$	MP006166

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO

Cement Fixed Resistors

Axial Leaded

multicomp PRO

Description	Part Number
Axial Leaded Wire Wound Resistor, 25W, 0.62R, $\pm 5\%$	MP006167
Axial Leaded Wire Wound Resistor, 25W, 0.68R, $\pm 5\%$	MP006168
Axial Leaded Wire Wound Resistor, 25W, 0.75R, $\pm 5\%$	MP006169
Axial Leaded Wire Wound Resistor, 25W, 0.82R, $\pm 5\%$	MP006170
Axial Leaded Wire Wound Resistor, 25W, 0.91R, $\pm 5\%$	MP006171
Axial Leaded Wire Wound Resistor, 25W, 1R, $\pm 5\%$	MP006172
Axial Leaded Wire Wound Resistor, 25W, 1.2R, $\pm 5\%$	MP006173
Axial Leaded Wire Wound Resistor, 25W, 1.5R, $\pm 5\%$	MP006174
Axial Leaded Wire Wound Resistor, 25W, 2R, $\pm 5\%$	MCPRW025JW20JB00
Axial Leaded Wire Wound Resistor, 25W, 2.2R, $\pm 5\%$	MP006176
Axial Leaded Wire Wound Resistor, 25W, 2.7R, $\pm 5\%$	MCPRW025JW27JB00
Axial Leaded Wire Wound Resistor, 25W, 3R, $\pm 5\%$	MCPRW025JW30JB00
Axial Leaded Wire Wound Resistor, 25W, 3.3R, $\pm 5\%$	MP006179
Axial Leaded Wire Wound Resistor, 25W, 3.9R, $\pm 5\%$	MCPRW025JW39JB00
Axial Leaded Wire Wound Resistor, 25W, 4.7R, $\pm 5\%$	MCPRW025JW47JB00
Axial Leaded Wire Wound Resistor, 25W, 5.1R, $\pm 5\%$	MP006182
Axial Leaded Wire Wound Resistor, 25W, 5.6R, $\pm 5\%$	MP006183
Axial Leaded Wire Wound Resistor, 25W, 6.8R, $\pm 5\%$	MCPRW025JW68JB00
Axial Leaded Wire Wound Resistor, 25W, 8.2R, $\pm 5\%$	MP006185
Axial Leaded Wire Wound Resistor, 25W, 10R, $\pm 5\%$	MP006186
Axial Leaded Wire Wound Resistor, 25W, 15R, $\pm 5\%$	MCPRW025JW150B00
Axial Leaded Wire Wound Resistor, 25W, 20R, $\pm 5\%$	MCPRW025JW200B00
Axial Leaded Wire Wound Resistor, 25W, 27R, $\pm 5\%$	MCPRW025JW270B00
Axial Leaded Wire Wound Resistor, 25W, 30R, $\pm 5\%$	MCPRW025JW300B00
Axial Leaded Wire Wound Resistor, 25W, 39R, $\pm 5\%$	MP006191
Axial Leaded Wire Wound Resistor, 25W, 47R, $\pm 5\%$	MP006192
Axial Leaded Wire Wound Resistor, 25W, 62R, $\pm 5\%$	MP006193
Axial Leaded Wire Wound Resistor, 25W, 75R, $\pm 5\%$	MP006194
Axial Leaded Wire Wound Resistor, 25W, 82R, $\pm 5\%$	MCPRW025JW820B00
Axial Leaded Wire Wound Resistor, 25W, 100R, $\pm 5\%$	MCPRW025JW101B00
Axial Leaded Wire Wound Resistor, 25W, 120R, $\pm 5\%$	MP006196
Axial Leaded Wire Wound Resistor, 25W, 150R, $\pm 5\%$	MP006197
Axial Leaded Wire Wound Resistor, 25W, 180R, $\pm 5\%$	MP006198
Axial Leaded Wire Wound Resistor, 25W, 220R, $\pm 5\%$	MP006199
Axial Leaded Wire Wound Resistor, 25W, 270R, $\pm 5\%$	MP006200
Axial Leaded Wire Wound Resistor, 25W, 330R, $\pm 5\%$	MCPRW025JW331B00
Axial Leaded Wire Wound Resistor, 25W, 390R, $\pm 5\%$	MP006202
Axial Leaded Wire Wound Resistor, 25W, 470R, $\pm 5\%$	MCPRW025JW471B00
Axial Leaded Wire Wound Resistor, 25W, 560R, $\pm 5\%$	MP006204

Newark.com/multicomp-pro
 Farnell.com/multicomp-pro
 Element14.com/multicomp-pro

multicomp PRO

Cement Fixed Resistors

Axial Leaded

multicomp PRO

Description	Part Number
Axial Leaded Wire Wound Resistor, 25W, 680R, $\pm 5\%$	MP006205
Axial Leaded Wire Wound Resistor, 25W, 820R, $\pm 5\%$	MCPRW025JW821B00
Axial Leaded Wire Wound Resistor, 25W, 1K, $\pm 5\%$	MCPRW025JW102B00
Axial Leaded Wire Wound Resistor, 25W, 1.2K, $\pm 5\%$	MP006208
Axial Leaded Power Film Resistor, 25W, 1.5K, $\pm 5\%$	MP006145
Axial Leaded Power Film Resistor, 25W, 1.8K, $\pm 5\%$	MP006146
Axial Leaded Power Film Resistor, 25W, 2.2K, $\pm 5\%$	MP006147
Axial Leaded Power Film Resistor, 25W, 2.3K, $\pm 5\%$	MP006148
Axial Leaded Power Film Resistor, 25W, 2.7K, $\pm 5\%$	MP006149
Axial Leaded Power Film Resistor, 25W, 3.9K, $\pm 5\%$	MP006150
Axial Leaded Power Film Resistor, 25W, 4.7K, $\pm 5\%$	MP006151
Axial Leaded Power Film Resistor, 25W, 5.6K, $\pm 5\%$	MP006152
Axial Leaded Power Film Resistor, 25W, 6.8K, $\pm 5\%$	MP006153
Axial Leaded Power Film Resistor, 25W, 8.2K, $\pm 5\%$	MP006154

Important Notice : This data sheet and its contents (the "Information") belong to the members of the AVNET group of companies (the "Group") or are licensed to it. No licence is granted for the use of it other than for information purposes in connection with the products to which it relates. No licence of any intellectual property rights is granted. The Information is subject to change without notice and replaces all data sheets previously supplied. The Information supplied is believed to be accurate but the Group assumes no responsibility for its accuracy or completeness, any error in or omission from it or for any use made of it. Users of this data sheet should check for themselves the Information and the suitability of the products for their purpose and not make any assumptions based on information included or omitted. Liability for loss or damage resulting from any reliance on the Information or use of it (including liability resulting from negligence or where the Group was aware of the possibility of such loss or damage arising) is excluded. This will not operate to limit or restrict the Group's liability for death or personal injury resulting from its negligence. Multicomp Pro is the registered trademark of Premier Farnell Limited 2019.

Newark.com/multicomp-pro
Farnell.com/multicomp-pro
Element14.com/multicomp-pro

multicomp PRO