

Specification Sheet

Part Number: 118-00110



Outside serrations minimize damage to cables, while still providing high tensile strength and low insertion force.

Contour style head design provides additional space in constrained areas.

Heat stabilized material provides excellent resistance to high heat exposures.

Outside Serrated Cable Tie, 5.9" Long, 50lb Tensile Strength, PA66HS, Black, 1000/pkg

Article Number 118-00110

Type T50SOS

Color Black (BK)

Quantity Per bag

Product Description HellermannTyton outside serrated cable ties are designed with a smooth inside surface to help minimize indentation or damage to wire and cable insulation, while offering high tensile strength and low insertion force. The contour style head takes up less space than traditional style cable ties making it ideal for space constrained areas. For high volume applications, tensioning tools are available to ensure consistent and safe installation.

Short Description	Outside Serrated Cable Tie, 5.9" Long, 50lb Tensile Strength, PA66HS, Black, 1000/pkg
Global Part Name	T50SOS-PA66HS-BK
Minimum Tensile Strength (Imperial)	50.0
Minimum Tensile Strength (Metric)	225
Length L (Imperial)	5.9
Length L (Metric)	150.0
Identification Plate Position	none
Releasable Closure	No
Tie Closure	plastic pawl
Variant	Outside Serrated
Width W (Imperial)	0.18
Width W (Metric)	4.6
Bundle Diameter Min (Imperial)	0.06
Bundle Diameter Min (Metric)	1.6
Bundle Diameter Max (Imperial)	1.4

Bundle Diameter Max (Metric) 35.0

Height H (Imperial) 0.05

Height H (Metric) 1.3

Material Polyamide 6.6 heat stabilized (PA66HS)

Material Shortcut PA66HS

Flammability UL 94 V-2

Halogen Free Yes

Operating Temperature -40°F to +257°F (-40°C to +125°C)

ROHS Compliant Yes

Package Quantity (Imperial) 1000

Package Quantity (Metric) 1000

Customs Number 3926909988

