

Series PVT412APbF

Microelectronic Power IC

HEXFET® Power MOSFET Photovoltaic Relay Single Pole, Normally Open, 0-400V, 240mA AC / 360mA DC

General Description

The PVT412A Series Photovoltaic Relay is a single-pole, normally open solid-state relay that can replace electromechanical relays in many applications. It utilizes International Rectifier's proprietary HEXFET power MOSFET as the output switch, driven by an integrated circuit photovoltaic generator of novel construction. The output switch is controlled by radiation from a GaAlAs light emitting diode (LED) which is optically isolated from the photovoltaic generator.

These SSRs are specifically designed for industrial control and peripheral telecom applications.

Series PVT412A Relays are packaged in a 6-lead molded DIP package with either thru-hole or surface mount ('gull-wing') terminals. It is available in standard plastic shipping tubes or on tape-and-reel. Please refer to part identification information

Applications

- Control of AC power line (up to 240 VAC) industrial loads
- Control of DC industrial loads up to +/-300 VDC
- On/Off hook switch
- Dial-pulse generation

Part Identification


PVT412APbF thru-hole PVT412ASPbF surface-mount

PVT412AS-TPbF surface-mount, Tape and Reel

Features

- HEXFET Power MOSFET output
- Bounce-free operation
- 4,000 V_{RMS} I/O isolation
- Very low on-resistance (R_{DD-ON})
- Linear AC/DC operation
- Solid-State Reliability
- UL Recognized
- ESD Tolerance:

4000V Human Body Model 500V Machine Model



(HEXFET is the registered trademark for International Rectifier Power MOSFETs)



$\textbf{Electrical Specifications} \ 0\text{-}400\text{V}, 240\text{ma}, AC \ (T_{A=} +25^{\circ}\text{C}) \ unless \ otherwise \ specified)$


INPUT CHARACTERISTICS	Limits	Units
Minimum Control Current (see figure 1)	3.0	mA
Maximum Control Current for Off-State Resistance	0.4	mA
Control Current Range (Caution: current limit input LED, see figure 5)	3.0 to 25	mA
Maximum Reverse Voltage	6.0	V


OUTPUT CHARACTERISTICS	Limits	Units	
Operating Voltage Range	0 to ±400	V peak	
Maximum Load Current @ T _A =+40°C 5mA Control (see figure 1)			
A Connection	240	mA	
B Connection	260	mA	
C Connection	360	mA	
Maximum On-State Resistance @Ta=+25°C			
100mA Pulsed Load, 5mA Control (see figures 2 & 3)			
A Connection	6	Ω	
B Connection	3	Ω	
C Connection	2	Ω	
Max. pulsed Load Current @Ta=+25°C, ±400V, 5mA Control (10mS @ 10% duty cycle)	750	mA	
Maximum Off-State Leakage @T _A =+25°C, ±400V	1.0	μA	
Maximum Turn-On Time @TA=+25°C (see figures 6 & 7)			
For 50mA, 100 V _{DC} load, 5mA Control (5mS pulse width @ 50% duty cycle)	3.0	ms	
Maximum Turn-Off Time @T _A =+25°C (see figures 6 & 7)			
For 50mA, 100 V _{DC} load, 5mA Control (5mS pulse width @ 50% duty cycle)	0.5	ms	
Maximum Output Capacitance @ 50V _{DC} , f=1MHz (Cout, see figure 8)	40.0	pF	


GENERAL CHARACTERISTICS		Limits	Units
Minimum Dielectric Strength, Input-Output		4000	V _{RMS}
Minimum Insulation Resistance, Input-Output		10 ¹²	Ω
Maximum Capacitance, Input-Output Vd=0V, f=1MHz		1.0	pF
Maximum Pin Soldering Temperature (10 seconds maximum)		+260	
Ambient Temperature Range:	Operating	-40 to +85	_ ℃
	Storage	-40 to +100	

International Rectifier does not recommend the use of this product in aerospace, avionics, military or life support applications. Users of this International Rectifier product in such applications assume all risks of such use and indemnify International Rectifier against all damages resulting from such use.

Connection Diagrams












Figure 1. Current Derating Curves




Figure 2. Typical On Characteristics




Figure 3. Typical On-Characteristics





Figure 4. Typical Normalized Off-State Leakage





10.00 "A" Connection

1.00

Tolf


0.10

1 2 3 4 5 6 7 8 9 10

ILED (mA)

Figure 5. Input Characteristics (Current Controlled)

Figure 6. Typical Delay Times










Figure 8. Typical Output Capacitance



Case Outlines





Note: For the most current drawing please refer to IR website at: http://www.irf.com/package/



Qualification information[†]

Qualification level	Industrial		
Qualification level	(per JEDEC JESD47I ^{††} guidelines)		
Moisture Sensitivity Level	PVT412APbF	N/A	
	PVT412ASPbF	MSL4	
	PVT412AS-TPbF	(per JEDEC J-STD-020E & JEDEC J-STD-033C ++)	
RoHS compliant	Yes		

qualification standards can be found at International Rectifier's web site: http://www.irf.com/product-info/reliability

Revision History

Date	Comments
6/2/2015	Added Qualification Information Table on page 6
0/2/2015	Updated data sheet with new IR corporate template



IR WORLD HEADQUARTERS: 101 N. Sepulveda Blvd., El Segundo, California 90245, USA
Data and specifications subject to change without notice
To contact International Rectifier, please visit http://www.irf.com/whoto-call/

^{††} Applicable version of JEDEC standard at the time of product release