

Metallized Polyester Film Capacitor

(Tape-wrapped Axial Compact Type)


- Non-inductive construction, compact size, metallized film capacitor with axial lead wires.
- Highly reliable with self-healing property.
- Minimum loss at high frequency.
- Tape-wrapped and epoxy endfilled at both leads for superior mechanical strength and humidity resistance.
- High capacitance value, offering a wide variety of applications.
- Compliant to the RoHS directive (2011/65/EU,(EU)2015/863).

Applications

 Filtering DC-blocking, coupling and so on of general communications equipment and use in AC circuits for motor starting, charging / discharging, lighting, etc.
 Some A.C. applications may cause capacitor failure, over heating of the capacitors and/or discharge may be the


result. Please contact us about details for A.C. application.

Specifications




Item	Performance Characteristics							
Category Temperature Range	-40 to +85°C							
Rated Voltage	250, 400, 630VDC							
Rated Capacitance Range	0.1 to 10μF							
Capacitance Tolerance	±5% (J), ±10% (K)							
Dielectric Loss Tangent	1.0% or less (at 1kHz 20°C)							
Insulation Resistance	C ≤ 0.33μF : 9000 MΩ or more C > 0.33μF : 3000 ΩF or more							
Withstand Voltage	Between Terminals Rated Voltage × 175%, 1 to 5 secs. Between Terminals and Coverage Rated Voltage × 200%, 1 to 5 secs.							
Encapsulation	Adhesive polyester film, epoxy resin							

Drawing



Type numbering system (Example: 250V 1.5µF)



Dimensions

Unit	:	mm

V(Code) 250VDC (2E)					400VDC (2G)				630VDC (2J)				
Cap.(µF)	de Size	Т	W	Н	d	Т	W	Н	d	Т	W	Н	d
0.1	104									6.0	30.0	12.5	0.8
0.15	154									7.5	30.0	14.0	0.8
0.22	224									8.5	30.0	16.5	0.8
0.33	334					7.5	25.0	15.5	0.8	10.5	30.0	18.5	0.8
0.47	474	5.5	25.0	12.0	0.8	9.0	25.0	17.0	0.8	11.0	35.0	19.0	0.8
0.68	684	7.0	25.0	13.0	0.8	9.0	30.0	17.0	0.8	11.5	40.0	21.0	1.0
1.0	105	7.5	25.0	15.5	0.8	11.0	30.0	19.0	0.8	12.5	46.0	22.0	1.0
1.5	155	8.0	30.0	16.0	0.8	13.0	30.0	22.5	0.8	16.0	46.0	25.0	1.0
2.2	225	9.5	30.0	17.5	0.8	13.5	35.0	23.0	0.8	18.0	52.0	27.5	1.0
3.3	335	9.5	35.0	19.5	0.8	17.0	35.0	26.5	0.8	22.5	52.0	31.5	1.0
4.7	475	12.0	35.0	21.5	0.8	18.5	41.0	28.0	1.0				
6.8	685	13.5	40.0	22.5	1.0								
10.0	106	16.5	40.0	25.5	1.0								