



mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		FCJ		www.fciconnect.com			
ltr	ecn no	dr	date	.X ± 0.30	projection	title					
H	T06-0074	AC	4/10/06	.XX ± 0.20	MM	MINI USB B-TYPE SMT RECEPTACLE					
J	T06-0137	AC	7/18/06	.XXX ± 0.10	scale	product family 511					
K	T06-0201	AC	12/14/06	0° ±2°		size A4					
L	T07-1002	JH	1/5/07			code TWN					
M	T10-0095	JH	12/27/10			sheet 1 of 2					
N	T-004667	JH	7/27/11			10033526					
sheet index	revision sheet	N 1	N 2	JASON HSU 12/27/10	JASON HSU 12/27/10	GARY HSIEH 12/27/10	JOSEPH HSIA 12/27/10				

PROD. NO  
SEE NOTES


5. PRODUCT ORDERING DATA :  
FOR LEAD-FREE



- NOTES:
- 1.MATERIAL:  
HOUSING: THERMOPLASTIC. UL 94V-0 RATED, COLOR: BLACK.  
CONTACT: COPPER ALLOY.  
SHELL: COPPER ALLOY  
MYLAR: KAPTON TAPE.  
2.FINISH:  
CONTACT: UNDERPLATED 50u" MIN. NICKEL OVERALL  
100u" MIN. MATTE TIN PLATED ON SOLDERING AREA,  
SELECTIVE GOLD PLATED ON CONTACT AREA.  
SHIELD: CODE N: NICKEL 40u" ~120u" PLATED OVERALL.  
T: SELECTIVE 60u" MIN. MATTE TIN ON LEGS OVER 40u" ~120u" NICKEL.
  - 3.10033526-X3212XLF MEETS THE EUROPEAN UNION DIRECTIVE AS DESCRIBE  
IN GS-22-008 AND ITS HSG WILL WITHSTAND EXPOSE TO 260 DEGREE C  
PEAK TEMPERATURE FOR 10 SECONDS IN A IR REFLOW APPLICATION.
  4. PRODUCT SPEC: GS-12-174 ; PACKAGE SPEC: GS-14-873.



RECOMMENDED PCB LAYOUT FOR 10033526-XXX2X  
GENERAL TOLERANCE +/- 0.05mm



RECOMMENDED PCB LAYOUT FOR 10033526-XXX1XX  
GENERAL TOLERANCE +/- 0.05mm

mat'l. code		tolerances unless otherwise specified		CUSTOMER COPY		www.fciconnect.com	
itr	ecn no	dr	date	linear	projection	title	
N				.X ± 0.30	⊕	MINI USB B-TYPE SMT RECEPTACLE	
				.XX ± 0.20			
				.XXX ± 0.10			
				0° ±2°			
		dr	JASON HSU	12/27/10	MM	product family	511
		engr	JASON HSU	12/27/10		size	TWN
		chr	GARY HSIEH	12/27/10		scale	sheet
		appd	JOSEPH HSIA	12/27/10		10033526	2 of 2
sheet	revision						
index	sheet						

