

May.1.2018 Copyright 2018 HIROSE ELECTRIC CO., LTD. All Rights Reserved.  
 In case of consideration for using Automotive equipment /  
 device which demand high reliability, kindly contact our sales window correspondents.

Applicable standard					
Rating	Operating temperature range	-40 °C to +90 °C( 90 %RH Max.)	Storage temperature range	-40 °C to +90 °C( 90 %RH Max.)	
	Power	-- W	Characteristic impedance	50 Ω( 0 to 6 GHz)	
	Peculiarity	----	Applicable cable	1.37 Dia. coaxial cable.	
<b>SPECIFICATIONS</b>					
ITEM	TEST METHOD		REQUIREMENTS	QT	AT
<b>CONSTRUCTION</b>					
General examination	Visually and by measuring instrument.		According to drawing.	X	X
<b>ELECTRICAL CHARACTERISTICS</b>					
Insulation resistance	100 V DC.		500 MΩ Min.	X	X
Withstanding voltage	200 V AC for 1 min. current leakage 2 mA Max.		No flashover or breakdown.	X	X
Voltage standing wave ratio	Frequency 0 to 3 GHz.		VSWR 1.3 Max.	X	-
	Frequency 3 to 6 GHz.		VSWR 1.4 Max.		
<b>MECHANICAL CHARACTERISTICS</b>					
Cable clamp strength (Against cable pull)	Using a pulling tester, pull the cable axially at a rate of 10 mm/min. and record the strength at which the cable or connector breaks.		9.8 N Min.	X	-
<div style="position: absolute; top: 50%; left: 50%; transform: translate(-50%, -50%); opacity: 0.1; font-size: 48px; pointer-events: none;">             DRAWING FOR REFERENCE           </div>					
Count	Description of revisions		Designed	Checked	Date
△					
Remark			Approved	NK.NINOMIYA	16.07.22
NOTE 1) VSWR was measured with SMA conversion adapters attached to both ends of the applicable cable assembled			Checked	MT.KANEKO	16.07.21
2. Specifications are subject to change without notice.			Designed	MS.MATSUMOTO	16.07.21
Unless otherwise specified, refer to IEC 60512.			Drawn	MS.MATSUMOTO	16.07.21
Note QT:Qualification Test AT:Assurance Test X:Applicable Test			Drawing No.		
<b>HRS</b>	SPECIFICATION SHEET		Part No.	U.FL-2LP-088**T-A-L	
	HIROSE ELECTRIC CO., LTD.		Code No.		
				△	1/1