



ICA-320-SGT



ICA-624-ZEGG

(2,54mm) .100"

ICA SERIES

AUTOMATED INSERTION DIP SOCKETS

Mates with:
APA

ICA

ROW SPACING &
NO. OF CONTACTS


STYLE
OPTION

PLATING
OPTION

OPTION
(Leave Blank for
Standard Version)

Specify from chart below

- Side & end stackable
- Great for auto insertion
- Open body design



	Row Space	No. of Contacts
-308	.300 (7,62)	08
-314		14
-316		16
-318		18
-320		20
-322*		22
-324	.400 (10,16)	24
-328		28
-422	.600 (15,24)	22
-624		24
-628		28
-632		32
-640		40
-648		48

GG
= 30μ" (0,76μm)
Gold contact,
10μ" (0,25μm)
Gold Shell

GT
= 30μ" (0,76μm)
Gold contact,
Tin Shell

ST
= 10μ" (0,25μm)
Gold contact,
Tin shell (Styles -S
& -ZS only)

-2
= .360 (9,14)
Tail
**Wire-Wrap
Option**
Requires Style
-W or -ZW
Specify desired
suffix for shorter
Wire-Wrap tail.

-3
= .260 (6,60)
Tail

-L
= Locking
Socket
Requires Style
-S or -ZS
Requires GT
Plating Option

SPECIFICATIONS

For complete specifications
see www.samtec.com?ICA

Insulator Material:
Black Glass Filled
Polyester
except -328 is LCP
Contact: BeCu
Shell: Brass



Plating:

Au or Sn over 50μ" Ni
Flammability Rating:
UL 94V-O

Insulation Resistance:
5000 MΩ min

Temperature Range:
-55°C to +105°C with Tin
-55°C to +125°C with Gold.

Withstanding Voltage:
1000 VRMS

Current Rating: 1A
Contact Resistance:
10mΩ max

Lead Size Range:
.015" (0,38mm) to .022"
(0,56mm) DIA and most IC leads

Insertion Force:
(Single contact only)
Standard = 9 oz avg, 16 oz max;
Low Insertion Force =
2.5 oz avg, 5.5 oz max


Withdrawal Force:
(Single contact only)
Standard = 2.5 oz avg, 1.5 oz
min; Low Insertion Force =
2.0 oz avg, 0.35 oz min

Lead-Free Solderable:
Wave only
RoHS Compliant: Yes

Note: Some sizes, styles and
options are non-standard,
non-returnable.


-S, -ZS, -ZA

= Printed Circuit
-ZS & -ZA = Low Insertion Force



LEAD STYLE	X DIA	Y TAIL	Z
-S or -ZS	(0,51) .020	(3,18) .125	(7,62) .300
-ZA	(0,51) .020	(4,57) .180	(8,89) .350


Locking lead
available with -S
and -ZS.
See OPTION.



Insertion Depth = .095" (2,41) to .145" (3,68):
Style S Component Part No. = SC-1P1
Style ZS Component Part No. = EZ-1P1
Style ZA Component Part No. = EZ-6P1
Option L Component Part No. = SC-1L1 or EZ-1L1

-W, -ZW

= Wire-Wrap
ZW = Low Insertion Force




Shorter wire-wrap tail
lengths available.
See OPTION.

Insertion Depth = .125" (3,18) to .157" (3,99)
Style W Component Part No. = SC-1W1(1)
Style W-2 Component Part No. = SC-1W1(2)
Style W-3 Component Part No. = SC-1W1(3)
Style ZW-2 Component Part No. = EZ-1W1(2)
Style ZW-3 Component Part No. = EZ-1W1(3)

-ZE

= Elevated
Low Insertion Force



Insertion Depth = .125" (3,18) to .170" (4,32)
Style ZE Component Part No. = EZ-2P3

Due to technical progress, all designs, specifications and components are subject to change without notice.

WWW.SAMTEC.COM

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Samtec:

[ICA-314-SST](#) [ICA-320-SGG](#) [ICA-316-STT](#) [ICA-318-STT](#) [ICA-308-STT](#) [ICA-320-SGT](#) [ICA-640-STT](#) [ICA-628-SGT](#)
[ICA-640-SGT](#) [ICA-316-SGT](#) [ICA-324-SGT](#) [ICA-632-STT](#) [ICA-324-SST](#) [ICA-632-SST](#) [ICA-324-STT](#) [ICA-314-SGG](#)
[ICA-628-STT](#) [ICA-308-SGT](#) [ICA-308-SST](#) [ICA-640-SGG](#) [ICA-314-SGT](#) [ICA-628-SST](#) [ICA-308-SGG](#) [ICA-316-SGG](#)
[ICA-632-SGT](#) [ICA-640-ATT](#) [ICA-316-WTT-3](#) [ICA-316-ZWGG](#) [ICA-316-ZWGG-3](#) [ICA-308-ZAGG](#) [ICA-314-WGG-3](#)
[ICA-314-ZWGT](#) [ICA-316-SST](#) [ICA-316-WGG](#) [ICA-316-ZHGT](#) [ICA-316-ZSGG](#) [ICA-318-ATT](#) [ICA-318-WTT-2](#) [ICA-](#)
[320-ATT](#) [ICA-316-JGG](#) [ICA-316-SGG-L](#) [ICA-316-ZHGG](#) [ICA-318-ZWTT-2](#) [ICA-308-AGT](#) [ICA-308-WTT](#) [ICA-308-](#)
[ZSGT](#) [ICA-308-ZWGT-3](#) [ICA-316-WGG-3](#) [ICA-316-ZSST](#) [ICA-320-SGG-L](#) [ICA-314-ZHGT](#) [ICA-316-AGG](#) [ICA-316-](#)
[ATT](#) [ICA-316-ZWGG-2](#) [ICA-316-ZWGT](#) [ICA-318-SST-L](#) [ICA-314-SGG-L](#) [ICA-314-ZSGG](#) [ICA-314-ZSGG-L](#) [ICA-](#)
[314-ZWTT-3](#) [ICA-316-AGT](#) [ICA-308-WGG-2](#) [ICA-308-WGG-3](#) [ICA-308-ZSTT](#) [ICA-308-ZWGG](#) [ICA-314-SGT-L](#) [ICA-](#)
[314-ZAGT](#) [ICA-316-WGT-3](#) [ICA-316-WTT](#) [ICA-316-WTT-2](#) [ICA-308-SGT-L](#) [ICA-314-KGT](#) [ICA-314-STT-L](#) [ICA-314-](#)
[WGG-2](#) [ICA-314-WTT](#) [ICA-318-SGT-L](#) [ICA-318-WGG-2](#) [ICA-318-WGT-3](#) [ICA-318-ZAGT](#) [ICA-318-ZWGT](#) [ICA-316-](#)
[ZWGT-2](#) [ICA-318-SST](#) [ICA-318-WGG](#) [ICA-318-ZSGT](#) [ICA-318-ZSST](#) [ICA-318-ZSTT](#) [ICA-318-ZWGG](#) [ICA-308-](#)
[WGT-2](#) [ICA-308-ZSGG](#) [ICA-314-JGG](#) [ICA-314-WGG](#) [ICA-314-ZAGG](#) [ICA-314-ZWTT](#) [ICA-316-KGT](#) [ICA-316-ZWTT](#)
[ICA-316-ZWTT-3](#) [ICA-318-KGT](#) [ICA-318-SGT](#) [ICA-318-WGT-2](#) [ICA-318-ZWGG-3](#)