

### FEATURES


- 1. Breakthrough height of 9.8 mm .386 inch beats the 10 mm .394 inch limit**  
1c and 2c all have the same height (9.8 mm .386 inch). The width of the relay is also the same (9.9 mm .390 inch). Since the only size variable is the length, the shared form makes mounting on printed printing wiring boards easy.
- 2. Suitable for use in difficult environments**  
Epoxy resin seals the parts and cut off the external atmosphere, thus enabling use in difficult environments.
- 3. Can be used with automatic solder and automatic wash systems**  
Automatic soldering and automatic washing can be carried out once the parts are mounted on PC boards.
- 4. Gold-clad twin contacts ensure high reliability**  
Highly stable gold cladding on the contacts ensures that contact resistance changes little over time. Furthermore, the use of twin contacts, a configuration that performs with superior contact reliability, ensures extremely low contact failure rates even under low level loads.

- 5. Polarized magnetic circuits realize resistance to shock and vibration**  
High-performance polarized magnetic circuits that utilize the energy of permanent magnets have made it possible to create relays with strong resistance to shock and vibration.
- 6. DIL terminal array enables use of IC sockets**
- 7. Widening scope of application with multicontact latching**  
In addition to single side stable types, you can take advantage of the memory of functions of convenient 1 coil or 2 coil latching relays.
- 8. Sealed according to RTIII (IP67)**

### TYPICAL APPLICATIONS

Besides telecommunications, measuring devices, office equipment, computers and related equipment, DS relays are also recommended for a broad range of applications including business devices, audio systems, and industrial equipment.

### ORDERING INFORMATION



## TYPES

## High sensitivity type

Contact arrangement	Nominal coil voltage	Single side stable type		2 coil latching type	
		Part No.	Part No.	Part No.	Part No.
1 Form C	1.5V DC	DS1E-S-DC1.5V		DS1E-SL2-DC1.5V	
	3V DC	DS1E-S-DC3V		DS1E-SL2-DC3V	
	5V DC	DS1E-S-DC5V		DS1E-SL2-DC5V	
	6V DC	DS1E-S-DC6V		DS1E-SL2-DC6V	
	9V DC	DS1E-S-DC9V		DS1E-SL2-DC9V	
	12V DC	DS1E-S-DC12V		DS1E-SL2-DC12V	
	24V DC	DS1E-S-DC24V		DS1E-SL2-DC24V	
	48V DC	DS1E-S-DC48V		DS1E-SL2-DC48V	
2 Form C	3V DC	DS2E-S-DC3V		DS2E-SL2-DC3V	
	5V DC	DS2E-S-DC5V		DS2E-SL2-DC5V	
	6V DC	DS2E-S-DC6V		DS2E-SL2-DC6V	
	9V DC	DS2E-S-DC9V		DS2E-SL2-DC9V	
	12V DC	DS2E-S-DC12V		DS2E-SL2-DC12V	
	24V DC	DS2E-S-DC24V		DS2E-SL2-DC24V	
	48V DC	DS2E-S-DC48V		DS2E-SL2-DC48V	

Standard packing: Tube: 50 pcs.; Case: 500 pcs.

## RATING

## 1. Coil data

## 1) Single side stable type

Type	Nominal coil voltage	Pick-up voltage (at 20°C 68°F)	Drop-out voltage (at 20°C 68°F)	Nominal operating current [ $\pm 10\%$ ] (at 20°C 68°F)		Coil resistance [ $\pm 10\%$ ] (at 20°C 68°F)	Nominal operating power	Max. applied voltage (at 50°C 122°F)
High sensitivity (S) type	1.5V DC*	1 Form C: 80%V or less of nominal voltage 2 Form C: 70%V or less of nominal voltage (Initial)	10%V or more of nominal voltage (Initial)	133.3mA		11.3 $\Omega$	200mW	1 Form C: 160%V of nominal voltage  2 Form C: 200%V of nominal voltage
	3V DC			66.7mA		45 $\Omega$		
	5V DC			40.0mA		125 $\Omega$		
	6V DC			33.3mA		180 $\Omega$		
	9V DC			22.2mA		405 $\Omega$		
	12V DC			16.7mA		720 $\Omega$		
	24V DC			8.3mA		2,880 $\Omega$		
48V DC	4.2mA		11,520 $\Omega$					

## 2) 2 coil latching type

Type	Nominal coil voltage	Set voltage (at 20°C 68°F)	Reset voltage (at 20°C 68°F)	Nominal operating current [ $\pm 10\%$ ] (at 20°C 68°F)		Coil resistance [ $\pm 10\%$ ] (at 20°C 68°F)		Nominal operating power		Max. applied voltage (at 50°C 122°F)
				Set coil	Reset coil	Set coil	Reset coil	Set coil	Reset coil	
High sensitivity (S) type	1.5V DC*	1 Form C: 80%V or less of nominal voltage  2 Form C: 70%V or less of nominal voltage (Initial)	1 Form C: 80%V or less of nominal voltage  2 Form C: 70%V or less of nominal voltage (Initial)	120mA	120mA	12.5 $\Omega$	12.5 $\Omega$	180mW	180mW	1 Form C: 160%V of nominal voltage  2 Form C: 200%V of nominal voltage
	3V DC			60mA	60mA	50 $\Omega$	50 $\Omega$			
	5V DC			36mA	36mA	139 $\Omega$	139 $\Omega$			
	6V DC			30mA	30mA	200 $\Omega$	200 $\Omega$			
	9V DC			20mA	20mA	450 $\Omega$	450 $\Omega$			
	12V DC			15mA	15mA	800 $\Omega$	800 $\Omega$			
	24V DC			7.5mA	7.5mA	3,200 $\Omega$	3,200 $\Omega$			
	48V DC			3.75mA	3.75mA	12,800 $\Omega$	12,800 $\Omega$			

\*Nominal coil voltage 1.5V types are 1 Form C only.

2. Specifications

Characteristics	Item	Specifications		
		1 Form C	2 Form C	
Contact	Arrangement			
	Initial contact resistance, max.	Max. 50 mΩ (By voltage drop 6 V DC 1A)		
	Contact material	Ag+Au clad		
Rating	Nominal switching capacity	2 A 30 V DC (resistive load)		
	Max. switching power	60 W, 125 VA (resistive load)		
	Max. switching voltage	220 V DC, 250 V AC		
	Max. carrying current	3 A		
	Min. switching capacity (Reference value) <sup>1</sup>	10μA 10m V DC		
	Nominal operating power	Single side stable (S type: 200 mW); latching (S type: 180 mW)		
Electrical characteristics	Insulation resistance (Initial)	Min. 100MΩ (at 500V DC) Measurement at same location as "Initial breakdown voltage" section.		
	Breakdown voltage (Initial)	Between open contacts	1,000 Vrms for 1min. (500 Vrms for 1min: 1 Form C high sensitivity type) (Detection current: 10mA.)	
		Between contact and coil	1,500 Vrms for 1min. (1,000 Vrms for 1min: 1 Form C high sensitivity type) (Detection current: 10mA.)	
	Temperature rise	Max. 65°C (By resistive method, nominal coil voltage applied to the coil, contact carrying current: 2A.)		
	Operate time [Set time] (at 20°C 68°F)	Max. 10 ms [10 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.)		
	Release time [Reset time] (at 20°C 68°F)	Max. 5 ms [10 ms] (Nominal coil voltage applied to the coil, excluding contact bounce time.) (without diode)		
	Mechanical characteristics	Shock resistance	Functional <sup>2</sup>	Min. 490 m/s <sup>2</sup>
Destructive			Min. 980 m/s <sup>2</sup> (Half-wave pulse of sine wave: 6 ms.)	
Vibration resistance		Functional	10 to 55 Hz at double amplitude of 3.3 mm (Detection time: 10μs.)	
		Destructive	10 to 55 Hz at double amplitude of 5 mm	
Expected life	Mechanical	Min. 10 <sup>8</sup> (10 <sup>7</sup> : 1 Form C latching type) (at 600 times/min.)		
	Electrical	Min. 5×10 <sup>5</sup> rated load (at 60 times/min.)		
Conditions	Conditions for operation, transport and storage <sup>3</sup>	Ambient temperature: -40°C to +70°C -40°F to +158°F Humidity: 5 to 85% R.H. (Not freezing and condensing at low temperature)		
	Max. operating speed (at rated load)	60 times/min.		
Unit weight		Approx. 3 g .11 oz	Approx. 4g .14oz	


1\* This value can change due to the switching frequency, environmental conditions, and desired reliability level, therefore it is recommended to check this with the actual load. (TX/TX-S/TX-D relay AgPd contact types are available for low level load switching [10V DC, 10mA max. level])

2\* Half-wave pulse of sine wave: 11ms; detection time: 10μs


3\* Refer to "6. Usage, Storage and Transport Conditions" in [AMBIENT ENVIRONMENT section in Relay Technical Information](#).

REFERENCE DATA

1. Maximum switching capacity




2. Life curve (Resistive load)




3. Contact reliability for AC loads

Tested sample: DS2E-S-DC24V 10 pcs.  
Operating speed: 20 times/min.. Detection level: 200 mΩ




4. Operate and release time characteristics (2 Form C single side stable type)


Test condition: Without diode connected to coil in parallel



5-(1). Influence of adjacent mounting (1 Form C)




5-(2). Influence of adjacent mounting (2 Form C)



**DS (1 Form C)**


Single side stable, 2 coil latching

[CAD Data](#) External dimensions



General tolerance:  $\pm 0.3 \pm .012$



PC board pattern (Bottom view)  
Single side stable      2 coil latching



Schematic (Bottom view)

Single side stable

2 coil latching



(Deenergized condition)

(Reset condition)


Tolerance:  $\pm 0.1 \pm .004$

Note: External dimensions of 1 coil latching types are same as single side stable type.

**DS (2 Form C)**


Single side stable

[CAD Data](#) External dimensions




General tolerance:  $\pm 0.3 \pm .012$

PC board pattern (Bottom view)



Schematic (Bottom view)



(Deenergized condition)


Tolerance:  $\pm 0.1 \pm .004$

Note: External dimensions of 1 coil latching types are same as single side stable type.

**DS (2 Form C)**


2 coil latching

[CAD Data](#) External dimensions




General tolerance:  $\pm 0.3 \pm .012$

PC board pattern (Bottom view)



Schematic (Bottom view)



(Reset condition)

Tolerance:  $\pm 0.1 \pm .004$

---

**NOTE****Coil connection**

When connecting coils, refer to the wiring diagram to prevent misoperation or malfunction.

---

**For Cautions for Use, see [Relay Technical Information](#).**

---