

GENERAL SPECIFICATIONS FOR SW3000s

B Electrical Capacity (Resistive & Inductive Load)**Power Level:** Shown in the following tables**Other Ratings****Contact Resistance:** 10 milliohms maximum**Insulation Resistance:** 1,000 megohms minimum @ 500V DC**Dielectric Strength:** 2,000V AC minimum for 1 minute minimum**Mechanical Life:** 30,000 operations minimum**Electrical Life:** 10,000 operations minimum**Angle of Throw (α):** Shown on drawings or following tables**Materials & Finishes****Rocker:** Urea resin; all rockers are white.**Mounting Frame:** Steel with chromate plating over zinc plating**Case Cover/Insulator:** Phenolic resin**Case:** Melamine phenol**Movable Contactor Plate:** Copper with silver plating**Movable & Stationary Contacts:** Silver alloy plus copper with silver plating**Terminals:** Copper with tin plating**Environmental Data****Operating Temp Range:** -10°C through +70°C (+14°F through +158°F)**Sealing:** Dustproof cover of silicone rubber on SW3006A, SW3007A, & SW3008A**Installation****Maximum Panel Thickness:** Shown with following drawings**Soldering Time & Temperature:** Manual Soldering: See Profile A in Supplement section.**Standards & Certifications****UL:** File No. E44145 - Recognized only when ordered with marking on switch.

Add "/U" or "/CUL" to end of part number to order UL recognized switch.

UL or cULus recognition designated beside part numbers on following pages.

See Supplement section to find UL or cULus rating details.

CSA: File No. 023535_0_000 - Certified only when ordered with marking on switch.

Add "/C" to end of part number to order CSA certified switch.

CSA certification designated beside part numbers on following pages.

See Supplement section to find CSA rating details.

Toggles

Rockets

Illuminated PB

programmable

Keylocks

otaries

Tactiles

iii

Touch

GENERAL SPECIFICATIONS FOR SW3800s

Electrical Capacity (Resistive & Inductive Load)

Power Level: Shown in the following tables
Note: See Supplement section for details of design for inductive DC loads.

Other Ratings

Contact Resistance:	10 milliohms maximum
Insulation Resistance:	1,000 megohms minimum @ 500V DC
Dielectric Strength:	2,000V AC minimum for 1 minute minimum
Mechanical Life:	50,000 operations minimum
Electrical Life:	25,000 operations minimum
Angle of Throw:	Shown on following drawings
Nominal Operating Force:	1,800 grams for SW3822
	2,200 grams for SW3823 Off to On
	800 grams for SW3823 On to Off

Materials & Finishes

Rocker:	Urea resin; all rockers are white.
Mounting Frame:	Steel with chromate plating over zinc plating
Case Cover/Insulator:	Phenolic resin
Case:	Melamine phenol
Movable Contacts:	Copper with silver plating
Stationary Contacts:	Silver alloy plus copper with silver plating
Terminals:	Brass (terminal screws of brass with nickel plating)



Environmental Data

Operating Temp Range: -10°C through +70°C (+14°F through +158°F)



Standards & Certifications

- UL:** File No. E44145 - Recognized only when ordered with marking on switch.
Add "/U" or "/CUL" to end of part number to order UL recognized switch.
UL or cULus recognition designated beside part numbers on following pages.
See Supplement section to find UL or cULus rating details.
- CSA:** File No. 023535_0_000 - Certified only when ordered with marking on switch.
Add "/C" to end of part number to order CSA certified switch.
CSA certification designated beside part numbers on following pages.
See Supplement section to find CSA rating details.

Wiring for SW3821D with Electrical Capacity of DC400V 10A




DOUBLE POLE WITH SCREW LUG


				Rocker Position/Connected Terminals							Electrical Capacity									
Model	*Approvals			Pole	Down			Center	Up		Resistive								Inductive	
									AC 125V	AC 250V	DC 30V	DC 48V	DC 125V	DC 250V	DC 400V	AC 125V PF 0.6	AC 250V PF 0.6			
SW3821	✓	✓	✓	DPST	ON	2-3	5-6	NONE	OFF	—	30A	30A	30A	—	1A	—	—	30A	15A	
SW3822	✓	✓	✓	DPDT	ON	2-3	5-6	NONE	ON	2-1 5-4	30A	30A	30A	—	1A	—	—	30A	15A	
SW3823	✓	✓	✓	DPDT	ON	2-3	5-6	OFF	ON	2-1 5-4	30A	30A	30A	—	1A	—	—	30A	15A	
SW3821D	✓	✓	✓	DPST	ON	2-3	5-6	NONE	OFF	—	—	—	30A	30A	20A	15A	4A (10A)	—	—	
SW3822D	✓	✓	✓	DPDT	ON	2-3	5-6	NONE	ON	2-1 5-4	—	—	30A	30A	20A	15A	4A	—	—	
SW3823D	✓	✓	✓	DPDT	ON	2-3	5-6	OFF	ON	2-1 5-4	—	—	30A	30A	15A	—	—	—	—	
Throw & Schematics:				DPST  DPDT 										Note: Terminal numbers are actually on the switch.						

Throw & Schematics:

DPST



DPDT






Note: Terminal numbers are actually on the switch.

* UL/CUL & CSA for the following ratings: UL/CUL: 30A @ 30V DC, 15A @ 125V DC; CSA: 30A @ 30V DC, 15A @ 125V DC

* UL, cULus & CSA recognized only when ordered with marking on switch (see General Specs)

() capacity is due to series wiring, see General Specifications page.



SW3821 & SW3821D do not have terminals 1 & 4.

Maximum Effective Panel Thickness .177" (4.5mm). Panel cutout shown below.

SW3822

THREE POLE WITH SCREW LUG

				Rocker Position/Connected Terminals								Electrical Capacity							
Model	*Approvals			Pole	Down				Center	Up			Resistive				Inductive		
									AC 125V	AC 250V	DC 30V	DC 125V	AC 125V PF 0.6	AC 250V PF 0.6					
SW3831	✓	✓	✓	3PST	ON	2-3	5-6	8-9	NONE	OFF	—			30A	30A	30A	1A	30A	15A
SW3832	✓	✓	✓	3PDT	ON	2-3	5-6	8-9	NONE	ON	2-1	5-4	8-7	30A	30A	30A	1A	30A	15A
SW3833	✓	✓	✓	3PDT	ON	2-3	5-6	8-9	OFF	ON	2-1	5-4	8-7	30A	30A	30A	1A	30A	15A
SW3831D	✓	✓	✓	3PST	ON	2-3	5-6	8-9	NONE	OFF	—			—	—	30A	15A	—	—
SW3832D	✓	✓	✓	3PDT	ON	2-3	5-6	8-9	NONE	ON	2-1	5-4	8-7	—	—	30A	15A	—	—
SW3833D	✓	✓	✓	3PDT	ON	2-3	5-6	8-9	OFF	ON	2-1	5-4	8-7	—	—	30A	15A	—	—
Throw & Schematics:				3PST 2 5 8 3 6 9 3PDT 2 5 8 3 1 6 4 9 7										Note: Terminal numbers are actually on the switch.					

Throw & Schematics:

3PST







3PDT



Note: Terminal numbers are actually on the switch.

* UL/CUL & CSA for the following ratings: UL/CUL: 30A @ 30V DC, 15A @ 125V DC; CSA: 30A @ 30V DC, 15A @ 125V DC

* UL, cULus & CSA recognized only when ordered with marking on switch (see General Specs)



SW3831 & SW3831D do not have terminals 1, 4 & 7.

Maximum Effective Panel Thickness .177" (4.5mm)