

# Common Mode SC Coils, SC-JH Series, Terminal Base Type

## Overview

The KEMET SC-JH coils are common mode chokes with a wide variety of characteristics. These toroidal coils are designed with our proprietary ferrite cores and are useful in various noise countermeasure fields.

## Applications

- Audio-visual equipment
- Home appliances
- Power supplies

## Benefits

- Proprietary 5H, 7H, 10H, and 700L ferrite material and equivalents
- Suitable for  $\geq 150$  kHz range
- High frequency (700L)
- Wide variety of sizes and specifications
- Operating temperature range from  $-25^{\circ}\text{C}$  to  $+105^{\circ}\text{C}$  or  $+120^{\circ}\text{C}$
- UL 94 V-2 or V-0 flame retardant rated base and cap



## Part Number System

SC-		10-		20	JH	
Series	Dimension Code (See Dimensions)	Rated Current (A)	Thermal Class	Inductance (mH) Minimum	Terminal Base Type	Internal Control Code
SC	Blank 22	x0 = x0 A xx = xx A  Examples: 10 = 10 A 15 = 15 A	Blank E = Class E  Note: With exceptions, see Table 1 for details.	x0 = x mH xx = x.x mH xxx = x.xx mH  Examples: 20 = 2 mH 15 = 1.5 mH 200 = 2.00 mH  Note: With exceptions, see Table 1 for details.	JH  Note: JR is the same terminal base type as JH	Blank P

## Magnetic Permeability of Ferrite Material


In order to achieve most efficient noise reduction, it is important to select the material according to the target frequency band. Depending on its magnetic permeability, a particular ferrite material will be effective in a certain frequency band. A schematic representation of the relationship between the magnetic permeability of each material and the corresponding effective band range is shown in Figure 1.

Materials with higher magnetic permeability are effective in the lower frequency range, while those with lower magnetic permeability are effective in the higher frequency range. Thus, Mn-Zn products are mainly used for reducing conduction noise, while Ni-Zn products are commonly used for radiation noise countermeasures.

The effective frequency range varies depending on core shape, size and number of windings. This frequency dependence of the magnetic permeability as shown in the figure serves for reference purposes only and it should be tested on the actual device to determine its effectiveness.

S18H, S15H, 10H, 7H, 5H, 1400L and 700L are KEMET’s proprietary ferrite material names. Other materials can also be available on request.

Figure 1 - Relationship between the magnetic permeability of each material and its effective frequency range



## Dimensions – Millimeters

Figure 1




Figure 2




Figure 3




Figure 4




Figure 5




Figure 6





Figure 7



Part Name	Dimensions (mm)				Pin Pitch <sup>1</sup> (Reference)		Figure
	OD (Maximum)	T (Maximum)	H (Maximum)	L	a	b	
SC-030-E110JH-P	31.0	32.0	15.0	3.5±1.0	25	27.5	Fig. 4
SC-030-E150JH-P	31.0	32.0	14.5	3.5±1.0	25	27.5	Fig. 4
SC-040-E063JH-P	31.0	32.0	15.0	3.5±1.0	25	27.5	Fig. 4
SC-040-E092JH-P	31.0	32.0	15.0	3.5±1.0	25	27.5	Fig. 4
SC22-05-30JH	29.0	31.0	23.0	5.0±2.0	14	22	Fig. 2
SC-05-E45JH	25.0	23.0	21.0	3.5±1.0	a1:10, a2:14	19	Fig. 3
SC-05-492JH	34.0	32.5	18.0	3.5±1.0	11	28	Fig. 5
SC22-05-70JH	28.0	-	19.5	5.0±2.0	20	14	Fig. 7
SC-05-700JH	34.0	33.0	18.0	3.5±1.0	11	28	Fig. 5
SC-05-812JH	34.0	32.5	18.0	3.5±1.0	11	28	Fig. 5
SC-06-182JH	35.0	32.5	18.0	3.5±1.0	11	28	Fig. 5
SC-06-E200JH	25.0	25.0	20.5	3.5±1.0	10	19	Fig. 2
SC-06-382JH	35.0	32.5	18.0	3.5±1.0	11	28	Fig. 5
SC-06-462JH	35.0	32.5	18.0	3.5±1.0	11	28	Fig. 5
SC22-06-70JH	28.0	-	19.5	5.0±2.0	20	14	Fig. 7
SC-07-E030JH-P	24.0	24.5	15.0	3.5±1.0	12	20	Fig. 6
SC-07-276JH	35.0	32.5	18.0	3.5±1.0	11	28	Fig. 5
SC-07-E042JH	34.0	-	27.0	4.5±1.0	11	28	Fig. 1
SC-09-E075JH	24.0	24.5	15.0	3.5±1.0	12	20	Fig. 6
SC-09-209JH	34.0	32.0	18.5	3.5±1.0	11	28	Fig. 5

<sup>1</sup> Pin pitch listed above for reference only. Values not guaranteed.

## Dimensions – Millimeters cont.

Figure 1




Figure 2




Figure 3




Figure 4




Figure 5




Figure 6





Figure 7



Part Name	Dimensions (mm)				Pin Pitch <sup>1</sup> (Reference)		Figure
	OD (Maximum)	T (Maximum)	H (Maximum)	L	a	b	
SC-10-20JH	42.0	41.0	30.0	5.0±2.0	17	30	Fig. 2
SC-10-55JH	51.0	-	34.0	5.0±2.0	26	30	Fig. 1
SC-10-E80JH	53.0	-	35.0	4.5±1.5	26	30	Fig. 1
SC-12-15JH	42.0	41.0	30.0	5.0±2.0	17	30	Fig. 2
SC-12-100JH	65.0	-	40.0	5.0±2.0	35	44	Fig. 1
SC-14-15JH	42.0	41.0	28.0	5.0±2.0	17	30	Fig. 2
SC-15-05JH	44.0	41.0	32.0	5.0±2.0	17	30	Fig. 2
SC-15-10JH	44.0	41.0	32.0	5.0±2.0	17	30	Fig. 2
SC-15-12JH	44.0	41.0	32.0	5.0±2.0	17	30	Fig. 2
SC-15-20JH	51.0	-	34.0	5.0±2.0	26	30	Fig. 1
SC-15-35JH	51.0	-	34.0	5.0±2.0	15	35	Fig. 1
SC-15-E50JH	42.0	41.0	30.0	5.0±2.0	17	30	Fig. 2
SC-17-E27JH	44.0	41.0	32.0	5.0±1.0	17	30	Fig. 2
SC-18-15JH	51.0	-	34.0	5.0±2.0	26	30	Fig. 1
SC-18-E15JH	51.0	-	34.0	5.0±2.0	26	30	Fig. 1
SC-20-10JH	51.0	-	34.0	5.0±2.0	15	35	Fig. 1
SC-20-10JR	51.0	-	34.0	5.0±2.0	15	35	Fig. 1
SC-20-20JH	51.0	-	34.0	5.0±2.0	26	30	Fig. 1
SC-20-E20JH	51.0	-	34.0	5.0±2.0	26	30	Fig. 1
SC-30-12JH	65.0	-	40.0	4.6±1.5	55	20	Fig. 1

<sup>1</sup> Pin pitch listed above for reference only. Values not guaranteed.

## Environmental Compliance

All KEMET AC line filters are RoHS Compliant.



## Performance Characteristics

Item	Performance Characteristics
Rated Voltage	250 VAC/VDC
Withstanding Voltage	2,400 V (2 seconds, between lines)
Insulation Resistance	> 100 MΩ at 500 VDC (between lines)
Rated Current Range	3 – 30 A
Rated Inductance Range	0.03 – 15 mH minimum
Inductance Measurement Condition	1 kHz, 10 kHz, and 100 kHz
Thermal Class	A (105°C) and E (120°C)
Operating Temperature Range	-25°C to +105°C (include self temperature rise) and -25°C to +120°C (include self temperature rise)

**Table 1 – Ratings & Part Number Reference**









Part Number	Rated Current (A)	Inductance (mH) Minimum	DC Resistance/Line (mΩ) Maximum	Temperature Rise (K) Maximum	Wire Diameter (mm)	Thermal Class	Weight (g) Approximate
SC-030-E110JH-P	3	10.99 <sup>3</sup>	42.0	60	0.70	E (120°C)	26.5
SC-030-E150JH-P	3	15.00 <sup>2</sup>	160.0	80	0.60	E (120°C)	22.0
SC-040-E063JH-P	4	6.30 <sup>2</sup>	58.8	56	0.80	E (120°C)	25.0
SC-040-E092JH-P	4	9.17 <sup>2</sup>	79.2	67	0.75	E (120°C)	26.5
SC22-05-30JH	5	3.00 <sup>2</sup>	60.0	60	0.80	E (120°C)	23.4
SC-05-E45JH	5	4.50 <sup>3</sup>	50.0	85	0.70	E (120°C)	19.0
SC-05-492JH	5	4.90 <sup>2</sup>	45.0	65	0.90	E (120°C)	30.0
SC22-05-70JH	5	7.00 <sup>2</sup>	60.0	85	0.80	E (120°C)	27.0
SC-05-700JH	5	7.00 <sup>2</sup>	55.0	75	0.90	E (120°C)	29.7
SC-05-812JH	5	8.10 <sup>2</sup>	65.0	75	0.90	E (120°C)	34.0
SC-06-182JH	6	1.80 <sup>2</sup>	30.0	40	1.10	E (120°C)	26.0
SC-06-E200JH	6	2.00 <sup>2</sup>	21.5	55	0.90	E (120°C)	19.0
SC-06-382JH	6	3.80 <sup>2</sup>	40.0	65	1.00	E (120°C)	29.0
SC-06-462JH	6	4.60 <sup>2</sup>	45.0	110	1.00	E (120°C)	31.0
SC22-06-70JH	6	7.00 <sup>2</sup>	70.0	75	0.90	E (120°C)	21.1
SC-07-E030JH-P	7	0.03 <sup>3</sup>	20.0	60	0.80	E (120°C)	15.0
SC-07-276JH	7	2.76 <sup>2</sup>	24.0	65	1.10	E (120°C)	32.0
SC-07-E042JH	7	4.20 <sup>3</sup>	42.0	65	1.10	E (120°C)	53.0
SC-09-E075JH	9	0.75 <sup>2</sup>	9.0	60	1.10	E (120°C)	13.0
SC-09-209JH	9	2.09 <sup>2</sup>	17.4	74	1.20	E (120°C)	31.0
SC-10-20JH	10	2.00 <sup>3</sup>	22.0	45	1.40	A (105°C)	72.0
SC-10-55JH	10	5.50 <sup>1</sup>	30.0	65	1.40	A (105°C)	112.3
SC-10-E80JH	10	8.00 <sup>2</sup>	40.0	75	1.40	E (120°C)	118.8
SC-12-15JH	12	1.50 <sup>3</sup>	18.0	45	1.50	A (105°C)	71.0
SC-12-100JH	12	10.00 <sup>3</sup>	32.0	78	1.60	A (105°C)	190.0
SC-14-15JH	14	1.50 <sup>3</sup>	14.0	55	1.60	A (105°C)	78.6
SC-15-05JH	15	0.50 <sup>3</sup>	8.0	40	1.70	A (105°C)	65.3
SC-15-10JH	15	1.00 <sup>3</sup>	12.0	50	1.70	A (105°C)	73.0
SC-15-12JH	15	1.20 <sup>2</sup>	12.0	55	1.70	A (105°C)	73.0
SC-15-20JH	15	2.00 <sup>3</sup>	12.0	45	1.80	A (105°C)	115.0
SC-15-35JH	15	3.50 <sup>1</sup>	20.0	80	1.60	A (105°C)	114.3
SC-15-E50JH	15	5.20 <sup>2</sup>	19.3	85	1.50	E (120°C)	83.8
SC-17-E27JH	17	2.75 <sup>3</sup>	14.0	110	1.60	E (120°C)	83.1
SC-18-15JH	18	1.50 <sup>3</sup>	10.0	55	1.90	A (105°C)	117.0
SC-18-E15JH	18	1.50 <sup>3</sup>	10.0	55	1.90	E (120°C)	114.0
SC-20-10JH	20	1.00 <sup>3</sup>	8.0	50	2.00	A (105°C)	110.0
SC-20-10JR	20	1.00 <sup>3</sup>	8.0	50	2.00	A (105°C)	109.0
SC-20-20JH	20	2.00 <sup>3</sup>	10.0	80	1.90	A (105°C)	114.1
SC-20-E20JH	20	2.00 <sup>3</sup>	10.0	80	1.90	E (120°C)	119.4
SC-30-12JH	30	1.20 <sup>3</sup>	6.0	40	2.60	A (105°C)	188.0

<sup>1</sup> Inductance Measurement Condition: 1 kHz









<sup>2</sup> Inductance Measurement Condition: 10 kHz

<sup>3</sup> Inductance Measurement Condition: 100 kHz

## Frequency Characteristics











## Frequency Characteristics cont.





















## Frequency Characteristics cont.



## Frequency Characteristics cont.



## Frequency Characteristics cont.



## Packaging

Type	Packaging Type	Pieces Per Box	
SC-030-E110JH-P	Tray	180	
SC-030-E150JH-P			
SC-040-E063JH-P			
SC-040-E092JH-P			
SC22-05-30JH			250
SC-05-E45JH			200
SC-05-492JH			180
SC22-05-70JH			200
SC-05-700JH			180
SC-05-812JH			
SC-06-182JH			
SC-06-E200JH		200	
SC-06-382JH		180	
SC-06-462JH			
SC22-06-70JH		250	
SC-07-E030JH-P		180	
SC-07-276JH		150	
SC-07-E042JH		250	
SC-09-E075JH		180	
SC-09-209JH			

Type	Packaging Type	Pieces Per Box	
SC-10-20JH	Tray	100	
SC-10-55JH			
SC-10-E80JH			
SC-12-15JH		45	
SC-12-100JH		100	
SC-14-15JH			
SC-15-05JH			
SC-15-10JH			
SC-15-12JH			
SC-15-20JH			
SC-15-35JH			
SC-15-E50JH			
SC-17-E27JH			
SC-18-15JH			
SC-18-E15JH			
SC-20-10JH			
SC-20-10JR			
SC-20-20JH			
SC-20-E20JH			48
SC-30-12JH			60

## Handling Precautions

### Precautions for product storage

AC Line Filters should be stored in normal working environments. While the chokes themselves are quite robust in other environments, solderability will be degraded by exposure to high temperatures, high humidity, corrosive atmospheres, and long term storage.

KEMET recommends that maximum storage temperature not exceed 40°C and maximum storage humidity not exceed 70% relative humidity. Atmospheres should be free of chlorine and sulfur bearing compounds. Temperature fluctuations should be minimized to avoid condensation on the parts. Avoid storage near strong magnetic fields, as this might magnetize the product.

For optimized solderability, AC line filters stock should be used promptly and preferably within 6 months of receipt.

### Product temperature rise values

The values listed for temperature rise are the result of self-heating in wires when the rated current (commercial frequency) is applied.

When using the product, check and evaluate the value of the core temperature rise under actual operating conditions.

## KEMET Electronics Corporation Sales Offices

For a complete list of our global sales offices, please visit [www.kemet.com/sales](http://www.kemet.com/sales).

---

### Disclaimer

YAGEO Corporation and its affiliates do not recommend the use of commercial or automotive grade products for high reliability applications or manned space flight.

All product specifications, statements, information and data (collectively, the "Information") in this datasheet are subject to change. The customer is responsible for checking and verifying the extent to which the Information contained in this publication is applicable to an order at the time the order is placed. All Information given herein is believed to be accurate and reliable, but it is presented without guarantee, warranty, or responsibility of any kind, expressed or implied.

Statements of suitability for certain applications are based on KEMET Electronics Corporation's ("KEMET") knowledge of typical operating conditions for such applications, but are not intended to constitute – and KEMET specifically disclaims – any warranty concerning suitability for a specific customer application or use. The Information is intended for use only by customers who have the requisite experience and capability to determine the correct products for their application. Any technical advice inferred from this Information or otherwise provided by KEMET with reference to the use of KEMET's products is given gratis, and KEMET assumes no obligation or liability for the advice given or results obtained.

Although KEMET designs and manufactures its products to the most stringent quality and safety standards, given the current state of the art, isolated component failures may still occur. Accordingly, customer applications which require a high degree of reliability or safety should employ suitable designs or other safeguards (such as installation of protective circuitry or redundancies) in order to ensure that the failure of an electrical component does not result in a risk of personal injury or property damage.

Although all product-related warnings, cautions and notes must be observed, the customer should not assume that all safety measures are indicated or that other measures may not be required.

When providing KEMET products and technologies contained herein to other countries, the customer must abide by the procedures and provisions stipulated in all applicable export laws and regulations, including without limitation the International Traffic in Arms Regulations (ITAR), the US Export Administration Regulations (EAR) and the Japan Foreign Exchange and Foreign Trade Act.

*KEMET is a registered trademark of KEMET Electronics Corporation.*

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## KEMET:

[SC-15-10JH](#) [SC-10-20JH](#) [SC-15-20JH](#) [SC-15-E50JH](#) [SC-18-E15JH](#) [SC-05-E45JH](#) [SC-06-E200JH](#) [SC-10-E80JH](#)  
[SC-040-E092JH-P](#) [SC-06-462JH](#) [SC-09-209JH](#) [SC-12-100JH](#) [SC22-06-70JH](#) [SC-30-12JH](#) [SC-030-E110JH-P](#) [SC-](#)  
[030-E150JH-P](#) [SC-06-382JH](#) [SC-09-E075JH](#) [SC-10-55JH](#) [SC-05-812JH](#) [SC-07-276JH](#) [SC-040-E063JH-P](#) [SC-07-](#)  
[E030JH-P](#) [SC-06-182JH](#) [SC22-05-30JH](#) [SC-05-700JH](#) [SC-14-15JH](#) [SC-15-05JH](#) [SC-15-12JH](#) [SC-15-35JH](#) [SC-07-](#)  
[E042JH](#) [SC-20-20JH](#) [SC-20-E20JH](#) [SC22-05-70JH](#) [SC-18-15JH](#) [SC-12-15JH](#) [SC-20-10JH](#) [SC-05-492JH](#) [SC-17-](#)  
[E27JH](#) [SC-20-10JR](#)