

**RMM 11/24 output relay IN: 24 VAC/DC - OUT: 250 VAC/DC / 5 A**

1 relay; 1 N/O contact  
5 A  
24 V AC/DC

**Image**

Vicarious picture

**Switching capacity according to (EN 60947)**

24 V	AC12;5 A	AC15; 3 A	DC13; 1.5 A
110 V	AC12;5 A	AC15; 3 A	DC13; 0.3 A
230 V	AC12;5 A	AC15; 3 A	DC13; 0.15 A

**Input**

Input voltage	24 V AC/DC ±10 %
Input current	15 mA
Plug link	-
LED display	LED (red)

**Output**

Switching voltage	max. 250 V AC/300 V DC
Switching current	max. 5 A
Min. load current	100 mA
Breaking capacity (voltage dependent)	max. 1250 VA/240 W
Switching frequency	max. 10 Hz
Contact material	Ag Ni 0.15 hv; Ag hv
Energize/release/contact bounce time	10/15/1.5 ms

**General data**

Mech./ elect. life	2 × 10 <sup>7</sup> /load dependent
Temperature range	-20...+50 °C
Mounting method	DIN-rail mountable TH35 or G32 (EN 60715)
Dimensions H × W × D	56 x 12 x 64 mm
Test isolation voltage	4 kV


All data on this data sheet was compiled carefully.

Liability regarding correctness, completeness, and actuality is limited to gross negligence. Created: 04/12

**Commercial data**

Gross weight	38
Net weight	38
Weight unit	gram
Basic unit	pc.
Customs tariff number	85364900
Unit (piece)	1
Limited value	1

## Circuit diagram



## Dimension drawing

