

Drg No :- C 44045

INSTALLATION DRAWING

ISSUE	REVISION	DATE
1	FIRST ISSUE	19/7/00
2	See DPCA 15761	04/08/07



SPECIFICATION

ACTUATING FORCE:-1.65N(6ozf)MAX
 RELEASE FORCE :- 0.42(1.5ozf)MIN
 FREE POSITION :- 18.1 (0.71) MAX
 OPERATING POSITION :- ± 1.0 14.9 (.59) MAX
 MOVEMENT DIFFERENTIAL :-1.0(0.04) MAX
 OVERTRAVEL :- DEPRESS TO CASE (AVAILABLE)

TESTED AND STAMPED TO U.L. CSA & ENEC 14 REQUIREMENTS

APPROVAL RATING :- 5AMP - 250 V.A.C.

DIAGRAM OF CONNECTIONS



DEGREE OF PROTECTION :- ENCLOSURE IEC IP67

SAIA-Burgess Electronics

SWITCHES • MOTORS • CONTROLLERS

SAIA-Burgess Electronics Limited
 Dukeway, Team Valley Trading Estate
 Gateshead, Tyne & Wear NE11 0UB
 Tel: (0191)4016100, Fax: (0191)4016322



DO NOT SCALE !
 This drawing must only be amended on CAD system

TOLERANCES UNLESS STATED:-
 NO DECIMAL PLACE ± 0.50 1 DECIMAL PLACES ± 0.25
 2 DECIMAL PLACES ± 0.15 ANGULAR $\pm 1^\circ$
 INCH - OUNCE UNITS (IN BRACKETS)

ALL DIMENSIONS SPECIFIED IN MILLIMETRES

DRAWN	T.BELL.	Approved	
DATE	19/7/00	DRAWING OFFICE	<i>[Signature]</i>
SCALE	2/1	ENGINEERING	<i>[Signature]</i>
DATE ISSUED		QUALITY ASSURANCE	<i>[Signature]</i>

TITLE / DESCRIPTION
V3SY1 UL

Drg No :- C 44045

A3