

1. Features

- Typical 1dB bandwidth of 16.1 MHz
- High attenuation
- Single Ended Operation
- Surface Mounted Package (SMD)

RoHS Compliant

Tested by SGS Testing Korea


2. Electrical Specifications

Source and Load Impedance = 50Ω

Operating Temperature : +25°C

		Minimum	Typical	Maximum
Center Frequency (fo)	MHz	-	120.0	-
Insertion Loss	dB	-	22.5	25.0
1dB Bandwidth	MHz	-	16.17	-
3dB Bandwidth	MHz	16.4	16.6	-
40dB Bandwidth	MHz	-	18.5	18.7
Amplitude Ripple (fo ± 7.7 MHz)	dB	-	0.55	1.0
Group Delay Variation (fo ± 7.7 MHz)	nsec	-	30	60
Absolute Delay	usec	-	1.52	-
Ultimate Rejection	dB	50	55	-
Temperature Coefficient of Frequency	ppm/°C	-	-72	-

S1365 Package Dimension



Matching Schematic



Dimensions shown are nominal in millimeters

Body : Al₂O₃

Lid : Kovar, Ni Plated

Termination : Au plating 0.3 ~ 1.0um, over a 1.27 ~ 8.89um Ni Plating

Input	11	Ground	12, 6
Output	5	Others	Ground

3. Typical Performance (at +25°C)

