

DATA SHEET

THIN FILM CHIP RESISTORS

<u>AUTOMOTIVE</u> GRADE

RP series
0.1% TO 1%, TC25 TO TC50
sizes 0402/0603/0805/1206
RoHS compliant



YAGEO





Chip Resistor Surface Mount

RP SERIES

0402 to 1206

SCOPE

This specification describes RP0402 to RP1206 high precision-high stability chip resistors made by thin film process.

APPLICATIONS

- Automotive electronics
- Industrial and medical equipment
- Test and measuring equipment
- Telecommunications

FEATURES

- · AEC-Q200 qualified
- Total lead free without RoHS exemption
- Halogen free epoxy
- Superior resistance against sulfur containing atmosphere
- Moisture sensitivity level: MSL I
- Reducing environmentally hazardous wastes
- High component and equipment reliability
- Non-forbidden materials used in products/production

ORDERING INFORMATION - GLOBAL PART NUMBER

Part number is identified by the series name, size, tolerance, packaging type, temperature coefficient, taping reel and resistance value.

GLOBAL PART NUMBER

RP XXXX X X X XX XXXXX L

(2) (3) (4) (5) (6)

(I) SIZE

0402 / 0603 / 0805 / 1206

(2) TOLERANCE

 $B = \pm 0.1\%$

 $C = \pm 0.25\%$

 $D = \pm 0.5\%$

 $F = \pm 1\%$

(3) PACKAGING TYPE

R = Paper taping reel

(4) TEMPERATURE COEFFICIENT OF RESISTANCE

 $D = \pm 25 \text{ ppm/}^{\circ}C$

 $E = \pm 50 \text{ ppm/}^{\circ}\text{C}$

(5) TAPING REEL

07 = 7 inch dia. Reel

(6) RESISTANCE VALUE

There are 2~4 digits indicated the resistor value.

Letter R/K/M is decimal point

Example: $100R = 100\Omega$

 $IK = I,000\Omega$

(7) DEFAULT CODE

Letter L is the system default code for ordering only. (NOTE)

ORDERING EXAMPLE

The ordering code of a RP0402 chip resistor, TC 25 value 56Ω with \pm 0.5% tolerance, supplied in 7-inch tape reel is: RP0402DRD0756RL.

NOTE

- I. All our Rchip products meet RoHS compliant and Halogen Free. "LFP" of the internal 2D reel label mentions "Lead Free Process".
- 2. On customized label, "LFP" or specific symbol can be printed.





MARKING

RP0402



No marking

RP0603



E-96 series: including values 10/11/13/15/20/75 of E-24 series, 3 digits



E-24 series: exception values 10/11/13/15/20/75 of E-24 series, one short bar under marking letter

RP0805 / RP1206



Both E-24 and E-96 series: 4 digits First three digits for significant figure and 4th digit for number of zeros


NOTE

For further marking information, please see special data sheet "Chip resistors marking".

CONSTRUCTION

The resistors are constructed out of a high grade ceramic body. Internal metal electrodes are added at each end connected by a resistive layer. This resistive layer is trimmed to its nominal value and on both ends a contact is made which will guarantee optimum solderability. This is achieved by applying several layers and for ease of soldering the outer layer consists of Ni/matte tin. Adding a special protective layer, passivation coating, on this series to enhance moisture resistance of the environment.

OUTLINES





Chip Resistor Surface Mount RP SERIES 0402 to 1206

DIMENSIONS

Table I

TYPE	L (mm)	W (mm)	H (mm)	I _I (mm)	I ₂ (mm)
RP0402	1.00 ±0.10	0.50 ±0.05	0.30 ±0.05	0.20 ±0.10	0.25 ±0.10
RP0603	1.60 ±0.10	0.80 ±0.10	0.45 ±0.10	0.25 ±0.15	0.25 ±0.15
RP0805	2.00 ±0.10	1.25 ±0.10	0.50 ±0.10	0.35 ±0.20	0.35 ±0.20
RP1206	3.10 ±0.10	1.60 ±0.10	0.55 ±0.10	0.45 ±0.20	0.40 ±0.20

ELECTRICAL CHARACTERISTICS

Table 2

	Operating			Max.—	Resistance Range (E-24/E-96 series)(Ω) & Tolerance ⁽¹⁾			ıce ^(I)		
	Temperature	Power	Max. Working	Overload	T.C.R.	±0.1%	±0.25%	±0.5%	±1%	
TYPE	Range	Rating	Voltage	Voltage	(ppm/°C) ⁽²⁾	(B)	(C)	(D)	(F)	
D DO 402		1/16W	50 V	100 V	±50 (E)		10 ≤ R ≤	≤ 240K		
RP0402					±25 (D)		10 ≤ R ≤	≤ 240K		
DD0403		1/10W	75V	V 150 V —	±50 (E)		10 ≤ R ≤	≤910K		
RP0603	FF 0C + 11FF 0C				±25 (D)		10 ≤ R ≤	≤910K		
D DOOG E	—–55 °C to +155 °C ⁻ —		150)/	50.1/	±50 (E)		10 ≤ R :	≤ IM5		
RP0805		1/8W	1/8W 150 V 3	1/8VV 150 V 300 V	300 V —	±25 (D)		10 ≤ R :	≤ IM5	
DDIOO		1/4W 200 N	200.1/	400.)/	±50 (E)		10 ≤ R :	≤ IM5		
RP1206			200 V	400 V —	±25 (D)		10 ≤ R :	≤ IM5		

NOTE: I. Global part number (code 7) 2. Global part number (code 9)



FOOTPRINT AND SOLDERING PROFILES

For recommended footprint and soldering profiles, please see the special data sheet "Chip resistors mounting".

PACKING STYLE AND PACKAGING QUANTITY

Table 3 Packing style and packaging quantity

PRODUCT TYPE	PATKING STYLE	REEL DIMENSION	QUANTITY PER REEL
RP0402	Paper taping reel	7" (178 mm)	10,000 Units
RP0603	Paper taping reel	7" (178 mm)	5,000 Units
RP0805	Paper taping reel	7" (178 mm)	5,000 Units
RPI206	Paper taping reel	7" (178 mm)	5,000 Units

NOTE: for paper tape and reel specification/dimensions, please see the special data sheet "packing" document.

FUNCTIONAL DESCRIPTION

OPERATING TEMPERATURE RANGE

Range: -55 °C to +155 °C

POWER RATING

Each type rated power at 70 °C: RP0402=1/16 W

RP0603=1/10 W

RP0805=1/8 W

RPI206=I/4 W

RATED VOLTAGE

The DC or AC (rms) continuous working voltage corresponding to the rated power is determined by the following formula:

$$V = \sqrt{(P \times R)}$$


Or max. working voltage whichever is less

Where

V=Continuous rated DC or AC (rms) working voltage (v)

P=Rated power

R=Resistance value (Ω)





Chip Resistor Surface Mount RP SERIES 0402 to 1206

TESTS AND REQUIREMENTS

Table 4 Test condition, procedure and requirements

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Short Time Overload	IEC60115-1 4.13	2.5 times of rated voltage or maximum overload voltage, the less of the above, for 5 sec at room temperature	±(0.05%+0.05Ω)
High Temperature Exposure	AEC-Q200 Test 3 MIL-STD-202 Method 108	1,000 hours at Tamb = 155 °C, unpowered	±(0.3%+0.05Ω)
Moisture Resistance	AEC-Q200 Test 6 MIL-STD-202 Method 106	Each temperature / humidity cycle is defined at 8 hours (method 106F), 3 cycles / 24 hours for 10d. with 25 °C / 65 °C 95% R.H, without steps 7a & 7b, unpowered Parts mounted on test-boards, without condensation on parts	±(0.1%+0.05Ω)
Biased Humidity	AEC-Q200 Test 7 MIL-STD-202 Method 103	I,000 hours; 85 °C / 85% RH I0% of operating power Measurement at 24±4 hours after test conclusion	±(0.1%+0.05Ω)
Life	AEC-Q200 Test 8 MIL-STD-202 Method 108	1,000 hours at 70 ± 5 °C, RCWV applied for 1.5 hours on, 0.5 hour off, still air required	±(0.1%+0.05Ω)
Resistance to Soldering Heat	AEC-Q200 Test 15 MIL-STD-202 Method 210	Condition B, no pre-heat of samples Lead-free solder, 260±5 °C, 10±1 seconds immersion time Procedure 2 for SMD: devices fluxed and cleaned with isopropanol	±(0.05%+0.05Ω)
Thermal Shock	AEC-Q200 Test 16 MIL-STD-202 Method 107	-55/+125 °C Number of cycles is 300. Devices mounted Maximum transfer time is 20 seconds. Dwell time is 15 minutes. Air – Air	±(0.1%+0.05Ω) No visible damage
Solderability - Wetting	AEC-Q200 Test 18 J-STD-002	Electrical Test not required Magnification 50X SMD conditions: (a) Method B, aging 4 hours at 155 °C dry heat, dipping at 235±3 °C for 5±0.5 seconds. (b) Method B, steam aging 8 hours, dipping at 215±3 °C for 5±0.5 seconds. (c) Method D, steam aging 8 hours, dipping at 260±3 °C for 7±0.5 seconds	Well tinned (>95% covered) No visible damage



Chip Resistor Surface Mount RP SERIES 0402 to 1206

TEST	TEST METHOD	PROCEDURE	REQUIREMENTS
Board Flex / Bending	AEC-Q200 Test 21 AEC-Q200-005	Chips mounted on a 90mm glass epoxy resin PCB (FR4) Bending for 0402: 5 mm 0603/0805: 3 mm 1206: 2mm Holding time: minimum 60 second	±(0.1%+0.05Ω)
Temperature Coefficient of Resistance (T.C.R.)	IEC 60115-1 4.8	At +25/–55 °C and Refer to table 2 +25/+125°C Formula: $T.C.R = \frac{R2 - R1}{R1(t2 - tl)} \times 10^{6} (ppm/^{\circ}C)$	
		Where t1=+25 °C or specified room temperature t2=-55 °C or +125 °C test temperature R1=resistance at reference temperature in ohms R2=resistance at test temperature in ohms	
Flower of Sulfur	ASTM-B-809-95* * Modified	Sulfur 750 hours, 105°C, unpowered. $\pm (2.0\% + 0.05\Omega)$	



Product specification

8 9

Chip Resistor Surface Mount RP SERIES 0402 to 1206

REVISION HISTORY

REVISION DATE CHANGE NOTIFICATION DESCRIPTION

Version 0 Jul. 25, 2022 - - First issue of this specification



Chip Resistor Surface Mount RP SERIES 0402 to 1206

LEGAL DISCLAIMER

YAGEO, its distributors and agents (collectively, "YAGEO"), hereby disclaims any and all liabilities for any errors, inaccuracies or incompleteness contained in any product related information, including but not limited to product specifications, datasheets, pictures and/or graphics. YAGEO may make changes, modifications and/or improvements to product related information at any time and without notice.

YAGEO makes no representation, warranty, and/or guarantee about the fitness of its products for any particular purpose or the continuing production of any of its products. To the maximum extent permitted by law, YAGEO disclaims (i) any and all liability arising out of the application or use of any YAGEO product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for a particular purpose, non-infringement and merchantability.

YAGEO statements regarding the suitability of products for certain types of applications are based on YAGEO's knowledge of typical operating conditions for such types of applications in a generic nature. Such statements are neither binding statements of YAGEO nor intended to constitute any warranty concerning the suitability for a specific customer application or use. They are intended for use only by customers with requisite knowledge and experience for determining whether YAGEO products are the correct products for their application or use. In addition, unpredicatable and isolated cases of product failure may still occur, therefore, customer application or use of YAGEO products which requires higher degree of reliability or safety, shall employ additional protective safeguard measures to ensure that product failure would not result in personal injury or property damage.

YAGEO products are not designed for application or use in medical, life-saving, or life-sustaining devices or for any other application or use in which the failure of YAGEO products could result in personal injury or death. Customers using or selling YAGEO products not expressly indicated for above-mentioned purposes shall do so at their own risk and agree to fully indemnify YAGEO and hold YAGEO harmless.

Information provided here is intended to indicate product specifications only. YAGEO reserves all the rights for revising this content without further notification, as long as products are unchanged. Any product change will be announced by PCN.



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

YAGEO:

```
RP0603BRD0736KL RP0603BRD0733KL RP0402BRD075K62L RP0402BRD0747KL RP0402BRD078K45L
RP0603DRE07499RL RP0805FRE0710KL RP0603BRE07200RL RP0402FRE0710KL RP0603BRD075K6L
RP0805BRD07510KL RP0603BRD074K99L RP0603BRD07470RL RP0603DRD0710KL RP0603BRD078K2L
RP0402BRD0751KL RP0603DRD071KL RP0603FRE07100KL RP0603BRE0775KL RP0603FRE0715KL
RP0805BRD071K5L RP0402BRD0733KL RP0603BRD0715KL RP0603FRE0724KL RP0805BRD07698RL
RP1206BRD07287KL RP0402BRD071KL RP0603BRD075K76L RP0402BRD0723K7L RP0402BRD07562RL
RP1206BRD07499KL RP0402BRD0749K9L RP0402FRE071KL RP0603BRD076K81L RP0402BRD073K3L
RP1206BRD07200KL RP0402BRD0722K1L RP0805BRD071KL RP0402BRD071K21L RP0603FRE0747KL
RP0603FRE0710KL RP0603BRD071K8L RP1206FRE0710K5L RP0402BRD074K75L RP0402BRD07110RL
RP0402BRD073K32L RP0603FRE073K6L RP1206BRD075K1L RP0402FRE071K5L RP0603BRD077K5L
RP0402FRE0717K8L RP0603BRD076K8L RP1206FRE072K74L RP0402BRD0711KL RP0603BRD0790K9L
RP1206BRD07300KL RP0603FRE071K5L RP0603BRD0720RL RP0402BRD0736K5L RP0402BRD0739KL
RP0402BRD075K9L RP0603BRE0712K1L RP0402BRD072K7L RP0402DRD0782KL RP0402BRD0730K1L
RP0603FRE072K2L RP0805BRD074K99L RP0603BRD073K3L RP0402BRD07845RL RP0603BRD0751KL
RP0402BRD072K2L RP0402BRD07100KL RP0603BRD073K9L RP0402BRD07143KL RP0402BRD0730KL
RP0805DRE0724KL RP0603BRD0716KL RP0603BRE0730KL RP0402BRD0712K4L RP0805FRE07470RL
RP0603BRD0732K4L RP0402BRD072K21L RP1206BRD0710KL RP0402BRE0726K1L RP0402BRD0713K7L
RP1206BRD07787KL RP0603FRE071KL RP0603BRD0710KL RP0402BRD07100RL RP0603BRD0768KL
RP0603DRE071K69L RP0402BRD0726K1L RP1206BRD071ML RP1206BRE07499KL RP0603BRE0712KL
RP0805BRD0720KL RP0805BRD07150RL RP0603BRD0712KL RP0805BRD07100KL RP0402BRD0710KL
```