TECHNICAL DATA

SAPPHIRE HI-LOAD 2

High Load Grease

Description

ROCOL Sapphire Hi-Load 2 is a long life bearing grease containing Molybdenum Disulphide to ensure the effective lubrication and protection of all types of ball, roller and plain bearings under higher load or wear conditions.

Outstanding Features

- · Revolutionary multi-complex soap technology
- · Greatly extended lubrication intervals
- · Extremely high load carrying properties
- Good corrosion resistance

Directions for use

ROCOL Sapphire Hi-Load 2 can be applied manually or by a suitable applicator, eg. ROCOL Grease Gun. ROCOL Sapphire Hi-Load 2 is compatible with other soap-thickened greases. However, for best results, bearings should be cleaned or purged of the previous lubricant

Technical Data

Appearance : Smooth, blue-black grease

NLGI No. (IP 50)(ASTM D217) : NLGI No. 2
Base fluid type : Mineral oil

Thickener : Multi-Complex Soap
Solid Lubricant : Molybdenum Disulphide

Shell 4 Ball (IP 239) ASTM D2596)

Weld Load : >800kg
Load-Wear Index : 144kg
Timken 'OK' Load : 70lb

Temperature range (ASTM D128) : -30°C to +150°C

 Corrosion test (IP 112)(ASTM D130)
 : 1a.

 Corrosion test - Emcor (IP 220)
 : 0:0

 Water Washout Test (IP 215)(ASTM D1264)
 : 2%

Storage : Store in a cool/dry place

continued......

ROCOL Limited

ROCOL House, Swillington, Leeds LS26 8BS, England.
Tel: 0113 232 2600 Fax:: 0113 232 2760
ROCOL is a BS EN ISO 9002 registered company.
ROCOL is a trade mark of ROCOL Limited

Health and Safety

Further Technical Data and Health and Safety information (COSHH, MSDS) is available from the Customer Service Department, ROCOL Ltd., ROCOL House, Swillington, Leeds, LS26 8BS, England. **Telephone:** 0113 232 2700, (When calling from outside UK: 44 113 232 2700); **Fax:** 0113 232 2740, (When faxing from outside UK: 44 113 232 2740).

Issue: 1276a 20/02/96

ROCOL Limited