

7801 SWITCH OPERATED 3/2 VALVE, MALE, OUTLET VERSION



for metric tubing

[Zoom](#)

- [Description](#)
- [Dimensions](#)
- [Specifications](#)
- [CAD drawings](#)
- [Related products](#)

[Display Part No for imperial tubing](#)

convert weight standard : [kg](#) | [oz](#)

	ØD (mm)	C	F (mm)	F1 (mm)	H (mm)	L1 (mm)	L2 (mm)	 (kg)
7801 04 10	4	G1/8	14,0	14,0	42,5	7,0	18,5	0,024
7801 06 10	6	G1/8	14,0	14,0	42,5	7,0	20,0	0,025
7801 06 13	6	G1/4	17,0	17,0	51,0	9,0	22,0	0,048
7801 08 10	8	G1/8	14,0	14,0	42,5	7,0	25,0	0,026
7801 08 13	8	G1/4	17,0	17,0	51,0	9,0	27,0	0,049
7801 10 13	10	G1/4	17,0	17,0	51,0	9,0	29,0	0,005



7801 SWITCH OPERATED 3/2 VALVE, MALE, OUTLET VERSION

[Description](#)
[Dimensions](#)
[Specifications](#)
[CAD drawings](#)
[Related products](#)

direction of medium: one way

maximum working pressure	bar 10	MPa 1	psi 145
working temperature	°C (Celsius) From -10 to 80	F (Fahrenheit) From 14 to 176	K (Kelvin) From 263 to 353
body	engineering grade polymer		
sub-base	nickel-plated brass		
'O'-rings	nitrile		