

FEATURES

- This capacitive sensor can detect both metal and non-metal objects
- It also has the ability to detect various media via non-metallic containers
- They provide reliable and accurate liquid level detection
- Provides a lower-cost solution for proximity sensor needs whilst featuring good resolution, stability, high speed and low power usage
- Each sensor has a simple in construction and is adjustable
- They can be used for the measurement of force, pressure and humidity, etc. and they have a higher sensitivity and can be operational with small magnitude of force
- Capacitive proximity sensing offers increased usability, improved industrial design, and increased functionality with many different consumer applications

RS PRO Capacitive Proximity Sensor - 65mm Non Flush Mount Capacitive sensor

RS Stock No.: 146-6756



RS Professionally Approved Products bring to you professional quality parts across all product categories. Our product range has been tested by engineers and provides a comparable quality to the leading brands without paying a premium price.



Product Description

RS PRO Non-Flush Mount Capacitive Proximity Sensor

Introducing the range of RS PRO Capacitive Proximity Sensors. These versatile and high-quality sensors are an essential addition to any environment where measurement of attributes like pressure, thickness, etc. are integral to business operations, like manufacturing plants and industrial environments. With the RS PRO seal of approval, you are guaranteed a premium performance product, without the premium product price tag.

General Specifications

Sensing/Detection Range	4mm
Rated Distance Sn	4mm
Output Type	PNP-NO
Connection/Terminal Type	M12 - 4 Pin
Power-on indication	Yellow LED
Shielding	Unshielded
Minimum Operating Temperature	-25°C
Maximum Operating Temperature	+70°C

Electrical Specifications

Operating Supply Voltage	10 → 30 V dc	
Switching Current	200 mA	
Switching Frequency	50 Hz	
Temperature drift / Hysteresis range	320%	
Contact Maximum DC Voltage	30V	
Short Circuit Overload Protection	YES	
Reverse Polarity Protection	YES	
Overload Protection	YES	

Mechanical Specifications

Body Style	Barrel	
Mounting Style	Non Flush	
Thread Size	M12 x 1	
Housing Material	Nickel Copper Alloy	
Length	65mm	

Capacitive Proximity Sensors



Protection Category

IP Rating IP67

Approvals

Declarations RoHS Certificate of Compliance

Similar Products

Stock No.	Brand	Product Name	Terminal Type	Sensing/Detection Range	Output Type
896-7248	RS PRO	Non Flush Mount Capacitive sensor	M12 - 4 Pin	8 mm	PNP-NO
896-7235	RS PRO	Non Flush Mount Capacitive sensor	Cable	8 mm	PNP-NO