




littelfuse.com

MINI® Blade Fuses Rated 32V

Dimensions

Dimensions in mm for reference only. See outline drawing for dimensions and tolerances.




Temperature Table

	max. allowed current load [A] at ambient temperature (typical derating)							
	-40°C	-20°C	0°C	20°C	40°C	60°C	80°C	100°C
2A	2.0	2.0	2.0	1.9	1.7	1.6	1.4	1.3
3A	3.0	2.8	2.7	2.5	2.4	2.2	2.0	1.8
4A	4.0	3.8	3.6	3.4	3.2	2.9	2.7	2.4
5A	5.0	4.8	4.5	4.3	4.0	3.7	3.4	3.0
7.5A	7.5	7.1	6.8	6.4	6.0	5.5	5.1	4.5
10A	10	10	9.8	9.2	8.6	8.0	7.3	6.5
15A	15	15	14	13	12	12	11	9.0
20A	20	19	18	17	16	15	14	12
25A	25	24	22	21	20	18	17	15
30A	30	29	27	26	24	22	20	18

Typical Derating of Fuse Melting Element

Temperature Security Margin is 20%

Please contact Littelfuse® for Details Regarding Derating Test Set-Up.



Derating curves may change depending on the final condition of the application (terminals characteristics, wire size etc.). Please ask Littelfuse® for more information.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

[OMIN003.V](#) [OMIN015.V](#) [LMIN015.V](#) [OMIN004.V](#) [LMIN004.V](#) [OMIN07.5V](#) [LMIN07.5V](#) [LMIN002.V](#) [OMIN002.V](#)
[LMIN010.V](#) [OMIN010.V](#) [OMIN030.V](#) [LMIN030.V](#) [297004](#) [297002](#) [297003](#) [297005](#) [29707.5](#) [297010](#) [297015](#)
[297020](#) [297025](#) [297030](#) [029707.5WXNV](#) [0297003.WXNV](#) [0297015.WXNV](#) [0297020.WXNV](#) [0297002.LXN](#)
[LMIN025.V](#) [OMIN025.V](#) [OMIN020.V](#) [LMIN020.V](#) [OMIN005.V](#) [LMIN005.V](#) [0297002.L](#) [0297005.WXNV](#)
[0297010.WXNV](#) [0297002.WXNV](#) [0297030.WXNV](#) [0297025.WXNV](#) [0297004.WXNV](#) [029707.5U](#) [0297025.U](#)
[0297005.L](#) [0297002.H](#) [LMIN030.VP](#) [0297025.L](#) [0297003.U](#) [OMIN030.ZXPRO](#) [0297004.WXUL](#) [OMIN025.ZXPRO](#)
[0297020.H](#) [029707.5H](#) [0297010.U](#) [0297030.WXUL](#) [0297004.H](#) [OMIN010.VP](#) [LMIN010.VP](#) [OMIN004.VP](#)
[029707.5WXUL](#) [OMIN030.VP](#) [OMIN015.VP](#) [0297015.WXUL](#) [0297005.H](#) [0297030.U](#) [OMIN020.ZXPRO](#)
[0297020.WXUL](#) [029707.5L](#) [OMIN025.VP](#) [0297003.WXUL](#) [0297025.H](#) [0297030.L](#) [LMIN005.VP](#) [OMIN002.VP](#)
[0297025.WXUL](#) [0297010.H](#) [0297003.H](#) [OMIN005.VP](#) [0297005.U](#) [OMIN020.VP](#) [0297010.WXUL](#) [0297003.L](#)
[OMIN07.5VP](#) [0297030.H](#) [OMIN003.VP](#) [0297020.L](#) [0297002.WXUL](#) [0297010.L](#) [LMIN015.VP](#) [0297005.WXUL](#)
[0297004.L](#) [0297015.H](#) [LMIN020.VP](#) [LMIN025.VP](#) [0297004.U](#) [0297002.U](#) [0297020.U](#) [0297010.LXN](#) [0297015.L](#)
[0297015.U](#)