

LD1117

Adjustable and fixed low drop positive voltage regulator

 Орак
 Орак

 TO-220
 Орак

 Хот-223
 SO-8

Features

- Low dropout voltage (1 V typ.)
- 2.85 V device performances are suitable for SCSI-2 active termination
- Output current up to 800 mA
- Fixed output voltage of: 1.2 V, 1.8 V, 2.5 V, 3.3 V, 5.0 V
- Adjustable version availability (V_{REF} = 1.25 V)
- Internal current and thermal limit
- Available in ± 1 % (at 25 °C) and 2 % in full temperature range
- Supply voltage rejection: 75 dB (typ.)

Datasheet - production data

Description

The LD1117 is a low drop voltage regulator able to provide up to 800 mA of output current, available even in adjustable version $(V_{BFF} = 1.25 \text{ V})$. Concerning fixed versions, are offered the following output voltages: 1.2 V, 1.8 V, 2.5 V, 2.85 V, 3.3 V and 5.0 V. The device is supplied in: SOT-223, DPAK, SO-8 and TO-220. The SOT-223 and DPAK surface mount packages optimize the thermal characteristics even offering a relevant space saving effect. High efficiency is assured by NPN pass transistor. In fact in this case, unlike than PNP one, the quiescent current flows mostly into the load. Only a very common 10 µF minimum capacitor is needed for stability. On chip trimming allows the regulator to reach a very tight output voltage tolerance, within ± 1 % at 25 °C. The adjustable LD1117 is pin to pin compatible with the other standard. Adjustable voltage regulators maintaining the better performances in terms of drop and tolerance.

February 2020

www.st.com

This is information on a product in full production.

Contents

1	Diagram
2	Pin configuration
3	Maximum ratings
4	Schematic application
5	Electrical characteristics9
6	Typical application
7	LD1117 adjustable: application note
8	Package information 25
9	Packaging mechanical data 38
10	Order codes 44
11	Revision history



List of tables

Table 1.	Absolute maximum ratings
Table 2.	Thermal data
Table 3.	Electrical characteristics of LD1117#129
Table 4.	Electrical characteristics of LD1117#18
Table 5.	Electrical characteristics of LD1117#25
Table 6.	Electrical characteristics of LD1117#33 12
Table 7.	Electrical characteristics of LD1117#50
Table 8.	Electrical characteristics of LD1117 (adjustable)
Table 9.	Electrical characteristics of LD1117#12C15
Table 10.	Electrical characteristics of LD1117#18C16
Table 11.	Electrical characteristics of LD1117#25C17
Table 12.	Electrical characteristics of LD1117#33C18
Table 13.	Electrical characteristics of LD1117#50C19
Table 14.	Electrical characteristics of LD1117C (adjustable)
Table 15.	TO-220 mechanical data (type STD-ST Dual Gauge)
Table 16.	TO-220 mechanical data (type STD-ST Single Gauge)
Table 17.	SOT-223 mechanical data
Table 18.	SO-8 mechanical data
Table 19.	DPAK (TO-252) mechanical data (type A) 31
Table 20.	DPAK (TO-252) mechanical data (type E)
Table 21.	DPAK (TO-252) mechanical data type I
Table 22.	Footprint data
Table 23.	SOT-223 tape and reel mechanical data
Table 24.	SO-8 tape and reel mechanical data
Table 25.	DPAK tape and reel mechanical data
Table 26.	Order codes
Table 27.	Document revision history



List of figures

Figure 1.	Block diagram
Figure 2.	Pin connections (top view)
Figure 3.	Application circuit (for 1.2 V)
Figure 4.	Application circuit (for other fixed output voltages)
Figure 5.	Negative supply
Figure 6.	Circuit for increasing output voltage
Figure 7.	Voltage regulator with reference
Figure 8.	Battery backed-up regulated supply 22
Figure 9.	Post-regulated dual supply
Figure 10.	Adjustable output voltage application
Figure 11.	Adjustable output voltage application with improved ripple rejection
Figure 12.	Drawing dimension TO-220 (type STD-ST Dual Gauge)
Figure 13.	Drawing dimension TO-220 (type STD-ST Single Gauge)
Figure 14.	Drawing dimension SOT-223
Figure 15.	Drawing dimension SO-8
Figure 16.	DPAK (TO-252) package outline A
Figure 17.	DPAK (TO-252) package outline E
Figure 18.	DPAK (TO-252) package outline I
Figure 19.	DPAK footprint recommended data
Figure 20.	Drawing dimension tube for TO-220 Dual Gauge (mm.)
Figure 21.	Drawing dimension tube for TO-220 Single Gauge (mm.)
Figure 22.	Tape for SOT-223 (dimensions are in mm)39
Figure 23.	Reel for SOT-223 (dimensions are in mm) 40
Figure 24.	SO-8 tape and reel dimensions
Figure 25.	Tape for DPAK
Figure 26.	Reel for DPAK



1 Diagram





Figure 1. Block diagram



2 Pin configuration



Note: The TAB is connected to the V_{OUT}.



3 Maximum ratings

Table 1	. Absolute	maximum	ratings
---------	------------	---------	---------

Symbol	Parameter	Value	Unit	
V _{IN} ⁽¹⁾	DC input voltage	15	V	
P _{TOT}	Power dissipation	12	W	
T _{STG}	Storage temperature range	-40 to +150	°C	
т		for C version	-40 to +125	°C
T _{OP}	Operating junction temperature range for standard version		0 to +125	°C

1. Absolute maximum rating of V_{IN} = 18 V, when I_{OUT} is lower than 20 mA.

Table 2. Thermal data

Symbol	Parameter	SOT-223	SO-8	DPAK	TO-220	Unit
R _{thJC}	Thermal resistance junction-case	15	20	8	5	°C/W
R _{thJA}	Thermal resistance junction-ambient	110	55	100	50	°C/W

4 Schematic application





Figure 4. Application circuit (for other fixed output voltages)





5 Electrical characteristics

Refer to the test circuits, T_J = 0 to 125 °C, C_O = 10 μ F, R = 120 Ω between GND and OUT pins, unless otherwise specified.

Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
Vo	Output voltage	$V_{in} = 3.2 \text{ V}, I_O = 10 \text{ mA}, T_J = 25 \text{ °C}$	1.188	1.20	1.212	V
V _O	Output voltage	$I_{O} = 10 \text{ to } 800 \text{ mA}$ V _{in} - V _O = 1.4 to 10 V	1.140	1.20	1.260	V
ΔV_{O}	Line regulation	$V_{in} - V_O = 1.5$ to 13.75 V, $I_O = 10$ mA		0.035	0.2	%
ΔV_{O}	Load regulation	$V_{in} - V_O = 3 V, I_O = 10 \text{ to } 800 \text{ mA}$		0.1	0.4	%
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage				15	V
I _{adj}	Adjustment pin current	$V_{in} \le 15 \text{ V}$		60	120	μA
ΔI_{adj}	Adjustment pin current change	$V_{in} - V_O = 1.4 \text{ to } 10 \text{ V}$ $I_O = 10 \text{ to } 800 \text{ mA}$		1	5	μA
I _{O(min)}	Minimum load current	V _{in} = 15 V		2	5	mA
Ι _Ο	Output current	$V_{in} - V_O = 5 V, T_J = 25 °C$	800	950	1300	mA
eN	Output noise (%V _O)	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		0.003		%
SVR	Supply voltage rejection	$\label{eq:IO} \begin{array}{l} I_O = 40 \text{ mA, f} = 120 \text{ Hz, T}_J = 25 \ ^\circ\text{C} \\ V_{\text{in}} \text{-} V_O = 3 \text{ V, } V_{\text{ripple}} = 1 \ V_{\text{PP}} \end{array}$	60	75		dB
		I _O = 100 mA		1	1.1	
V _d	Dropout voltage	I _O = 500 mA		1.05	1.15	V
		I _O = 800 mA		1.10	1.2	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit	
V _O	Output voltage	$V_{in} = 3.8 \text{ V}, I_O = 10 \text{ mA}, T_J = 25 \text{ °C}$	1.78	1.8	1.82	V	
Vo	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 3.3$ to 8 V	1.76		1.84	V	
ΔV_{O}	Line regulation	$V_{in} = 3.3 \text{ to } 8 \text{ V}, I_O = 0 \text{ mA}$		1	6	mV	
ΔV_{O}	Load regulation	$V_{in} = 3.3 \text{ V}, I_{O} = 0 \text{ to } 800 \text{ mA}$		1	10	mV	
ΔV_O	Temperature stability			0.5		%	
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%	
V _{in}	Operating input voltage	I _O = 100 mA			15	V	
l _d	Quiescent current	$V_{in} \le 8 V$		5	10	mA	
Ι _Ο	Output current	V _{in} = 6.8 V, T _J = 25 °C	800	950	1300	mA	
eN	Output noise voltage	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		100		μV	
SVR	Supply voltage rejection	I_{O} = 40 mA, f = 120 Hz, T _J = 25 °C V _{in} = 5.5 V, V _{ripple} = 1 V _{PP}	60	75		dB	
		I _O = 100 mA		1	1.1		
V _d	Dropout voltage	I _O = 500 mA		1.05	1.15	V	
		I _O = 800 mA		1.10	1.2		
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W	



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
Vo	Output voltage	V_{in} = 4.5 V, I_O = 10 mA, T_J = 25 °C	2.475	2.5	2.525	V
Vo	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 3.9$ to 10 V	2.45		2.55	V
ΔV_{O}	Line regulation	$V_{in} = 3.9$ to 10 V, $I_O = 0$ mA		1	6	mV
ΔV_{O}	Load regulation	$V_{in} = 3.9 \text{ V}, I_O = 0 \text{ to } 800 \text{ mA}$		1	10	mV
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage	I _O = 100 mA			15	V
I _d	Quiescent current	V _{in} ≤ 10 V		5	10	mA
Ι _Ο	Output current	V _{in} = 7.5 V T _J = 25 °C	800	950	1300	mA
eN	Output noise voltage	B = 10 Hz to 10 kHz, T_{J} = 25 °C		100		μV
SVR	Supply voltage rejection	$I_{O} = 40 \text{ mA, f} = 120 \text{ Hz, T}_{J} = 25 \text{ °C}$ $V_{in} = 5.5 \text{ V, } V_{ripple} = 1 \text{ V}_{PP}$	60	75		dB
		I _O = 100 mA		1	1.1	
V_{d}	Dropout voltage	I _O = 500 mA		1.05	1.15	V
		I _O = 800 mA		1.10	1.2	
	Thermal regulation	$T_a = 25 \text{ °C}, 30 \text{ ms Pulse}$		0.01	0.1	%/W

Table 5.	Electrical	characteristics	of LD1117#25
----------	------------	-----------------	--------------



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _O	Output voltage	V_{in} = 5.3 V, I _O = 10 mA, T _J = 25 °C	3.267	3.3	3.333	V
Vo	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 4.75$ to 10 V	3.235		3.365	V
ΔV_{O}	Line regulation	$V_{in} = 4.75$ to 15 V, $I_O = 0$ mA		1	6	mV
ΔV_{O}	Load regulation	$V_{in} = 4.75 \text{ V}, I_O = 0 \text{ to } 800 \text{ mA}$		1	10	mV
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage	I _O = 100 mA			15	V
۱ _d	Quiescent current	$V_{in} \le 15 \text{ V}$		5	10	mA
Ι _Ο	Output current	V _{in} = 8.3 V, T _J = 25 °C	800	950	1300	mA
eN	Output noise voltage	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		100		μV
SVR	Supply voltage rejection	$I_{O} = 40 \text{ mA}, f = 120 \text{ Hz}, T_{J} = 25 \text{ °C}$ $V_{in} = 6.3 \text{ V}, V_{ripple} = 1 \text{ V}_{PP}$	60	75		dB
		I _O = 100 mA		1	1.1	
V _d	Dropout voltage	I _O = 500 mA		1.05	1.15	V
		I _O = 800 mA		1.10	1.2	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
Vo	Output voltage	V _{in} = 7 V, I _O = 10 mA, T _J = 25 °C	4.95	5	5.05	V
Vo	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 6.5$ to 15 V	4.9		5.1	V
ΔV_O	Line regulation	$V_{in} = 6.5 \text{ to } 15 \text{ V}, I_{O} = 0 \text{ mA}$		1	10	mV
ΔV_O	Load regulation	$V_{in} = 6.5 \text{ V}, I_{O} = 0 \text{ to } 800 \text{ mA}$		1	15	mV
ΔV_O	Temperature stability			0.5		%
ΔV_O	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage	I _O = 100 mA			15	V
I _d	Quiescent current	$V_{in} \le 15 \text{ V}$		5	10	mA
Ι _Ο	Output current	V _{in} = 10 V, T _J = 25 °C	800	950	1300	mA
eN	Output noise voltage	B = 10 Hz to 10 kHz, T _J = 25 °C		100		μV
SVR	Supply voltage rejection	$ I_O = 40 \text{ mA, } f = 120 \text{ Hz, } T_J = 25 \text{ °C} $ $ V_{in} = 8 \text{ V, } V_{ripple} = 1 \text{ V}_{PP} $	60	75		dB
		I _O = 100 mA		1	1.1	
V _d	Dropout voltage	I _O = 500 mA		1.05	1.15	V
		I _O = 800 mA		1.10	1.2	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W

Table 7. Electrical cha	aracteristics of LD1117#50
-------------------------	----------------------------



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _{ref}	Reference voltage	V_{in} - V_O = 2 V, I_O = 10 mA, T_J = 25 °C	1.238	1.25	1.262	V
V _{ref}	Reference voltage	I_{O} = 10 to 800 mA, V_{in} - V_{O} = 1.4 to 10 V	1.225		1.275	V
ΔV_O	Line regulation	$V_{in} - V_O = 1.5$ to 13.75 V, $I_O = 10$ mA		0.035	0.2	%
ΔV_O	Load regulation	$V_{in} - V_O = 3 V, I_O = 10 \text{ to } 800 \text{ mA}$		0.1	0.4	%
ΔV_O	Temperature stability			0.5		%
ΔV_O	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage				15	V
I _{adj}	Adjustment pin current	$V_{in} \le 15 \text{ V}$		60	120	μA
ΔI_{adj}	Adjustment pin current change	V_{in} - V_O = 1.4 to 10 V, I_O = 10 to 800 mA		1	5	μA
I _{O(min)}	Minimum load current	V _{in} = 15 V		2	5	mA
Ι _Ο	Output current	V _{in} - V _O = 5 V, T _J = 25 °C	800	950	1300	mA
eN	Output noise (%V _O)	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		0.003		%
SVR	Supply voltage rejection	$\begin{split} I_{O} &= 40 \text{ mA, } f = 120 \text{ Hz, } T_{J} = 25 ^{\circ}\text{C} \\ V_{in} ^{\circ} V_{O} &= 3 \text{V, } V_{ripple} = 1 V_{PP} \end{split}$	60	75		dB
		I _O = 100 mA		1	1.1	
V _d	Dropout voltage	I _O = 500 mA		1.05	1.15	V
		I _O = 800 mA		1.10	1.2	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W



Refer to the test circuits, T_J = -40 to 125 °C, C_O = 10 μ F, R = 120 Ω between GND and OUT pins, unless otherwise specified.

Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _O	Output voltage	$V_{in} - V_O = 2 V, I_O = 10 mA, T_J = 25 °C$	1.176	1.20	1.224	V
V _O	Output voltage	$I_{O} = 10$ to 800 mA, $V_{in} - V_{O} = 1.4$ to 10 V	1.120	1.20	1.280	V
ΔV_{O}	Line regulation	$V_{in} - V_O = 1.5$ to 13.75 V, $I_O = 10$ mA			1	%
ΔV_{O}	Load regulation	$V_{in} - V_O = 3 V, I_O = 10 \text{ to } 800 \text{ mA}$			1	%
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage				15	V
I _{adj}	Adjustment pin current	$V_{in} \le 15 \text{ V}$		60	120	μA
ΔI_{adj}	Adjustment pin current change	$V_{in} - V_O = 1.4 \text{ to } 10 \text{ V}$ $I_O = 10 \text{ to } 800 \text{ mA}$		1	5	μA
I _{O(min)}	Minimum load current	V _{in} = 15 V		2	5	mA
Ι _Ο	Output current	V _{in} - V _O = 5 V, T _J = 25 °C	800	950	1300	mA
eN	Output noise (%V _O)	B = 10 Hz to 10 kHz, T_J = 25 °C		0.003		%
SVR	Supply voltage rejection	$I_{O} = 40 \text{ mA}, \text{ f} = 120 \text{ Hz}, \text{ T}_{J} = 25 \text{ °C}$ $V_{in} - V_{O} = 3 \text{ V}, V_{ripple} = 1 \text{ V}_{PP}$	60	75		dB
		$I_{O} = 100 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1	1.1	
V_{d}	Dropout voltage	$I_{O} = 500 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.05	1.2	V
		$I_{O} = 800 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.10	1.3	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W

Table 9. Electrical characteristics of LD1117#12C



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _O	Output voltage	V_{in} = 3.8 V, I_{O} = 10 mA, T_{J} = 25 °C	1.76	1.8	1.84	V
Vo	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 3.9$ to 10 V	1.73		1.87	V
ΔV_{O}	Line regulation	$V_{in} = 3.3 \text{ to } 8 \text{ V}, I_{O} = 0 \text{ mA}$		1	30	mV
ΔV_{O}	Load regulation	$V_{in} = 3.3 \text{ V}, I_{O} = 0 \text{ to } 800 \text{ mA}$		1	30	mV
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage	I _O = 100 mA			15	V
۱ _d	Quiescent current	$V_{in} \le 8 V$		5	10	mA
Ι _Ο	Output current	V _{in} = 6.8 V T _J = 25 °C	800	950	1300	mA
eN	Output noise voltage	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		100		μV
SVR	Supply voltage rejection	$I_{O} = 40 \text{ mA, } f = 120 \text{ Hz, } T_{J} = 25 \text{ °C}$ $V_{in} = 5.5 \text{ V, } V_{ripple} = 1 \text{ V}_{PP}$	60	75		dB
		$I_{O} = 100 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1	1.1	
V_{d}	Dropout voltage	$I_{O} = 500 \text{ mA}, \text{T}_{\text{J}} = 0 \text{ to } 125 ^{\circ}\text{C}$		1.05	1.15	V
		$I_{O} = 800 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.10	1.2	
		l _O = 100 mA			1.1	
V_{d}	Dropout voltage	I _O = 500 mA			1.2	V
		I _O = 800 mA			1.3	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _O	Output voltage	V_{in} = 4.5 V, I_{O} = 10 mA, T_{J} = 25 °C	2.45	2.5	2.55	V
Vo	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 3.9$ to 10 V	2.4		2.6	V
ΔV_{O}	Line regulation	$V_{in} = 3.9$ to 10 V, $I_0 = 0$ mA		1	30	mV
ΔV_{O}	Load regulation	$V_{in} = 3.9 \text{ V}, I_{O} = 0 \text{ to } 800 \text{ mA}$		1	30	mV
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage	I _O = 100 mA			15	V
I _d	Quiescent current	$V_{in} \le 10 \text{ V}$		5	10	mA
Ι _Ο	Output current	V _{in} = 7.5 V T _J = 25 °C	800	950	1300	mA
eN	Output noise voltage	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		100		μV
SVR	Supply voltage rejection	$\label{eq:loss} \begin{array}{l} I_O = 40 \text{ mA, } f = 120 \text{ Hz, } T_J = 25 \text{ °C} \\ V_{in} = 5.5 \text{ V, } V_{ripple} = 1 \text{ V}_{PP} \end{array}$	60	75		dB
		$I_{O} = 100 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1	1.1	
V _d	Dropout voltage	$I_{O} = 500 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.05	1.15	V
		$I_{O} = 800 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.10	1.2	
		I _O = 100 mA			1.1	
V _d	Dropout voltage	I _O = 500 mA			1.2	V
		I _O = 800 mA			1.3	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _O	Output voltage	$V_{in} = 5.3 \text{ V}, \text{ I}_{O} = 10 \text{ mA}, \text{ T}_{J} = 25 \text{ °C}$	3.24	3.3	3.36	V
Vo	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 4.75$ to 10 V	3.16		3.44	V
ΔV_{O}	Line regulation	$V_{in} = 4.75$ to 15 V, $I_{O} = 0$ mA		1	30	mV
ΔV_{O}	Load regulation	$V_{in} = 4.75 \text{ V}, I_{O} = 0 \text{ to } 800 \text{ mA}$		1	30	mV
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage	I _O = 100 mA			15	V
I _d	Quiescent current	$V_{in} \le 15 \text{ V}$		5	10	mA
Ι _Ο	Output current	V _{in} = 8.3 V, T _J = 25 °C	800	950	1300	mA
eN	Output noise voltage	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		100		μV
SVR	Supply voltage rejection	$I_{O} = 40$ mA, f = 120 Hz, T _J = 25 °C V _{in} = 6.3 V, V _{ripple} = 1 V _{PP}	60	75		dB
		$I_{O} = 100 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1	1.1	
V_{d}	Dropout voltage	$I_{O} = 500 \text{ mA}, \text{T}_{\text{J}} = 0 \text{ to } 125 ^{\circ}\text{C}$		1.05	1.15	V
		$I_{O} = 800 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.10	1.2	
		I _O = 100 mA			1.1	
V_{d}	Dropout voltage	I _O = 500 mA			1.2	V
		I _O = 800 mA			1.3	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W

 Table 12. Electrical characteristics of LD1117#33C



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _O	Output voltage	V_{in} = 7 V, I_{O} = 10 mA, T_{J} = 25 °C	4.9	5	5.1	V
V _O	Output voltage	$I_{O} = 0$ to 800 mA, $V_{in} = 6.5$ to 15 V	4.8		5.2	V
ΔV_{O}	Line regulation	V_{in} = 6.5 to 15 V, I _O = 0 mA		1	50	mV
ΔV_{O}	Load regulation	$V_{in} = 6.5 \text{ V}, I_{O} = 0 \text{ to } 800 \text{ mA}$		1	50	mV
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage	I _O = 100 mA			15	V
۱ _d	Quiescent current	$V_{in} \le 15 V$		5	10	mA
Ι _Ο	Output current	V _{in} = 10 V, T _J = 25 °C	800	950	1300	mA
eN	Output noise voltage	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		100		μV
SVR	Supply voltage rejection	$I_{O} = 40 \text{ mA}, \text{ f} = 120 \text{ Hz}, \text{ T}_{J} = 25 \text{ °C}$ $V_{in} = 8 \text{ V}, \text{ V}_{ripple} = 1 \text{ V}_{PP}$	60	75		dB
		$I_{O} = 100 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1	1.1	
V _d	Dropout voltage	$I_{O} = 500 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.05	1.15	V
		$I_{O} = 800 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.10	1.2	
		l _O = 100 mA			1.1	
V_{d}	Dropout voltage	I _O = 500 mA			1.2	V
		I _O = 800 mA			1.3	
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W



Symbol	Parameter	Test condition	Min.	Тур.	Max.	Unit
V _{ref}	Reference voltage	$V_{in} - V_O = 2 \text{ V}, \text{ I}_O = 10 \text{ mA}, \text{ T}_J = 25 \text{ °C}$	1.225	1.25	1.275	V
V _{ref}	Reference voltage	I_{O} = 10 to 800 mA, V_{in} - V_{O} = 1.4 to 10 V	1.2		1.3	V
ΔV_{O}	Line regulation	$V_{in} - V_O = 1.5$ to 13.75 V, $I_O = 10$ mA			1	%
ΔV_{O}	Load regulation	$V_{in} - V_O = 3 V, I_O = 10 \text{ to } 800 \text{ mA}$			1	%
ΔV_{O}	Temperature stability			0.5		%
ΔV_{O}	Long term stability	1000 hrs, T _J = 125 °C		0.3		%
V _{in}	Operating input voltage				15	V
I _{adj}	Adjustment pin current	$V_{in} \le 15 \text{ V}$		60	120	μA
ΔI_{adj}	Adjustment pin current change	V_{in} - V_O = 1.4 to 10 V, I_O = 10 to 800 mA		1	10	μA
I _{O(min)}	Minimum load current	V _{in} = 15 V		2	5	mA
Ι _Ο	Output current	V _{in} - V _O = 5 V, T _J = 25 °C	800	950	1300	mA
eN	Output noise (%V _O)	B = 10 Hz to 10 kHz, $T_J = 25 \text{ °C}$		0.003		%
SVR	Supply voltage rejection	$I_{O} = 40$ mA, f = 120 Hz, T _J = 25 °C V _{in} - V _O = 3 V, V _{ripple} = 1 V _{PP}	60	75		dB
		I_{O} = 100 mA, T_{J} = 0 to 125 °C		1	1.1	
V _d	Dropout voltage	I _O = 500 mA, T _J = 0 to 125 °C		1.05	1.15	V
		$I_{O} = 800 \text{ mA}, T_{J} = 0 \text{ to } 125 \text{ °C}$		1.10	1.2	1
		I _O = 100 mA			1.1	
V_{d}	Dropout voltage	I _O = 500 mA			1.2	V
		I _O = 800 mA			1.3	1
	Thermal regulation	T _a = 25 °C, 30 ms Pulse		0.01	0.1	%/W

Table 14. Electrical characteristics of LD1117C (adjustable)



6 Typical application






Figure 6. Circuit for increasing output voltage





Figure 7. Voltage regulator with reference







Figure 8. Battery backed-up regulated supply



Figure 9. Post-regulated dual supply





7 LD1117 adjustable: application note

The LD1117 adjustable has a thermal stabilized 1.25 \pm 0.012 V reference voltage between the OUT and ADJ pins. I_{ADJ} is 60 μ A typ. (120 μ A max.) and ΔI_{ADJ} is 1 μ A typ. (5 μ A max.).


 R_1 is normally fixed to 120 Ω . From *Figure 9* we obtain:

 $V_{OUT} = V_{REF} + R_2 \left(I_{ADJ} + I_{R1} \right) = V_{REF} + R_2 \left(I_{ADJ} + V_{REF} / R_1 \right) = V_{REF} \left(1 + R_2 / R_1 \right) + R_2 \times I_{ADJ}.$

In normal application R₂ value is in the range of few k Ω , so the R₂ x I_{ADJ} product could not be considered in the V_{OUT} calculation; then the above expression becomes:

 $V_{OUT} = V_{REF} (1 + R_2 / R_1).$

In order to have the better load regulation it is important to realize a good Kelvin connection of R₁ and R₂ resistors. In particular R₁ connection must be realized very close to OUT and ADJ pin, while R₂ ground connection must be placed as near as possible to the negative Load pin. Ripple rejection can be improved by introducing a 10 μ F electrolytic capacitor placed in parallel to the R₂ resistor (see *Figure 10*).







Figure 11. Adjustable output voltage application with improved ripple rejection




8 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK packages, depending on their level of environmental compliance. ECOPACK specifications, grade definitions and product status are available at: *www.st.com*. ECOPACK is an ST trademark.

Dim.		mm	
Dim.	Min.	Тур.	Max.
А	4.40		4.60
b	0.61		0.88
b1	1.14		1.70
с	0.48		0.70
D	15.25		15.75
D1		1.27	
E	10		10.40
е	2.40		2.70
e1	4.95		5.15
F	1.23		1.32
H1	6.20		6.60
J1	2.40		2.72
L	13		14
L1	3.50		3.93
L20		16.40	
L30		28.90	
Øр	3.75		3.85
Q	2.65		2.95

Table 15. TO-220 mechanical data (type STD-ST Dual Gauge)









Dim	mm				
Dim. —	Min.	Тур.	Max.		
А	4.40		4.60		
b	0.61		0.88		
b1	1.14		1.70		
С	0.48		0.70		
D	15.25		15.75		
E	10		10.40		
е	2.40		2.70		
e1	4.95		5.15		
F	0.51		0.60		
H1	6.20		6.60		
J1	2.40		2.72		
L	13		14		
L1	3.50		3.93		
L20		16.40			
L30		28.90			
Øр	3.75		3.85		
Q	2.65		2.95		

Table 16. TO-220 mechanical data (type STD-ST Single Gauge)







Figure 13. Drawing dimension TO-220 (type STD-ST Single Gauge)



Dim		mm			
Dim.	Min.	Тур.	Max.		
А			1.80		
A1	0.02		0.10		
В	0.60	0.70	0.85		
B1	2.90	3.00	3.15		
С	0.24	0.26	0.35		
D	6.30	6.50	6.70		
е		2.30			
e1		4.60			
E	3.30	3.50	3.70		
Н	6.70	7.00	7.30		
V			10°		

Table 17. SOT-223 mechanical data


Figure 14. Drawing dimension SOT-223



		mm	
Dim.	N 4 ¹	[N
	Min.	Тур.	Max.
A			1.75
A1	0.10		0.25
A2	1.25		
b	0.28		0.48
с	0.17		0.23
D	4.80	4.90	5.00
E	5.80	6.00	6.20
E1	3.80	3.90	4.00
е		1.27	
h	0.25		0.50
L	0.40		1.27
L1		1.04	
k	0°		8°
ссс			0.10

Table	18.	SO-8	mechanica	l data
Tuble			meenamou	n aata

Figure 15. Drawing dimension SO-8





D :		mm	
Dim.	Min.	Тур.	Max.
А	2.20		2.40
A1	0.90		1.10
A2	0.03		0.23
b	0.64		0.90
b4	5.20		5.40
С	0.45		0.60
c2	0.48		0.60
D	6.00		6.20
D1	4.95	5.10	5.25
E	6.40		6.60
E1	4.60	4.70	4.80
е	2.159	2.286	2.143
e1	4.445	4.572	4.699
Н	9.35		10.10
L	1.00		1.50
L1	2.60	2.80	1.50
L2			3.00
L4	0.60		1.00
R		0.20	
V2	0°		8°

Table 19. DPAK (TO-252) mechanical data (type A)






Figure 16. DPAK (TO-252) package outline A



Table 20. DPAK (TO-252) mechanical data (type E)					
Dim		mm			
Dim.	Min.	Тур.	Max.		
А	2.18		2.39		
A2			0.13		
b	0.65		0.884		
b4	4.95		5.46		
С	0.46		0.61		
c2	0.46		0.60		
D	5.97		6.22		
D1	5.21				
E	6.35		6.73		
E1	4.32				
е		2.286			
e1		4.572			
Н	9.94		10.34		
L	1.50		1.78		
L1		2.74			
L2	0.89		1.27		
L4			1.02		

Table 20. DPAK (TO-252) mechanical data (type E)







Figure 17. DPAK (TO-252) package outline E




	-	2) mechanical data type mm	
Dim.	Min.	Тур.	Max.
А	2.20	2.30	2.38
A1	0.90	1.01	1.10
A2	0.00	-	0.10
b	0.77	-	0.89
b1	0.76	0.81	0.86
b2	0.77	-	1.10
b3	5.23	5.33	5.43
С	0.47	-	0.60
c1	0.46	0.51	0.56
c2	0.47	-	0.60
D	6.00	6.10	6.20
D1	5.25	5.40	5.60
E	6.50	6.60	6.70
E1	4.70	4.85	5.00
е		2.286 BSC	
Н	9.80	10.10	10.40
L	1.40	1.50	1.70
L1		2.90 REF	
L2	0.90	-	1.25
L3		0.51 BSC	
L4	0.60	0.80	1.00
L5	0.90	-	1.50
L6		1.80 BSC	
Θ	0°	-	8°
Θ1	3°	5°	7°
Θ2	1°	3°	5°

Table 21. DPAK (TO-252) mechanical data type I










Values				
	mm.	inch.		
А	6.70	0.264		
В	6.70	0.64		
С	1.8	0.070		
D	3.0	0.118		
E	1.60	0.063		
F	2.30	0.091		
G	2.30	0.091		

Table 22. Footprint data

Figure 19. DPAK footprint recommended data





9 Packaging mechanical data





Figure 20. Drawing dimension tube for TO-220 Dual Gauge (mm.)

Figure 21. Drawing dimension tube for TO-220 Single Gauge (mm.)



38/46


DocID2572 Rev 37

T

	Tak			reel mechanic		
	Таре			Reel		
Dim.		mm			m	Im
Dim.	Min.	Тур.	Max.	– Dim.	Min.	Max.
A0	6.75	6.85	6.95	А		180
B0	7.30	7.40	7.50	N	60	
K0	1.80	1.90	2.00	W1		12.4
F	5.40	5.50	5.60	W2		18.4
Е	1.65	1.75	1.85	W3	11.9	15.4
W	11.7	12	12.3		•	•
P2	1.90	2	2.10	Base qua	antity pcs	1000
P0	3.90	4	4.10	Bulk qua	antity pcs	1000
P1	7.90	8	8.10			•
Т	0.25	0.30	0.35			
DØ	1.50	1.55	1.60			
D1¢	1.50	1.60	1.70			

Table 23. SOT-223 tape and reel mechanical data

Figure 22. Tape for SOT-223 (dimensions are in mm)










Figure 23. Reel for SOT-223 (dimensions are in mm)



Dim		mm				
Dim.	Min.	Тур.	Max.			
А			330			
С	12.8		13.2			
D	20.2					
N	60					
Т			22.4			
Ao	8.1		8.5			
Bo	5.5		5.9			
Ko	2.1		2.3			
Po	3.9		4.1			
Р	7.9		8.1			

Table 24. SO-8 tape and reel mechanical data





	Таре			Reel	
. .	mm			mm	
Dim.	Min.	Max.	Dim.	Min.	Max.
A0	6.8	7	А		330
B0	10.4	10.6	В	1.5	
B1		12.1	С	12.8	13.2
D	1.5	1.6	D	20.2	
D1	1.5		G	16.4	18.4
E	1.65	1.85	N	50	
F	7.4	7.6	Т		22.4
K0	2.55	2.75		·	
P0	3.9	4.1		Base qty.	2500
P1	7.9	8.1		Bulk qty.	2500
P2	1.9	2.1			
R	40				
Т	0.25	0.35			
W	15.7	16.3			

Table 25. DPAK tape and reel mechanical data
--









Figure 26. Reel for DPAK



10 Order codes

Packages					
SOT-223	SO-8	DPAK (Tape and reel)	TO-220	TO-220 (Dual Gauge)	Output voltages
LD1117S12TR		LD1117DT12TR			1.2 V
LD1117S12CTR		LD1117DT12CTR			1.2 V
LD1117S18TR		LD1117DT18TR	LD1117V18		1.8 V
LD1117S18CTR		LD1117DT18CTR			1.8 V
LD1117S25TR		LD1117DT25TR			2.5 V
LD1117S25CTR		LD1117DT25CTR			2.5 V
LD1117S33TR	LD1117D33TR	LD1117DT33TR	LD1117V33	LD1117V33-DG	3.3 V
				LD1117V33C-DG	3.3 V
LD1117S33CTR	LD1117D33CTR	LD1117DT33CTR	LD1117V33C		3.3 V
LD1117S50TR		LD1117DT50TR	LD1117V50	LD1117V50-DG	5 V
					5 V
LD1117S50CTR		LD1117DT50CTR	LD1117V50C		5 V
LD1117STR		LD1117DTTR	LD1117V	LD1117V-DG	ADJ from 1.25 to 15 V
					ADJ from 1.25 to 15 V
LD1117SC-R		LD1117DTC-R			ADJ from 1.25 to 15 V



11 Revision history

Table 27. Document revision histor

Date	Revision	Changes
22-Sep-2004	15	Add new part number #12C; typing error: note on table 2.
25-Oct-2004	16	Add V _{ref} reference voltage on table 12.
18-Jul-2005	17	The DPAK mechanical data updated.
25-Nov-2005	18	The TO220FM package removed.
14-Dec-2005	19	The T _{op} on table 2 updated.
06-Dec-2006	20	DPAK mechanical data updated and added footprint data.
05-Apr-2007	21	Order codes updated.
30-Nov-2007	22	Added Table 1.
16-Apr-2008	23	Modified: Table 24 on page 42.
08-Jul-2008	24	Added note 1. on page 7.
30-Mar-2009	25	Modified: V _{IN} max value Table 4 on page 10 and Figure 9 on page 23
29-Jul-2009	26	Modified: Table 24 on page 42.
03-Feb-2010	27	Modified Table 9 on page 15.
22-Mar-2010	28	Added: Table 16 on page 22, Figure 13 on page 23, Figure 14 on page 24, Figure 17 and Figure 18 on page 33
15-Nov-2010	29	Modified: R _{thJC} value for TO-220 Table 2 on page 7.
30-Nov-2011	30	Added: order code LD1117V33-DG Table 24 on page 42.
13-Feb-2012	31	Added: order codes LD1117V50-DG and LD1117V-DG Table 24 on page 42.
19-Oct-2012	32	Added: R _{thJA} value for DPAK, SOT-223 and SO-8 Table 2 on page 7.
20-Nov-2013	33	Part number LD1117xx changed to LD1117. Updated the Description in cover page, Section 8: Package mechanical data and Table 24: Order codes. Cancelled Table 1: Device summary. Added Section 9: Packaging mechanical data. Minor text changes.
12-Jun-2019	34	Updated Table 19, Table 20, Figure 16, Figure 17 and Figure 18.
16-Oct-2019	35	Updated Figure 2: Pin connections (top view).
04-Dec-2019	36	Added Table 20: DPAK (TO-252) mechanical data (type E). Updated pin 3 DPAK package in Figure 2: Pin connections (top view).
11-Feb-2020	37	Updated Figure 14: Drawing dimension SOT-223.

IMPORTANT NOTICE – PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. For additional information about ST trademarks, please refer to *www.st.com/trademarks*. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2020 STMicroelectronics - All rights reserved

