
2PRO DEVICES



The 2Pro product is an integrated overcurrent/ over-voltage protection device. The RoHS-compliant component incorporates PolySwitch PPTC (Polymeric Positive Temperature Coefficient) technology and MOV (Metal Oxide Varistor) technology in a single device to help reduce board space requirements and component count.

Damage to telephony communications equipment can be caused by various sources including lightning, electrostatic discharge (ESD), power contact and induction with AC lines. The 2Pro TM2P-10271 devices help provide current limiting during overcurrent events and voltage clamping during overvoltage events. After a fault condition is removed and power is cycled, 2Pro devices will reset so that the equipment remains operational.



The 2Pro device helps address the need for resettable circuit protection devices for use in cost-sensitive PSTN (Public Switched Telephone Network) and VoIP (Voice over Internet Protocol) telephony equipment. The widespread use of VoIP gateways in homes and enterprise environments as the primary means of voice delivery requires the utmost safety and reliability in equipment. 2Pro circuit protection devices help manufacturers comply with global safety standards, including UL 60950, TIA-968-A, IEC 60950 and ITU-T K.20/K.21. The UL 497A listed protector also helps provide ESD protection.

BENEFITS

- Single device helps reduce component count and footprint
- Helps reduce warranty returns
- Helps equipment comply with surge tests per: TIA-968-A, IEC 60950, ITU-T K.20/K.21
- Helps simplify UL 60950 testing
- Helps equipment comply with UL 60950

FEATURES

- RoHS compliant
- Halogen free (refers to: Br≥900ppm, Cl≥900ppm, Br+Cl≥1500ppm)
- Single overcurrent, overvoltage and ESD protection device
- Resettable overcurrent protection

APPLICATIONS


- Cordless telephones
- VoIP gateways
- Fax machines
- Data modems
- Set-top boxes
- · Security systems
- MDF modules
- Analog and ISDN linecards

Radial-Leaded Devices

Table 2P1 — Electrical Characteristics

| Overcurrent (terminals 1 – 2) — Performance ratings @ 20°C | | | | | | | | |
|--|--|------|------------------|------------------|---------------------|------|------|-------|
| | Resistance [†] I_{HOLD} I_{TRIP} (Ω) | | | | Time Trip | | | |
| Part Number | (A) | (A) | R _{MIN} | R _{MAX} | R _{1 MAX*} | Тур | Max | - |
| TM2P-10271 | 0.15 | 0.30 | 6.50 | 14.00 | 16.00 | 0.90 | 3.00 | (@1A) |
| LVM2P-015R10431 | 0.15 | 0.30 | 6.50 | 14.00 | 16.00 | 0.90 | 3.00 | (@1A) |
| LVM2P-035R14431 | 0.35 | 0.75 | 1.40 | 2.20 | 2.80 | 0.50 | 2.00 | (@3A) |
| LVM2P-075R14431 | 0.75 | 1.50 | 0.37 | 0.80 | 1.00 | 0.90 | 1.20 | (@7A) |

| Overvoltage (Terminal | ls 2 – 3) | | | | |
|-----------------------|-----------|--------------------|-------------------------|---------------------|------------------|
| | | r Voltage ? 1mA | DC Resistance @ 100V | Maximum Clamping | Rated Wattage |
| Part Number | DC (V) | Tolerance | (MΩ) | (V) | (W) |
| TM2P-10271 | 260 | +14% -7% | >10 | 455 (@25A) | 0.25 |
| LVM2P-015R10431 | 430 | +10% -10% | >10 | 710 (@ 25A) | 0.25 |
| LVM2P-035R14431 | 430 | +10% -10% | >10 | 710 (@ 50A) | 0.60 |
| LVM2P-075R14431 | 430 | +10% -10% | >10 | 710 (@ 50A) | 1.00 |



[†] Corresponds to operation below varistor voltages.

Electrical Schematic





Table 2P2 — Dimensions in Millimeters and (Inches*)

| Part | | A | | В | | С | |) | E | ı | F | <u>-</u> . |
|-----------------|-----|--------|-----|--------|-----|--------|--------|--------|--------|-----|--------|------------|
| Number | Min | Max | Min | Max | Min | Max | Min | Max | Nom | Min | Max | Figure |
| TM2P-10271 | | | | | | | | | | | | |
| mm | _ | 12.0 | _ | 15.0 | _ | 6.6 | 6.0 | _ | 2.5 | _ | 12.0 | 2P1 |
| in* | _ | (0.47) | _ | (0.59) | _ | (0.26) | (0.24) | _ | (0.10) | _ | (0.47) | |
| LVM2P-015R10431 | | | | | | | | | | | | |
| mm | _ | 12.0 | _ | 17.0 | _ | 7.4 | 8.5 | 11.5 | 5.1 | | | 2P2 |
| in* | _ | (0.47) | _ | (0.67) | _ | (0.29) | (0.34) | (0.45) | (0.20) | | | |
| LVM2P-035R14431 | | | | | | | | | | | | |
| mm | _ | 16.0 | _ | 21.0 | _ | 7.4 | 3.0 | 5.0 | 5.1 | | | 2P2 |
| in* | _ | (0.63) | _ | (0.83) | _ | (0.29) | (0.12) | (0.20) | (0.20) | | | |
| LVM2P-075R14431 | | | | | | | | | | | | |
| mm | _ | 16.0 | _ | 21.0 | _ | 7.4 | 3.0 | 5.0 | 2.5 | | | 2P3 |
| in* | _ | (0.63) | _ | (0.83) | _ | (0.29) | (0.12) | (0.20) | (0.10) | | | |

^{*} The dimensions in inches are rounded approximations.

Figures 2P1-2P3 — Dimension Figures



Radial-Leaded Devices

Figure 2P4 — Typical Time-to-Trip at 25°C




Table 2P3 — Physical Characteristics and Environmental Specifications

| Physical Characteristi | cs |
|-------------------------------|--|
| Lead Material | Tin-plated Copper, 0.33mm² (22AWG), 0.64mm (0.025in) |
| Flammability | IEC 695-2-2 Needle Flame Test for 20s |
| Soldering Characteristics | ANSI Approved IPC/EIA/JEDEC J-STD-002, Category 3 |
| Solder Heat Withstand | per IEC-STD 68-2-20, Test Tb, Method1A, Condition B, can withstand 10 Seconds at 260°C ± 5°C |
| Environmental Specif | ications |
| Test | Conditions |
| Passive Aging | 60°C, 1000 Hours / 85°C, 1000 Hours |
| Humidity Aging | 85°C, 85% RH, 500 Hours |
| Active Aging | 60°C, 90% RH, 60VDC Bias,1000 Hours |
| Thermal Shock | 125°C, -55°C (10 Times) |
| Solvent Resistance | MIL-STD-202, Method 215K |

Note: Storage conditions: 40°C max, 70% RH max, devices should remain in original sealed bag prior to use. Devices may not meet specified values if these storage conditions are exceeded.

Radial-Leaded Devices

Table 2P4 — Packaging and Marking Information

| Part Number | Bag Quantity | Tape and Reel Quantity | Standard Package | Part Marking |
|-----------------|--------------|------------------------|------------------|----------------|
| TM2P-10271 | 250 | _ | 3,000 | 1027 & Batch # |
| TM2P-10271-2 | _ | 1,000 | 5,000 | 1027 & Batch # |
| LVM2P-015R10431 | 250 | _ | 3,000 | C431 & Batch # |
| LVM2P-035R14431 | 250 | _ | 3,000 | A431 & Batch # |
| LVM2P-075R14431 | 250 | _ | 3,000 | B431 & Batch # |

Table 2P5 — Ordering Information

| Bulk | 250 | pieces/bag |
|-------------|-------|-------------|
| | 3,000 | pieces/box |
| Tape & Reel | 1,000 | pieces/reel |
| | 5,000 | pieces/box |


Wave Soldering and Rework Recommendations

Recommended Wave Soldering for Radial-leaded Devices

• Soldering temperature profile (Temperature characteristic at component terminal with dual wave soldering)

Rework

• If a device is removed from the board, it should be discarded and replaced with a new device



HF Halogen Free


Table 2P6 — Tape and Reel Specifications in Millimeters (mm)

2Pro devices are available in tape and reel packaging per EIA 468-B standard.

| Description | EIA Mark | IEC Mark | Dimension (mm) | Tolerance |
|---------------------------------------|---------------------------------|---------------------------------|----------------|-------------|
| Carrier Tape Width | W | W | 18 | -0.5/ +1.0 |
| Hold Down Tape Width | W_4 | VV ₀ | 5 | Min |
| Top Distance Between Tape Edges | W ₆ | W ₂ | 3 | Max |
| Sprocket Hole Position | VV ₅ | VV ₁ | 9 | -0.5/ +0.75 |
| Sprocket Hole Diameter | D ₀ | D ₀ | 4 | ±0.2 |
| Abcissa to Plane (Kinked Lead)* | H ₀ | H ₀ | 16 | -0.5/0.6 |
| Abcissa to Top | H ₁ | H ₁ | 32.2 | Max |
| Overall Width with Lead Protrusion | _ | C ₁ | 43.2 | Max |
| Overall Width Without Lead Protrusion | _ | C ₂ | 42.5 | Max |
| Lead Protrusion | L ₁ | I ₁ | 1.0 | Max |
| Protrusion of Cut-out | L | L | 11 | Max |
| Protrusion Beyond Hold Down Tape | | l ₂ | Not Specified | _ |
| Sprocket Hole Pitch | P ₀ | P ₀ | 12.7 | ±0.3 |
| Pitch Tolerance | _ | _ | 20 Consecutive | ±1 |
| Tape Thickness | t | t | 0.9 | Max |
| Tape Thickness with Splice* | t ₁ | _ | 2.0 | Max |
| Splice Sprocket Hole Alignment | _ | _ | 0 | ±0.3 |
| Body Lateral Deviation | Dh | Dh | 0 | ±0.1 |
| Body Tape Plane Deviation | Dp | Dp | 0 | ±1.3 |
| Ordinate to Component Center Lead | P ₂ | P ₂ | 6.35 | ±0.7 |
| Lead Spacing* | F ₁ , F ₂ | F ₁ , F ₂ | 2.54 | -0.1/+0.4 |
| Reel Width | W ₂ | W | 56 | Max |
| Reel Diameter | а | d | 370 | Max |
| Space Between Flanges | W ₁ | _ | 51.2 | Max |
| Arbor Hole Diameter | С | f | 26 | ±12.0 |
| Core Diameter | n | h | 80 | Max |
| Вох | _ | _ | 56/372/372 | Max |
| Consecutive Missing Pieces* | _ | _ | 3 Max | _ |
| Empty Places Per Reel* | _ | _ | Not Specified | _ |


Note: *Differs from EIA specification.

Figure 2P6 — EIA Referenced Taped Component Dimensions





Radial-Leaded Devices

Figure 2P7 — EIA Referenced Reel Dimensions



Part Numbering System





Notice:

Littelfuse products are not designed for, and shall not be used for, any purpose (including, without limitation, automotive, military, aerospace, medical, life-saving, life-sustaining or nuclear facility applications, devices intended for surgical implant into the body, or any other application in which the failure or lack of desired operation of the product may result in personal injury, death, or property damage) other than those expressly set forth in applicable Littelfuse product documentation. Warranties granted by Littelfuse shall be deemed void for products used for any purpose not expressly set forth in applicable Littelfuse documentation. Littelfuse shall not be liable for any claims or damages arising out of products used in applications not expressly intended by Littelfuse as set forth in applicable Littelfuse documentation. The sale and use of Littelfuse products is subject to Littelfuse Terms and Conditions of Sale, unless otherwise agreed by Littelfuse.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Littelfuse:

LVM2P-035R14431 LVM2P-015R10431 LVM2P-075R14431