



IDEALPOWER

experts in power conversion

Ideal Power Ltd Product Specification Document

Description	Ext. PSU
Model Number	77DE-06-09
Revision	A1
Notes	-

Ideal Power Ltd

Ideal Power, Ideal House, Tree Beech Enterprise Park, Gunn, Barnstaple, Devon, EX32 7NZ, England, UK

Tel: +44 (0) 845 260 3400



Email: sales@idealpower.co.uk

Web: www.idealpower.co.uk

77DE-06-09

INPUT VOLTAGE **230VAC**
OUTPUT VOLTAGE **9VAC**

ELECTRICAL & MECHANICAL SPECIFICATION



Output Cable: **2468 22AWG/2C 80°C 1.8M LENGTH+5.5*2.1*10(L)PLUG**

ELECTRONICAL SPECIFICATION

Input Voltage	230	Volts
Frequency (Hz)	50	Hz
Power Rated (W)	10	W
Exciting Current With No load	60	mA Max
Exciting Current With Full load	80	mA Max
Output Voltage	9.0	Volts±5%
Output Current	0.67	Amp
Output Voltage Without Load	11.5	Volts±5%

HI-POT :

Test Time	1	Min
PRI TO SEC	4200	Volts
PRI TO CORE	4200	Volts
SEC TO CORE	2100	Volts
Efficiency	70	%
Insulation Class	B (130)	°C

MECHANICAL SPECIFICATION

Dimensions (L*W*H)	66.5*48.5*40.0	mm
Weight	265	g
Environment:		
Operating Temperature	-10 To 40	°C
Storage Temperature	-20 To 70	°C
Relative Temperature	40°C ±2°C	
RELATIVE HUMIDITY	90% RH	

ELECTRICAL CIRCUIT

