

www.vishay.com


Vishay General Semiconductor

## **Glass Passivated Ultrafast Plastic Rectifier**



PRIMARY CHARACTERISTICS						
I <sub>F(AV)</sub>	2.0 A					
$V_{RRM}$	50 V, 100 V, 150 V, 200 V, 300 V, 400 V					
I <sub>FSM</sub>	75 A					
t <sub>rr</sub>	50 ns					
$V_{F}$	0.95 V, 1.25 V					
T <sub>J</sub> max.	150 °C					
Package	DO-204AC (DO-15)					
Diode variations	Single die					

#### **FEATURES**





Cavity-free glass-passivated junction

Ultrafast reverse recovery time



Low forward voltage drop

ROHS

Low lorward voltage di

Low leakage current

· Low switching losses, high efficiency

• High forward surge capability

Solder dip 275 °C max. 10 s, per JESD 22-B106

 Material categorization: for definitions of compliance please see <a href="https://www.vishay.com/doc?99912"><u>www.vishay.com/doc?99912</u></a>

#### **TYPICAL APPLICATIONS**

For use in high frequency rectification and freewheeling application in switching mode converters and inverters for consumer, computer and telecommunication.

#### **MECHANICAL DATA**

**Case:** DO-204AC, molded epoxy over glass body Molding compound meets UL 94 V-0 flammability rating Base P/N-E3 - RoHS-compliant, commercial grade

Terminals: Matte tin plated leads, solderable per

J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test

Polarity: Color band denotes cathode end

MAXIMUM RATINGS (T <sub>A</sub> = 25 °C unless otherwise noted)								
PARAMETER	SYMBOL	EGP20A	EGP20B	EGP20C	EGP20D	EGP20F	EGP20G	UNIT
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	150	200	300	400	V
Maximum RMS voltage	V <sub>RMS</sub>	35	70	105	140	210	280	V
Maximum DC blocking voltage	V <sub>DC</sub>	50	100	150	200	300	400	V
Maximum average forward rectified current 0.375" (9.5 mm) lead length at T <sub>A</sub> = 55 °C	I <sub>F(AV)</sub>	(AV) 2.0						А
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	I <sub>FSM</sub>	FSM 75					Α	
Operating and storage temperature range	T <sub>J</sub> , T <sub>STG</sub>	, T <sub>STG</sub> -65 to +150					°C	



www.vishay.com

## Vishay General Semiconductor

ELECTRICAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)										
PARAMETER	TEST CONDITIONS		SYMBOL	EGP20A	EGP20B	EGP20C	EGP20D	EGP20F	EGP20G	UNIT
Maximum instantaneous forward voltage	2.0 A		V <sub>F</sub>	V <sub>F</sub> 0.95 1.25				25	V	
Maximum DC reverse current at rated DC		T <sub>A</sub> = 25 °C	I-	5.0						
blocking voltage		T <sub>A</sub> = 125 °C	l <sub>R</sub>	100						- μA
Maximum reverse recovery time	I <sub>F</sub> = 0.5 I <sub>rr</sub> = 0.2	A, I <sub>R</sub> = 1.0 A, 5 A	t <sub>rr</sub>	50				ns		
Typical junction capacitance	4.0 V, 1	MHz	CJ	70 45			5	pF		

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)								
PARAMETER SYMBOL EGP20A EGP20B EGP20C EGP20D EGP20F EGP20C					EGP20G	UNIT		
Typical thormal resistance	R <sub>0JA</sub> (1)	40						°C/W
Typical thermal resistance	R <sub>0</sub> JL (1)	15						C/VV

#### Note

<sup>(1)</sup> Thermal resistance from junction to ambient, and from junction to lead at 0.375" (9.5 mm) lead length, PCB mounted

ORDERING INFORMATION (Example)								
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE				
EGP20D-E3/54	0.452	54	4000	13" Diameter paper tape and reel				
EGP20D-E3/73	0.452	73	2000	Ammo pack packaging				

### **RATINGS AND CHARACTERISTICS CURVES** (T<sub>A</sub> = 25 °C unless otherwise noted)




Fig. 1 - Maximum Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current



www.vishay.com

# Vishay General Semiconductor




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 6 - Typical Reverse Leakage Characteristics




Fig. 4 - Typical Reverse Leakage Characteristics




Fig. 7 - Typical Junction Capacitance




Fig. 5 - Typical Instantaneous Forward Characteristics




Fig. 8 - Typical Transient Thermal Impedance




www.vishay.com

Vishay General Semiconductor

### **PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

### DO-204AC (DO-15)



## **Legal Disclaimer Notice**



Vishay

## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

© 2019 VISHAY INTERTECHNOLOGY, INC. ALL RIGHTS RESERVED