## Stackpole Electronics, Inc.

Carbon Film Resistor Resistive Product Solutions

#### Features:

- General purpose resistor ideal for commercial/industrial applications
- Flame retardant coatings standard
- Flameproof version available as CFF and CFFM
- Panasert available on selected sizes contact Stackpole
- Auto sequencing/insertion compatible
- CFM (mini) ideal choice when size constraints apply
- Cut and formed product is available on select sizes contact Stackpole
- Standard lead wire for CF and CFM is copper plated steel, with 100% tin over plate
- 100% tin plate on copper wire is available as type CFQ and CFQM
- 100% RoHS compliant and lead free without exemption
- Halogen free
- REACH compliant



	Electrical Specifications - CF								
Type/Code	Size	Power Rating (W) @ 70°C	VVOIKING	Maximum Overload	Dielectric Withstanding	TCR (ppm/ºC) per Ohmic Range	Ohmic Ran Toler	• , ,	
		@ 70 C	Voltage (V) (1)	Voltage (V)	Voltage (V)		2%	5%	
CF, CFQ	18	0.125	250	500	350	$< 10 \Omega = \pm 400 \text{ ppm/}^{\circ}\text{C}$	10 - 1M	1 - 22M	
CF, CFQ, PCF	14	0.25	350	600	350	10 Ω to 9.99K Ω = 0 ~ -400 ppm/°C	1 - 1M	1 - 22M	
CF, CFQ	12	0.5	350	700	600	10 K $\Omega$ to 99K $\Omega$ = 0 ~ -500 ppm/°C	10 - 1M	1 - 22M	
CF, CFQ	1	1	500	1000	600	100 K Ω to 999K Ω = 0 ~ -850 ppm/°C	1 - 1M	1 - 10M	
CF, CFQ	2	2	500	1000	600	1M $\Omega$ and above = 0 ~ -1500 ppm/°C	1 - 1M	1 - 10M	

<sup>(1)</sup> Lesser of  $\sqrt{P^*R}$  or maximum working voltage.


	Electrical Specifications - CFM								
Type/Code	Size	Power Rating (W) @ 70°C	Maximum Working	Maximum Overload	Dielectric Withstanding	TCR (ppm/°C) per Ohmic Range	Ohmic Range (Ω) and Tolerance		
		@ 70°C	Voltage (V) (1)	Voltage (V) Voltage (V)		2%	5%		
CFM, CFQM	14	0.25	250	500	350	$< 10 \Omega = \pm 400 \text{ ppm/}^{\circ}\text{C}$ 10 Ω to 9.99K Ω = 0 ~ -400 ppm/ $^{\circ}\text{C}$	1 - 1M	1 - 10M	
CFM, CFQM, PCFM	12	0.5	350	600	350	10 K Ω to 99K Ω = 0 ~ -500 ppm/°C 100 K Ω to 999K Ω = 0 ~ -850 ppm/°C	1 - 1M	1 - 10M	
CFM, CFQM	1	1	600	1000	600	1M $\Omega$ and above = 0 ~ -1500 ppm/°C	1 - 1M	1 - 10M	

<sup>(1)</sup> Lesser of  $\sqrt{P^*R}$  or maximum working voltage.

	Electrical Specifications – CFF/CFFM									
Type/Code			TCR (ppm/ºC) per Ohmic Range	Ohmic Range (Ω) and Tolerance						
		0.00	Voltage (V) (1)	Voltage (V)	Voltage (V)		2%, 5%			
	18	0.166	200	400	300	$< 10 \Omega = \pm 400 \text{ ppm/}^{\circ}\text{C}$	1 - 2.2M			
CFF	14	0.25	300	600	500	10 Ω to 9.99K Ω = 0 ~ -400 ppm/°C	1 - 5.1M			
	12	0.5	350	700	500	10 K $\Omega$ to 99K $\Omega$ = 0 ~ -500 ppm/°C	1 - 5.1101			
CFFM	14	0.25	250	500	300	100 K Ω to 999K Ω = 0 ~ -850 ppm/ $^{\circ}$ C 1M Ω and above = 0 ~ -1500 ppm/ $^{\circ}$ C	1 - 2.2M			
CITIVI	12	0.5	300	600	500	22 2 2 2 2	1 - 2.2101			

<sup>(1)</sup> Lesser of  $\sqrt{P^*R}$  or maximum working voltage.

## **Mechanical Specifications**




Type/Code	Size	А	В	С	D - Lead Diameter	Unit
1 ype/Code	Size	Body Length	Body Diameter	Lead Length (Bulk)	D - Leau Diameter	Offic
CF					$0.016 \pm 0.003$	inches
Ci	18	$0.130 \pm 0.012$	0.067 ± 0.012		$0.40 \pm 0.08$	mm
CFQ	10	$3.30 \pm 0.30$	1.70 ± 0.30		$0.018 \pm 0.003$	inches
CI Q					$0.45 \pm 0.08$	mm
CFF	18	0.126 ± 0.008	$0.073 \pm 0.008$		$0.018 \pm 0.002$	inches
OFF	10	$3.20 \pm 0.20$	1.85 ± 0.20		$0.45 \pm 0.05$	mm
CF, CFF, CFQ, PCF		$0.236 \pm 0.012$	0.091 ± 0.012		$0.022 \pm 0.003$	inches
61, 611, 61 Q, 1 61		$6.00 \pm 0.30$	2.30 ± 0.30		$0.55 \pm 0.08$	mm
CFFM		0.126 ± 0.008	$0.073 \pm 0.008$	1.102 ± 0.118	$0.018 \pm 0.002$	inches
OI T W	14	$3.20 \pm 0.20$	1.85 ± 0.20	28.00 ± 3.00	0.45 ± 0.05	mm
CFM	'				$0.016 \pm 0.003$	inches
OT IVI		$0.130 \pm 0.012$	0.067 ± 0.012		$0.40 \pm 0.08$	mm
CFQM		$3.30 \pm 0.30$	1.70 ± 0.30		$0.018 \pm 0.003$	inches
OI QIVI					0.45 ± 0.08	mm
CF					$0.022 \pm 0.003$	inches
OI .		$0.335 \pm 0.039$	0.106 ± 0.020		$0.55 \pm 0.08$	mm
CFF, CFQ	12	8.50 ± 1.00	2.70 ± 0.50		$0.028 \pm 0.004$	inches
011,010	12				0.70 ± 0.10	mm
CFM, CFQM, CFFM		$0.236 \pm 0.012$	0.091 ± 0.012		$0.022 \pm 0.003$	inches
Of M, Of QM, Of TM		$6.00 \pm 0.30$	2.30 ± 0.30		$0.55 \pm 0.08$	mm
CF, CFQ		$0.433 \pm 0.039$	0.177 ± 0.020	1.181 ± 0.118	$0.031 \pm 0.004$	inches
01 , 01 Q	1	11.00 ± 1.00	4.50 ± 0.50	30.00 ± 3.00	$0.80 \pm 0.10$	mm
CFM, CFQM	'	$0.354 \pm 0.020$	$0.138 \pm 0.020$	1.102 ± 0.118	$0.028 \pm 0.002$	inches
Of W, Of QW		9.00 ± 0.50	$3.50 \pm 0.50$	28.00 ± 3.00	0.70 ± 0.05	mm
CF, CFQ	2	$0.591 \pm 0.039$	0.197 ± 0.020	1.339 ± 0.157	$0.031 \pm 0.004$	inches
OI, OIQ		15.00 ± 1.00	$5.00 \pm 0.50$	34.00 ± 4.00	$0.80 \pm 0.10$	mm

Performance Characteristics										
Test	Test Method	Typical Result Test Limit					Typical Result			
Current Noise	MIL-STD 202, Method 308	1Ω ~ 91KΩ 0.15μ V/V				100KΩ ~ 910KΩ 0.4μ V/V	1MΩ ~ 22MΩ 0.6μ V/V			
Short Time Overload	JIS C5201-1, IEC60115-1, 4.13	$< \pm 0.25\%$ $\leq \pm (0.75\% + 0.05\Omega)$				Ω)				
Resistance to Soldering Heat	JIS C5201-1, IEC60115-1, 4.18	< ± 0.3%			≤ ± (0.5% + 0.05Ω)					
Rapid Change of Temperature	JIS C5201-1, IEC60115-1, 4.19		< ± 0.3%		≤ ± (1% + 0.05Ω)					
Endurance at 70°C	JIS C5201-1, IEC60115-1, 4.25.1		< ± 1%			R < 100KΩ: $\leq \pm (2\% + 0.05\Omega)$ R $\geq 100$ KΩ: $\leq \pm (3\% + 0.05\Omega)$				
Terminal Strength	MIL-STD 202, Method 211	$< \pm 0.2\%$ $\leq \pm (0.5\% + 0.05\Omega)$		Ω)						
Damp Heat (Steady state)	JIS C5201-1, IEC60115-1, 4.24		< ± 1.5%			100KΩ: ≤ ± (3% + 100KΩ: ≤ ± (5% +	,			

Operating temperature range is -55°C to +155°C

Resistive Product Solutions

## Power Derating Curve:



#### Recommended Solder Profiles

This information is intended as a reference for solder profiles for Stackpole resistive components. These profiles should be compatible with most soldering processes. These are only recommendations. Actual numbers will depend on board density, geometry, packages used, etc., especially those cells labeled with "\*".

## 100% Matte Tin / RoHS Compliant Terminations

Soldering iron recommended temperatures: 330°C to 350°C with minimum duration. Maximum number of reflow cycles: 3.


Wave So	Wave Soldering – 100% Matte Tin / RoHS Compliant Terminations							
Description	Maximum	Recommended	Minimum					
Preheat Time	80 seconds	70 seconds	60 seconds					
Temperature Diff.	140°C	120°C	100°C					
Solder Temp.	260°C	250°C	240°C					
Dwell Time at Max.	10 seconds	5 seconds	*					
Ramp DN (°C/sec)	N/A	N/A	N/A					

Temperature Diff. = Defference between final preheat stage and soldering stage.


Convection	Convection IR Reflow – 100% Matte Tin / RoHS Compliant Terminations							
Description	Maximum	Recommended	Minimum					
Ramp Up (°C/sec)	3°C/sec	2°C/sec	*					
Dwell Time > 217°C	150 seconds	90 seconds	60 seconds					
Solder Temp.	260°C	245°C	*					
Dwell Time at Max.	30 seconds	15 seconds	10 seconds					
Ramp DN (°C/sec)	6°C/sec	3°C/sec	*					

3

Rev Date: 3/3/2022



## Single Pulse Power:




## Repetitive Pulse Information

If repetitive pulses are applied to resistors, pulse wave form must be less than "Pulse limiting voltage", "Pulse limiting current" or "Pulse limiting wattage" calculated by the formula below.

$$Vp = K\sqrt{P \times R \times T/t}$$

$$Ip = K\sqrt{P/R \times T/t}$$

$$Pp = K^2 \times P \times T/t$$



Where: Vp: Pulse limiting voltage (V)

Ip: Pulse limiting current (A)

Pp: Pulse limiting wattage (W)

P: Power rating (W)

R: Nominal resistance (ohm)
T: Repetitive period (sec.)

t: Pulse duration (sec.)

K: Coefficient: 0.8

[Vr: Rated Voltage (V), Ir: Rated Current (A)]

Note 1: If T > 10  $\rightarrow$  T = 10 (sec.), T / t > 1000  $\rightarrow$  T / t = 1000.

Note 2: If T > 10 and T / t > 1000, "Pulse Limiting power (single pulse) is applied.

Note 3: If Vp < Vr (Ip < Ir or Pp < P), Vr (Ir, P) is Vp (Ip, Pp).

Note 4: Pulse limiting voltage (Current, Wattage) is applied at less than rated ambient temperature. If ambient temperature is more than the rated temperature (70°C), please decrease power rating according to "Power Derating Curve".


Note 5: Please assure sufficient margin for use period and conditions for "Pulse limiting voltage".

Note 6: If the pulse waveform is not square wave, please judge after transform the waveform into square wave according to the "Waveform Transformation to Square Wave".


Resistive Product Solutions

Waveform Transformation to Square Wave


1. Discharge curve wave with time constant "t" → Square wave




2. Damping oscillation wave with time constant of envelope "t" → Square wave




3. Half-wave rectification wave → Square wave




4. Triangular wave → Square wave



5. Special wave → Square wave



#### **Current Noise:**




# Reel Packaging Specifications Points are cut at dotted line for 10° (25mm) reel only

Type/Code	Size	Class	Tape	A Max <sup>(1).</sup>	B Max	С	D <sup>(2)</sup>	Unit
CF, CFQ	18			2.508				inches
01, 01 &	10			63.70				mm
CFF	18			2.508				inches
011	10			63.70				mm
	14			2.638		$0.197 \pm 0.020$		inches
CF, CFQ, CFF	17			67.00		$5.00 \pm 0.50$		mm
Ci , Ci Q, Ci i	12			2.736				inches
	12			69.50				mm
	1	1	0.250	2.972	13.504		$2.063 \pm 0.079$	inches
CF, CFQ	'	•	6.35	75.50	343.00		52.40 ± 2.00	mm
Ci , Ci Q	2			3.130		$0.394 \pm 0.020$		inches
				79.50		10.00 ± 0.50		mm
	14			2.508				inches
CFM, CFQM, CFFM	14			63.70				mm
Ci ivi, Ci Qivi, Ci i ivi	12			2.638		$0.197 \pm 0.020$		inches
	12			67.00		$5.00 \pm 0.50$		mm
CFM, CFQM	1			2.736				inches
Of IVI, Of QIVI	ı			69.50				mm

This is a non-critical dimension that does not have a tolerance in the standard. Dimension "E": Range of diameters is from 0.547 inches (13.90 mm) to 1.500 inches (38.10 mm).

- (1) Reference value only. The "A" dimension shall be governed by the overall length of the taped component. The distance between flanges shall be 0.059 inches (1.50 mm) to 0.315 (8.00 mm) greater than the overall component.
- (2) The given dimension "D" expresses the standard width spacing. A 26 mm narrow spacing is available as option "N" packaging code. Contact Stackpole for more details.

## Radial Lead Taping Specifications (Pana-Sert PCF14)



Symbol	Description	PANA-SERT	Unit	Symbol	Description	PANA-SERT	Unit
А	Resistor body length	0.256 ± 0.020 6.50 ± 0.50	inches mm	L	Cutout Length (1)	0.433 max. 11.00 max.	inches mm
С	Height of bending	0.098 ± 0.020 2.50 ± 0.50	inches mm	Р	Resitor pitch (1)	0.500 ± 0.039 12.70 ± 1.00	inches mm
D	Resistor body diameter	0.091 ± 0.008 2.30 ± 0.20	inches mm	$P_0$	Sprocket-hole pitch (1)	0.500 ± 0.012 12.70 ± 0.30	inches mm
D <sub>0</sub>	Sprocket-hole diameter	0.157 ± 0.012 4.00 ± 0.30	inches mm	P <sub>1</sub>	Sprocket-hole center to lead center	0.152 ± 0.028 3.85 ± 0.70	inches mm
F	Resistor lead spacing	0.197 ± 0.039 5.00 ± 1.00	inches mm	P <sub>2</sub>	Sprocket-hole center to resistor center (1)	0.250 ± 0.051 6.35 ± 1.30	inches mm
Н	Height to bottom of resistor	0.748 ± 0.039 19.00 ± 1.00	inches mm	Т	Thickness (chipboard and tape)	0.028 ± 0.008 0.70 ± 0.20	inches mm
H <sub>0</sub>	Height to lead clinch	0.630 ± 0.020 16.00 ± 0.50	inches mm	W	Chipboard width (1)	0.709 + 0.039 / -0.020 18.00 + 1.00 / -0.50	inches mm
H <sub>1</sub>	Height of resistor	1.122 max. 28.50 max.	inches mm	W <sub>0</sub>	Hold-down tape width	0.49 <sub>min.</sub> 12.50 min.	inches mm
h	Resistor alignment	$0 \pm 0.079  (0 \pm 5^{\circ})$ $0 \pm 2.00  (0 \pm 5^{\circ})$	inches mm	W <sub>1</sub>	Sprocket-hole position	0.354 + 0.030 / -0.020 9.00 + 0.75 / -0.50	inches mm
h <sub>1</sub>	Resistor alignment	$0 \pm 0.079  (0 \pm 5^{\circ})$ $0 \pm 2.00  (0 \pm 5^{\circ})$	inches mm	W <sub>2</sub>	Hold-down tape position	0.118 max. 3.00 max.	inches mm
I	Lead protrusion	0.079 max. 2.00 max.	inches mm				<u> </u>

CFQ, CFQM

1


inches

mm

#### **Ammo Packaging Specifications** Type/Code С Size Unit $2.756 \pm 0.118$ inches CF, CFQ 16 $70.00 \pm 3.00$ mm $3.937 \pm 0.118$ inches CF, CFQ 14 $100.00 \pm 3.00$ mm $2.756 \pm 0.118$ inches CF, CFQ 12 $70.00 \pm 3.00$ $\,mm\,$ $2.953 \pm 0.079$ $3.543 \pm 0.118$ $10.039 \pm 0.197$ inches **CFQ** 2 $75.00 \pm 2.00$ $90.00 \pm 3.00$ 255.00 ± 5.00 mm $2.756 \pm 0.118$ inches CFM, CFQM 14 $70.00 \pm 3.00$ mm $3.937 \pm 0.118$ inches CFM, CFQM 12 $100.00 \pm 3.00$ mm

 $2.953 \pm 0.118$ 

 $75.00 \pm 3.00$ 



Multiplier

Resistive Product Solutions

Tolerance (%)

## Standard Color Codes



**PRECISION** - Have three significant-figure bands, a multiplier band and a tolerance band. Tolerances 1% or less.

**GENERAL PURPOSE** - Have two significant-figure bands, a multiplier band and a tolerance band. Tolerances 2% or greater.

Color Band Description						
Band	Precision	General Purpose				
1st Band	Nominal	Nominal				
2nd Band	Nominal	Nominal				
3rd Band	Nominal	Multiplier				
4th Band	Multiplier	Tolerance				
5th Band	Tolerance	-				

Nominal

	NOTHINA	Multipliel	TOTELATICE (70)
Black	0	1	-
Brown	1	10	1
Red	2	100	2
Orange	3	1 K	-
Yellow	4	10 K	-
Green	5	100 K	0.5
Blue	6	1000 K	0.25
Violet	7	-	0.1
Gray	8	-	-
	9	0.001	-
Silver	-	0.01	10
Gold	-	0.1	5

### **RoHS Compliance**

Stackpole Electronics has joined the worldwide effort to reduce the amount of lead in electronic components and to meet the various regulatory requirements now prevalent, such as the European Union's directive regarding "Restrictions on Hazardous Substances" (RoHS 3). As part of this ongoing program, we periodically update this document with the status regarding the availability of our compliant components. All our standard part numbers are compliant to EU Directive 2011/65/EU of the European Parliament as amended by Directive (EU) 2015/863/EU as regards the list of restricted substances.

	RoHS Compliance Status									
Standard Product Series	Description	Package / Termination Type	Standard Series RoHS Compliant	Lead-Free Termination Composition	Lead-Free Mfg. Effective Date (Std Product Series)	Lead-Free Effective Date Code (YY/WW)				
CF	Carbon Film Leaded Resistor	Axial	YES	100% Matte Sn	Jan-04 (Taiwan, China)	04/01				
CFM	Mini-Carbon Film Leaded Resistor	Axial	YES	100% Matte Sn	Jan-04 (Taiwan, China)	04/01				

#### "Conflict Metals" Commitment

We at Stackpole Electronics, Inc. are joined with our industry in opposing the use of metals mined in the "conflict region" of the eastern Democratic Republic of the Congo (DRC) in our products. Recognizing that the supply chain for metals used in the electronics industry is very complex, we work closely with our own suppliers to verify to the extent possible that the materials and products we supply do not contain metals sourced from this conflict region. As such, we are in compliance with the requirements of Dodd-Frank Act regarding Conflict Minerals.

#### Compliance to "REACH"


We certify that all passive components supplied by Stackpole Electronics, Inc. are SVHC (Substances of Very High Concern) free and compliant with the requirements of EU Directive 1907/2006/EC, "The Registration, Evaluation, Authorization and Restriction of Chemicals", otherwise referred to as REACH. Contact us for complete list of REACH Substance Candidate List.

# Stackpole Electronics, Inc.

Resistive Product Solutions

## **Environmental Policy**

It is the policy of Stackpole Electronics, Inc. (SEI) to protect the environment in all localities in which we operate. We continually strive to improve our effect on the environment. We observe all applicable laws and regulations regarding the protection of our environment and all requests related to the environment to which we have agreed. We are committed to the prevention of all forms of pollution.



(\*) Bulk packaging may be subject to 25Kpc MOQ

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## SEI Stackpole:

CF14JT2K00 CF18JT2K00 CF12JT680R CF18JT100R CF18JT2M20 CF12JT1R00 CF12JT33R0 CF12JT56K0 CF14JT1K10 CF14JT82R0 CF18JT56R0 CF18JT8K20 CFM14JT18K0 CF12JA15K0 CF12JA1K20 CF12JA33K0 CF14JA100R CF14JA680K CFM14GT680R CF12JA12K0 CF12JA3M30 CF12JT100K CF12JT10K0 CF14JT1K00 CF18JT51R0 CF12JT33K0 CF14JT1M20 CF14JT3M30 CF14JT910R CF18JT270K CF18JT33K0 CFM12JT22R0 CFM12JT510R CFM14JT5R10 CF12JA47R0 CF14JA15K0 CF14JA47K0 CFM14GT20R0 CF12JA10M0 CF14JA680R CF14JT1K20 CF14JT3K90 CF18JT22K0 CF14JT1K50 CF14JT220R CF14JT6K80 CF14JT680R CF18JT110R CF18JT82K0 CF12JT27K0 CF14JT30K0 CF14JT68K0 CF18JT18K0 CF18JT5K10 CFM12JT120R CFM12JT820R CFM14JT52R0 CFM14JT5K10 CFM14JT51R0 CFM14JT560R CF14JA130K CF14JA1M50 CF14JA510K CF14JA75K0 CF14JA820R CF18JT220R CF14JT510K CF12JT22R0 CF18JT100K CFM12JT10K0 CF14JT110K CF12JT3K00 CF14JA18K0 CF14JA18C0 CF14JT510K CF12JT3K00 CF18JT170K0 CF14JT11K0 CF14JA1K30 CF18JT3K30 CF14JT1M50 CF14JT4K70 CF18JT1K20 CF18JT1CK0 CF18JT1K20 CF18JT1CK0 CF18JT1C