

SS12L - SS115L


1.0 AMP. Surface Mount Schottky Barrier Rectifiers

Sub SMA



Features

- ✧ For surface mounted application
- ✧ Low-Profile Package
- ✧ Ideal for automated pick & place
- ✧ Low power loss, high efficiency
- ✧ High current capability, low VF
- ✧ High surge current capability
- ✧ Plastic material used carriers Underwriters Laboratory Classification 94V-0
- ✧ Epitaxial construction
- ✧ High temperature soldering: 260°C / 10 seconds at terminals
- ✧ Green compound with suffix "G" on packing code & prefix "G" on datecode.



Dimensions in inches and (millimeters)

Marking Diagram



- 1XL = Specific Device Code
- G = Green Compound
- Y = Year
- M = Work Month

Mechanical Data

- ✧ Cases: Sub SMA plastic case
- ✧ Terminal : Pure tin plated, lead free.
- ✧ Polarity: Color band denotes cathode end
- ✧ Packaging: 12mm tape per EIA STD RS-481
- ✧ Weight:0.0196 grams

Maximum Ratings and Electrical Characteristics

Rating at 25 °C ambient temperature unless otherwise specified.

Single phase, half wave, 60 Hz, resistive or inductive load.

For capacitive load, de-rate current by 20%

Type Number	Symbol	SS 12L	SS 13L	SS 14L	SS 15L	SS 16L	SS 19L	SS 110L	SS 115L	Units	
Maximum Recurrent Peak Reverse Voltage	V_{RRM}	20	30	40	50	60	90	100	150	V	
Maximum RMS Voltage	V_{RMS}	14	21	28	35	42	63	70	105	V	
Maximum DC Blocking Voltage	V_{DC}	20	30	40	50	60	90	100	150	V	
Maximum Average Forward Rectified Current	$I_{F(AV)}$	1.0								A	
Peak Forward Surge Current, 8.3 ms Single Half Sine-wave Superimposed on Rated Load (JEDEC method)	I_{FSM}	30								A	
Maximum Instantaneous Forward Voltage @ 0.5A @ 1.0A	V_F	0.385 0.45	0.43 0.50	0.51 0.55	0.58 0.70	0.70 0.80	0.75 0.90			V	
Maximum DC Reverse Current @ $T_A = 25^\circ\text{C}$ at Rated DC Blocking Voltage @ $T_A = 100^\circ\text{C}$ (Note 1) @ $T_A = 125^\circ\text{C}$	I_R	0.4				0.05				mA mA mA	
		8.0	6.0				-				
		-				0.5					
Maximum Thermal Resistance (Note 2)	$R_{\theta JA}$	100								$^\circ\text{C/W}$	
	$R_{\theta JL}$	45									
Operating Temperature Range	T_J	-55 to +150								$^\circ\text{C}$	
Storage Temperature Range	T_{STG}	-55 to + 150								$^\circ\text{C}$	

Notes: 1. Pulse Test with PW=300 usec, 1% Duty Cycle.

2. Measured on P.C.Board with 0.2" x 0.2" (5.0mm x 5.0mm) Copper Pad Areas

Version: J10

RATINGS AND CHARACTERISTIC CURVES (SS12L THRU SS115L)

FIG.1- MAXIMUM FORWARD CURRENT DERATING CURVE




FIG.2- MAXIMUM REPETITIVE FORWARD SURGE CURRENT




FIG.3- TYPICAL FORWARD CHARACTERISTICS




FIG.4- TYPICAL REVERSE CHARACTERISTICS




FIG.5- TYPICAL JUNCTION CAPACITANCE




FIG.6- TYPICAL TRANSIENT THERMAL CHARACTERISTICS

