
OPERATING CHARACTERISTICS AT 25°C AMBIENT										
LED CHARACTERISITICS	MIN	TYP	MAX	UNITS	TEST CONDITION					
LUMINOUS INTENSITY	2500	4200	7200	mc d	Ir = 20 mA					
PEAK WAVELENGTH		518		nm						
DOMINANT WAVELENGTH	520	527	535	nm						
VIEWING ANGLE (2 ⊖1/2)		30		DEG						
FORWARD VOLTAGE		3.8	4.3	٧	IF = 20 mA					


REV	ECN NO	REVISIONS	DRN	CKD	APP	DATE
Α		NEW RELEASE	TC	Ν.Ο.	MES	10-5-06
В		UPDATED LED SPECS. REMOVED NOTES 2 & 4.	KLJ	JLC	N.O.	4-15-09


ABSOLUTE MAXIMUM RATINGS 25°C AMBIENT		
PARAMETER	VALUE	UNITS
DC FORWARD CURRENT	30	m A
PEAK FORWARD CURRENT (1/10 DUTY CYCLE, 0.1ms PULSE WIDTH)	100	mΑ
POWER DISSIPATION	135	mW
DERATING LINEARLY FROM 30°C	0.5	mA/°C
REVERSE VOLTAGE (IR = 100μA)	5	٧
OPERATING TEMPERATURE RANGE	-40 to +85	°C
STORAGE TEMPERATURE RANGE	-40 to +100	°C
DIP-DRAG SOLDER TEMPERATURE (FOR 5 SEC.)	260	°C

## NOTES:

- I. LENS COLOR: WATER CLEAR
- 2. LEAD SPACING MEASURED NEAR EPOXY PACKAGE.
- 3. THIS ASSEMBLY CONTAINS ELECTROSTATIC DISCHARGE SENSITIVE DEVICES (ESDS). MAINTAIN ALL PRECAUTIONARY MEASURES DURING ASSEMBLY, HANDLING, AND STORAGE IN ACCORDANCE WITH IPC-A-610.
- 4. DIALIGHT PART NUMBER: 521-9947F
- 5. PART NUMBER WITH "F" SUFFIX ENDING IS ROHS COMPLIANT. THE BAG PACKAGING IS MARKED WITH "ROHS COMPLIANT" LABEL OR EQUIVALENT MARKINGS. PART CAN BE WAVE SOLDERED, DIP SOLDERED, OR HAND SOLDERED USING TYPICAL LEAD-FREE SOLDERING PROCESS WITH MAX. 260°C TEMPERATURE FOR 5 SEC.







## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Dialight: 521-9947F