





# MARKETING SALES DRAWING

Electrical Testing  
per Tusonix standard  
test plans and Mil-Std-202  
Test Methods.

**DIMENSIONS IN INCHES - DO NOT SCALE THIS DRAWING**  
**DIMENSIONS IN METRIC - [ ]**



### MOUNTING HARDWARE



### NOTES:

1. TUSONIX STANDARD PART NUMBER: 4400-000.  
TUSONIX RoHS COMPLIANT PART NUMBER: 4400-000 LF.  
CUSTOMER MUST SPECIFY STANDARD OR RoHS PART NUMBER WHEN ORDERING.
2. LEAD, BUSHING, AND MOUNTING HARDWARE: SILVER PLATED.
3. PART MARKING: TRADEMARK AND VARIATION NUMBER ON HEX FLATS. STANDARD PART: BLACK INK. RoHS PART: GREEN INK.
4. OPERATING TEMPERATURE RANGE : -55°C TO +125°C.
5. MAX. RECOMMENDED SOLDERING TEMPERATURE: 260°C.
6. SUPPLIED WITH HEX NUT AND INTERNAL TOOTH LOCK WASHER.
7. MAX. RECOMMENDED MOUNTING TORQUE - 2.0 lb.-in. [.226 Nm].

100	GMV	300	200	10 G Ω	500	10	---	---	3	20	28
CAP.(pf)	TOLERANCE	85°C	125°C	I.R. MIN. @ 100 (VDC.)	DWV (VDC)	DC CURRENT (AMPS)	1 MHz	10 MHz	100 MHz	1 GHz	10 GHz
							MIN. NO LOAD INSERTION LOSS (dB) @ 25°C PER MIL-STD-220				

X-2015 Rev-0	<b>REVISION RECORD</b>		Title	
	Original Release C.O.	0	<b>BUSHING STYLE EMI FILTER</b>	
	REDRAWN & REVISED ADDED 008,009, E.C. 05-30-90	10	Drawn S.M. 11-07-01 Scale 5 X	
	5261 VARS 005,006,007 & 1MHz COLUMN ADDED. L.E. 11-07-90	11	Approved B.Mc 11-07-01	
	5591 RDN TO COMP FMT & ADDED METRIC. S.M. 11-08-01	12	<b>A</b> <b>4400-000</b>	
20000926-3-01 REVISED DWG. DRAWING MADE FOR EACH VAR. S.M. 12-02-02	13			
20021125-1-01 10 (AMPS) WAS 5 (AMPS) L.E. 06-23-04	14			
20040621-1-01 ADDED & REVISED NOTES. S.M. 12-14-05	15			
20051122-2-02				
--TOLERANCES-- Unless Otherwise Specified DECIMAL ± NOTED ANGLES ±			<b>TUSONIX</b> TUCSON, ARIZONA	

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Tusonix / CTS:](#)

[4400-000LF](#)