

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild guestions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



August 2016

UF4001 - UF4007 Fast Rectifiers

Features

- Low Forward Voltage Drop
- · High Surge Current Capability
- High Reliability
- · High Current Capability
- · Glass-Passivated Junction



Ordering Information

Part Number	Top Mark	Package	Packing Method
UF4001	UF4001	DO-204AL (DO-41)	Tape and Reel
UF4002	UF4002	DO-204AL (DO-41)	Tape and Reel
UF4003	UF4003	DO-204AL (DO-41)	Tape and Reel
UF4004	UF4004	DO-204AL (DO-41)	Tape and Reel
UF4005	UF4005	DO-204AL (DO-41)	Tape and Reel
UF4006	UF4006	DO-204AL (DO-41)	Tape and Reel
UF4007	UF4007	DO-204AL (DO-41)	Tape and Reel

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at $T_A = 25^{\circ}\text{C}$ unless otherwise noted.

	Parameter		Value						
Symbol			UF 4002	UF 4003	UF 4004	UF 4005	UF 4006	UF 4007	Unit
V_{RRM}	Maximum Repetitive Reverse Voltage	50 100 200 400 600 800 1000		1000	V				
I _{F(AV)}	Average Rectified Forward Current .375 " Lead Length at T _A = 75°C 1.0				А				
I _{FSM}	Non-Repetitive Peak Forward Surge Current 8.3 ms Single Half-Sine-Wave			А					
T _{STG}	Storage Temperature Range		-65 to +150						°C
T_J	Operating Junction Temperature		-65 to +150					°C	

Thermal Characteristics

Values are at $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Value	Unit
P _D	Power Dissipation	2.08	W
$R_{\theta JA}$	Thermal Resistance, Junction-to-Ambient	60	°C/W
$R_{\theta JL}$	Thermal Resistance, Junction-to-Lead	30	°C/W

Electrical Characteristics

Values are at $T_A = 25$ °C unless otherwise noted.

			Value							
Symbol	Parameter	Conditions	UF 4001	UF 4002	UF 4003	UF 4004	UF 4005	UF 4006	UF 4007	Unit
V _F	Maximum Forward Voltage	I _F = 1.0 A		1	.0			1.7		V
t _{rr}	Maximum Reverse Recovery Time	$I_F = 0.5 A,$ $I_R = 1.0 A,$ $I_{RR} = 0.25 A$		5	50			75		ns
1_	Maximum Reverse Current	$T_A = 25^{\circ}C$		10					μА	
I _R	at Rated V _R	T _A = 100°C	50			μΛ				
C _T	Maximum Total Capacitance	$V_R = 4.0 \text{ V},$ f = 1.0 MHz				17				pF

Typical Performance Characteristics




Figure 1. Forward Current Derating Curve




Figure 3. Non-Repetitive Surge Current





Figure 5. Typical Junction Capacitance



1. Rise time = 7.0 ns max; Input impedance = 1.0 megaohm 22 pf. 2. Rise time = 10 ns max; Source impedance = 50 ohms.




Figure 2. Forward Characteristics




Figure 4. Reverse Characteristics





Figure 6. Reverse Recovery Time Characteristic and Test Circuit Diagram

	Ú¢WÓXÓÜ				
ÞÓÜ	ÖÒÙÔÜŒVŒÞ	ÖŒ/Ò	ÓŸĐŒÚÚ©		
F	ÜÒŠÒŒÙÒÖÁ/UÁÖÔÔ	GJRWŠ€Ì	PŸŒÞÕÐÁÛWZPUW		
G	ÔPCEÞŐÒÁ KESEÁUÁ KEFÈ ÔPCEÞŐÒÁÞUVÒÁÓÁKKEÖÖÖÖÁÚŠCEÚVÔGÓUÖŸÈ ŰÖTUXÓÁŐŠCEJUÁÚÞÁVQSŐÉ	FJÙÒÚ€Ì	PŸŒÞÕÐÂÛWZPUW		



ÞU V Ò Ù KÁN Þ Š Ò Ù Ú ÁU V P Ò Ü Y QÙ Ò ÁU Ú Ò Ô Q Q Ò Ö

AMOEMÁJOEÔS CEÕ ÒÁJVOEÞÖCE JÖÁJ ÒZOÒU ÒÞÔÒKÁ
RÒÖOÔÁÖU EÐEL ÁK CEJ QEVQU ÞÁQEŠÈ
AMÓDÁJOEÔS CEÑ ÒÁÓU ÖŸ ÁÔCEÞÁÓ ÁJ ŠCEÙ VQĎÁJ Ü ÁK
AMMIMIR ÒÜT ÒV QÔCEŠŠÝ ÁJ ÒCEŠOÖ ÁŐ ŠCEÙ ÚÆ:
AMÖDÁGEŠÁÖGT ÒÞ ÙQU Þ ÙÁQEJ ÒÁQÞÁT (SŠST ÒV ÒÜ ÙÈ
AMÖDÁGEŠÝÖGT QÞÔÁZSŠÒÁÞ CET ÒKÖU I FOEÜ ÒX G

ŒÚÚÜUXŒŠÙ	ÓVÆOÖ					
ÖÜGY ÞK ÓUÓUŸÁT ŒŠÖU	FJÙÒÚ€Ì	FAIRCHILD				
^{ôpòòsòòK} PÒÞÜŸÁŸŒÞÕ		SEMICONDUCTOR TM				
ŒŰŰÜUXÒÖK ÓŸÁRWŒÐÕ		AŽIČOĆEDOŽAŽEDO YED				
œúúuxòök PUY ŒÜÖÁŒŠŠÒÞ		RÒÖÒÔÁÖUGEIĒÁKOŒÜQŒVQUÞÁQEŠ				
ÚÚURÓÓVQIÞ ŽT T Á QCÓP		FIFE PEDE T SVEÖUI FOE G				
		ØUÜTÖÜŠŸK ÞEŒ ÙPÒÒVÁK FÁUØÁF				

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdt/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

UF4001 UF4002 UF4003 UF4004 UF4005 UF4006 UF4007