
Crystal oscillator: SG2016/3225/5032/7050CAN & SG-210STF

Features

- Crystal oscillator (SPXO)
 - Frequency: 20 standard frequencies (4 MHz to 72 MHz)
- Output: CMOS
- Supply voltage: 1.6 V to 3.63 V
- Operating temperature: -20 °C to +70 °C
 - -40 °C to +105 °C

Applications

- IoT, Wearable device
- Data center, Storage
- Medical, Industrial automation




Description

Epson's SGxxxxCAN & SG-210STF are Simple Packaged Crystal Oscillator (SPXO) series with CMOS output. These SPXO's are ideal for variety of applications from IoT, wearables, medical, industrial automation, etc. These SPXO have low current consumption, wide operating voltage from 1.6 V to 3.63 V and wide operating temperature range from -40 °C to 85 °C, in addition operation up to 105 °C is available. These SPXO's are available in five different package size from 2.0 x 1.6 mm to 7.0 x 5.0 mm and available in

These SPXO's are available in five different package size from 2.0 × 1.6 mm to 7.0 × 5.0 mm and available in standard pin out's.

Outline Drawing and Terminal Assignment

0.55



[1] Product Name / Product Number

(1-1) SG2016CAN

(1) Product Name (Standard Form)

SG2016 CAN 25.00000MHz TJHA

1 2 3 4567

①Model ②Output (C:CMOS) ③Frequency ④Supply voltage 5 Frequency tolerance 6 Onerating temperati

Frequ	Frequency tolerance [®] Operating temperature ^⑦ Internal identification code ("A" is default)						
Supply voltage Refer to Figure 1 SFrequency tolerance / Operating temperature							
Т	1.8 V to 3.3 V Typ.		DB	±25 × 10 ⁻⁶ / -20 °C to +70 °C			
K 2.5 V to 3.3 V Typ.			JG	±50 × 10 ⁻⁶ / -40 ºC to +85 ºC			
*Figure 1 is on the next page			JH	±50 × 10 ⁻⁶ / -40 ⁰C to +105 ⁰C			

	Frequency tolerance / Operating temperature		
Frequency [MHz]	DB	JG	JH
	±25 × 10 ⁻⁶	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶
	-20 °C to +70 °C	-40 °C to +85 °C	-40 °C to +105 °C
4	-	X1G004801003000	X1G004801004900
8	-	X1G004801004500	X1G004801004600
10	-	X1G004801002900	X1G004801002700
12	X1G004801005000	X1G004801000700	X1G004801005100
12.288	X1G004801005200	X1G004801004400	X1G004801005300
14.7456	-	X1G004801005400	X1G004801005500
16	-	X1G004801001400	X1G004801005600
20	X1G004801005700	X1G004801005800	X1G004801001800
24	X1G004801005900	X1G004801000200	X1G004801004000
24.576	-	X1G004801006000	X1G004801003100
25	X1G004801002400	X1G004801001200	X1G004801003500
26	-	X1G004801000300	X1G004801003900
27	-	X1G004801006100	X1G004801002100
32	-	X1G004801006200	X1G004801006300
33.33	-	X1G004801006400	X1G004801006500
33.3333	-	X1G004801002600	X1G004801006600
40	-	X1G004801006700	X1G004801003600
48	X1G004801006800	X1G004801002000	X1G004801006900
50	X1G004801007000	X1G004801001300	X1G004801002800
72	X1G004801007100	X1G004801007200	X1G004801007300

(1-2) SG-210STF

(1) Product Name (Standard Form)

<u>SG-210 STF</u> 25.00000MHz Y

1 23 4 5

①Model ②Function (S:Standby) ③Supply voltage

④ Frequency ⑤ Frequency tolerance / Operating temperature
 ③ Supply voltage Refer to Figure 1
 ⑥ Frequency tolerance /

 -		3
Ŧ	4 0 V 40 0 0 V Tom	
	1.8 V to 3.3 V Typ	
	· · · · · · · · · · · · · · · · · · ·	

*Figure 1 is on the next page

⑤Frequency tolerance / Operating temperature					
S ±25 × 10 ⁻⁶ / -20 °C to +70 °C					
	±50 × 10 ⁻⁶ / -40 ºC to +85 ºC				
Υ	±50 × 10 ⁻⁶ / -40 ⁰C to +105 ⁰C				

	Frequency	tolerance / Operating te	emperature
Frequency [MHz]	S	L	Y
	±25 × 10 ⁻⁶	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶
	-20 °C to +70 °C	-40 °C to +85 °C	-40 °C to +105 °C
4	4 - X1G004171000900		X1G004171029900
8	-	X1G004171001500	X1G004171006900
10	-	X1G004171001600	X1G004171036500
12	X1G004171016300	X1G004171001800	X1G004171028000
12.288	X1G004171006100	X1G004171001900	X1G004171036600
14.7456	-	X1G004171002500	X1G004171036700
16	-	X1G004171002700	X1G004171015400
20	X1G004171021800	X1G004171002900	X1G004171023800
24	X1G004171015600	X1G004171003100	X1G004171019700
24.576	-	X1G004171003200	X1G004171036800
25	X1G004171007700	X1G004171003300	X1G004171005900
26	-	X1G004171003400	X1G004171024400
27	-	X1G004171003500	X1G004171025000
32	-	X1G004171004000	X1G004171012700
33.33	-	X1G004171011900	X1G004171030000
33.3333	-	X1G004171012000	X1G004171007500
40	-	X1G004171004500	X1G004171020600
48	X1G004171007800	X1G004171004600	X1G004171036900
50	X1G004171007900	X1G004171004700	X1G004171012600
72	X1G004171037000	X1G004171012400	X1G004171037100

(1-3) SG3225CAN

(1) Product Name (Standard Form)

SG3225 CAN 25.00000MHz TJHA

1 2 3 4567

①Model ②Output (C:CMOS) ③Frequency ④Supply voltage ⑤Frequency tolerance ⑥Operating temperature ⑦Internal ider

Sincer Sector (c.e. and) Sincer Sector							
⑤Frequency tolerance ⑥Operating temperature ⑦Internal identification code ("A" is default)							
Operating temperature Supply voltage Refer to Figure 1 SFrequency tolerance / Operating temperature							
T 1.8 V to 3.3 V Typ.	DB ±25 × 10 ⁻⁶ / -20 °C to +70 °C						
K 2.5 V to 3.3 V Typ.	$JG \pm 50 \times 10^{-6} / -40 \ ^{\circ}C \text{ to } +85 \ ^{\circ}C$						
*Figure 1 is on the next page	JH ±50 × 10 ⁻⁶ / -40 °C to +105 °C						

	Frequency	tolerance / Operating te	emperature
Frequency [MHz]	DB	JG	JH
	±25 × 10 ⁻⁶	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶
	-20 °C to +70 °C	-40 °C to +85 °C	-40 °C to +105 °C
4	-	X1G005961001115	X1G005961001215
8	-	X1G005961000415	X1G005961001315
10	-	X1G005961000515	X1G005961001415
12	X1G005961001515	X1G005961000615	X1G005961001615
12.288	X1G005961001715	X1G005961001815	X1G005961001915
14.7456	-	X1G005961002015	X1G005961002115
16	-	X1G005961002215	X1G005961002315
20	X1G005961002415	X1G005961000715	X1G005961002515
24	X1G005961002615	X1G005961000115	X1G005961002715
24.576	-	X1G005961000815	X1G005961002815
25	X1G005961002915	X1G005961000215	X1G005961003015
26	-	X1G005961003115	X1G005961003215
27	-	X1G005961003315	X1G005961003415
32	-	X1G005961003515	X1G005961003615
33.33	-	X1G005961003715	X1G005961003815
33.3333	-	X1G005961003915	X1G005961004015
40	-	X1G005961000915	X1G005961004115
48	X1G005961004215	X1G005961000315	X1G005961004315
50	X1G005961004415	X1G005961001015	X1G005961004515
72	X1G005961004615	X1G005961004715	X1G005961004815

(1-4) SG5032CAN

(1) Product Name (Standard Form)

<u>SG5032CAN</u> 25.00000MHz <u>TJHA</u>

0 2 3 4567

(1)Model (2)Output (C:CMOS) (3)Frequency (4)Supply voltage (5)Frequency tolerance (6)Operating temperature (7)Internal ide

Frequency tolerance Operating temperature ⑦Internal identification code ("A" is defaulted and the second secon							
④Supply voltage Refer to	gure 1 5 Frequency tolerance	e /					
T 1.8 V to 3.3 V Typ.	DB ±25 × 10 ⁻⁶ / -20 °	C to +70 °C					
K 2.5 V to 3.3 V Typ.	JG ±50 × 10 ⁻⁶ / -40 °	C to +85 °C					
*Figure 1 is on the	xt page JH ±50 × 10 ⁻⁶ / -40 °	C to +105 °C					

	Frequency tolerance / Operating temperature			
Frequency [MHz]	DB	JG	JH	
	±25 × 10 ⁻⁶	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶	
	-20 °C to +70 °C	-40 °C to +85 °C	-40 °C to +105 °C	
4	-	X1G004451003400	X1G004451019600	
8	-	X1G004451002100	X1G004451019700	
10	-	X1G004451001300	X1G004451017800	
12	X1G004451019800	X1G004451002800	X1G004451019900	
12.288	X1G004451020000	X1G004451000100	X1G004451020100	
14.7456	-	X1G004451001900	X1G004451020200	
16	-	X1G004451000200	X1G004451020300	
20	X1G004451020400	X1G004451001100	X1G004451020500	
24	X1G004451017200	X1G004451000300	X1G004451020600	
24.576	-	X1G004451002900	X1G004451020700	
25	X1G004451009700	X1G004451000400	X1G004451020800	
26	-	X1G004451008200	X1G004451020900	
27	-	X1G004451000500	X1G004451021000	
32	-	X1G004451001400	X1G004451021100	
33.33	-	X1G004451021200	X1G004451021300	
33.3333	-	X1G004451016700	X1G004451021400	
40	-	X1G004451001200	X1G004451021500	
48	X1G004451014900	X1G004451000700	X1G004451011200	
50	X1G004451011500	X1G004451000800	X1G004451003600	
72	X1G004451021600	X1G004451021700	X1G004451021800	

(1-5) SG7050CAN

(1) Product Name (Standard Form)

SG7050 CAN 25.00000MHz TJHA

1 2 3 4567

①Model ②Output (C:CMOS) ③Frequency ④Supply voltage
 ⑤Frequency tolerance ⑥Operating temperature ⑦Internal ider

Sincer Sector (c.e. and) Sincer Sector							
⑤Frequency tolerance ⑥Operating temperature ⑦Internal identification code ("A" is default)							
④Supply voltage Refer to Figure 1 ⑤Frequency tolerance / ⑥Operating temperature							
T 1.8 V to 3.3 V Typ.	DB ±25 × 10 ⁻⁶ / -20 °C to +70 °C						
K 2.5 V to 3.3 V Typ.	$JG \pm 50 \times 10^{-6} / -40 \ ^{\circ}C \text{ to } +85 \ ^{\circ}C$						
*Figure 1 is on the next page	JH ±50 × 10 ⁻⁶ / -40 °C to +105 °C						

	Frequency	tolerance / Operating te	emperature	
Frequency [MHz]	DB	JG	JH	
	±25 × 10 ⁻⁶	±50 × 10 ⁻⁶	±50 × 10 ⁻⁶	
	-20 °C to +70 °C	-40 °C to +85 °C	-40 °C to +105 °C	
4	-	X1G004481005100	X1G004481025200	
8	-	X1G004481001400	X1G004481025300	
10	-	X1G004481000500	X1G004481025400	
12	X1G004481025500	X1G004481000600	X1G004481025600	
12.288	X1G004481025700	X1G004481000100	X1G004481025800	
14.7456	-	X1G004481002500	X1G004481025900	
16	-	X1G004481000700	X1G004481026000	
20	X1G004481012800	X1G004481000800	X1G004481026100	
24	X1G004481002200	X1G004481000200	X1G004481026200	
24.576	-	X1G004481001600	X1G004481026300	
25	X1G004481011600	X1G004481000300	X1G004481026400	
26	-	X1G004481003500	X1G004481026500	
27	-	X1G004481000400	X1G004481026600	
32	-	X1G004481000900	X1G004481026700	
33.33	-	X1G004481017900	X1G004481026800	
33.3333	-	X1G004481003300	X1G004481026900	
40	-	X1G004481001500	X1G004481027000	
48	X1G004481022600	X1G004481001100	X1G004481027100	
50	X1G004481011200	X1G004481001200	X1G004481016000	
72	X1G004481027200	X1G004481018300	X1G004481027300	

[2] Absolute Maximum Ratings


Parameter	Symbol	Specification			Unit	Conditions
Falameter		Min.	Тур.	Max.	Onit	Conditions
Maximum supply voltage	V _{CC}	-0.3	-	4	V	
Input voltage	Vin	-0.3	-	V _{CC} + 0.3	V	ST terminal
Storago tomporaturo rango	Tota	-55	-	+125	°C	SG2016CAN
Storage temperature range	T_stg	-40	-	+125	°C	All other

[3] Operating Range

Parameter	Symbol	Specification			Unit	Conditions
Falameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Supply voltage		1.6	-	3.63	V	fo \leq 50 MHz, T_use = +105 °C Max.
	V _{cc}	1.71	-	3.63	V	fo = 72 MHz, T_use = +85 °C Max.
		2.25	-	3.63	V	fo = 72 MHz, T_use = +105 °C Max.
Supply voltage	GND	0.0	0.0	0.0	V	
Operating temperature range (Refer to Figure 1)	T_use	-20	+25	+70	°C	
		-40	+25	+85	°C	
		-40	+25	+105	°C	
CMOS load condition	L_CMOS	-	-	15	pF	

* Power supply startup time (0 $\%V_{CC} \rightarrow 90 \%V_{CC}$) should be more than 150 µs

* A 0.01 µF to a 0.1 µF bypass capacitor should be connected between V_{cc} and GND pins located close to the device



Please note that Supply voltage range (V_{CC}) depends on Output frequency(fo) and upper limit of Operating temperature(T_use Max.).

Figure 1: The upper limit of Operating temperature and the related conditions

[4] Frequency Characteristics

(Unless stated otherwise [3] Operating Range)

		(
Parameter	Deremeter		Specification			Conditions
Falameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Output frequency	fo	4, 8, 10, 12, 12.288, 14.7456, 16, 20, 24, 24.576, 25, 26, 27, 32, 33.33, 33.3333, 40, 48, 50, 72		MHz		
		-50	-	+50	×10 ⁻⁶	T_use = -20 °C to +70 °C
Frequency tolerance *1	f_tol	-100		+100	×10 ⁻⁶	T_use = -40 °C to +105 °C T_use = -40 °C to +85 °C *2
Frequency aging	f_age	-3		+3	×10 ⁻⁶	+25 °C, First year


*1 Frequency tolerance includes initial frequency tolerance, temperature variation, supply voltage change and load drift.


*2 This temperature range is only for fo = 75 MHz

5] Electrical Characteristics					stated othe	erwise [3] Operating Range
Parameter	Symbol		Specificatior		Unit	Conditions
	Cynisor	Min.	Тур.	Max.	onit	
Start-up time	t_str	-	-	3	ms	t = 0 at 90 %V _{CC}
Current consumption (No load)		-	-	1.5	mA	$1 \text{ MHz} \le \text{fo} \le 20 \text{ MHz}$
$V_{CC} = 1.8 \text{ V} \pm 10 \%$		-	-	1.8	mA	20 MHz < fo \leq 40 MHz
		-	-	2.1	mA	40 MHz < fo \leq 50 MHz
$V_{CC} = 1.8 V \pm 5 \%$		-	-	2.4	mA	fo = 72 MHz
		-	-	1.6	mA	1 MHz \leq fo \leq 20 MHz
Current consumption (No load)	1	-	-	2.0	mA	20 MHz < fo \leq 40 MHz
$V_{CC} = 2.5 \text{ V} \pm 10 \%$	I _{CC}	-	-	2.4	mA	40 MHz < fo \leq 50 MHz
		-	-	2.8	mA	fo = 72 MHz
		-	-	1.8	mA	1 MHz \leq fo \leq 20 MHz
Current consumption (No load)		-	-	2.2	mA	20 MHz < fo \leq 40 MHz
$V_{CC} = 3.3 \text{ V} \pm 10 \%$		-	-	2.6	mA	40 MHz < fo \leq 50 MHz
		-	-	3.0	mA	fo = 72 MHz
		-	-	2.1	μA	V _{CC} = 1.8 V ± 10 % or ± 5 %, ST = GND
Stand-by current	I_std	-	-	2.5	μA	$V_{CC} = 2.5 \text{ V} \pm 10 \%, \overline{ST} = GND$
		-	-	2.7	μA	V _{CC} = 3.3 V ± 10 %, ST = GND
	V _{OH}	90 % V _{CC}	-	-	V	Load current condition 1.8 V ± 10 % 2.5 V ± 10 % 3.3 V ± 1
	V _{OL}	-	-	10 % V _{CC}	V	loн -1.5 mA -3 mA -4 m. lo∟ 1.5 mA 3 mA 4 mA
Output voltage	V _{OH}	V _{CC} - 0.4	-	-	V	Load current condition 1.8 V ± 10 % 2.5 V ± 10 % 3.3 V ± 1
	V _{OL}	-	-	0.4	V	l _{OH} -1.5 mA -3 mA -4 m/ l _{OL} 1.5 mA 3 mA 4 mA
Symmetry	SYM	45	50	55	%	50 % V _{CC} level, L_CMOS ≤ 15 pF
Rise time / Fall time	tr / tf	-	-	3	ns	$V_{CC} = 2.5 \text{ V or } 3.3 \text{ V} \pm 10 \%$ 20 % V_{CC} to 80 % V_{CC} Leve L_CMOS = 15 pF
	u / u	-	-	3.5	ns	$V_{CC} = 1.8 V \pm 10 \% \text{ or } \pm 5 \%$ 20 % V_{CC} to 80 % V_{CC} Leve L_CMOS = 15 pF
	V _{IH}	80 % Vcc	-	-	V	ST terminal
Input voltage	V _{IL}	-	-	20 % Vcc	V	
Output disable time (ST)	tstp_st	-	-	100	ns	\overline{ST} terminal HIGH \rightarrow LOW
Output enable time (ST)	tsta_st	-	-	3	ms	\overline{ST} terminal LOW \rightarrow HIGH


[6] Thermal resistance (For reference only)

Parameter	Symbol	Specification			Unit	Conditions
Parameter	Symbol	Min.	Тур.	Max.	Unit	Conditions
Junction temperature	Tj	-	-	+125	°C	
		-	10	-	°C/W	SG2016CAN
		-	15	-	°C/W	SG-210STF
Junction to case	Өјс	-	28	-	°C/W	SG3225CAN
Junction to ambient		-	16	-	°C/W	SG5032CAN
		-	23	-	°C/W	SG7050CAN
		-	100	-	°C/W	SG2016CAN
		-	92	-	°C/W	SG-210STF
	θja	-	79	-	°C/W	SG3225CAN
		-	82	-	°C/W	SG5032CAN
		-	104	-	°C/W	SG7050CAN







* Output load condition under L_CMOS > 15 pF (dotted line area) is not guaranteed, and the data is for reference. The actual current consumption is the total of the current under the condition of no load and the current to drive the output load (fo x L_CMOS x V_{CC}). To reduce the current consumption, it is effective to use lower frequency, lower supply voltage and lower output load.




* Output load condition under L_CMOS > 15 pF (dotted line area) is not guaranteed, and the data is for reference.



^{*} Output load condition under L_CMOS > 15 pF (dotted line area) is not guaranteed, and the data is for reference.




* Output load condition under L_CMOS > 15 pF (dotted line area) is not guaranteed, and the data is for reference.




* Output load condition under L_CMOS > 15 pF (dotted line area) is not guaranteed, and the data is for reference.


Page 12 / 34




* Output load condition under L_CMOS > 15 pF (dotted line area) is not guaranteed, and the data is for reference. There are some missing data in the graph. It is unmeasurable because of low amplitude under the condition of L_CMOS > 15 pF.




* Output load condition under L_CMOS > 15 pF (dotted line area) is not guaranteed, and the data is for reference. There are some missing data in the graph. It is unmeasurable because of low amplitude under the condition of L_CMOS > 15 pF.




fo = 40 MHz




fo = 72 MHz





fo = 40 MHz



fo = 72 MHz

3.5

3

2

2.5

1.5

1

0.5

0


Temperature [ºC]

voltage (V_{OH}) [V]

Output


V_{OH}, L_CMOS = 15 pF, Temp. Char. V_{OL}, L_CMOS = 15 pF, Temp. Char. 3.5 _____Vcc=1.8 V 3 -Vcc=2.5 V [V] (^{∟0}N) -Vcc=3.3 V 2.5 2 voltage (' 1.5 Output 1 -Vcc=1.8 V 0.5 0 -40 -30 -20 -10 0 10 20 30 40 50 60 70 80 90 100 -40 -30 -20 -10 0 10 20 30 40 50 60 70 80 90 100 110 120

Temperature [ºC]





Page 16 / 34


Spec No : SGxxxxCAN_E_Ver1.94




Page 17 / 34








[8] Test Circuit





*Standby current test should be $\overline{ST} = GND$.

(8-3) Condition

(1) Oscilloscope

The bandwidth should be minimum 5 times wider than measurement frequency The probe ground should be placed closely to the test point and the lead length should be as short as possible


* It is recommended to use miniature socket. (Don't use earth lead.)

- (2) L_CMOS includes probe capacitance.
- (3) A 0.01 μF to a 0.1 μF bypass capacitor should be connected between V_{CC} and GND pins located close to the device
- (4) Use a current meter with a low internal impedance
- (5) Power Supply


Power supply startup time (0 $\% V_{CC} \rightarrow 90 \ \% V_{CC})$ should be more than 150 μs Power supply impedance should be as low as possible

(8-4) Timing Chart


(1) Output Waveform and Level



(2) Output Frequency Timing



(3) ST Function and Timing



- *1 The period from $\overline{ST} = V_{IL}$ to OUT = High impedance (Disable)
- *2 The period from $\overline{ST} = V_{IH}$ to OUT = Enable
- * Judge of starting output: $V_{OH} \geq 80~\% V_{CC},~V_{OL} \leq 20~\% Vcc,$ fout is within fo ± 1 000 × 10^{-6}
- * ST terminal voltage level should not exceed supply voltage when using ST function. Please note that ST rise time should not exceed supply voltage rise time at the start-up.

[9] Outline Drawing and Recommended Footprint (9-1) SG2016CAN

2.0±0.1 #4 #3 #3 4 0.5 1.6±0.1 C0.2-45 Ö. **#**2 #1 #1 0.55 0.7 0.1 0.1 5 6 Terminal coating : Au plating 0.9 0.8 For stable operation, it is recommended that +0.01 µF to 0.1 µF bypass capacitors should be] connected between V_{CC} and GND and placed

Reference Weight Typ.: 9.9 mg


1.4

Terminal Assignment

Pin #	Connection	Function				
			ST terminal			
#1	ST	ST function	Osc. Circuit	Output		
#1	51	"H" or OPEN	Oscillation	Specified frequency: Enable		
		"L"	Oscillation stop	High impedance: Disable		
#2	GND	GND terminal				
#3	OUT	Output terminal				
#4	V _{cc}	V _{CC} terminal				


as close to the V_{CC} pin as possible.


Marking



Units: mm

Units: mm







Reference Weight Typ.: 14 mg

Terminal Assignment

~								
	Pin #	Connection	Function					
			ST terminal	ST terminal				
	#1	ST	ST function	Osc. Circuit	Output			
	#1		"H" or OPEN	Oscillation	Specified frequency: Enable			
			"L"	Oscillation stop	High impedance: Disable			
	#2	GND	GND terminal					
	#3	OUT	Output terminal					
	#4	V _{cc}	V _{CC} terminal					







Reference Weight Typ.: 25 mg

Terminal Assignment

ciffind Assignment							
Pin #	Connection	Function					
		ST terminal	T terminal				
#1	ST	ST function	Osc. Circuit	Output			
#1		"H" or OPEN	Oscillation	Specified frequency: Enable			
		"L"	Oscillation stop	High impedance: Disable			
#2	GND	GND terminal					
#3	OUT	Output terminal					
#4	V _{cc}	V _{CC} terminal					





Reference Weight Typ.: 52 mg


Terminal Assignment


ei							
	Pin #	Connection	Function				
			ST terminal				
	#1	ST	ST function	Osc. Circuit	Output		
	#1		"H" or OPEN	Oscillation	Specified frequency: Enable		
			"L"	Oscillation stop	High impedance: Disable		
	#2	GND	GND terminal				
	#3	OUT	Output terminal				
	#4	V _{cc}	V _{CC} terminal				

Symbol	E25. 000	Frequency [MHz]
Location of Pin #1	OCAN361S	Production lot number
Model		

Units: mm

(9-5) SG7050CAN





Terminal coating : Au plating

For stable operation, it is recommended that 0.01 μF to 0.1 μF bypass capacitors should be connected between V_{CC} and GND and placed as close to the V_{CC} pin as possible.

Reference Weight Typ.: 147 mg

Terminal Assignment

Pin #	Connection	Function					
			ST terminal				
#1	ST	ST function	Osc. Circuit	Output			
#1	51	"H" or OPEN	Oscillation	Specified frequency: Enable			
		"L"	Oscillation stop	High impedance: Disable			
#2	GND	GND terminal					
#3	OUT	Output terminal					
#4	V _{cc}	V _{CC} terminal					

Symbol	E25. 000	Frequency [MHz]
Location of Pin #1	OCAN361S	Production lot number
Model		

[10] Moisture Sensitivity Level and Electro-Static Discharge Ratings

(10-1) Moisture Sensitivity L	_evel (MSL)	
Parameter	Specification	Conditions
MSL	LEVEL 1	IPC/JEDEC J-STD-020D.1

(10-2) Electro-Static Discharge (ESD)


Parameter	Specification	Conditions
HBM	2 000 V Min.	EIAJ ED-4701-1 C111A, 100 pF, 1.5 kΩ, 3 times
MM	200 V Min.	EIAJ ED-4701-1 C111, 200 pF, 0 Ω, 1 time
CDM	750 V Min	AEC-Q100-011 (DCDM) * only for SG2016CAN

(10-3) Latch-Up

Parameter	Specification	Conditions
Latch-up	100 mA Min.	EIAJ ED-4701-1 C113

[11] Reflow Profiles

IPC/JEDEC J-STD-020D.1



[12] Packing Information

(12-1) SG2016CAN

(1) Packing Quantity

The last two digits of the Product Number (X1G004801xxxx<u>xx</u>) are a code that defines the packing quantity. The standard is "00" for a 3 000 pcs/Reel.

(2) Taping Specification


Subject to EIA-481, IEC-60286 and JIS C0806

1) Tape Dimensions

Carrier Tape Material: PS (Polystyrene)

Top Tape Material: PET (Polyethylene Terephthalate) +PE (Polyethylene)

Units: mm



3) Storage Environment

(12-2) SG-210STF

(1) Packing Quantity

The last two digits of the Product Number (X1G004171xxxx<u>xx</u>) are a code that defines the packing quantity. The standard is "00" for a 3 000 pcs/Reel.

(2) Taping Specification


Subject to EIA-481, IEC-60286 and JIS C0806

1) Tape Dimensions

Carrier Tape Material: PS (Polystyrene)

Top Tape Material: PET (Polyethylene Terephthalate) +PE (Polyethylene)

Units: mm



3) Storage Environment

(12-3) SG3225CAN

(1) Packing Quantity

The last two digits of the Product Number (X1G005961xxxx<u>xx</u>) are a code that defines the packing quantity. The standard is "15" for a 2 000 pcs/Reel.

(2) Taping Specification


Subject to EIA-481, IEC-60286 and JIS C0806

1) Tape Dimensions

Carrier Tape Material: PS (Polystyrene)

Top Tape Material: PET (Polyethylene Terephthalate) +PE (Polyethylene)

Units: mm



3) Storage Environment

(12-4) SG5032CAN

(1) Packing Quantity

The last two digits of the Product Number (X1G004451xxxx<u>xx</u>) are a code that defines the packing quantity. The standard is "00" for a 1 000 pcs/Reel.

(2) Taping Specification


Subject to EIA-481, IEC-60286 and JIS C0806

1) Tape Dimensions

Carrier Tape Material: PS (Polystyrene)

Top Tape Material: PET (Polyethylene Terephthalate) +PE (Polyethylene)


Units: mm



2) Reel Dimensions

Center Material: PS (Polystyrene) Reel Material: PS (Polystyrene)

Units: mm



3) Storage Environment

We recommend to keep less than +30 °C and 85 %RH of humidity in a packed condition, and to use it less than 6 months after delivery.

Spec No : SGxxxxCAN_E_Ver1.94

(12-5) SG7050CAN

(1) Packing Quantity

The last two digits of the Product Number (X1G004481xxxx<u>xx</u>) are a code that defines the packing quantity. The standard is "00" for a 1 000 pcs/Reel.

(2) Taping Specification


Subject to EIA-481, IEC-60286 and JIS C0806

1) Tape Dimensions

Carrier Tape Material: PS (Polystyrene)

Top Tape Material: PET (Polyethylene Terephthalate) +PE (Polyethylene)


Units: mm



2) Reel Dimensions Center Material: PS (Polystyrene)

Reel Material: PS (Polystyrene)

Units: mm



3) Storage Environment

[13] Handling Precautions

Prior to using this product, please carefully read the section entitled "Precautions" on our Web site (https://www5.epsondevice.com/en/information/#precaution) for instructions on how to handle and use the product properly to ensure optimal performance of the product in your equipment.

Before using the product under any conditions other than those specified therein,

please consult with us to verify and confirm that the performance

affected by use under such conditions.

In addition to the foregoing precautions, in order to avoid the deteriorating performance of the product, we strongly recommend that you DO NOT use the product under ANY of the following conditions:

- (1) Mounting the product on a board using water-soluble solder flux and using the product without removing the residue of the flux completely from the board. The residue of such flux that is soluble in water or water-soluble cleaning agent, especially the residues which contains active halogens, will negatively affect the performance and reliability of the product.
- (2) Using the product in any manner that will result in any shock or impact to the product.
- (3) Using the product in places where the product is exposed to water, chemicals, organic solvent, sunlight, dust, corrosive gasses, or other materials.
- (4) Using the product in places where the product is exposed to static electricity or electromagnetic waves.
- (5) Applying ultrasonic cleaning without advance verification and confirmation that the product will not be affected by such a cleaning process, because it may damage the crystal,
- (6) Using the product under any other conditions that may negatively affect the performance and/or reliability of the product.
- (7) Power supply with ripple may cause of incorrect operation or degradation of phase noise characteristics, so please evaluate before use.
- (8) Supply voltage should be increased monotonically. In addition, please do not power on at midpoint potential since that may cause malfunction or not output.
- (9) Frequency aging is from environmental tests results to the expectation of the amount of the frequency variation. This doesn't guarantee the product-life cycle.

Should any customer use the product in any manner contrary to the precautions and/or advice herein, such use shall be done at the customer's own risk.

PROMOTION OF ENVIRONMENTAL MANAGEMENT SYSTEM CONFORMING TO INTERNATIONAL STANDARDS

At Seiko Epson, all environmental initiatives operate under the Plan-Do-Check-Action (PDCA) cycle designed to achieve continuous improvements. The environmental management system (EMS) operates under the ISO 14001 environmental management standard.

All of our major manufacturing and non-manufacturing sites, in Japan and overseas, completed the acquisition of ISO 14001 certification.

WORKING FOR HIGH QUALITY

In order provide high quality and reliable products and services than meet customer needs, Seiko Epson made early efforts towards obtaining ISO9000 series certification and has acquired ISO9001 for all business establishments in Japan and abroad. We have also acquired IATF 16949 certification that is requested strongly by major manufacturers as standard.

Explanation of marks used in this datasheet

ISO 14000 is an international standard for environmental management that was established by the International Standards Organization in 1996 against the background of growing concern regarding global warming, destruction of the ozone layer, and global deforestation.

IATF 16949 is the international standard that added the sectorspecific supplemental requirements for automotive industry based on ISO9001.

Pb	●Pb free.
Compliant	 Complies with EU RoHS directive. *About the products without the Pb-free mark. Contains Pb in products exempted by EU RoHS directive (Contains Pb in sealing glass, high melting temperature type solder or other)

NOTICE: PLEASE READ CAREFULLY BELOW BEFORE THE USE OF THIS DOCUMENT ©Seiko Epson Corporation 2020 1. The content of this document is subject to change without notice. Before purchasing or using Epson products, please contact with sales representative of Seiko Epson Corporation ("Epson") for the latest information and be always sure to check the latest information

- published on Epson's official web sites and resources.
- 2. This document may not be copied, reproduced, or used for any other purposes, in whole or in part, without Epson's prior consent.
- 3. Information provided in this document including, but not limited to application circuits, programs and usage, is for reference purpose only. Epson makes no guarantees against any infringements or damages to any third parties' intellectual property rights or any other rights resulting from the information. This document does not grant you any licenses, any intellectual property rights or any other rights with respect to Epson products owned by Epson or any third parties.
- 4. Using Epson products, you shall be responsible for safe design in your products; that is, your hardware, software, and/or systems shall be designed enough to prevent any critical harm or damages to life, health or property, even if any malfunction or failure might be caused by Epson products. In designing your products with Epson products, please be sure to check and comply with the latest information regarding Epson products (including, but not limited to this document, specifications, data sheets, manuals, and Epson's web site). Using technical contents such as product data, graphic and chart, and technical information, including programs, algorithms and application circuit examples under this document, you shall evaluate your products thoroughly both in stand-alone basis and within your overall systems. You shall be solely responsible for deciding whether to adopt/use Epson products with your products.
- 5. Epson has prepared this document carefully to be accurate and dependable, but Epson does not guarantee that the information is always accurate and complete. Epson assumes no responsibility for any damages you incurred due to any misinformation in this document.
- No dismantling, analysis, reverse engineering, modification, alteration, adaptation, reproduction, etc., of Epson products is allowed.
 Epson products have been designed, developed and manufactured to be used in general electronic applications and specifically
- requires particular quality or extremely high reliability in order to refrain from causing any malfunction or failure leading to critical harm to life and health, serious property damage, or severe impact on society, including, but not limited to listed below ("Specific Purpose"). Therefore, you are strongly advised to use Epson products only for the Anticipated Purpose. Should you desire to purchase and use Epson products for Specific Purpose, Epson makes no warranty and disclaims with respect to Epson products, whether express or implied, including without limitation any implied warranty of merchantability or fitness for any Specific Purpose. Please be sure to contact our sales representative in advance, if you desire Epson products for Specific Purpose:

Space equipment (artificial satellites, rockets, etc.)/ Transportation vehicles and their control equipment (automobiles, aircraft, trains, ships, etc.) / Medical equipment/ Relay equipment to be placed on sea floor/ Power station control equipment / Disaster or crime prevention equipment/Traffic control equipment/ Financial equipment

- Other applications requiring similar levels of reliability as the above
- 8. Epson products listed in this document and our associated technologies shall not be used in any equipment or systems that laws and regulations in Japan or any other countries prohibit to manufacture, use or sell. Furthermore, Epson products and our associated technologies shall not be used for the purposes of military weapons development (e.g. mass destruction weapons), military use, or any other military applications. If exporting Epson products or our associated technologies, please be sure to comply with the Foreign Exchange and Foreign Trade Control Act in Japan, Export Administration Regulations in the U.S.A (EAR) and other export-related laws and regulations in Japan and any other countries and to follow their required procedures.
- 9. Epson assumes no responsibility for any damages (whether direct or indirect) caused by or in relation with your non-compliance with the terms and conditions in this document or for any damages (whether direct or indirect) incurred by any third party that you give, transfer or assign Epson products.
- 10. For more details or other concerns about this document, please contact our sales representative.
- 11. Company names and product names listed in this document are trademarks or registered trademarks of their respective companies.