
Amphenol[®] High Frequency Contacts for Multi-pin Connectors

12-130-4

HIGH PERFORMANCE CONNECTORS AND CONTACTS PROVIDE SECURE, RELIABLE DATA TRANSMISSION



Amphenol High Frequency Contacts



High Frequency Contacts Typical Markets:

- Military & Commercial Aviation
- Military Vehicles
- Missiles & Ordnance
- C4ISR



Amphenol[®] High Frequency Contacts Provide High Speed Transmission and **Operate in High Frequency Conditions**



When you need superior electrical performance plus shielding to eliminate interference from outside electrical sources in a connector, Amphenol has the most reliable contact solutions.

Amphenol offers a very wide range of contacts that provide high speed transmission and operate in high frequency conditions. You can be assured of interconnection compatibility when you come to Amphenol for your contact needs as well as your connector needs. Amphenol's expertise in interconnection solutions assures that your contacts will mate properly and will perform to the application specifications of your particular requirements.

MIL-DTL-38999 CONNECTORS - The high performance series most ideal for integrating high speed and high frequency contacts. MIL-DTL-38999, Series I, II and III are by far the choice of connector for today's avionics needs - these subminiature family connectors are ideally suited for the incorporation of shielded contacts.

This catalog section is primarily devoted to the high speed and high frequency contact op

options for use in MIL-DTL-38999 Connectors, which include:							
Coaxial	Concentric Twinax	Triax	Quadrax	Differential Twinax	High Frequency	Transition Adapters	
Pin and socket contacts designed for RF/microwave and shielded wire applica- tions. Sizes 4, 8, 12 & 16	Pin and socket contacts designed for protection from magnetic and electro- static interference including nuclear electromagnetic pulse. Sizes 8 & 12	Pin and socket contacts designed for shielded wire applications with 3 conductors. Sizes 8, 10 & 12	Size 8 pin and socket contacts. An outer contact with 4 strategically spaced inner contacts forming two 100 or 150 Ohm matched impedance differential pairs	Size 8 pin and socket contacts. An outer contact with 2 inner contacts spaced to form one 100 or 150 Ohm matched impedance differential pair.	Size 8 Coaxial contacts that provide high frequencies (DC to 40 GHz). Unique "Float Mount" technology maintains tight mechanical tolerances.	Matched impedance quadrax and twinax transition adapters provide a method of launching from the high speed connectors to PCB boards.	

Other series of connectors from Amphenol Aerospace, in addition to 38999 connectors, can incorporate shielded contacts. These include the following (and are also covered in this catalog section):

 Amphenol[®] Heavy Duty Circular Connectors, MIL-DTL-22992 with coax contacts.

- Amphenol® Printed Circuit Board Connectors Rectangular connectors with standard low mating force brush contacts can have hybrid arrangements with coax contacts.
- LRM Interconnects Rectangular module and backplane connectors with standard low mating force brush contacts can have hybrid arrangements with coax contacts.
- Amphenol[®] ARINC 600 and R27 Rack & Panel Connectors are available with quadrax, coax, twinax and differential twinax contacts.

The Cable Usage Guide is a key reference to help guide you in selecting the contacts best suited to your needs. Since most shielded wire applications start with a fixed requirement for cable types, the guide refers you to the Amphenol connector family utilizing contacts which are compatible with the cable characteristics.

For more information on other Amphenol connectors with shielded contacts:

- Amphenol® Circular Connectors, MIL-DTL-26482, Series 1 are available with coaxial contacts, size 8 and 12 for crimp and solder type. See catalog 12-070 on-line at www.amphenol-industrial.com, or consult Amphenol Industrial Operations.
- Amphenol® MS/Standard, MIL-DTL-5015 Circular Connectors are available with size 4, 8 and 12 coax contacts. Consult Amphenol Industrial Operations for more information or on-line at www.amphenol-industrial.com.

For more information on connectors with fiber optics see the Fiber Optic section of this catalog or consult Amphenol Aerospace, Sidney, NY.

Contact Designer's Guide at end of this catalog

See High Frequency





Amphenol Aerospace

High Speed Quadrax and Differential Twinax Contacts



Amphenol provides the latest technology in high speed contacts - differential twinax and quadrax contacts, size 8, for use in MIL-DTL-38999 Special* Circular Connectors.

DIFFERENTIAL TWINAX CONTACTS

High speed Differential Twinax contacts consist of an outer contact with two inner contacts spaced to form one 100 or 150 Ohm controlled impedance differential pair. See pages 385 and 386 for performance data and ordering of Differential Twinax contacts, and consult Amphenol Aerospace for more information.

 High speed Quadrax contacts consist of an outer contact with four inner contacts spaced to form two 100 or 150 Ohm

controlled impedance differential pair.

• Both contacts, when used in Amphenol MIL-DTL-38999 Series III and ARINC

type connectors, provide an excellent

Gigabit Ethernet 1000 Base-T-100 Ohm

alternative for harsh environment



Differential Twinax Contact



Quadrax Contact

Differential Twinax and Quadrax contacts provide high data transfer rates, low power consumption, and excellent EMI capability. They offer controlled impedance of 100 or 150 Ohm and are ideal for use in harsh environments.





D38999 Series III Ground Plane Connectors with Quadrax PCB Socket contacts



D38999 Series III with Quadrax and Power Contacts

D38999 Series III Connectors (standoff shell at right and standard shell below) with Quadrax PC Tail Contacts





• IEEE1394B FireWire-110 Ohm

applications such as: • Ethernet 100 Base-T-100 Ohm

• Fibre Channel-150 Ohm

4

QUADRAX CONTACTS

Differential Twinax and Quadrax contact options include:

- Crimp or printed circuit board termination
- Established designs to accommodate a variety of cable types and gages
- Ground plane connectors can incorporate quadrax contacts. These

connections have conductive inserts that ground the outer conductor of the contact body to the shell of the connector. They accommodate size 8 and 12 shielded contacts of which the size 8 can be quadrax type. See pages 378-380 for performance data of Quadrax contacts. Consult Amphenol Aerospace for further information needed.

* Requires modified connector to accommodate keyed contacts.

Quadrax Contacts, Quadrax Terminators, Transition Adapters



QUADRAX CONTACTS FOR ARINC CONNECTORS

Amphenol ARINC 600 Rack and Panel connectors can incorporate high speed quadrax contacts as well as coax, twinax and differential twinax contacts. R27 Rack and Panel connectors use the same contacts as ARINC 600 connectors. For more information about rack and panel connectors contact Amphenol Aerospace, Sidney, NY.

BOARD LEVEL CONNECTORS WITH COMPLIANT QUADRAX CONTACTS

Amphenol also provides compliant quadrax socket contacts and Quadrax pin contacts with PC tails for attaching to printed circuit boards. See page 387 for more information.

FEED-THROUGH CON-NECTOR WITH QUADRAX CONTACTS

Amphenol's feed-through connector is double-ended for through bulkhead applications. Consult Amphenol for more information.



Quadrax Contact for ARINC Connectors



Compliant Quadrax Socket and PCB Tail Quadrax Pin



Quadrax Terminators

Amphenol offers a terminator assembly which is a low reactance, resistive impedance match to the characteristic impedance of a transmission line. It is used to terminate the far ends of a transmission line or an open tap so that the energy from signals traveling down the transmission line is absorbed within the resistor and not reflected back down the transmission line causing signal interference (noise). Consult Amphenol for more information.





Quadrax Terminator

Transition Adapters

In conjunction with its Differential Twinax and Quadrax contacts, Amphenol has developed a full line of Transition Adapters in order to facilitate launching of controlled impedance signals to printed circuit boards. These use differential twinax or quadrax 90° or straight receptacles and they can be either threaded or cable to board direct. The threaded transition adapters provide an ideal method of disconnecting the differential twinax or quadrax connector from the board.

See pages 388-390 for further description, performance data and ordering of transition adapters.



Board Level Connector

with Compliant

Quadrax Contacts

90° Quadrax Receptacle and Plug Transition Adapter



90° Differential Twinax Receptacle and Plug Transition Adapter

High Speed Coax and Twinax Contacts

Optional choices, other than standard crimp or solder 500 cycle and 1500 cycle contacts, are often required for high frequency interconnections. Amphenol offers shielded contacts for RF applications as well as balanced high sensitivity circuits.

SHIELDED COAXIAL CONTACTS

Amphenol Aerospace

> High speed Coax contacts within a connector provide the shielding protection, and many cases the RF/microwave performance, needed in the circuitry of many applications.



Shielded Coax Contacts

All popular series of Amphenol circular connectors and many rectangular connectors are available with coax contacts. Diameters are standardized in sizes 4, 8, 12 and 16 so that coaxial contacts may be interchanged with power contacts in connector arrangements which include those sizes. Popular RG cable types and a variety of other commercial coaxial cables can be accommodated. See page 398 for coax contact performance data. Matched impedance size 12 coax contacts are also available (see page 402). The use of coax contacts within a connector, compared to the use of individual coaxial/shielded connectors, offers advantages of savings in space and weight and no cross-mating difficulties. Coax and standard contacts may be mixed within the connector to meet special signal needs. The connector itself offers further protection and environmental integrity through the grommets and seals used, and coaxial junction is protected by the connector outer shell.

CONCENTRIC TWINAX SHIELDED CONTACTS

High performance shielding capabilities are available with Concentric Twinax contacts. These are designed for protection from magnetic and electrostatic interference including nuclear electro-magnetic pulse. The contact is crimp terminable to twisted shielded cable and is fully scoop-proof (recessed pins) in MIL-DTL-38999 connectors. The concentric twinax contact is engineered to maintain shield integrity through a multi-pin circular connector and does not require contact polarization within the insert. Size 8 concentric twinax contacts were developed for use in MIL-STD-1553B Airborne multiplex data bus applications. Ideal for this application need is the high performance Tri-Start connector with its fully scoop-proof feature of recessed pins.

6



Concentric Twinax Contacts Size 8



MIL-DTL-38999 Lanyard "Breakaway" Connector with Concentric Twinax Contacts, Qualified for MIL-STD-1760

The concentric twinax contact is crimp terminable to twisted shielded cable. Size 12 concentric twinax contacts were developed for SAAB. They can be used in any size 12 cavity of D38999 I, II or III or SJT connector. Size 8 & 12 coax, triax or twinax contacts or size 16 coax contacts are available in Ground Plane Connectors (See photo preceding page). These are MIL-DTL-38999 Series III connectors for data bus, LAN and coax/triax/twinax transmission lines with conductive inserts that ground the outer contact conductor to the shell. They are sold "less contacts" Amphenol[®] Shielded Contacts provide design versatility for electrical circuitry. Shielded contacts are used to eliminate interference from outside electrical sources, when standard crimp or solder contacts are not enough.



Coax Contacts with Frequency Range of DC to 40 GHz



HIGH FREQUENCY COAX CONTACTS WITH "FLOAT MOUNT" TECHNOLOGY

Amphenol Aerospace now offers DC to 40 GHz size 8 coaxial contacts for the D38999 housing and standard inserts. These contacts can be terminated to a multiple of cable types depending on the application.



High Frequency Size 8 Coax Contacts with "Float Mount" Technology

By using standard interfaces that are based on MIL-STD-348 and can be installed in any D38999 size 8 insert, Amphenol has transformed the circular connector industry. This technology expands the use of D38999 connectors to include the microwave transmission lines within the multi-port configuration without change to a custom connector.

The high frequencies are maintained by Amphenol's unique "Float Mount" technology. This technology allows for consistent microwave performance while maintaining tight mechanical tolerances. This consistency provides superior electrical performance and, unlike other blindmate connectors, will maintain an accurate phase length when mated. See page 404 for specifications, performances and ordering of this contact.

Twinax Contacts for Printed Circuit Board Applications

PCTAILTWINAX CONTACTS


Amphenol provides Printed Circuit Tail Twinax contacts for MIL-DTL-38999 Series I and III circular connectors and also for ARINC 404 and ARINC 600 rectangular connectors. High reliability is assured with factory pre-assembled contacts and standardized termination to the board.



Variety of PC Tail Twinax Contacts

See pages 409-411 for performance data and ordering of PC tail twinax contacts, and consult Amphenol Aerospace for further information needed. Also see the Printed Circuit Board, and the Series I, II, III section for MIL-DTL-38999 connectors.

TRIAX CONTACTS WITH THREE CONDUCTORS FOR **USE WITH TRIAX CABLE**





Triax Contacts

tacts provide additional shielding when terminated to triax cable having solid or stranded center conductors. See cable compatibility in the Cable Usage Guide and performance data and ordering of triax contacts on pages 408-411. Each of the three conductors of the triax contact is separated by dielectric insulation to isolate ground planes and to improve shielding effectiveness. All conductors are crimp terminated for high reliability and ease of assembly. Triax contacts may be specified for direct connection to printed circuit boards. For maximum system flexibility, triax contacts may be mixed with coax, twinax and power contacts in a single connector.

D38999 Connectors

Twinax Contacts



Printed Circuit Twinax Contacts provide a cost effective packaging solution for limited space applications where connectors are attached to printed circuit boards.

> Rail Launch MIL-STD-1760 Connector with Triax Contacts



HF38999 - D38999 Connectors with High Frequency Coax Contacts



Cable Systems with High Frequency Contacts

CABLE ASSEMBLY CAPABILITIES

Amphenol provides a large array of cable assemblies with high speed quadrax and differential twinax contacts, as well as coax and concentric twinax contacts. This page shows a few examples. The Cable Usage Guide pages that follow list the design possibilities for these high speed contacts.

Amphenol strives to offer customers the widest range of cable assemblies, keeping abreast of the latest cable types in the marketplace. Please consult with the contact product managers at Amphenol Aerospace for assistance in designing the cable assembly that suits your particular needs. From a simple onecable interconnection, to a multiple cable system, Amphenol can design and supply your cable needs for high frequency contacts and connectors. See the High Frequency Contact Designer's Guide at the end of this catalog



Variety of Quadrax Cable Assemblies

TESTING OF CABLES

8

Rigid testing is performed 100% on cable assemblies at Amphenol before they are shipped to make sure they meet customer requirements. These requirements include tests such as DWV, resistance and continuity. Amphenol has the background experience and understanding of harsh environmental testing to assure reliable "end-to-end" interconnect solutions.





Eight Wire Gigabit Ethernet Assembly



Quadrax Contact with 8P8C "I Jack Ethernet Assembly

Quadrax Cable Assembly can be attached to any connector application

Quadrax Cable Assembly attached to Board Level Compliant Quadrax Connector




Use the Cable Usage Guide on pages 373-376 as follows:

- 1. Locate the cable you are using in Cable Type column. For cables not listed consult Amphenol Aerospace.
- 2. Refer to the Amphenol Connector section which features contacts/adapters for this cable. Connector size, performance features and insert pattern availability may influence your choice.
- 3. Order your connector and contacts or transition adapters by following the procedure given in the section for the connector series selected. These instructions are supplemented by the Amphenol Catalog Section covering the basic connector.

Quadrax Contacts CABLE USAGE GUIDE D38999 Series III* Connectors



Differential Twinax Contacts CABLE USAGE GUIDE D38999 Series III* Connectors




	Cable Type				
	F-4703-3				
Draka Fileca	F-4703-4	1			
Draka Fileca	F-4704-5	1			
	F-47-4-6]			
Filotex	ET2PC236]			
Filotex	ET2PF870	1			
	E50424]			
PIC Wire	E50426]			
	E51424]			
	NF22Q100]			
	NF24Q100]			
	NF24Q100-1]			
	NF24Q100-01-200C]			
	NF26Q100]			
Tensolite	NF26Q100-1	100			
Tensolite	NF26-2Q100	100			
	24443/03130X-4(LD)	-			
	24443/03166X-4(LD)				
	24443/9P025X-4(LD)				
	23450/04090X-4 (LD)				
	24443/C20714X-4(LD)]			
	RCN7688]			
Gore	RCN8513]			
	RCN8672]			
S280W502-4]			
JSF-18-3]			
	956-4TN]			
Themax	956-5]			
memax	T956-4T200]			
	MX100Q-24				
Tensolite	24450/03089X-4(LD)				
Gore	Gore RCN8487				
JSFY02-1		110			
JSF18					
Tensolite	ensolite 26473/02006X-4(LD)				
Gore	RCN8328	150			

* Requires modified connector to accommodate keyed contacts.


	Cable Type				
Tensolite	26463/70460X-2	98			
ST5M1284-0	03				
Draka Fileca	2709-3				
PIC Wire	PIC Wire E10224				
	NF24T100-200C Space				
	23460/05114X-2(LD)				
Tensolite	24463/03220T-2(LD)				
Tensonie	24463/05099X-8(LD)				
	26453/03184X-2(LD)				
	24463/9P025X-2(LD)	100			
Raychem	0026A0024, 0024G0024				
S280W502-6					
JSFY11-24					
Gore	GSC-05-827300-00				
	956-6262, 956-1T200				
Thermax	12814				
	MX 100-24				
Tensolite	26483/03071X-2(LD)	150			

Quadrax Transition Adapters CABLE USAGE GUIDE D38999 Series III* Connectors or ARINC 600 Connectors



	Cable Type	Nominal Impedance (ohms)		
Draka Fileca	F-4703-3			
Diaka Fileca	F-4704-4			
	NF22Q100			
Tensolite	NF22Q100-01	100		
Tensonite	NF24Q100	100		
	NF26Q100			
Thermax	956-5			
Gore	GSC-10-8273900			
Tensolite	26473/02006X-4(LD)	150		

Differential Twinax Transition Adapters CABLE USAGE GUIDE D38999 Series III* Connectors or ARINC 600 Connectors



Cable Usage Guide, cont.

Quadrax Contacts CABLE USAGE GUIDE ARINC 600 Rack & Panel Connectors

Amphenol Aerospace



Nominal **Cable Type** Impedance (ohms) F-4703-3 Draka Fileca F-4704-5, F4704-4 NF22Q100 100 NF24Q100 Tensolite 24443/03130X-4(LD) 24443/9P025X-4(LD) S280W502-4 JSFY02-1 110 RCN8328 Gore 150 26473/02006X-4(LD) Tensolite

Concentric Twinax Contacts CABLE USAGE GUIDE



D38999 Series I, II, III & SJT Connectors

	Nominal Impedance (ohms)	
EPD32263A		77
EPD22189B		77
M17/176-000	002	77
GSC-12-254	8-00	77
GC875TM24	ŀΗ	77
GSC-12-810	95-00	77
	10602	77
	10606	77
Raychem	10612	77
	10613	77
	10614	77
23089/RC		77
05A0771		77
T10971		77
7724C8664		77
7726D0664		77
782OD0111	(20 AWG)	78
0024G0024		100
5M2022-003	100	
HS5930		100
S280W502-1		100
CXN2268		100

Concentric Twinax Contacts CABLE USAGE GUIDE ARINC 600 Rack & Panel Connectors



Nominal **Cable Type** Impedance . (ohms) S280W502-1 100


Differential Twinax Contacts CABLE USAGE GUIDE



ARINC 600 Rack & Panel Connectors

	Cable Type					
ABS0386WF	100					
ASNE0272T	100					
ASNE0272T	ASNE0272TK24					
Tensolite	100					

Triax Contacts CABLE USAGE GUIDE D38999 Series I, II, III & SJT Connectors





Use the Cable Usage Guides on this page for Coax Contacts as follows:

- 1. Locate the cable you are using in Cable Type column. For cables not listed consult Amphenol Aerospace.
- Refer to the Amphenol connector section which features contacts for this cable, as indicated by a in the appropriate column. If more than one connector series utilizes contacts designed for your cable, investigate each of them. Connector size, performance features and insert pattern availability may influence your choice.
- Order your connector and coax contact by following the procedure given in the section for the connector series
- selected. These instructions are supplemented by the Amphenol Catalog Section covering the basic connector.
 The Additional Contacts column of this guide is used to indicate an additional availability of contact designs for older cable types or capability. Consult Amphenol Aerospace for further information.

Coax Contacts CABLE USAGE GUIDE




CABLE US	AGE GUIDE								
Cable Type		Nominal Impedance (ohms)	For Circular (MIL-DTL-38999 type)	For Standard & Heavy Duty Circular (MIL-DTL-5015 type) (MIL-DTL-22992 type)	For Rectangular Connectors	Additional Contacts (Consult Amphenol)			
RG-5B/U	(M17/073-RG212)	50		(_ , , , . ,		•			
RG-6A/U	(M17/2-RG6)	75				•			
RG-7/U	/	97				•			
RG-9B/U	(M17/075-RG214)	50				•			
RG-11A/U	(M17/6-RG11)	75				•			
RG-12A/U	(M17/6-RG12)	75				•			
RG-13A/U	(74				•			
RG-21A/U		53				•			
RG-55B/U	(M17/084-RG223)	53		•	•				
RG-58C/U	(M17/028-RG058)	50		•	•				
RG-58	(M17/155-00001)	50	•						
RG-59B/U	(M17/29-RG59)	75		•					
RG-62A/U	(M17/030-RG062)	93		•					
RG-62B/U		93		•					
RG-63B/U	(M17/31-RG63)	125				•			
RG-71B/U	(M17/90-RG71)	93				•			
RG-87A/U		50				•			
RG-115/U		50							
RG-115A/U		50				•			
RG-116/U		50				•			
RG-122/U	(M17/054-RG122)	50			•	•			
RG-133A/U	(M17/100-RG133)	95			•	•			
RG-140/U	(M17/110-RG302)					•			
RG-140/0 RG-141A/U	(WIT7/TT0-RG302)	75 50		•					
RG-141A/U RG-142A/U		50			•				
RG-142A/U RG-142B/U	(1417/000 D0140)	50		•	•	•			
RG-142B/U RG-143A/U	(M17/060-RG142)	50	•	•	•	•			
						•			
RG-161/U		70	•	•					
RG-174A/U	(M17/119-RG174)	50	•	•					
RG-178B/U	(M17/093-RG178)	50	•	•					
RG-179B/U	(M17/094-RG179)	75	•	•					
RG-180B/U	(M17/095-RG180)	95	•	•	•	_			
RG-187A/U	(M17/094-RG179)	75	•	•					
RG-188A/U	(M17/113-RG316)	50	•	•					
RG-188 Doub		50							
RG-195A/U	(M17/095-RG180)	95	•	•	•				
RG-195 Doub		95							
RG-196A/U	(M17/169-00001)	50	•	•					
RG-210/U		93		•					
RG-212/U	(M17/073-RG212)	50		•		•			
RG-214/U	(M17/075-RG214)	50				•			
RG-216/U	(M17/77-RG216)	75				•			
RG-222/U		50				•			
RG-223/U	(M17/084-RG223)	50	•	•	•				
RG-225/U	(M17/86-RG225)	50				•			
RG-227/U		50				•			
RG-302/U	(M17/110-RG302)	75		•					

CHART CONTINUES ON NEXT PAGE NOTE: For information on coax contacts for Miniature circular connectors, MIL-DTL-26482 Series 1, see catalog 12-070 and consult Amphenol Industrial Operations. NOTE: MIL-DTL-38999 supersedes MIL-C-38999. MIL-DTL-5015 supersedes MIL-C-38999. MIL-DTL-22992 supersedes MIL-C-22992



Cable Usage Guide, cont.

Coax Contacts CABLE USAGE GUIDE, cont.



Cable Type		Nominal Impedance (ohms)	For Circular (MIL-DTL-38999 type)	For Standard & Heavy Duty Circular (MIL-DTL-5015 type) (MIL-DTL-22992 type)	For Rectangular Connectors	Additional Contacts (Consult Amphenol)	
RG-303/U	(M17/111-RG303)	50		•	•		
RG-304/U	(M17/112-RG304)	50				•	
RG-316/U	(M17/113-RG316)	50	•	•			
RD-316 Double Braid	(M17/152-00001)	50	•				
RG-400	(M17/128-RG400)	50	•				
M/A-COM 5M2	869-001	50	•		•		
5022A1311-D		50	•				
Beldon 9307		50	•				
FA-19X		50	•				
T-Flex-402		50	•				
T-Flex-405		50	•				
Filotex ET124962		50	•				
JN1088WT	(Triax)	50	•				
JN1088WU	(Triax)	75	•				
PAN6422XQ		50	•				
PAN6422XY		75	•				
PAN6595XM	(Triax)	75	•				
	51-04486		•				
Haveg	81-00207		•				
<u>^</u>	GWN1159A		•				
Gore	CXN3403		•				
Times	AA3248		•				
Teledyne	11299		•				
,	5021D1331-0	50	•				
	5021D1331-9	50	•				
	5022D1312-9	50	•				
_ .	7527A1318	75	•				
Raychem	9527A1314	95	•				
	9528A1318	95	•				
	9530A5314	95	•				
	9530D5314	95	•				
Thermatics	2929-29		•				
Tensolite	30850/87T-1		•				
Thermax	50C-25A-DS-1		•				
	ESC352001	50	•				
	ESC432101	50	•				

For Cable not found in the Coax Contact Cable Usage Guide, refer to these general dimensional ranges: (In general, for D38999 Connectors, the size 8, 12 and 16 Coax Contacts will terminate cable in the following ranges)

SIZE 16

.012 / .0215 Center Conductor (Stranded)
.031 / .066 Dielectric
.085 Max Outer braid (must be round for crimp termination)
.102 Max. Jacket

SIZE 8

.012 / .0395 Center Conductor (Stranded)
.055 / .133 Dielectric
.180 Max Outer braid (must be round for crimp termination)
.201 Max. Jacket

SIZE 12

.012/.021	5 Center Conductor (Stranded)
.031 / .105	Dielectric
.126 Max (Outer braid (must be round for crimp termination)
.145 Max.	Jacket

Special coax contacts may be available for cables outside of ranges shown. Consult Amphenol Aerospace for further assistance in selection of coax contact cables.

MIL-DTL-38999 Circular Connector

Overview

Amphenol® Connectors are ideally suited for the incorporation of shielded contacts for high performance interconnection applications. The circular family is built around MIL-DTL-38999 specifications, with Mil-approved and commercial styles offered. Normal operating voltage for circulars with power contacts only is up to 900 VAC (RMS) at sea level.

The MIL-DTL-38999 family offer these features for contact termination flexibility:

- Widest selection of insert arrangements that can incorporate:
 - Size 8 high speed Quadrax and Differential Twinax contacts for MIL-DTL-38999 Series III (specially modified to accommodate keyed contacts)
 - Transition adapters for use in attaching D38999 Series III connectors with high speed quadrax or differential contacts to PCB boards
 - Size 8, 12 and 16 Coax contacts
 - Size 8 and 12 Twinax contacts
 - Size 8, 10 & 12 Triax contacts
- Wide selection of connector shell styles and sizes
- Scoop-Proof recessed design in LJT-R, TV-R and SJT-R connectors provide protection for contacts
- Standard power contacts are crimp rear release, qualified to SAE AS39029
- Coax, Twinax, and Triax contacts employ the same retention system as power contacts, simplifying user substitution

GENERAL ORDERING INFORMATION

Amphenol MIL-DTL-38999, which feature rear removable contacts, are normally supplied with a full complement of power contacts, separately packaged. Coax, twinax and triax contacts are ordered by part number as referenced in the part number charts on the following pages of this catalog, and are substituted for the power contacts at the time of the cable or equipment assembly. If the application is for coax, twinax or triax contacts only, the connector may be ordered *less contacts* and no power contacts will be supplied.

HOW TO ORDER CONNECTORS AND HIGH FREQUENCY CONTACTS

 Select the Circular Series desired. (See features of each series given briefly on this page and in-depth in the other sections of this catalog, which are on-line at www.amphenol-aerospace.com). Series I - LJT-R Connectors Series II - JT-R Connectors Series III - TV-R Connectors SJT* - SJT-R Connectors

See Amphe-Lite (Industrial 38999 type) Catalog 12-094

- Select the quadrax, differential twinax, coax, twinax and/or triax contacts or the transition adapters that are needed from the tables on the following pages that correspond to the cable being used.
- Select the insert arrangement to accommodate required number of contacts. Insert patterns for quadrax and differential twinax contacts are on pages 395,396. Insert patterns for coax, twinax and triax contacts are on pages 404-406.
- Complete the connector part number from the connector series catalog, incorporating the chosen insert pattern number. See detailed how to order page 397 for ordering 38999, Series III with quadrax and differential twinax contacts. Consult Amphenol for assistance in ordering 38999 circulars with coax, twinax and triax contacts.
- Consult Amphenol Aerospace for ordering information for connectors with PC tail contacts, and for transition adapters.
- If connector is ordered less contacts, power contacts and/or sealing plugs may be ordered separately to fill out the insert arrangement.



JT-R, D38999 Series II

See 38999 section Series II, JT for complete information on this series.

- Shorter profile connector series for applications requiring maximum
- space savings
- Bayonet coupling, crimp termination
 Also available in solder termination types under MIL-DTL-27599 Series II



TV-R, Tri-Start, D38999 Series III

- High performance capability series for both general duty and severe environment applications
- Offers the widest range of Subminiature Family Mil-Spec qualified options in contact and connector styles
- Threaded coupling; completely mates in one turn; crimp termination
- Superior EMI/EMP shielding effectiveness
- Scoop-proof design (recessed pins)
- Available in aluminum, stainless steel and firewall, or lightweight composite styles See 38999 section Series III for complete information on this section.



LJT-R, D38999 Series I

See 38999 section Series I, LJT for complete information on this series.

- Scoop-proof (recessed pins)
- Bayonet coupling, crimp termination
- Also available in solder termination types under MIL-DTL-27599 Series II



Amphe-Lite, 38999 Type

See Catalog 12-094 for complete information on this series.

- Commercial/Industrial
 28000 Series III type
- 38999 Series III type • Cost effective high performance connector for severe environments or
- general duty industrial applications • Consult Amphenol Industrial
- Operations for further information 12-094 catalog is on-line at www. amphenol-industrial.com.

NOTE: SAE AS39029 supersedes MIL-C-39029. NOTE: MIL-DTL-38999 supersedes MIL-C-38999. MIL-DTL-27599 supersedes MIL-C-27599



SJT-R, 38999 Type

- See the SJT section of this catalog.
- Amphenol proprietary series (non-MS) which is a further
- expansion of the basic JT family, but incorporates the LJT scoop-proof design
- Compliant with several European specifications






Quadrax Contacts, MIL-DTL-38999, Series III General Description

Amphenol[®] Quadrax Contacts -offer several advantages

for high data transfer rates, low power consumption and excellent EMI compatibility:

- Four strategically spaced inner contacts form two 100 or 150 Ohm matched impedance differential pairs
- · Outer contact has rugged wall section for durability
- Available in size 8 crimp termination style
- Also available in size 8 with PC tails (see page 379)
- Requires modification of MIL-DTL-38999 connector to accommodate keyed contacts



(4) CENTER CONDUCTORS INSULATION

Cable Illustration - Quadrax Contact



Quadrax Pin with 8P8C "RJ45" Jack



has pin outer contact with a pin

inner contact

Quadrax Pin Size 8 and MIL-DTL-38999 Series III Connector




Quadrax in an Eight Wire Gigabit Ethernet Assembly

Suggested Strain Relief - Insert Arrangements 9-5 or 19-18 with Quadrax Contacts

Due to the piggyback grommet interference with normal strain reliefs on the shell size 9 only, the recommended strain relief for the connector is: Amphenol part number TGW-R-5309-10 (OD Cad) or TGF-

R-5309-10 (Electroless nickel) - shell size 9 only. For 19-18 insert pattern, recommended backshell: Glenair 367-221-NF. This is recommended due to the proximity of the size 8 contacts in relation to the shell.



Also see Quadrax contacts for ARINC 600 and R27 Rack and Panel Connectors on page 419 and 420.


Quadrax Contacts are gold plated, crimp termination

Finish of mating contacts parts: supplied with 0.000050 min. gold over nickel on mating parts. Consult Amphenol for availability of other finishes.

Quadrax Size 8 Contact Performance:

- Bandwidth: Up to 3 Gigahertz
- Data Rate: Exceeding 3 Gbits/sec.
- Voltage Rating: 500 Vrms max. @ sea level
- Dielectric Withstanding Voltage: 1000 VAC rms between all inner contacts
 @ sea level, 500 VAC rms between inner and outer contacts
 @ sea level

Suggested Numbering for Quadrax



Differential Pairs, contacts 1-3, 2-4.

See page 397 for part number ordering of popularly used 38999 Series III connectors with 100 ohm quadrax contacts.

Quadrax differential pairs are 1 and 3, 2 and 4.

Quadrax Contacts for MIL-DTL-38999

Series III, Application Data

TV-R Series, MIL-DTL-38999 Series III* Connectors

QUADRAX CONTACTS FOR USE IN TV-R CONNECTORS									
Cable		art Number	Impedance (Ohms)	Inner Conductor (AWG)	Contact Size	Electrical Protocol††	Crimpi	Crimping Tools	
	Pin Socket			(AWG)			Inner Contact	Outer Contact	
Draka Fileca F-4703-3, F4704-4, Filotex ET 2PC236, Filotex ET2PF870, PIC Wire E50424 ABS0972, Tensolite 23450/04090X-4(LD) Draka Fileca F-4704-5, ABS1503 KD 24	21-033384-021 (L-2119-A)	21-033385-021 (L-2119-A)		24		Ethernet, 1000 Base-T Gigabit Ethernet			
Tensolite NF24Q100, NF24Q100-01, 24443/9P025X-4(LD), S280W502-4, 24443/03130X-4(LD), 24443/020714X-4(LD), 24443/020714X-4(LD), NF24-2Q100, TYCO CEC- RWC-18664, GORE GSC-01-81869- 01, 24443/03166X-4(LD), Thermax T956-4T200, Pic Wire E51424, Thermax MX100Q-24, NF24Q100-01-200C (Space)	21-033384-051 (L-2119-D)	21-033385-051 (L-2119-D)		24		Ethernet, 1000 Base-T Gigabit Ethernet			
Tensolite NF22Q100, NF22Q100-01, Thermax 956-5, GORE RCN 7688	21-033384-061 (L-2119-H)	21-033385-061 (L-2119-H)	-	22		Ethernet (100 Mbps), 1000 Base-T Gigabit Ethernet (1 Gbps)			
Tensolite NF26Q100, NF26Q100-01, NF26-2Q100, PIC E51426	21-033384-071 (L-2119-AB)	21-033385-071 (L-2119-AB)	100	26		Ethernet (100 Mbps), 1000 Base-T Gigabit Ethernet (1 Gbps)			
S280W502-4/BMS13- 72T03C04G024	21-033384-141 (BACC47GM1)	21-033385-141 (BACC45GN1)		24					
Draka Fileca F-4704-6, Gore RCN 8672	21-033384-151 (L-2119-AW)	21-033385-151 (L-2119-AW)		26		Ethernet (100 Mbps), 1000 Base-T Gigabit Ethernet (1 Gbps)	M22520/2-01 with Positioner	M22520/5-01	
Tensolite NF24Q100-01 (same as 21-03338() -51, uses EMI Piggyback)	21-033384-161 (L-2119-BE)	21-033385-161 (L-2119-BE)		24	8	Ethernet (100 Mbps), 1000 Base-T Gigabit Ethernet (1 Gbps)	M22520/2-37 or with Daniels	with Die Set M22520/5-45 (Location A)	
Gore RCN8513, JSFY18-3	21-033384-171 (L-2119-BN)	21-033385-171 (L-2119-BN)		22		Ethernet (100 Mbps), 1000 Base-T Gigabit Ethernet (1 Gbps)	Positioner K709		
Tensolite NF22Q100 Special Box pattern, only mates with 21-0333 ()-181	21-033384-181 (L-2119-BP)	21-033384-181 (L-2119-BP)		22		Ethernet (100 Mbps), 1000 Base-T Gigabit Ethernet (1 Gbps)			
Tensolite NF24Q100, NF24Q100-01 for 2.5 Gbps applications	21-033384-191 (L-2119-BS)	21-033385-191 (L-2119-BS)		24		•Serial FPDP Applications (2.5 Gbps) (Typical app run at 150 Ohms) • HDMI 1.3			
USB2 (28433/02171LX-4)	21-033384-101†	21-033385-101†	90			USB2.0 (480 Mbps)			
Tensolite 24450/03089X-4(LD) Gore RCN8647	21-033384-211	21-033385-211		24		IEEE 1394B Firewire			
JSFY02-1, JSFY18	21-033384-221	21-033385-221		24		IEEE 1394B Firewire			
Gore RCN8487, JSFY18	21-033384-231	21-033385-231	110	24		IEEE 1394B Firewire			
Tensolite 24450/03089X-4(LD) Same as 21-03338()-211 but Box pattern, mates with 21-03338()-241 only	21-033384-241†	21-033385-241†		24		IEEE 1394B Firewire			
F-4703, ABS1503KD24	21-033384-281	21-033385-281	100			Meets EN3155-074			
Tensolite 26473/02006X-4(LD)/Gore RCN8328 (not for new designs, use 21-033450/1 series)	21-033384-31 (L-2119-B)	21-033385-031 (L-2119-B)	150	26					
CHART CONTINUES ON NEXT PAGE Daniels crimping tools available from Daniels Mfg. Corp. 6103 Anno Ave.,									

CHART CONTINUES ON NEXT PAGE QUADRAX CONTACT DATA

Contacts are inserted by hand. Refer to termination instructions listed. Contacts are removed with a removal tool. Recommended tool is MIL-I-81969/14-06, Daniels DRK-264-8. Refer to termination instructions listed. Finish of mating contact parts: Contact part numbers shown in the chart above are supplied gold plated per ASTM B488 Type II, Code C, 000050 † Consult Amphenol for current release of this contact or instruction sheet min. thick over nickel plate per AMS-QQ-N-290, Class 2, .000030/.000150 thick.

Daniels crimping tools available from Daniels Mfg. Corp. 6103 Anno Ave., Orlando, FL 32809

Amphenol Aerospace

Requires modified connector to accommodate keyed contacts.

Termination instructions are packaged with each contact and can be

found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp if applicable.

tt Test reports available for indicated protocols. Consult Amphenol Aerospace Typical applications run at 150 Ohms



21-033398-491 21-033397-491 100 Ohm

21-033398-501 21-033397-501 100 Ohm

21-033398-521 21-033397-521

21-033398-531 21-033397-531

21-033398-541 21-033397-541

21-033398-551 21-033397-551

21-033398-561 21-033397-561

21-033398-511 21-033397-511 100/150 Ohm

Quadrax Contacts, MIL-DTL-38999, Series III

Application Data

TV-R Series MIL-DTL-38999 Series III* Connectors

IV-R Series, MIL-DIL-38999 Series III" Connectors								
QUADRAX CONTACTS FOR USE IN TV-R CONNECTORS								
Cable	Contact Part Number (Termination Instruction Sheet)**		Impedance (Ohms)	Inner Conductor (AWG)	Contact Size	Electrical Protocol++	Crimping Tools	
	Pin	Socket		(And)			Inner Contact	Outer Contact
Tensolite 26473/02006X-4(LD) Same as 21-033384/5-31 but box pattern (not for new designs, use 21-033450/1 series) Gore RCN8328	21-033384-201†	21-033385-201†		26				
Gore RCN7625	21-033384-271	21-033385-271					M22520/2-01 with Positioner	M22520/5-01 with Die Set
Tensolite 26473/02006X-4(LD), Gore RCN8328	21-033450-001 (L-2119-BW)	21-033451-001 (L-2119-BW)	150	26	8	Fibre-Channel (1 GBPS, 2 GBPS, 1G/2G), 1000 Base-CX (1.25 GBPS), SCSI-2 (3.2 GBPS)	M22520/2-37 or with Daniels Positioner K709	M22520/5-45
Tensolite 26473/02006X-4(LD), Gore RCN8328 (same as 21-033450/1-1 except box pattern. Mates with 21-033450/1-11 only.	21-033450-011†	21-033451-011†		26		Fibre-Channel (1 GBPS, 2 GBPS, 1G/2G), 1000 Base-CX (1.25 GBPS), SCSI-2 (3.2 GBPS)		

Contact Pa	art Number	Impedance	L Dim	Pretinned	Contact Pa	art Number	Imped		L Dim	Pretinned
Pin	Socket	(Ohms)		Treamed	Pin	Socket	(Öhr	ns)		Treatmen
21-033398-021	21-033397-021	100 Ohm	1.035	X	21-033398-581	21-033397-581	100 C	Dhm	0.721	
21-033398-031	21-033397-031	100 Ohm	0.866		21-033398-591	21-033397-591	100/150) Ohm	0.939	
21-033398-061	21-033397-061	150 Ohm	1.035			21-033397-601	100 C	Dhm	0.939	
21-033398-071	21-033397-071	150 Ohm	0.494	X	21-033398-611	21-033397-611	100 C	Dhm	1.366	
21-033398-081	21-033397-081	150 Ohm	0.780	X	21-033452-011	21-033453-011	150 C		1.035 (mates to 21-033450/51 series)	
21-033398-091	21-033397-091	100 Ohm	0.840	X	21-033452-021		150 C		0.815 (mates to 21-033450/51 series)	
21-033398-111	21-033397-111	100 Ohm	0.708	1	21-033452-031		150 C		0.815 (mates to 21-033450/51 series)	X
21-033398-121	21-033397-121	100 Ohm	0.859			21-033453-041	150 C		0.866 (mates to 21-033450/51 series)	
21-033398-131	21-033397-131	150 Ohm	0.780	X		21-033453-051	150 C		0.494 (mates to 21-033450/51 series)	
21-033398-141	21-033397-141	100 Ohm	0.615		21-033452-061	21-033453-061	150 C	Dhm	0.582 (mates to 21-033450/51 series)	
21-033398-151	21-033397-151	150 Ohm	0.815		21-033452-071	21-033453-071	150 C	Dhm	0.939 (mates to 21-033450/51 series)	
21-033398-191	21-033397-191	100 Ohm	0.605	1						
21-033398-211	21-033397-211	150 Ohm	0.815	X	Daniels crimnir	ng tools are ava	ailahle			
21-033398-221	21-033397-221	100 Ohm	0.775	1		Ifg. Corp. 6103			SEALING PLUGS	
21-033398-231	21-033397-231	100 Ohm	0.494		Ave., Orlando,				Sealing Plugs	
21-033398-241	21-033397-241	100 Ohm	0.741		* Requires m accommod	nodified connec	tor to	for u	Ise with D38999 Connectors	Part Numbe
21-033398-251	21-033397-251	100 Ohm	0.788		keyed conta			u	ising Quadrax Contacts -	Part Numbe
21-033398-271	21-033397-271	100 Ohm	0.741			n instructions a	re		Size 8 Cavities	
21-033398-281	21-033397-281	100 Ohm	0.806			with each conta			***Standard Plastic	T3-4008-59P
21-033398-291		100 Ohm	1.035		can be four amphenol-a	nd on-line at: w	NW.	Stan	dard Plastic to be used with PCB tails	T3-4008-59P1
21-033398-301	21-033397-301	100 Ohm	0.836			einstructions.as	D		(shorter tail length)	13-4006-59P1
21-033398-311	21-033397-311	100 Ohm	0.940		† Consult Arr	nphenol Aerosp	ace for	***M	etal sealing plug - can be used when	21-033899-8Q
21-033398-341	21-033397-341	100 Ohm	0.901			ease of this con		m	ating with contacts on mating half	21-033099-00
21-033398-351	21-033397-351	100 Ohm	0.871		thest reports	sheet if applica	ble.	Met	al sealing plug used with PCB's and	21-033899-8Q2
21-033398-361	21-033397-361	100 Ohm	0.939		indicated p				mating contact on mating half	21-032099-007
21-033398-371	21-033397-371	100 Ohm	0.672		Consult Arr	nphenol Aerosp				
21-033398-381	21-033397-381	100 Ohm	0.914			ed with 21-033	321-005			
21-033398-391	21-033397-391	100 Ohm	0.360		piggyback (grommet seal.			PIGGYBACK GROMME	ET
21-033398-401	21-033397-401	100 Ohm	1.009					G	rommet for use with D38999	
21-033398-411	21-033397-411	150 Ohm	0.866						Connectors	Part Numb
21-033398-421	21-033397-421	100 Ohm	1.169						using Quadrax Contacts	
21-033398-431	21-033397-431	100 Ohm	0.819						Metallized piggyback grommet	21-033321-02
21-033398-451	21-033397-451	150 Ohm	0.494							
21-033398-461	21-033397-461	100 Ohm	0.761							
21-033398-471	21-033397-471	100 Ohm	0.889							
21-033398-481	21-033397-481	100 Ohm	0.971					Indic	ated length given in chart at left is	the distance

Indicated length given in chart at left is the distance from the rear of the contact retention shoulder to the tip of the PCB tails.

_	L DIM. LENGTH INDICATED IN TABLE COLUMN	-

Note: it does not indicate stickout length when installed in D38999 connector.

X

0.418

0.875

0.699

0.582

0.666

0.946

0.788

0.815

100 Ohm

100 Ohm

100 Ohm

100 Ohm

100 Ohm

New "Split-Pair" Quadrax Contacts & Cables

Assemblies for MIL-DTL-38999, Series III



for use with CAT6A Type Cable

Amphenol Aerospace offers the high performance interconnect solution for CAT6A type cable.

FEATURES & BENEFITS:

- Overall higher bandwidth than standard CAT5E quadrax
- Enhanced crosstalk performance (compared to standard quadrax) due to compatibility with shielded twisted pair of cables
- Can be used for a variety of high speed applications beyond current quadrax design**
- Four strategically spaced inner contacts form two 100 Ohm matched impedance differential pairs
- · Outer contact has rugged wall section for durability
- Available in size 8 crimp termination style
- Also available in size 8 PC tails
- · Can be installed into existing quadrax contact connector cavities
- Requires modification of MIL-DTL-38999 connector to accommodate keyed contacts



MIL-DTL-38999 Series III Connectors with "Split-Pair" Quadrax Contacts for use with CAT6A Type Cable




"Split-Pair" Quadrax Contacts for use with CAT6A Type Cable

APPLICATIONS:

For use with, but not limited to, the following electrical protocols :

- 10/100/1000/10GBASE-T Ethernet
- DVI
- USB 2.0
- Serial RapidIO (up to 3.125 Gbps)
- PCI-Express 2.0
- HDMI 1.3a
- SATA 2.0 (up to 3 GHz)

Suggested Numbering for Quadrax Contacts



Differential Pairs: 1 & 4, 2 & 3

SPLIT-PAIR QUADRAX CONTACT*

Crimp Style Part Number	Cable	AWG	
PIN 21-033470-001	Thermax	24	
SOCKET 21-033471-001	1536-224	24	
PIN 21-033470-021	Thermax	26	
SOCKET 21-033471-021	1536-195	20	


CRIMP TOOLS:

Outer Contact	Inner Contact
DANIELS M22520/5-01 with die set Y1999 or M22520/5-45	DANIELS M22520/2-01 with positioner K1777

Daniels crimping tools are available from Daniels Mfg. Corp. 6103 Anno Ave., Orlando, FL 32809

REMOVAL TOOL: M81969/14-12

* Patent pending.





PCB QUADRAX PIN

PCB Pin Part Numbers	Impedance	Length ±.015
21-033466-011		1.035
21-033466-021	100 Ohm	.815
21-033466-031*	100 Ohm	.815
21-033466-041	100 Onm	.866
21-033466-051		.494
21-033466-061		.582
21-033466-071		.815
21-033466-081		.840

PCB QUADRAX SOCKET

PCB Socket Part Numbers	Impedance	Length ±.015
21-033467-011		1.035
21-033467-021	-	.815
21-033467-031*	100 Ohm	.815
21-033467-041	100 Onm	.866
21-033467-051	-	.494
21-033467-061	100 Ohm	.582
21-033467-071		.815
21-033467-081		.840

*Pretinned

Indicated length given in charts above is the distance from the rear of the contact retention shoulder to the tip of the PCB tails.

Note: it does not indicate stickout length when installed in D38999 connector.

-	LENGTH INDICATED IN TABLE COLUMN

TRANSITION ADAPTERS FOR LAUNCHING SIGNALS TO PC BOARDS

100 OHM QUADRAX TRANSITION ADAPTERS FOR LAUNCHING CONTROLLED IMPEDANCE SIGNALS TO PC BOARDS								
Quadrax Type Adapter/		Illustration of Adapter	Part N	Impedance	Mating Thread			
Cable or PCB Tail Length			Plug	Receptacle	(Ohms)	Size		
Quadrax Plug Adapter/ Thermax 1536-224	receptacles		21-033468-011					
PCB Quadrax Receptacle 90 Degree Adapter/ Tail Length .110	plugs and rec			21-033469-001				
PCB Quadrax Receptacle Straight Adapter/ Tail Length .110	Mating pl			21-033469-011	100	.375		
Quadrax Receptacle 90 degree Adapter with cable to board/ Thermax 1536-224	to board			21-033469-021				
Quadrax Receptacle Straight Adapter with cable to board/ .195 tail length Thermax 1536-224	Wired to			21-033469-031				



For use with the following, but not limited to, electrical protocols: 10/100/1000/10GBASE-T Ethernet


- DVI
- USB 2.0
- Serial RapidIO (up to 3.125 Gbps)
- PCI-Express 2.0
- HDMI 1.3a
- SATA 2.0 (up to 3 GHz)


FREQUENCIES OF INTEREST

Frequency (GHz)	Insertion Loss (dB)	Return Loss (dB)	NEXT (dB)	FEXT (dB)
0.1	0.09	35.68	62.36	59.29
0.24	0.22	36.44	42.87	62.25
0.5	0.45	43.66	43.63	55.22
0.625	0.57	43.49	53.68	43.53
1	0.98	17.82	49.26	48.33
1.25	1.29	15.1	43.57	44.12
1.5	1.47	17.94	46.02	40.78
1.7	1.86	12.23	48.01	47.23
2	2.11	12.9	37.45	38.12
2.5	2.42	15.97	29.9	31.52
3	2.86	16.52	35.94	29.36


PERFORMANCE DATA

The following graphs on this page and the next page provide performance data on Amphenol® 10GBASE signal integrity (SI) quadrax contacts. Testing was done with 2 mated contacts terminated on both ends of 1 meter Thermax cable.









Differential Twinax Contacts, MIL-DTL-38999


Series III, General Description



Amphenol® Differential Twinax Contacts -

Offer several advantages for high data transfer rates, low power consumption and excellent EMI compatibility:


- Two strategically spaced inner contacts form two 100 or 150 Ohm matched impedance differential pairs
- · Outer contact has rugged wall section for durability
- Available in size 8 crimp termination style
- Also available in size 8 with PC tails (see page 386)
- Requires modification of MIL-DTL-38999 connector to accommodate keyed contacts



Cable Illustration - Differential Twinax Contact



Differential Twinax Socket Contact



Differential Twinax Pin Contact

TYPICAL DIFFERENTIAL TWINAX SOCKET CONTACT has socket outer contact with a socket inner contact


> TYPICAL DIFFERENTIAL TWINAX PIN CONTACT has pin outer contact with a pin inner contact

Differential Twinax Contacts are Gold plated, Crimp Termination

Finish of mating contacts parts: supplied with 0.000050 min. gold over nickel on mating parts. Consult Amphenol for availability of other finishes.

Differential Twinax Size 8 Contact Performance:

- Bandwidth: Up to 3 Gigahertz
- Data Rate: Exceeding 3 Gbits/sec.
- Voltage Rating: 500 Vrms max. @ sea level
- Dielectric Withstanding Voltage: 1000 VAC rms between all inner contacts @ sea level 500 VAC rms between inner and outer contacts @ sea level



TV-R Series, MIL-DTL-38999 Series III* Connectors

DIFFERENTIAL TWINAX CONTACTS FOR USE IN TV-R CONNECTORS									
Cable	Contact Part Number (Termination Instruction Sheet)**		Impedance (Ohms)	Contact Size	Electrical Protocol+†	Crimping Tools			
	Pin	Socket				Inner Contact	Outer Contact		
Tensolite 24463/05099X-8(LD), Thermax MX 100-24, Tensolite 24463/9P025X-2(LD), Thermax 12814, ST5M1284-003 (98 Ohm), 26463/70460X- 2 (98 Ohm), PIC E10224, Fileca 2709-3, NF24T100-200C (Space), S280W502-1	21-033387-021 (L-2119-E)	21-033388-021 (L-2119-E)							
GORE GSC-05-827300-00 Tensolite 26453/03184X-2(LD) Thermax 956-626Z	21-033387-051*** (L-2119-AY)	21-033388-051*** (L-2119-AY)					M22520/5-01 with Die Set M22520/5-45 (Location A)		
Tensolite 26453/03184X-2(LD), Thermax 956-626Z, GORE GSC-05-827300-00 ASNE08072003-09	21-033387-041 (L-2119-T)	21-033388-041 (L-2119-T)	100		Ethernet, USB				
23460/05114X-2(LD), PIC E1024	21-033387-061 (L-2119-BH)	21-033388-061 (L-2119-BH)							
Raychem 0026A0024, M17/176-00002 (77 Ohm)	21-033387-071 (L-2119-BJ)	21-033388-071 (L-2119-BJ)		8					
JSFY11-24, Tensolite 24463/03220T-2(LD), Thermax 956-1T200	21-033387-091 (L-2119-BT)	21-033388-091 (L-2119-BT)							
S280W502-6, Tensolite 24463/9P026X-2(LD)	21-033387-101 (L-2119-AK)	21-033388-101 (L-2119-AK)							
AXON P509782	21-033387-131	21-033388-131	100						
Tensolite 26453/03184X-2(LD)	21-033387-151	21-033388-151	100						
Tensolite 26483/03071X-2(LD)	21-033387-031 (L-2119-AC)	21-033388-031 (L-2119-AC)	150						
Tensolite 26483/03071X-2(LD)	21-033456-001 (L-2119-BX)†	21-033457-001 (L-2119-BX)†			Fibre Channel, 1000 Base-CX Ethernet				

PCB DIFFERENTIAL TWINAX CONTACTS FOR USE IN TV-R CONNECTORS

PCB Quadrax	Contact P	art Number	Impedance	Contact
Contacts	Pin	Socket	(Ohms)	Size
PCB (1.035 Length)	21-033834-001	21-033835-001		
PCB (.788 Length)	21-033834-031	21-033835-031]	
PCB (.494 Length)	21-033834-041	21-033835-041		
PCB (.939 Length)	21-033834-051	21-033835-051		
PCB (.780 Length)	21-033834-061	21-033835-061		
PCB (.871 Length)	21-033834-071	21-033835-071		8
PCB (.937 Length)	21-033834-081	21-033835-081	100	
PCB (1.035 Length)	21-033834-091	21-033835-091		
PCB (.843 Length)	21-033834-101	21-033835-101		
PCB (.806 Length)	21-033834-111	21-033835-111		
PCB (.908 Length)	21-033834-121	21-033835-121		
PCB (.530 Length)	21-033834-131	21-033835-131		
PCB (.819 Length)	21-033834-141	21-033835-141		
PCB (1.035 Length)	21-033834-021	21-033835-021		
PCB (1.035 Length) mates to 210-33456/57 series	21-033458-001	21-033457-001	150	

DIFFERENTIAL TWINAX CONTACT DATA

Contacts are inserted by hand. Refer to termination instructions listed. Contacts are removed with a removal tool. Recommended tool is MIL-I-81969/14-06, Daniels DRK-264-8. Refer to termination instructions listed.


Finish of mating contact parts: Contact part numbers shown in the chart above are supplied gold plated per ASTM B488 Type II, Code C, .000050 min. thick over nickel plate per AMS-QQ-N-290, Class 2, .000030/.000150 thick.

Daniels crimping tools are available from Daniels Mfg. Corp. 6103 Anno Ave., Orlando, FL 32809

 Requires modified connector to accommodate keyed contacts.

- *** Indicated contact is vacuum degassed
- †† Test reports available for indicated protocols. Consult Amphenol Aerospace.
- **Termination instructions are packaged with each contact and can be found on-line at:
- www.amphenol-aerospace.com/serviceinstructions.asp † Consult Amphenol Aerospace for current release of this instruction sheet

Indicated length given in chart at left is the distance
from the rear of the contact retention shoulder to the
tip of the PCB tails.



Note: it does not indicate stickout length when installed in D38999 connector.

Compliant Quadrax Contacts and PC Tail

Quadrax Contacts for Attachment to PC Boards

General Description

Amphenol® Quadrax Contacts for Printed

Circuit Board Attachment- Available for MIL-DTL-38999 Series III Circular connectors with straight PC tail termination and with compliant pin termination. These provide the ideal solution for bringing high speed data transmission to the board.



Compliant Pin Quadrax and PC Tail Quadrax Contacts



MIL-DTL-38999, SERIES III CONNECTOR WITH PC TAIL CONTACTS. This arrangement has 33 size 22D and 2 Quadrax PC tail contacts.

Amphenol Aerospace


MIL-DTL-38999, SERIES III CONNECTOR WITH PC TAIL CONTACTS. This arrangement has 8 Quadrax PC tail contacts.



Amphenol[®] Quadrax Contacts for Rectangular Board Level


Connectors - Incorporate the same size 8 Quadrax PCB contacts as used in circular 38999 connectors.

- Size 8 Quadrax Compliant contacts with hole diameters: .025 ±.002 PTH Quadrax contact
 .040 ±.003 PTH shell grounding Accommodates backplane .125 inch min. thickness
- · Consult Amphenol Aerospace for availability of additional connector configurations





Compliant Pin Quadrax Board Level Connector



Quadrax Transition Adapters and Differential Twinax Transition Adapters

General Description

Amphenol[®] Transition Adapters - Are used to facilitate launching of controlled impedance signals to printed circuit boards. Amphenol provides transition adapters in both contact types:


• Quadrax transition adapters, 90° or straight receptacles threaded or cable to board style

Amphenol Aerospace

• Differential twinax transition adapters, 90° or straight receptacles, threaded or cable to board style



90° Quadrax Receptacle and Plug Transition Adapter






90° Differential Twinax Receptacle and Plug Transition Adapter

TRANSITION ADAPTER DATA

Finish of mating contact parts: Contacts are supplied gold plated per ASTM B488 Type II, Code C, .000050 min. thick over nickel plate per AMS-QQ-N-290, Class 2, .000030/.000150 thick.



ELECTRICAL PROTOCOLS FOR

	QUADRAX TRANSI	TION ADAPT	ERS	
Pa	art Number	Impedance	Electrical	
Plug	Receptacle	(Ohms)	Protocol++	
21-033836-031			Ethernet, gigabit Ethe	
21-033836-041			Ethernet, gigabit Ethe	
21-033836-051			Ethernet, gigabit Ethe	
21-033836-061			Ethernet, gigabit Ethe	
	21-033837-081 (90 degree)			
	21-033837-091 (90 degree)	100		
	21-033837-041 (90 degree)			
	21-033837-051 (straight)		Ethernet, gigabit Ethe	
	21-033837-061 (90 degree)			
	21-033837-141 (90 degree)			
21-033837-101				
21-033836-021			1000 Base CX, Fibre channel	
	21-033837-021 (90 degree)		1000 Base CX,	
	21-033837-211 (jam nut)	150	Fibre channel	
	21-033837-031 (straight)			
	21-033837-071 (90 degree)			
21-033837-111				

ELECTRICAL PROTOCOLS FOR DIFFERENTIAL TWINAX TRANSITION ADAPTERS

P	art Number	Impedance	Electrical
Plug	Receptacle	(Ohms)	Protocol ^{††}
21-033832-81			
21-033832-21			Ethernet
	21-033833-021 (90 degree)		
	21-033833-031 (90 degree)		Ethernet
	21-033833-151 (90 degree)		
21-033832-111†		100	
	21-033833-161† (90 degree)		
	21-033833-171† (90 degree)		
	21-033833-091 (90 degree)		
	21-033833-051 (90 degree)		
	21-033833-141 (90 degree)		
21-033832-91			
	21-033833-111 (90 degree)	150	
	21-033833-181† (90 degree)	150	
	21-033833-101 (90 degree)		

† Consult Amphenol Aerospace for current release of this adapter. ††Test reports available for indicated protocols; consult Amphenol Aerospace.

24 Contact Amphenol Aerospace for more information at 800-678-0141 • www.amphenol-aerospace.com

Quadrax Transition Adapters

for Attachment to PC Boards

Application Data

100 OHM QUADRAX TRANSITION ADAPTERS FOR LAUNCHING CONTROLLED IMPEDANCE SIGNALS TO PC BOARDS																	
Quadrax Type Adapter/			Part Number (Termination Instruction Sheet)**		Impedance	Mating	Crimping Tools										
Cable or PCB Tail Length		Illustration of Adapter	Plug	Receptacle	(Ohms)	Thread Size	Inner Contact	Outer Contact									
Quadrax Plug Adapter/ Tensolite NF24Q100, NF24Q100-01 24443/9P025X-4(LD) S280W502-4 24443/03130X-4(LD) Thermax 956-4TN			21-033836-031 (L-2119-U)	neceptacie			inner oontact	Outer Contact									
Quadrax Plug Adapter/ Tensolite NF22Q100, NF22Q100-01, Thermax 956-5, Tensolite 24450/030894-4(LD) Draka Fileca F-4704-5			21-033836-041 (L-2119-W)†														
Quadrax Plug Adapter/ Draka Fileca F-4703-3, F-4704-4			21-033836-051 (L-2119-Y)														
Quadrax Plug Adapter/ NF26Q100			21-033836-061 (L-2119-AM)†				M22520/2-01										
Gore RCN8724 (30 awg)			21-033836-071		_		with Positioner M22520/2-37	M22520/5-01 with Die Set									
Gore ACN1042 (28 awg) Gore RCN8973	acles		21-033836-101				or with Daniels Positioner	M22520/5-45 (Location A)									
Quadrax Plug Adapter/ Hexnut with Lock Wire Holes Tensolite NF24Q100-01	and receptacles		21-033836-081				K709	()									
Quadrax Receptacle Straight Adapter in-line jam nut (threaded)/ GSC-10-8273900	plugs and			21-033837-081 (L-2119-AR)†	100	.375											
Quadrax Receptacle Straight Adapter in-line jam nut (threaded) Tensolite NF24Q100-01	Mating p			21-033837-261													
Quadrax Receptacle Straight Adapter in-line (threaded)/NF24Q100 Tensolite NF24Q100-01, Tensolite 24443/9P025X -4 (LD), S280W502-4, Tensolite 24443/03130X-4 (LD), Thermax 956-4TN		·			~	2				2			21-033837-091 (L-2119-BL)				
PCB Quadrax Receptacle 90 Degree Adapter/Tail Length .110						21-033837-041											
PCB Quadrax Receptacle 90 Degree Adapter/Tail Length .200				21-033837-201	-												
PCB Quadrax Receptacle Straight Adapter/Tail Length .110				21-033837-051]		NA	NA									
PCB Quadrax Receptacle Straight Adapter/Special Tail Length (.200)				21-033837-061													
Straight adapter Tail Length .175		ערעענעל		21-033837-131													
Quadrax Receptacle 90 degree Adapter with cable to board/ NF24Q100 Tail Length .110				21-033837-141 (L-2119-BB)†													
Quadrax Receptacle 90 degree Adapter with cable to board/ ABS1503KD24 Tail Length .110 Tensolite NF22Q100-01 Thermax 956-5 Draka Fileca F4704-5	Wired to board			21-033837-231	100		M22520/2-01 with Positioner M22520/2-37 or with	M22520/5-01 with Die Set									
Quadrax Receptacle Straight Adapter with cable to board/ NF24Q100, NF24Q100-01 Tail Length .195				21-033837-101 (L-2119-AN)			Daniels Positioner K709	M22520/5-45 (Location A)									
Quadrax receptacle straight adapter w/ cable to board, Tail length .195 Draka Fileca F-4703-3, F-4703-4				21-033837-241													

Daniels crimping tools are available from Daniels Mfg. Corp. 6103 Anno Ave., Orlando, FL $\,$ 32809

Termination instructions are packaged with each contact and can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp

Amphenol Aerospace

† Consult Amphenol Aerospace for current release of this adapter and

instruction sheet if applicable.

See electrical protocols for transition adapters on page 388.



Quadrax Transition Adapters For Attachment to PC Boards

Application Data

150 OHM QUADRAX TRANSITION ADAPTERS FOR LAUNCHING CONTROLLED IMPEDANCE SIGNALS TO PC BOARDS								
Quadrax Type Adapter/		Illustration of Adapter	Part Number (Termination Instruction Sheet)**		Impedance (Ohms)	Mating Thread	Crimpir	ng Tools
Cable or PCB Tail Length			Plug	Receptacle	(Onins)	Size	Inner Contact	Outer Contact
Quadrax Plug Adapter/ Tensolite 26473/02006X-4(LD), Gore RCN8328	cles		21-033836-021 (L-2119-S)				M22520/2-01 with Positioner M22520/2-34	
PCB Quadrax Receptacle 90 Degree Adapter/Tail Length .110	g plugs and receptacles			21-033837-021	450	075		
PCB Receptacle 90 Degree Adapter/ Tail Length .200		e tutt		21-033837-251	150	.375	NA	NA
PCB Quadrax Receptacle Straight Adapter/Tail Length .110	Mating			21-033837-031				
Quadrax Receptacle Straight Adapter in-line Jam Nut (threaded) Tensolite 26473/02006X-4 (LD), Gore RCN8328				21-033837-211 (L-2119-BY)				
Quadrax Receptacle 90 degree Adapter with cable to board/ Tensolite 26473/02006X-4	Wired to board			21-033837-071 (L-2119-AI)†	150		M22520/2-01 with Positioner	M22520/5-01 with Die Set
Quadrax Receptacle Straight Adapter with cable to board/ Tensolite 26473/02006X-4 (LD)	Wire			21-033837-111 (L-2119-AP)			M22520/2-34	M22520/5-45 (Location A)

Daniels crimping tools are available from Daniels Mfg. Corp. 6103 Anno Ave., Orlando, FL 32809

**Termination instructions are packaged with each contact and can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp

† Consult Amphenol Aerospace for current release of this adapter and instruction sheet if applicable.

See electrical protocols for transition adapters on page 388.

Differential Twinax Transition Adapters

for Attachment to PC Boards - Application Data

Am	Aerospace
	Aerospace

100 OHM DIFFERENTIAL TWINAX TRANSITION ADAPTERS FOR LAUNCHING CONTROLLED IMPEDANCE SIGNALS TO PC BOARDS								
Differential Twinax Type Adap	ter/	Illustration of Adapter	ion of Adapter (Termination Instruction Sheet)** Impedance Mating			Crimping Tools		
Cable or PCB Tail Length			Plug	Receptacle	(Ohms)	Size	Inner Contact	Outer Contact
Differential Twinax Plug Adapter/ M17/176-00002 (77 ohms) 24463/9P026X-2	cles		21-033832-081 (L-2119-AJ)		-		M22520/2-01 with Positioner	M22520/5-01 with Die Set
Differential Twinax Plug Adapter/ Tensolite 24463/9P025X-2(LD) 10-646060	and receptacles		21-033832-021 (L-2119-P)				M22520/2-34	M22520/5-05 (Location B)
PCB Differential Twinax Receptacle 90 Degree Adapter/ Tail Length .110	Mating plugs and			21-033833-021	100	.3125		
PCB Differential Twinax Receptacle Straight Adapter/ Tail Length .110	Mating			21-033833-031			N/A	N/A
PCB Differential Twinax Receptacle Straight Adapter/ Tail Length .165				21-033833-151				
Differential Twinax Plug Adapter/ Tensolite CAN22TDT120 (120 Ohm)	eptacles		21-033832-111†				M22520/2-01 with Positioner M22520/2-34	M22520/5-01 with Die Set M22520/5-45 (Location A)
PCB Differential Twinax Receptacle 90 degree Adapter/Tail Length .283	plugs and receptacles			21-033833-161†	100	.375		
PCB Differential Twinax Receptacle Straight Adapter/Tail Length .283	Mating pl			21-033833-171†			N/A	N/A
Differential Twinax Receptacle 90 degree Adapter (low profile) with cable to board/ Tensolite 24463/9P026X-2	p			21-033833-091 (L-2119-AF)				M22520/5-01
Differential Twinax Receptacle 90 degree Adapter with cable to board/ Tensolite 24463/9P025X-2	Wired to board			21-033833-051 (L-2119-V)	100	N/A	M22520/2-01 with Positioner M22520/2-34	with Die Set M22520/5-45 (Location A)
Differential Twinax Receptacle 90 degree Adapter with cable to board/ Tensolite 24463/9P025X-2	×			21-033833-141 (L-2119-BU)				(2000.00

150 OHM DIFFERENTIAL TWINAX TRANSITION ADAPTERS FOR LAUNCHING CONTROLLED IMPEDANCE SIGNALS TO PC BOARDS								
Differential Twinax Type Adap	ter/	Illustration of Adapter		Number	Impedance	Mating Thread	Crimp	ing Tools
Cable or PCB Tail Length		•	Plug	Receptacle	(Ohms)	Size	Inner Contact	Outer Contact
Differential Twinax Plug Adapter/ Tensolite 26483/03071X-2	receptacles		21-033832-091 (L-2119-BR)				M22520/2-01 with Positioner M22520/2-34	M22520/5-01 with Die Set M22520/5-45 (Location A)
PCB Differential Twinax Receptacle 90 Degree Adapter/ Tail Length .110	plugs and			21-033833-111	150	.375	N/A	N/A
PCB Differential Twinax Receptacle Straight Adapter/ Tail Length .110	Mating			21-033833-181†			N/A	N/A
Differential Twinax Receptacle 90 degree Adapter with cable to board/ Tensolite 26483/03071X-2	Wired to board			21-033833-101 (L-2119-BM)†	150	N/A	M22520/2-01 with Positioner M22520/2-34	M22520/5-01 with Die Set M22520/5-45 (Location A)

**Termination instructions are packaged with each contact and can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp

† Consult Amphenol Aerospace for current release of this adapter and instruction sheet if applicable. See electrical protocols for transition adapters on page 388.

Micro D-Twinax Transition Adapters Push-Pull Quick disconnect Interconnects

Amphenol now offers differential twinax transition adapters in smaller sizes that provide matched impedance interconnection to PCB boards. Our unique push-pull quick disconnect adapter design offers:

- Advantages over traditional threaded type adapters
- Launching of controlled impedance (100 ohm) signals for high speed twinax contacts with push-pull quick disconnect coupling
 Rugged construction, 100+ mating cycles for reliable and secure
- Rugged construction, 100+ mating cycles for reliable and secure data transmission
- Miniature size for tighter spacing on boards
- Intermountability with existing threaded solutions having the same PCB tail footprint

Styles include:


Amphenol Aerospace

- Plug standard length and extended length options
- Straight PCB receptacle, 90° PCB receptacle
- Two jam nut receptacle styles both with standard length and extended length options
- Bushing assembly 90° adapter (used with plug or jam nut receptacle)



Micro D-Twinax Transition Adapters Shown right: Straight receptacle mated to plug Shown left: Jam nut and 90° receptacles

Micro D-Twinax Transition Adapter Plug






Part Number	Cable Type*	Impedance (Ohms)
21-033832-151	Calmont 3007-1923-12-7	
21-033832-161	Tensolite 26453/03184X-2LD	100
21-033832-161	Thermax 956-626Z	100
21-033832-121**	Calmont 3007-1923-12-7	

* See page 3 for information on other cable terminations.

** Same as -151 with extended ferrule for added cable support

Micro D-Twinax Transition Adapter Straight PCB Receptacle








Part Number	Impedance (Ohms)
21-033833-191	100


All dimensions for reference only.

Micro D-Twinax Transition Adapters Push-Pull Quick disconnect Interconnects



Micro D-Twinax Transition Adapter 90° PCB Receptacle








Part Number	Impedance (Ohms)
21-033833-201	
21-033833-281 .140 PCB tail length	100


All dimensions for reference only.

Micro D-Twinax Transition Adapter Jam Nut Receptacles

Jam Nut Receptacle, Style 1

Smaller diameter front shell requires a smaller mounting D-hole dimension in panel.









	Part Number	Cable Type*	Impedance (Ohms)
	21-033833-241	Calmont 3007-1923-12-7	
	21-033833-261	Tensolite 26453/03184X-2LD	100
ב	21-033633-201	Thermax 956-626Z	100
	21-033833-211**	Calmont 3007-1923-12-7	

* See page 3 for information on other cable terminations. ** Same as -241 with extended ferrule for added cable support

Jam Nut Receptacle, Style 2

Has a larger diameter front shell than Style 1. Requires a larger mounting D-hole in panel.







Part Number	Cable Type*	Impedance (Ohms)
21-033833-251	Calmont 3007-1923-12-7	
01 000000 071	Tensolite 26453/03184X-2LD	100
21-033833-271	Thermax 956-626Z	100
21-033833-231**	Calmont 3007-1923-12-7	

* See page 3 for information on other cable terminations.
 ** Same as -251 with extended ferrule for added


cable support



Micro D-Twinax Transition Adapters Push-Pull Quick disconnect Interconnects

90° Bushing Assemblies for use with Wired Micro D Transition Adapters

To facilitate tight cable bend requirements, Amphenol provides 90° bushing assemblies which convert straight plug and receptacle wired adapters into 90° wired adapters.




90° Bushing Assembly Part Number
21-033425-201

90° bushing assembly is ordered separately. Adapters are not included with bushing assembly.




90° Bushing Assembly with Jam Nut Micro D Transition Adapter

Illustrations below show how the 90° bushing assembly attaches to either a plug or a jam nut receptacle adapter.



90° Bushing Assembly with Wired Micro D Plug Transition Adapter

All dimensions for reference only.



^{90°} Bushing Assembly with Wired Micro D Jam Nut Receptacle Transition Adapter

Amphenol transition adapters are capable of terminating to additional 100 Ohm cables beyond what are listed in the charts on pages 1 and 2. Cables need to have the following dimensions:

- .0210/.011 Dia. stranded center conductor (26/30 AWG)
- .045 Dia. max. inner wire insulation
- .115 Dia. max. outer braid (round type preferred)
- .150 Dia. max. jacket

Consult Amphenol Aerospace for other cable termination possibilities.

Insert Arrangements - MIL-DTL-38999, Series III Incorporating Quadrax & Differential Twinax Contacts



This illustrated listing represents the most readily available patterns incorporating quadrax and differential twinax contacts within D38999, Series III connectors. If you require other arrangements than what are shown here, consult Amphenol for further availability. In most cases, unless otherwise stated, size 8 cavities can be filled with quadrax or differential twinax contacts. Arrangements can be mixed with any size 8 coax, and/or concentric twinax or triax contacts.


Front face of pin inserts illustrated

				A B	$\begin{pmatrix} 8 & \textcircled{0}^{1} & e^{2} \\ 7 & \textcircled{0}_{10} & e^{9} & e^{3} \\ s & \textcircled{0}_{5} & \textcircled{0}_{4} \end{pmatrix}$
Insert Arrangement	9-5	17-2	17-22	17-52	17-60
Number of Contacts	1	38 1	2 2	2	8 2
Contact Size	8 Grounded	22D 8 Twinax	12 8	8 Meets Boeing Specification	22D 8
				$14 15 \Theta \Theta^{1} 2 \Theta^{3}$ $14 15 \Theta \Theta^{2} 2 \Theta^{3}$ $13 \Theta \Theta^{3} \Theta^{4}$ $12 \Theta \Theta^{5}$ $11 \Theta \Theta^{7} \Theta^{8}$ $10 \Theta^{7} \Theta^{8}$	
Insert Arrangement	19-18	19-31	19-AB	19-AD	21-75
Number of Contacts	14 4	12 1 2	4	16 1	4
Contact Size	22D 8	22D 12 8	8 Note: 19-AB same as 19-18 but no 22D contacts. Ground plane only.	20 8	8
11	$ \begin{array}{c} S & T & A \\ R & \bullet & \bullet \\ \end{array} \\ \begin{array}{c} \bullet \\ \bullet \\ \bullet \\ \end{array} \\ \begin{array}{c} \bullet \\ \bullet \\ \bullet \\ \bullet \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ \\ $				
Insert Arrangement	21-79		23-6	25-7	
Number of Contacts	17 2		6	97	2
Contact Size	22D 8		8	22D	8
B 10 Quadrax or Differential Twinax	CONTACT LEGEN	ө ө	0 22D		



Front face of pin inserts illustrated

		$\begin{array}{c} \begin{array}{c} U \\ \bullet \\$	$ \begin{array}{c} & & & \\ & $
Insert Arrangement	25-8	25-17	25-20
Number of Contacts	8	36 6	10 13 3 4
Contact Size	8	22D 8	20 16 8 12



Insert Arrangement		25-26				25-46			25-	62	
Number of Contacts	16	5	41		40	4	2		8	4	
Contact Size	20	12	8		20	16	8		16	8	
									- ·		

Ground plane only





Amphenol Tri-Start, 38999 Series III* Connectors can be ordered with the following popularly used Quadrax contacts: 100 ohm quadrax 21-033385-051 socket contacts 100 ohm quadrax 21-033384-051 pin contacts Use the following coded number ordering procedure :

1.	2.	3.	4.	5.	6.	
Connector Type	Shell Type	Service Class	Shell Size – Insert Arrangement	Contact Type	Alternate Keying Position	
TVP	00	RQW	21–75	Р	В	

For ordering of connectors with any other quadrax contacts or differential twinax contacts, please consult Amphenol Aerospace for part numbers.

Step 1. Select a Connector Type

τν	Tri-Start Series Connector with metal shells
TVP	Back panel mounted receptacle with metal shells
СТУ	Tri-Start Series Connector with composite shells
CTVP	Back panel mounted receptacle with composite shells

Step 2. Select a Shell Style

00	Wall mount receptacle
02	Box mount receptacle available only with the PCB tails and epoxy backfilled (non-removable)
06	Straight plug
07	Jam nut receptacle

Step 3. Select a Service Class with Quadrax

RQFElectroless nickel platedRGQFElectroless nickel plated ground planeRQWOlive drab cadmium plateRGQWOlive drab cadmium plated ground planeRQBNiAlBronzeRGQBNiAlBronze ground planeRQKCorrosion resistance stainless steelRGQKStainless steel ground plane	
RQW Olive drab cadmium plate RGQW Olive drab cadmium plated ground plane RQB NiAlBronze RGQB NiAlBronze ground plane RQK Corrosion resistance stainless steel	
RGQW Olive drab cadmium plated ground plane RQB NiAlBronze RGQB NiAlBronze ground plane RQK Corrosion resistance stainless steel	
RQB NiAlBronze RGQB NiAlBronze ground plane RQK Corrosion resistance stainless steel	
RGQB NiAlBronze ground plane RQK Corrosion resistance stainless steel	
RQK Corrosion resistance stainless steel	
RGQK Stainless steel ground plane	
QDT Durmalon plated, Nickel-PTFE alternative to cade	nium
GQDT Groundplane Durmalon	

Step 4. Select a Shell Size and

Insert Arrangement

See insert arrangements available with quadrax contacts on preceding pages. Shell Size and Insert Arrangements are together in one chart. First number represents Shell Size, second number is the Insert Arrangement

Step 5. Select Contact Type

Р	Pin contacts	
S	Socket contacts] [

* The incorporation of quadrax or differential twinax contacts requires a modified connector to accommodate keyed contacts.

For more information on Tri-Start, MIL-DTL-38999 Series III connectors see the section in this catalog.

Step 6. Select an Alternate Keying Position

Locksmith keying-rotation of minor keys. See Series III Alternate Positions below "N" not required for normal position

Tri-Start Alternate MAIN KEYWAY Positions RECEPTACLE A plug with a given rotation (front face shown) letter will mate with a receptacle with the same rotation letter. The angles for a given connector are MAIN KEYWA the same whether it PLUG contains pins or sockets. (front face shown Inserts are not rotated in conjunction with the master key/keyway.

Shell Size	Key & Keyway Arrangement Identification Letter	AR° or AP° BSC	BR° or BP° BSC	CR° or CP° BSC	DR° or DP° BSC
	N	105	140	215	265
	A	102	132	248	320
9	В	80	118	230	312
	С	35	140	205	275
	D E	64	155	234	304
	E	91	131	197	240
	Ν	95	141	208	236
	А	113	156	182	292
11, 13,	В	90	145	195	252
and 15	С	53	156	220	255
	D	119	146	176	298
	E	51	141	184	242
	Ν	80	142	196	293
	А	135	170	200	310
17 and 19	В	49	169	200	244
17 8110 19	С	66	140	200	257
	D	62	145	180	280
	Е	79	153	197	272
	Ν	80	142	196	293
	А	135	170	200	310
21, 23,	В	49	169	200	244
and 25	С	66	140	200	257
	D	62	145	180	280
	Е	79	153	197	272
	Ν	80	142	188	293
	A	135	170	188	310
25L, 33,	В	49	169	188	244
and 37	С	66	140	188	257
	D	62	145	188	280
	Е	79	153	188	272



Coaxial Contacts for MIL-DTL-38999 General Description

Amphenol[®] Coaxial Contacts -Offer several advantages

for reliable interconnection and continued performance:


- Large crimping area assures low contact resistance and high tensile strength
- Back insulator positively captivates inner contact against axial loads
- · Front insulator provides closed entry for socket inner contact
- Recessed inner contact is protected
- · Outer contact has rugged wall section for durability

TYPICAL SUBMINIATURE COAX , SOCKET CONTACT has socket outer contact with a pin inner contact

> TYPICAL SUBMINIATURE COAX PIN CONTACT has pin outer contact with a socket inner contact




MIL-DTL-38999 LJT-R, JT-R, TV-R, SJT-R MS Type, Coax Size 12 Socket Assembled Contact




MIL-DTL-38999 LJT-R, JT-R, TV-R, SJT-R MS Type, Coax Size 16 Pin Unassembled Contact



MIL-DTL-38999 LJT-R, JT-R, TV-R, SJT-R MS Type, Coax Size 8 Pin Assembled Contact



MIL-DTL-38999 LJT-R, JT-R, TV-R, SJT-R MS Type, Coax Size 8 Socket Unassembled Contact



Cable Illustration - Coax Contact

Coax Contacts are gold plated, crimp termination

Finish of mating contacts parts: supplied with 0.000050 min. gold over nickel on mating parts. Other finishes are available; consult Amphenol for further information.

Coax Size 12 & 16 Contact Performance:

- Typical VSWR: 1.5:1 maximum up to 700 MHz and 500 MHz respectively, for properly cabled size 12 and 16 coaxial contacts in the M38999 Series I, II and III
- Insulation Resistance: 5,000 megohms minimum @ 25°C
- Dielectric Withstanding Voltage: Size 12: 1,000 VAC Rms @ sea level, 250 VAC Rms @ 50,000 ft. Size 16: 800 VAC Rms @ sea level, 250 VAC Rms @ 50,000 ft.
- Contact Resistance: See MIL-C-39029/27, /28, /75, /76, /77, /78

Coax Size 8 Contact Performance:

- Typical VSWR when terminated to specified 50 ohm cable: 1.5:1 maximum up to 3 GHz (excluding 21-033101/2-27)
- Insulation Resistance: 5,000 megohms minimum @ 25°C
- Dielectric Withstanding Voltage:
 1,300 VAC Rms @ sea level, 250 VAC Rms @ 50,000 ft.
- Contact Resistance: See MIL-C-39029/59, /60



JT-R Series, MIL-DTL-38999 Series II, SAE AS39029 (27, 28, 76, 78)

COAX CONTACTS FOR USE IN JT-R CONNECTORS									
Cable	Contact Part Number (Termination Instruction Sheet)**		Contact Size	Crimping Tools		Installation Tools			
	Pin	Socket	1	Inner Contact	Crimp Ferrule	Insertion	Removal		
RG-178B/U, RG-196A/U	21-033122-564 (M39029/76-425) (L-2035-AG)	21-033121-564 (M39029/78-433) (L-2035-AH)				M81969/8-07	M81969/8-08		
Haveg 30-00761, 30-02024, 30-02033 Tensolite 24713/A955KK1, 26723/ A955KK1	21-033122-562† (L-2035-AN)	21-033121-562† (L-2035-AP)	16	M22520/2-01 with Positioner M22520/2-35 or with Daniels Positioner	M22520/4-01 with Positioner M22520/4-02	or M81969/14-03 or Amphenol 11-8674-16 11-8794-16	or M81969/14-03 or Amphenol 11-8675-16 11-8795-16		
Haveg 61-02051	21-033122-561† (L-2035-AK)	21-033121-561† (L-2035-AL)		K532		or MS27495A16 or	or MS27495R16 or		
RG-174A/U, RG-188A/U, RG-161/U, RG-187A/U, RG-316/U,	21-033122-563 (M39029/76-424) (L-2035-AD)	21-033121-563 (M39029/78-432) (L-2035-AE)				MS27534-16	MS27534-16		
RG-179B/U, Haveg 8100207, Times (HS-179) AA3248, Teledyne 11299, Raychem 7528H1424	21-033122-546 (M39029/28-211) (L-2035-F)	21-033121-546 (M39029/27-210) (L-2035-G)				M81969/8-09	M81969/8-10		
RG-180B/U, RG-195A/U, Raychem 9528A1318	21-033122-541 (M39029/28-409) (L-2035-C)	21-033121-541 (M39029/27-402) (L-2035-E)	- 12	M22520/2-01 with Positioner M22520/2-34	M22520/31-01 with Positioner M22520/31-02 or	or M81969/14-04 or Amphenol	or M81969/14-04 or Amphenol		
Raychem 5022E5111	21-033122-543† (L-2035-M)	21-033121-543† (L-2035-N)		or with Daniels Positioner	Daniels GS-200 Tool	11-8674-12 11-8794-12 or	11-8675-12 11-8795-12 or		
Raychem 9530A5314	21-033122-544 (L-2035-R)	21-033121-544 (L-2035-S)		K323	with Positioner G2P330	MS27495A12 or	MS27495R12 or		
Raychem 9527A1318	21-033122-545 (L-2035-U)	21-033121-545 (L-2035-V)				MS27534-12	MS27534-12		
Gore GWN1159A	21-033122-547† (L-2035-X)	21-033121-547† (L-2035-Y)							

MIL-DTL-38999 CONTACT DATA

All contacts mate with other contacts in this series which have the same inner and outer contact diameters.

NOTE: SAE AS39029 supersedes MIL-C-39029

**Termination instructions are packaged with each contact and can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp

JT Example:	Socket 21-033121-564 on RG-196A/U cable will mate with pin 21-033122-563 on RG-188A/U cable which is used in both this and the LJT-R series.
LJT, TV, SJT, Amphe-Lite Example:	Socket 21-033123-564 on RG-196A/U cable will mate with pin 21-033122-563 on RG-188A/Ucable which is used in both this and the JT-R series.

Finish of mating contact parts: Contact part numbers shown in the chart above are supplied with 0.000050 min. gold (Knoop hardness 130-200) over nickel on mating parts. Other finishes are available; consult Amphenol.

Daniels crimping tools are available from: Daniels Mfg. Corp. 6103 Anno Ave., Orlando FL 32809

LJT-R, MIL-DTL-38999 Series I; TV-R, MIL-DTL-38999 Series III; Amphe-Lite and SJT-R Series, SAE AS39029 (28, 59, 60, 75, 76, 77)

COAX CONTACTS FOR USE IN LJT-R, TV-R, AMPHE-LITE AND SJT-R CONNECTORS									
Cable	Contact Part Number		Contact Size	Crimping Tools		Installation Tools			
	Pin	Socket		Inner Contact	Crimp Ferrule	Insertion	Removal		
RG-178B/U, RG-196A/U	21-033122-564 (M39029/76-425) (L-2035-AG)	21-033123-564 (M39029/77-429) (L-2035-AJ	16	M22520/2-01 with Positioner M22520/2-35 or with Daniels Positioner K532	M22520/4-01 with Positioner M22520/4-02	M81969/8-07 or	M81969/8-08 or		
Haveg 30-00761, 30-02024, 30-02033 Tensolite 24713/A955KK1, 26723/A955KK1	21-033122-562† (L-2035-AN)	21-033123-562† (L-2035-AR)†				M81969/14-03 or Amphenol 11-8674-16 11-8794-16	M81969/14-03 or Amphenol 11-8675-16 11-8795-16		
Haveg 61-02051	21-033122-561† (L-2035-AK)†	21-033123-561† (L-2035-AM)†				or MS27495A16	or MS27495R16		
RG-174A/U, RG-188A/U, RG-316/U, RG-161/U RG-187A/U,	21-033122-563 (M39029/76-424) (L-2035-AD)	21-033123-563 (M39029/77-428) (L-2035-AF)				or MS27534-16	or MS27534-16		
RG-179B/U, Haveg 8100207, Times (HS-179) Raychem 7528H1424 AA3248, Teledyne 11299	21-033122-546 (M39029/28-211) (L-2035-F)	21-033123-546 (M39029/75-416) (L-2035-H)	12	M22520/2-01 with Positioner M22520/2-34 or with Daniels Positioner K323	M22520/31-01 with Positioner M22520/31-02 or Daniels GS-200 Tool with Positioner G2P330	M81969/8-09 or M81969/14-04 or Amphenol 11-8674-12 11-8794-12 or MS27495A12 or MS27534-12	M81969/8-10 or M81969/14-04 or Amphenol 11-8675-12 11-8795-12 or MS27495R12 or MS27534-12		
RG-180B/U, RG-195A/U, Raychem 9528A1318	21-033122-541 (M39029/28-409) (L-2035-C)	21-033123-541 (M39029/75-417) (L-2035-D)							
Raychem 5022E5111	21-033122-543† (L-2035-M)†	21-033123-543† (L-2035-P)							
Raychem 9530A5314	21-033122-544† (L-2035R)	21-033123-544† (L-2035-T)†							
Raychem 9527A1318	21-033122-545† (L-2035-U)†	21-033123-545† (L-2035-W)							
Raychem 9527A1314	21-033122-585 (L-2035-GG)	21-033123-585 (L-2035-GH)							
Gore GWN1159A, Nexans RG179-DT	21-033122-547 (L-2035-X)†	21-033123-547 (L-2035-Z) †							
M/A-Com 5M2869-001	21-033122-589 (L-2035-GR)	21-033123-589 (L-2035-GT)							
RG-187A/U, RG-179B/U, RG-174A/U, RG-188A/U, RG-316/U, RG-161/U Haveg 8100207, Times (HS-179)AA3248, Teledyne 11299	21-033102-023† (L-1107-C)	21-033101-023† (L-1107-G)	8	M22520/2-01 with Positioner M22520/2-31†† or solder	M22520/5-01 with die set M22520/5-03 (A) or M22520/5-08 (A) M22520/5-35 (B) or M22520/10-01 with Die Set M22520/10-05 (A)	Hand - inserted	11-9170 or MS		
RG-142B/U, RG-223/U	21-033102-024* (L-1107-D)	21-033101-024* (L-1107-H)			M22520/5-01 with die set M22520/5-05 (A) or M22520/5-19 (B) or M22520/10-01 with Die Set M22520/10-07 (A)				

NOTE: SAE AS39029 supersedes MIL-C-39029

Amphenol Aerospace

CRIMPING TOOLS: Italicized letters in parenthesis that follow positioner part numbers indicate applicable die closure. Commercial equivalents with the same die closure dimension may be used. CHART CONTINUES ON NEXT PAGE † Consult Amphenol Aerospace for current release of this contact or instruction sheet if applicable.

†† When inner contact is installed by crimping only. 11-10134 Expander Tool Kit must be used to assemble rear insulator over contact.

**Termination instructions are packaged with each contact and can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp



Application Data, cont.

LJT-R, MIL-DTL-38999 Series I; TV-R, MIL-DTL-38999 Series III; Amphe-Lite and SJT-R Series, SAE AS39029 (28, 59, 60, 75, 76, 77), cont.

COAX CONTACTS FOR USE IN LJT-R, TV-R, AMPHE-LITE AND SJT-R CONNECTORS, CONT.								
Cable	Contact Part Number (Termination Instruction Sheet)***		Contact Size	Crimp	CrimpingTools		Installation Tools	
	Pin	Socket	-	Inner Contact	Crimp Ferrule	Insertion	Removal	
Haveg 51-03111, Tensolite 28895/2X1	21-033102-022 (L-1107-B)	21-033101-022 (L-1107-F)		M22520/2-01 with Positioner	M22520/5-01 with die set M22520/5-05 (B) or M22520/5-41			
RG-180B/U, RG-195A/U, Raychem 9528A1318	21-033102-021 (M39029/60-367 Supersedes MS27536) (L-1107-A)	21-033101-021 (M39029/59-366 Supersedes MS27535) (L-1107-E)		M22520/2-31** or solder	(B) or M22520/10-01 with Die Set M22520/10-07 (B)))		
RD-316 Double Shield (M17/152-00001)	21-033102-025 (L-1107-J)	21-033101-025 (L-1107-N)		M22520/2-01 with Positioner M22520/2-31	M22520/5-01 with Die Set M22520/5-37 (B) or M22520/10-01 with Die Set M22520/10-15 (A)			
Raychem 7524D5111-9 (triax cable - contact will terminate inner coax portion only)	21-033102-026 (L-1107-M)	21-033101-026 (L-1107-M)	8				11-9170 or MS	
RG-400, ECS3C058A ECS352001 ECS432101	21-033102-027 (L-1286-B)	21-033101-027 (L-1293-B)		M22520/2-01 with Positioner M22520/2-10	M22520/5-01 with Die Set M22520/5-45 (A)			
RG-58 (M17/155-00001), M17/028-RG-058 RG303 Times LMR-195-UF	21-033102-029 (L-1107-AA)	21-033101-029 (L-1107-Y)†		Solder	M22520/5-01 with Die Set M22520/5-05 (B)			
5021D1331-0	21-033102-036 (L-1107-P)	21-033101-036† (L-1107-Q)			M22520/5-01 with Die Set			
5M2869-001 ESC432101 BMS13-65	21-033102-037 (L-1107-V)	21-033101-037 (L-1107-W)			M22520/2-01 with Positioner M22520/2-31	M22520/5-05 (B) or M22520/10-01		
5022A1311-0	21-033102-039 (L-1107-AC)	21-033101-036† (L-1107-AB)			with Die Set M22520/10-07 (B)			
FA-19X	21-033652-001 (L-2091-A)	21-033653-001 (L-2091-B)		M22520/2-01 with Positioner K1106	M22520/5-01 with Die Set Y25 (B)			
T Flex-402 Utiflex UFB142G	21-033102-041 (L-1107-AG)	21-033101-041 (L-1107-AF)		Solder	M22520/5-01 with Die Set M22520/5-05 (B)			

NOTE: SAE AS39029 supersedes MIL-C-39029

NOTE: Contacts can be ordered by part numbers given in chart

CRIMPING TOOLS: Italicized letters in parenthesis that follow positioner part numbers indicate applicable die closure. Commercial equivalents with the same die closure dimension may be used.

† Consult Amphenol Aerospace for current release of this contact or instruction sheet if applicable

**When inner contact is installed by crimping only. 11-10134 Expander Tool Kit must be used to assemble rear insulator over contact.

**Termination instructions are packaged with each contact and can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp



Matched Impedance Coaxial Contacts for MIL-DTL-38999

Amphenol[®] Matched Impedance Size 12 Coaxial Contacts for RF/Microwave, High Frequency and High Performance Requirements

The matched impedance coax contact is available in size 12. It incorporates a captivated inner contact which "snaps into" the outer contact preventing displacement or pull back of the inner contact in situations where the cable may be bent.

TYPICAL MATCHED IMPEDANCE COAX SOCKET CONTACT has socket outer contact with a captivated pin inner contact

> TYPICAL MATCHED IMPEDANCE COAX PIN CONTACT has pin outer contact with a captivated socket inner contact

Design features and benefits of the Matched Impedance:

- For use in 90 degree angle or bent cable applications
- Provides 50 ohm matched impedance resulting in low VSWR and low insertion loss
- Frequency range for a mated pair extends to 3 GHz and beyond, higher than other coaxial contacts previously offered.
- Ideally suited for D38999 high performance and MIL-STD-1760 high band coaxial contact requirements

High Performance Size 12 Coax 50 Ohm matched

LJT-R, MIL-DTL-38999 Series I, JT-R, MIL-DTL-38999 Series II, and TV-R, MIL-DTL-38999 Series III

Use with Cable	Comment	Pin (Termination Instruction Sheet)***	Socket (Termination Instruction Sheet)***
RG316, T-Flex-405 Semflex SM405	M39029/102/103	21-033651-011 (L-2092-C)	21-033650-011 (L-2092-C)
RG-316, T-Flex-405	JT-R, MIL-DTL-38999 Series II		21-033729-011 (L-2092-P)
RD316, Filotex, ET124962, M17/152-00001	M39029/102/103 Type	21-033651-017 (L-2092-F)	21-033650-017 (L-2092-F)
JN1088WT	JN1104*50C	21-033213-042	21-033214-042 (L-2092-D)
PAN6422XQ	PAN6841*50C	21-033651-012 (L-2092-E)	21-033650-012
RG178, Gore CXN 3403	M39029/102/103 Type	21-033651-018 (L-2092-K)	21-033650-018 (L-2092-K)
RG178, Gore CXN 3403	JT-R, MIL-DTL-38999 Series II		21-033729-018 (L-2092-K)
SFT-316-TR	M39029/102/103 Type	21-033651-022 (L-2092-N)	21-033650-022 (L-2092-N)
Semflex SW060	M39029/102/103 Type	21-033651-025	21-033650-025
Semflex SW086 (solid inner conductor)	M39029/102/103 Type	21-033651-026	21-033650-026

* Add P or S for pin or socket

*Termination instructions are packaged with each contact and can be found on-line at:

www.amphenol-aerospace.com/serviceinstructions.asp

Matched Impedance Coax Contact Performance: Electrical Specifications:

- Contact impedance = 50 ohms nominal
- Frequency range = 0–3 GHz Operable at higher frequencies depending on cable selection. Consult Amphenol for details.
- Dielectric withstanding voltage (for a mated pair): At sea level = 1000 VRMS At 50, 000 ft. = 250 VRMS
- Insulation resistance: 5 gigaohms min. @ 25°C
- VSWR: 1.20 + .04F (F in GHz) max. up to 3 GHz
- Insertion Loss: .11 / fGHz dB max.
- **Environmental Specifications:**
- Thermal limits: –55 ° to 200°C

Mechanical Specifications:

- Mating: slide-on
- Mounting: conforms to M39029/102 & /103 envelope dimensions

Typical Contact Installation Instructions for Coax Contacts



The following is an example of a contact instruction sheet that would be shipped within the package of contacts for a Crimp, Size 12 Coax Contact for use in Subminiature, D38999 connectors. The sheet provides detailed instructions for assembling the component parts and for crimping the contact to coaxial cable, along with the recommended cable and tooling to be used. Installation instructions are included within all contacts for D38999 connectors. For installation instructions for other connector series, there are separate documents (not included in packaging of parts) as follows: L- 633 for Miniature solder types, L-613 for Miniature SE types, L-660 for Miniature CE types, and L-650 for MS/Standard and Heavy Duty types. For any other instructions needed, consult Amphenol. Most installation instructions can be found on-line at www.amphenol-aerospace.com (from home page, go to Service Instructions and enter contact part number or instruction sheet number).

21-033651-011 (PIN) 21-033650-011 (SOCKET)

Contact, Pin and Socket, Coaxial,

Type LJT-R & TV-R, (MIL-DTL-38999 Series I & III) Crimp, Size 12 Installation Instructions

See table on reverse side for coaxial cable recommended and crimp tool information.

- A. 1. Slide outer crimp ferrule over cable outer jacket as shown.
 - Strip cable outer braid as illustrated. Ends must be cut cleanly and at right angles to the axial plane of the cable. The cable must not be deformed while making cuts.
- 3. Flare outer braid, then strip cable dielectric as shown.
- B. 1. Assemble inner contact assembly over cable center conductor and cable dielectric until inside bore of bushing butts against cable dielectric.
 - 2. Cable center conductor must be visible through the inspection hole in the inner contact wire well.
 - 3. Crimp inner contact wire well using crimp tool listed in table.
- C. 1. Carefully slide outer contact assembly over inner contact assembly and under cable outer braid until inner contact butts against insulator shoulder as illustrated. (Inner contact assembly will snap into the locked position when fully assembled inside the outer contact assembly.)
 - 2. Bring outer crimp ferrule forward over cable outer braid as illustrated. (Continue to push the inner contact assembly fully forward while bringing the outer crimp ferrule into position.)
 - 3. Crimp outer crimp ferrule using crimp tool listed in table (.156 Max. over ferrule after crimping). Trim excess braid ahead of crimp ferrule, if necessary.

CONTACT INSERTION INTO CONNECTOR

Using insertion tool (part number M81969/8-09 or M81969/14-04), insert contact assembly into rear connector grommet hole. Contact must be aligned with hole and not inserted at an angle. Push forward until contact is felt to snap into position within insert. Remove tool.


CONTACT REMOVAL FROM CONNECTOR

1-2092-C

October 2001

Position removal tool (part number M81969/8-10 or M81969/14-04) around cable and slide tool down wire until tool tips enter rear grommet and come to a positive stop. Hold tool tip firmly against positive stop on contact, grip wire and simultaneously remove tool, contact and cable.

21-033651-011 (PIN) 21-033650-011 (SOCKET)



			Tools					
Amphenol [®]	Description	Coaxial Cable	Inne	r Contact		Outer Contact		
Part Number	Description	Accommodated	Crimp Tool	Setting	Positioner (Daniels)	ΤοοΙ	Positioner	
01 000051 011	Matched Impedance*	RG316 (M17/113-RG316)	MH992 (Daniels)	5	K1360	- M22520/5-01	M22520/5-03 (A) or M22520/5-35 (B)	
21-033651-011	Size 12 Coax Pin	RG179 (M17/094-RG179)	MH992 (Daniels)	4	K1360			
	Matched Impedance* Size 12 Coax Socket	RG316 (M17/113-RG316)	MH992 (Daniels)	5	K1360			
21-033650-011		RG179 (M17/094-RG179)	MH992 (Daniels)	4	K1360			

FSCM77820

* Matched Impedance applies when contacts are terminated to RG316 cable only.



High Frequency Contacts for MIL-DTL-38999 Series III Circular General Description

Amphenol® High Frequency Contacts

Amphenol and SV Microwave (an Amphenol company) offer DC to 40 GHz high frequency size 8, 12 and 16 coaxial contacts for the D38999 Series III housing and standard inserts. These contacts allow any application to continue to use the D38999 connector and be able to expand the use to include the microwave transmission lines. Features include:

- Superior electrical performance and high frequency capability
- Blindmate advantage and maintance of an accurate phase length when mated
- Can be terminated to a multiple of cable types depending on the application
- Uses standard interfaces based on MIL-STD-348, and can be installed in any MIL-DTL-38999 size 8, 12 or 16 insert
- Unique "Float Mount" technology allows for consistent microwave performance while maintaining tight mechanical tolerances



HIGH FREQUENCY CONTACTS SPECIFICATIONS

Electrical

4	Mated	nair size 8	- RG 405	Semi-Rigid	Cable)
	mateu		- 110 403	oenn-mgiu	Cable)

`	. ,
Impedance	50 Ω
Frequency Range	DC - 40 GHz
VSWR	1.05 +.01 (freq. GHz)
Insertion Loss	0.03.√(freq.GHz)
Insulation Resistance (Min.)	10,000 M Ω
Contact Resistance (Max.)	
Center conductor:	6.0 m Ω
outer conductor:	3.0 m Ω
outer to cable:	0.5 m Ω
Dielectric Withstanding Voltage	1,000 VRMS
Corona Extinction Voltage	250 VRMS
RF High Potential Voltage	500 VRMS
RF Leakage	- (80-freq. GHz)

Materials and Finish

Body and Sleeve	Stainless steel per AMS-5640 Alloy UNS S30300 Type 1
Ferrule	Brass per ASTM B16, Alloy UNS C36000
Contact & Lock Ring	Beryllium copper per ASTM B196 Alloy UNS C17300, Td04
Insulator	PTFE per ASTM D1710, Type 1, Grade 1, Class B
Spring	Stainless steel per ASTM A313 Type 631
Rear Body & Contacts	Gold per ASTM B488 Type II, Code C, Class 1.27; over Nickel per AMS-QQ-N-290 Class 1 (60µ inches); over Copper per MIL-C-14550 (10µ inches) Passivated per AMS-2700. Type 2
	Passivaleu per ANIS-2700, Type 2

Subminiature MIL-DTL-38999 Series III	
Connector with Size 8 High Frequency Contacts	

HIGH FREQUENCY COAX CONTACTS FOR USE IN D38999, SERIES III CONNECTORS						
High Frequency Amphenol Part Number (Termination Instruction Sheet)	Inter- face	Frequency	For use with Cable	Туре	Cavity Size	Piggyback Grommet
21-033449-001HF (300-17-008)	BMZ	40 GHZ	TFLEX-405	Socket	8	21-033321-007
21-033448-001HF (300-17-008)				Pin		
21-033449-002HF (300-89-009)	BMZ	18 GHZ	TFLEX-405	Socket	8	21-033321-007
21-033448-002HF (300-89-009)				Pin		
21-033449-003HF (300-89-008)	BMZ	12 GHZ	RG-400/	Socket	8	21-033321-009
21-033448-003HF (300-89-008)			RG-142	Pin		
21-033449-004HF (300-89-002)	BMZ	18 GHZ	TFLEX-402	Socket	8	21-033321-010
21-033448-004HF (300-89-002)				Pin		
21-033449-006HF	вма	26.5 GHZ	TFLEX-405	Socket	8	21-033321-007
21-033448-006HF		20.0 0112		Pin		21 000021 007
21-033449-007HF	ВМА	26.5 GHZ	TFLEX-402	Socket	8	21-033321-010
21-033448-007HF	DIVIA	20.5 0112	11 LLX-402	Pin	0	21-033321-010
21-033449-008HF	BMZ- 75	2 GHZ	LMR-240-	Socket	8	21-033321-008
21-033448-008HF	Ohm	2 GHZ	75	Pin	0	21-033321-008
21-033449-009HF	SMPM	65 GHZ	TFLEX-405	Socket	12	N/A
21-033448-009HF	SIVIFIVI		IFLEX-405	Pin	12	IN/A
21-033449-010HF	01400		0.047 Dia.	Socket	10	N1/A
21-033448-010HF	SMPS	65 GHZ	Cable	Pin	16	N/A

Environmental

 Temperature Range
 -65°C to +125°C

 Corrosion (Salt Spray)
 MIL-STD-202, Method 101, Condition B

 Vibration
 MIL-STD-202, Method 204, Condition D, 20 Gs

 Shock
 MIL-STD-202, Method 213, Condition 1, 100 Gxs

 Thermal Shock
 MIL-STD-202, Method 107, Condition B, -65°C to +125°C

 Moisture Resistance
 MIL-STD-202, Method 106, Less step 7B

 Barometric Pressure (Altitude) MIL-STD-202, Method 105, Condition C, 70,000 ft.

Twinax Contacts for MIL-DTL-38999 General Description, Application Data - Size 10 & 12



Amphenol[®] Twinax Contacts -Were designed for

use with twinax cable in Data Bus systems. Twinax contacts provide the following benefits:

- Protection from magnetic interference
- Protection from electrostatic interference including nuclear electromagnetic pulse
- Meets parameters defined by MIL-STD-1553B
- Maintains shield integrity through a multi-pin circular connector and does not require contact polarization within the insert

SIZE 10 & 12 CONCENTRIC TWINAX CONTACTS


The size 12 concentric twinax contact interface was developed for JN1104 EuroFighter contacts, and can be used in any size 12 cavity M38999 I, II or III or SJT connector. Features:

- Operating temperature -55°C to 175°C
- Pins are scoop-proof
- Meets performance levels of M38999 connector
- 4 components, gold plated crimp termination
- For use with a variety of cables (See chart below)

TYPICAL ELECTRICAL PERFORMANCE

Size 10 & 12 Concentric Twinax Contacts Voltage Rating: 500 Vrms max. @ sea level Contact Resistance:


Center @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Intermediate @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Outer @ 12 Amps, 85 millivolts max. voltage drop @ 25°C Operating Frequency: 0–30 MHz Dielectric Withstanding Voltage: Center to Intermediate 800 VAC Rms @ Sea Level Intermediate to Outer 500 VAC Rms @ Sea Level



Cable Illustration - Twinax Contact



Concentric Twinax Contacts Size 12



Unassembled Components of Size 12 Concentric Twinax Contact

SIZE 10 & 12 CONCENTRIC TWINAX CONTACTS FOR USE IN D38999 CONNECTORS						
For use with Cable	Concentric Twinaxial Contact Part Number (Termination Instruction Sheet)**		Contact Size	Comments	Connector Series	
	Pin	Socket				
M17/176-00002, ST5M1212-002, TWC-78-1	21-033909-025 (L-2092-G)	21-033908-025 (L-2092-G)				
0024A0024, Fileca F2709-13-CA	21-033909-028 (L-2092-G)	21-033908-028 (L-2092-G)		JN1104 Interface	D38999 Series I, III	
EPD32263A,10612, GSC-12-2548-00	21-033909-029 (L-2092-H)	21-033908-029 (L-2092-H)	12			
ASNE0849, 5PTM1T04-1	21-033909-081 (L-2092-AB)	21-033908-081 (L-2092-AB)	12			
VG95218T023D002	21-033909-091 (L-2092-AC)	21-033908-091 (L-2092-AC)				
VG95218T023D002	21-033909-101 (L-2092-AC)	21-033908-101 (L-2092-AC)		Same as -91 except new ferrule with wire support		
M17/176-00002, GSC-12-2549-00		21-033640-025 (L-2092-W)	12	JN1104 Interface	D38999 Series II	
0024A0024		21-033640-028 (L-2092-V)	12	JNT 104 Interface	Doossa Selles II	
5M2022-003	21-033844-001 (L-1255-A)	21-033843-001 (L-1255-B)	10	Supplied with Thermal fit sleeve	D38999 Series I, III	

**Termination instructions are packaged with each contact and can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp

Amphenol Aerospace

Twinax Contacts for MIL-DTL-38999 General Description, Application Data - Size 8

High performance connectors within the D38999 families are the most commonly used connectors for incorporation of Twinax contacts. These connectors offer wide versatility in insert arrangements for not only concentric Twinax contacts, but also coax, triax, PCB, wire wrap, thermocouples and EMI filter contacts.

Other connectors available with concentric Twinax contacts:

- Wire Integrated Connectors (WICS) for Data Bus Systems. Consult Amphenol Aerospace, Sidney, NY.
- ARINC 404, ARINC 600 and R27 Series rectangular connectors. Supplied by Amphenol Canada.

SIZE 8 CONCENTRIC TWINAX CONTACTS

The size 8 concentric Twinax contact was developed for use in MIL-STD-1553 Airborne multiplex data bus applications which require high performance interconnect characteristics in multi-pin connectors. Ideal for this application need is the high performance Tri-Start connector with its fully scoop-proof feature of recessed pins. The concentric Twinax contact is crimp terminable to twisted shielded cable. Features include:

- Provides protection from magnetic and electrostatic interference including nuclear electromagnetic pulse
- Maintains shield integrity through a multi-pin circular connector and does not require contact polarization within the insert
- 175°C rated and meets performance levels of MIL-DTL-38999 Series III connectors
- MIL-C-17/176-00002 cable termination
- Gold plated full crimp termination contacts qualified to M39029/90 & /91
- Integral part of the MIL-STD-1760 interconnection system
- Also available in modified but intermateable versions for termination to a host of cables (See chart on next page)

TYPICAL ELECTRICAL PERFORMANCE

Size 8 Concentric Twinax Contacts Voltage Rating: 500 Vrms max. @ sea level Contact Resistance: Center @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Intermediate @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Outer @ 12 Amps, 75 millivolts max. voltage drop @ 25°C Operating Frequency: 0–20 MHz Dielectric Withstanding Voltage: Center to Intermediate: 1000 VAC Rms @ Sea Level Intermediate to Outer: 500 VAC Rms @ Sea Level

SHORT PROFILE TWINAX CONTACT OPTION

A Short Profile size 8 Twinax is available that can be used with a low profile right angle backshell and can offer increased packaging efficiency. Consult Amphenol Aerospace for further information.



MIL-DTL-38999 Series III Connector with Twinax Contacts and Standard Contacts



Concentric Twinax Contacts Size 8



Short Profile Twinax vs Standard Length Twinax Contact

Twinax Contacts for MIL-DTL-38999 General Description, Application Data - Size 8, cont.



SIZE 8 CONCENTRIC TWINAX CONTACTS FOR USE IN D38999 CONNECTORS							
	Size 8 Concentric Part Nu						
For use with	(Termination Inst			Connector			
Cable	Pin	Socket	Comments	Series			
M17/176-00002	21-033190-625 (L-1253-AG)	21-033191-628 (L-1253-AG)	AS39029/113-625 & /114-628 (Amphenol) Supplied with heat shrink seal				
M17/176-00002, 5PTM1T04-2	21-033190-529 (L-1253-A)	21-033191-530 (L-1253-B)	AS39029/90/91 (Amphenol) Supplied with heat shrink seal				
M17/176-00002	T3-46T08-LD (PN-430)	T3-47T08-LD (PN-430)	M39029/90/91 (Pyle) Supplied with heat shrink seal				
M17/176-00002	21-033190-000 (L-1253-A)	21-033191-000 (L-1253-B)	Without seals				
M17/176-00002	21-033190-001 (L-1253-A)	21-033191-001 (L-1253-B)	Supplied with piggyback grommet seal				
Raychem 10612, 5M2022-003	21-033190-026 (L-1253-AA)	21-033191-026†	Without seals				
Raychem 10614, EPD22189B, 7724C8664, 05A0771, GC875TM24H, T10971	21-033190-022 (L-1253-C)	21-033191-022 (L-1253-D)	Without seals				
Raychem 10613, PAN711-6421, 23089/RC	21-033190-027 (L-1253-K)	21-033191-027 (L-1253-L)	Supplied with heat shrink seal				
Raychem 10613, PAN711-6421, 23089/RC	21-033190-029 (L-1253-K)	21-033191-029 (L-1253-L)	Supplied with piggyback grommet seal				
Raychem 10613, PAN711-6421, 23089/RC	21-033190-030 (L-1253-K)	21-033191-030 (L-1253-L)	Without seals				
GSC-12-2548-00, 7726D0664, ASNE 08072003-09	21-033190-040 (L-1253-S)	21-033191-040 (L-1253-T)	Supplied with heat shrink sleeve				
Axon P517417	21-033190-081 (L-1253-W)†	21-033191-081 (L-1253-Y)†	Supplied with piggyback grommet seal				
Raychem 10612, 5M2022-003	21-033190-261 (L-1253-AA)	21-033191-261†	Supplied with piggyback grommet seal				
Raychem 10612, 5M2022-003	21-033190-262 (L-1253-AA)	21-033190-262†	Supplied with heat shrink seal				
Raychem 10614, 7724C8664	T3-46TB08-LD (PN-494)	T3-47TB08-LD (PN-494)	Without seals				
7820D0111 (20 AWG)	T3-467C08-LD (PN-537)	T3-47TC08-LD (PN-537)	Without seals	D38999 Series I, III			
Gore CXN2268	T3-46TE08-LD (PN-1001)	T3-47TE08-LD (PN-1001)	Short profile Supplied with heat shrink seal (.465)				
M17/176-00002	T3-46TD08-LD (PN-1000)	T3-47TD08-LD (PN-1000)	Short profile Supplied with heat shrink seal (.465)				
M17/176-00002	21-033910-015† (PN-1005)	21-033922-015 (PN-1005)	Short profile Without seals (.263)				
M17/176-00002	21-033617-001 (REF PN-100)		Short profile Supplied with piggyback grommet seal (.465)				
Gore CNX2702	T3-46TF08-LD (PN-1002)	T3-47TF08-LD (PN-1002)	Short profile Supplied with heat shrink seal (.465)				
M17/176-00002		P-209546-27†	Short profile Without seals (.303)				
S280W502-1, Fileca F2709-13-CA, HS5930, Raychem 10602 0024G0024, 0024A0024	21-033190-070 (L-1253-U)	21-033191-070 (L-1253-V)	Without seals				
S280W502-1, Fileca F2709-13-CA, HS5930, Raychem 10602 0024G0024, 0024A0024 Tensolite 24463/9P025x-2(LD)	21-033190-071 (L-1253-U)	21-033191-071 (L-1253-V)	Supplied with piggyback grommet seal				
S280W502-1, Fileca F2709-13-CA, HS5930, Raychem 10602 0024G0024, 0024A0024	21-033190-072 (L-1253-U)	21-033191-072 (L-1253-V)	Supplied with heat shrink seal				
0024A0311, PIC E10244	21-033190-090†	21-033191-090 (L-1253-AD)	Without seals				
0024A0311, PIC E1024	21-033190-091†	21-033191-091 (L-1253-AD)	Supplied with piggyback grommet seal				
0024A0311, PIC E1024	21-033190-092†	21-033191-092 (L-1253-AD)	Supplied with heat shrink seal				
M17/176-00002	21-033190-625 (L-1253-AG)	21-033191-628 (L-1253-AG)	M39029/113-625 & /114-628 Supplied with heat shrink seal				

**Termination instructions are packaged with each contact and can be foundon-line at: www.amphenol-aerospace.com/serviceinstructions.asp † Consult Amphenol Aerospace for current release of this contact or instruction sheet if applicable.




Amphenol[®] Triax Contacts - Provide additional shielding when terminated to triax cable having solid or stranded center conductors. Amphenol supplies triax contacts in sizes 8, 10 and 12 and they are ideally suited for use in D38999 Series I, II and III circular

Features and benefits of Amphenol triax contacts include:

connectors.


- Incorporates three conductors, designed for use with triax cableEach of the three conductors are separated by dielectric
- insulation to isolate ground planes
- Shielding effectiveness is improved with two isolated shields
- May be specified for direct connection to printed circuit boards
- May be mixed with coax, twinax and power contacts in a single connector



Cable Illustration - Triax Contact



Triax Size 8 Pin Contact



Triax Size 12 Socket Contact

TYPICAL ELECTRICAL PERFORMANCE

Size 8, 10 and 12 Triax Contacts

Center @ 1 Amp, 120 millivolts max. voltage drop @ 25°C Intermediate @ 1 Amp, 60 millivolts max. voltage drop @ 25°C Outer @ 12 Amps, 90 millivolts max. voltage drop @ 25°C

Operating Frequency: Size 12: 0-30 MHz Size 10: 0-300 MHz Size 8: 0-500 MHz

Dielectric Withstanding Voltage: Center to Intermediate 800 VAC Rms @ Sea Level Intermediate to Outer 500 VAC Rms @ Sea Level

Insulation Resistance: 1000 megohms minimum @ 25°C

For use with Cable	Size	Size 8, 10, 12 Triax Contact Part Number (Termination Instruction Sheet)**		Comments
Cable		Pin	Socket	
5M2397-002, 81264-02, RGX-179, RT-179, Champlain 81-00321A, Tensolite 28883/02060X-1(LD), 7528A5314, Thermatics 12447, 28883/02060X-1, RTG 179, Semflex RT316	8	21-033198-003 (L-1254-F)	21-033197-003 (L-1254-E)	
752866314, 7528G6314	8	21-033198-011 (L-1254-V)	21-033197-011 (L-1254-T)	
5M2559-001, 81264-01, Tensolite 28598/9J063T-1, Teledyne 13809, Cheminax 9530F5214	8	21-033198-004 (L-1254-D)	21-033197-004 (L-1254-C)	
ST5M1323-001, Champlain 81-00700, Teledyne 11914/1, Times AA6603, Tensolite 26895/90334X-1	8	21-033198-010 (L-1254-S)	21-033197-010 (L-1254-S)	
5M2397-002	10	21-033800-001 (L-1256-A)	21-033801-001 (L-1256-B)	
JN1088WU (75Ω), JN1088WT (50Ω)	12	21-033909-012 (L-1256-J)	21-033908-012 (L-1256-J)	JN1104 Interface
GSC-03-81497-00 (75Ω)	12	21-033909-023 (L-1256-M)	21-033908-023 (L-1256-M)	Replaced by -33 with improved rear insulator
GSC-03-81497-00 (75Ω)	12	21-033909-033 (L-1256-P)	21-033908-033 (L-1256-P)	
Harbour TRX179, Times Microwave AA-6151 (RT-179), Axon RGX-179, 540-1050-000 (75Ω)	12	21-033909-071 (L-1256-AA)	21-033908-071 (L-1256-AA)	JN1104 Interface
10602 (Twinax)	8	21-033724-015 (L-1255-C)	(Consult with Amphenol for availability)	Special design with triax mating end and twinax cable termination

**Termination instructions are packaged with each contact and can be found on-line at:

www.amphenol-aerospace.com/serviceinstructions.asp

Coax, Twinax & Triax PC Tail Contacts General Description, Application Data




Amphenol[®] Printed Circuit Tail Contacts

are currently supplied as follows:

- 8, 12 and 16 Coax
- 8, 10 and 12 Twinax
- 8 Triax (socket only)

PC Tail shielded contacts provide a cost effective packaging solution for limited space applications where connectors are attached to printed circuit boards. High reliability is assured with factory pre-assembled contacts and standardization termination to the board. PC Tail contacts are available for MIL-DTL-38999 Series I and III circular connectors and also for ARINC 404, ARINC 600 and R27 rectangular connectors. The following pages (410 & 411) show the available PC Tail contact part numbers for 38999 Circular connectors. See page 420 Rectangular Section of this catalog for information on twinax contacts for ARINC Rectangular connectors along with compatible cable terminations. Consult Amphenol Aerospace for further information on the applicable tooling for these contacts.



PC Tail Coax and Twinax Contacts for Attachment to Printed Circuit Boards

TYPICAL ELECTRICAL PERFORMANCE


Size 8, 12 & 16 PC Tail Coax Contacts Contact Resistance: Center @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Outer @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Operating Frequency: 0–500 MHz Dielectric Withstanding Voltage: Center to Outer 500 VAC Rms @ Sea Level Insulation Resistance 1,000 megohms minimum @ 25°C

TYPICAL ELECTRICAL PERFORMANCE


Size 8, 10 & 12 PC Tail Twinax Contacts Contact Resistance: Center @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Intermediate @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Outer @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Operating Frequency: 0–20 MHz Dielectric Withstanding Voltage: Center to Intermediate 500 VAC Rms @ Sea Level Intermediate to Outer 500 VAC Rms @ Sea Level Insulation Resistance 1,000 megohms minimum @ 25°C

TYPICAL ELECTRICAL PERFORMANCE

Size 8 PC Tail Triax Contacts Contact Resistance: Center @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Intermediate @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Outer @ 1 Amp, 55 millivolts max. voltage drop @ 25°C Operating Frequency: 0–500 MHz Dielectric Withstanding Voltage: Center to Intermediate 500 VAC Rms @ Sea Level Intermediate to Outer 500 VAC Rms @ Sea Level Insulation Resistance 1,000 megohms minimum @ 25°C



Size 8, PC Tail Twinax Socket Contact for use in D38999 Connectors



D38999 Connector with PC Tail Coax Contacts, Sealing Plugs in unused contact cavities and PC Tail Alignment Disc

Amphenol Aerospace

	PC TAIL COAX, TW	INAX, AND TRIAX CON	TACTS FOR USE IN D3	8999 SERIES I & III CON	INECTORS
Size	PC Tail Coax Contact Part Number	PC Tail Twinax Contact Part Number	PC Tail Triax Contact Part Number	Tails*	Comments
8 Pin	21-033733-007			PCB 2 tails	
8 Pin	21-033733-002			PCB 2 tails	For epoxy filled connector
8 Pin	21-033733-004			PCB 2 tails	For epoxy filled connector
8 Pin	21-033733-005			PCB 4 outer tails, 1 inner	
8 Pin	21-033733-009			PCB 2 tails	
8 Pin	21-033733-008			PCB 2 tails	
8 Socket	21-033426-001			PCB 2 tails	
8 Pin		21-033967-115		PCB 3 tails	
8 Pin		21-033967-125		PCB 3 tails	
8 Pin		21-033967-015		PCB 3 tails	
8 Pin		21-033967-045		PCB 3 tails	
8 Pin		21-033967-055		PCB 3 tails	
8 Pin		21-033967-065		PCB 3 tails	
8 Pin		21-033967-085		PCB 3 tails	
8 Pin		21-033967-095		PCB 3 tails	
8 Pin		P-209550†		PCB 3 tails	M39029/90/91 Interface
8 Pin		P-209532-1		PCB 9 tails	
8 Pin		P-209532-2		PCB 9 tails	
8 Socket		21-033921-015		PCB 3 tails	-
8 Socket		21-033921-045		PCB 3 tails	
8 Socket		21-033921-035		PCB 3 tails	
8 Socket		21-033921-065		PCB 3 tails	•
8 Socket		21-033921-075		PCB 3 tails	-
8 Socket		21-033921-115†		PCB 3 tails	
8 Socket		21-033479-001		PCB 3 tails	AS39029/114 Type (with hood)
8 Socket		21-033479-021		PCB 3 tails	AS39029/114 Type (with hood)
8 Socket		21-033921-105†		PCB 3 tails	M39029/90/91 Interface .040 dia. tails
8 Socket		DB-109002		PCB 2 tails	
8 Socket		21-033919-015		PCB 2 tails	M39029/91 Interface Outer body grounded to shel
8 Socket		21-033919-025		PCB 2 tails	Outer body grounded to she
8 Pin			21-033828-001	PCB 3 tails	
3 Pin			21-033828-021	PCB 3 tails	
8 Pin			21-033828-041	PCB 3 tails	
8 Socket			21-033840-001	PCB 3 tails	
8 Socket			21-033840-021	PCB 2 tails	Outer body grounded to shel
8 Socket			21-033841-001	PCB 2 tails	Outer body grounded to shel
10 Pin 12 Socket		21-033844-002†		PCB 2 tails	Outer body grounded to she

* Consult Amphenol Aerospace for tail configurations and tail diameters. † Consult Amphenol Aerospace for current release of this contact.

Coax, Twinax & Triax PC Tail Contacts

Application Data, cont.



	PC TAIL COAX, TW	VINAX, AND TRIA	X CONTACTS FOR	RUSE IN D38999 SERIE	SI&III CONNECTORS
Size	PC Tail Coax Contact Part Number	PC Tail Twinax Contact Part Number	PC Tail Triax Contact Part Number	Tails*	Comments
12 Pin	21-033686-008			PCB 2 tails	
12 Pin	21-033686-009			PCB 2 tails	Output to it align to go
12 Pin	21-033686-005			PCB 2 tails	Outer tail clip type
12 Pin	21-033686-010			PCB 2 tails	
12 Pin	21-033686-013			PCB 2 tails	Outer tail clip type
12 Pin	21-033687-006			PCB 2 tails	For epoxy filled connector
12 Pin	21-033687-007			PCB 2 tails	
12 Pin	21-033686-016†			PCB 2 tails	
12 Socket	21-033614-001			PCB 2 tails	
12 Socket	21-033614-021			PCB 2 tails	
12 Socket	21-033614-041			PCB 2 tails	
12 Socket	21-033611-003			PCB 2 tails	Outer tail clip type
12 Socket	21-033440-001			PCB 3 tails	
12 Socket	21-033430-001			PCB 2 tails	Outer tail clip type, M38999 Series II
12 Socket	21-033430-021			PCB 2 tails	M38999 Series II
12 Socket	21-033430-041				M38999 Series II
12 Pin		21-0336	33-001†**	PCB 4 tails	
12 Pin		21-0336	633-002**	PCB 4 tails	_
12 Pin		21-0336	633-006**	PCB 4 tails	-
12 Pin		21-0336	33-007**	PCB 4 tails	JN1104 Interface
12 Socket		21-0333	893-006**	PCB 4 tails	-
12 Socket		21-0333	893-005**	PCB 4 tails	_
12 Socket		21-0334	33-001**	PCB 4 tails	M38999 Series II, JN1104 Interface
16 Pin	21-033856-015			PCB 2 tails	
16 Pin	21-033856-025			PCB 90 degree, 2 tails	
16 Pin	21-033856-065			PCB 2 tails	
16 Pin	21-033634-015			PCB 1 tail	Outer body grounded to shell
16 Pin	21-033634-035			PCB 1 tail	
16 Pin	21-033634-045			PCB 1 tail	_
16 Pin	21-033386-001			PCB 2 tails	_
16 Socket	21-033857-001			PCB 2 tails	-
16 Socket	21-033857-008			PCB 2 tails	Outer body grounded to shell
16 Socket	21-033857-007			PCB 2 tails	
16 Socket	21-033610-001			PCB 2 tails	1
16 Socket	21-033610-002			PCB 2 tails	1
16 Socket	21-033441-001			PCB 2 tails	1
16 Socket	21-033606-001			PCB 2 tails	
16 Socket	21-033606-021†			PCB 2 tails	M38999 Series II
16 Socket	21-033606-031†			PCB 2 tails	1
16 Socket	21-033610-003			PCB 2 tails	
16 Socket	21-033857-003			PCB 2 tails	

* Consult Amphenol Aerospace for tail configurations and tail diameters. ** Size 12 twinax and triax contacts are intermatable.

† Consult Amphenol Aerospace for current release of this contact.

Amphenol Aerospace

Insert Arrangements - MIL-DTL-38999 Incorporating Coax, Twinax and Triax Contacts

Front face of pin inserts illustrated

Front face of pin inserts illustrated					
			$\begin{pmatrix} c \oplus \oplus_A \\ \oplus_B \end{pmatrix}$		
Insert Arrangement	9-5	10-2 11-2	12-3 13-3	12-4 13-4	14-4 15-4
Connector Series	тv	SJT LJT, TV	JT LJT	JT, SJT LJT, TV	JT LJT
Service Rating	Grounded	I	П	I	I
Number of Contact	1	2	3	4	4
Contact Size	8 Twinax	16	16	16	12

		$ \begin{array}{c} \Theta^{L} & \Theta^{L} & \Theta^{B} \\ \Theta^{L} & \Theta^{M} & \Theta^{B} \\ \Theta^{J} & \Theta^{R} & N \Theta & \Theta \\ \Theta^{J} & \Theta^{P} & \Theta^{P} \\ \Theta^{L} & \Theta^{L} & \Theta^{P} \\ \Theta^{L} & \Theta^{L} & \Theta^{L} \\ \Theta$	$ \begin{array}{c} & \oplus & \oplus^{A} \oplus_{B} \\ & \oplus & \oplus_{B} \\ & \oplus & \oplus \oplus_{C} \\ & \oplus & \oplus_{D} \end{array} \end{array} $	$ \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} $	
Insert Arrangement	14-5 15-5	14-15 15-15	14-68 15-68	14-97 15-97	16-6 17-6
Available in Connector Series	JT, SJT LJT, TV	JT, SJT LJT, TV	JT LJT	JT, SJT LJT, TV	JT, SJT LJT, TV
Service Rating	II	I	I	I	I
Number of Contact	5	14 1	8	8 4	6
Contact Size	16	20 16	16	20 16	12

	$ \begin{array}{c} $	$\begin{matrix} \overset{K}{\to} & \overset{R}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} \\ \overset{J}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} \\ \overset{R}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} \\ \overset{R}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} & \overset{R}{\oplus} \\ \overset{R}{\oplus} & \overset$	$ \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} $		
Insert Arrangement	16-8 17-8	16-13 17-13	16-99 17-99	17-2 17-22	16-6 17-6
Connector Series	JT, SJT LJT, TV	JT, SJT LJT	JT, SJT LJT, TV	LJT TV	LJT TV
Service Rating	Ш	I	I	Μ	Coax
Number of Contact	8	13	21 2	38 1	2 2
Contact Size	16	16	20 16	22D 8	12 8

	(1000000000000000000000000000000000000	$ \begin{array}{c} \overset{J}{\oplus} \oplus \overset{\Phi^{A}}{\oplus} \\ \overset{H}{\oplus} & \overset{K}{\oplus} \oplus \overset{\Phi^{B}}{\oplus} \\ \overset{G}{\oplus} & \overset{L}{\oplus} \oplus \overset{\Phi^{C}}{\oplus} \\ \overset{F}{\oplus} \oplus \overset{\Phi^{D}}{\oplus} \\ \end{array} $	$\begin{array}{c} \begin{array}{c} & & \\ & & \\ & \\ & \\ & \\ & \\ & \\ & \\ & $	$\begin{array}{c} & & & \\$	$ \begin{array}{c} \begin{array}{c} & & \\$
Insert Arrangement	17-25	18-11 19-11	18-28 19-28	18-30 19-30	19-31
Connector Series	LJT	JT, SJT LJT, TV	JT LJT	JT LJT	τν
Service Rating	М	Ш	I	I	М
Number of Contact	22 2	2 11	26 2	29 1	2 1 12
Contact Size	22D 8	3 16	20 16	20 16	8 12 22D

The insert arrangements shown on this page and the next page represent the most readily available patterns within the 38999 Circular Series. If you require other arrangements than what are shown here, consult Amphenol for further availability. In most cases, unless otherwise stated, size 8 and size 12 cavities can be filled with either coax, twinax, triax or power contacts.

CONTACT LEGEND


	0	Θ	\oplus	θ	٢
8	10	12	16	20	22D
Coax/Twinax/ Triax or Power	Twinax/Triax/ or Power	Coax/Twinax/ Triax or Power	Coax or Power	Power	Power


Insert Patterns - MIL-DTL-38999 Incorporating Coax, Twinax and Triax Contacts



Front face of pin inserts illustrated

[$ \begin{array}{c} \overset{L}{ \oplus} \overset{\oplus}{ \oplus} \overset{A}{ \oplus} \overset{\oplus}{ \oplus} \overset{B}{ \oplus} \overset{C}{ \oplus} \overset{C}{ \oplus} \overset{D}{ \oplus} \overset{D}{\overset{D}}{ \oplus} \overset{D}{ & \overset{D}{\overset{D}{ & \overset{D}{ & & \overset{D}{ & \overset{D}{ & \overset{D}{ & \overset{D}{ & \overset{D}{ & \overset{&} & \overset{D}{\overset{&} & \overset{D}{\overset{&} & \overset{D}{\overset{&} & \overset{&} & & & \overset{&} & & & & & & & & & & & & & & & & & & $		$ \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\ \end{array} \\ \end{array} \\ \begin{array}{c} \end{array} \\ \end{array} \\$	$ \begin{array}{c} I \bigoplus \bigoplus_{A} \\ K \bigoplus \bigoplus^{M} \bigoplus_{B} \\ J \bigoplus^{S} \bigoplus \bigoplus^{N} \bigoplus_{C} \\ H \bigoplus^{B} \bigoplus^{P} \bigoplus^{P} \bigoplus_{D} \\ G \bigoplus_{F} \bigoplus_{E} \end{array} $
Insert Arrangement	18-68 19-68	18-96	20-11 21-11	20-16 21-16
Connector Series	JT LJT	JT	JT, SJT LJT, TV	JT, SJT LJT, TV
Service Rating	I	I.	L	П
Number of Contact	18	9	11	16
Contact Size	16	12	12	16






Insert Arrangement		23-54		23-97	23-99	24-4 25-4	
Connector Series		тν		LJT	LJT	JT, SJT LJT, TV	
Service Rating		М		II	II	I	
Number of Contact	40	9	4	16	11	48 8	
Contact Size	22D	16	12	16	16	20 16	

CONTACT LEGEND (\bigcirc) \oplus θ ø 10 22D 8 12 16 20 Coax/Twinax/ Twinax/Triax/ Coax/Twinax/ Coax or Power Power Triax or Power or Power Triax or Power

Power

Amphenol Aerospace Insert Patterns - MIL-DTL-38999 Incorporating Coax, Twinax and Triax Contacts sө θB RФ θc ₽ ብ ⊕⊤ ⊕ z⊕ ⊕,⊕ ₄⊖ Ð, ⊕ Ð vӨ Θ_{v} θ ę Ð Ð Ð٢ ⊕¢ Ð, ⊕. Ð 24-20 Insert Arrangement 24-19 25-19 25-20* 24-24 25-24 **Connector Series** JT, SJT LJT, TV SJT LJT, TV JT, SJT LJT, TV Ν Service Rating I I Number of Contact 19 12 12 10 13 3 4 Contact Size 12 20 16 8 12 16 12 (Locations U and Y - Dedicated to Fiber Optics) ⊕́ ⊕^B Ð Ð ₽⊕ Ð т⊕ ⊕° °⊕ nĤ Æ ě Ф ₫ Ĕ, ₽⊕ Φr sФ ⊕Ľ Φ ė ₽ θu ዀ Ð Ĥ Ð Ð Ð Ъ́ф Ð ⊕ ⊕ ⊕[×] ⊕⊧ в⊕ Ð a⊕ ф ĥ Ð Ð٧ ⊕ ₽ $\oplus^{\mathsf{m}} \oplus^{\mathsf{Y}} \oplus_{\mathsf{L}}$ ₽ Ð ₽ Ð ⊕r ⊕^a⊕^z ⊕, Ð Ð ⊕w Ð, °Ф Ð Ð Ð Ð b⊕ Ð ⊕x °⊕ ₽ ₽ Ð ⊕G ⊕ ⊕к Ð Ð Æ Insert Arrangement 24-29 25-29 24-37 25-37 24-43 25-43 **Connector Series** JT, SJT LJT, TV JT, SJT LJT, TV JT, SJT LJT, TV Service Rating I I 1 Number of Contact 29 37 23 20 Contact Size 16 16 20 16



Connector Series SJT LJT, TV LJT, TV Ν Service Rating I Number of Contact 2 2 9 40 4 20 10 Contact Size 20 8 16

* For use in MIL-STD-1760 applications with MIL-DTL-38999 Series III.

CONTACT LEGEND

	0	Θ	\oplus	θ	0
8	10	12	16	20	22D
Coax/Twinax/ Triax or Power	Twinax/Triax/ or Power	Coax/Twinax/ Triax or Power	Coax or Power	Power	Power

MIL-DTL-5015, MIL-DTL-22992 Circular

Connector Overview



Amphenol's medium to heavy weight circular include the MS/Standard MIL-DTL-5015 series and the heaviest weight, largest size circular is the Heavy Duty MIL-DTL-22992 series. These time-tested circulars have been used for several years. They are dependable general duty and environmentally resistant connectors for military and industrial applications.

Shielded coax contacts, although more popularly used in 38999 types and 26482 types, can be incorporated into some arrangements of the 5015 and 22992 type circulars. Shielded coaxial contacts within these series are considered MS modifications to the MIL-spec connector and the coax contacts are pre-installed in the connector. Normal operating voltage with power contacts only is up to 3000 VAC (RMS) at sea level for MIL-DTL-5015 circulars. The Heavy Duty types are designed for high current capacity and have current ratings (with power contacts only) of up to 200 amps.

Standard and Heavy Duty Circular offer these features for contact termination flexibility:

- Insert arrangements that can incorporate:
- Size 4, 8 & 12 Crimp Coax contacts, pre-installed in the connector
- · Wide selection of connector shell styles and sizes
- Standard power contact options within the various connector styles include: solder type, crimp front release, crimp rear release
- Coax contacts are designed to the same high performance standards as power contacts. Coax and power contacts may be intermixed with no degradation of connector reliability.

Amphenol[®] MS/Standard Circular

MIL-DTL-5015* Type Connector Family: See MS/Standard catalog 12-020 for complete information on these styles MS-A, MS-C, MS-E, MS-F, MS-R

- Produced in strict accordance with MIL-DTL-5015
- Threaded coupling, solder or crimp rear insertion contacts (coax available in crimp type only)
- Class A, Solid Shell intended for general connector usage
- Class C, Pressurized for use on pressurized bulkheads or pressure barriers
- Class E/F, Environmental Resisting ideally suited for installation where condensation, vibration and rapid changes in pressure or temperature are considerations
- Class R, Lightweight Environmental Resisting shorter in length and lighter in weight than Class E

MS/Standard MIL-DTL-5015 Type Connectors



Heavy Duty QWLD, MIL-DTL-22992 Connectors

Amphenol® Heavy Duty Circular MIL-DTL-22992 Connector Family: QWLD

- Designed for most power and control circuits
- Military MIL-DTL-22992 qualified versions and proprietary equivalents See Catalog 12-052 for complete information on these styles.
- QWL
- A more compact heavy duty design for industrial power and control applications
- See Catalog 12-053 for complete information on these styles.

GENERAL ORDERING INFORMATION

Amphenol MS/Standard MIL-DTL-5015 type and Heavy Duty MIL-DTL-22992 type circulars are normally supplied with a full complement of power contacts, separately packaged. Coax contacts are ordered by part number as referenced in the part number charts on the following pages of this catalog, and are substituted for the power contacts at the time of the cable or equipment assembly. Coax contacts are pre-installed in these series. Installation instructions for the coax contacts for these series are provided in Amphenol document L-650. HOW TO ORDER:

- 1. Select the coax contacts designed for the cable being used from the chart on page 409 of this catalog. Select a connector insert from those shown on page 44 which will accommodate the quantity and size of coaxial contacts needed plus any power contacts required.
- Determine the MS/Standard or Heavy Duty Series style desired. (See features of each series referenced above). The catalog referenced for each series will guide you in determining shell style, finish, service class and insert rotation required for your application. MS/Standard MIL-DTL-5015 Type Connectors (Catalog 12-020 on-line at www.amphenol-industrial.com) Catalog 12-052 - MIL-DTL-22992 QWLD Connectors (on-line at www.amphenol-aerospace.com) Catalog 12-053 - QWL Connectors (currently not on-line; consult Amphenol Aerospace for hardcopy)
- 3. Consult Amphenol, Sidney, NY with the pertinent cable, contact, insert arrangement and connector style choices for complete connector part number.

* Amphenol also offers the following other MIL-DTL-5015 Circular Connectors which are threaded coupling

- (consult Amphenol Industrial for availability of shielded contacts in any of these series):
- Amphenol®/Matrix® MIL-DTL-5015 with crimp rear releasable and rear insertable contacts. (See Matrix 5015 section of this catalog)
- Amphenol® MIL-DTL-5015 Modifications (Ask for Industrial Catalog 12-021)
- Amphenol[®] GT Series with reverse bayonet coupling (Ask for Catalog 12-024)
 Amphenol[®] AC Threaded and AC-B Bayonet Series
- (Ask for Industrial Catalog 12-025)

NOTE: MIL-DTL-5015 supersedes MIL-C-5015 MIL-DTL-22992 supersedes MIL-C-22992



Amphenol[®] Coaxial Contacts- can be incorporated into MS/Standard MIL-DTL-5015 Type Circular Connectors and Heavy Duty MIL-DTL-22992 Connectors. They offer the same durability advantages and design benefits for reliable interconnection as the Amphenol coax contacts used in high performance D38999 connectors. A variety of military and commercial shielded cables are accommodated within these circular series.

Other features of the coax contacts available for MS/Standard and Heavy Duty circulars include:

- Several insert arrangements that can incorporate: •
- Size 4, 8 and 12 coax contacts
- Advanced shielding wire technology in a rugged military connector
- Single connector with multiple coaxial connection eliminates cross-mating
- Positive contact captivation especially important in these series with its much higher coupling/uncoupling force
- Older shielded cable type availability



Coax Contact, Pin for use in MS/Standard MIL-DTL-5015 and Heavy Duty MIL-DTL-22992 Connectors



Coax Contact, Socket for use in MS/Standard MIL-DTL-5015 and Heavy Duty MIL-DTL-22992 Connectors

TYPICAL ELECTRICAL PERFORMANCE

Size 4, 8 & 12 Contacts Contact Resistance: Center @ 1 Amp, 170 millivolts max. voltage drop @ 25°C Outer @ 12 Amps, 150 millivolts max. voltage drop @ 25°C **Dielectric Withstanding Voltage:** Size 4 & 8: 1,300 VAC Rms @ sea level Size 12: 1,000 VAC Rms @ sea level Size 4, 8 & 12: 250 VAC Rms @ 50,000 ft. Insulation Resistance 5,000 megohms minimum @ 25°C

All contacts in these series are non-impedance matched contacts.

Part numbers 21-033063-XX() and 21-033064-XX() are moisture seal design (internal O-ring).

CONTACT FINISHES:


Suffix Finish

1

- 0.00020 min. silver over copper flash
- 0.00005 min. gold (Knoop hardness 130-200) over silver 2
- 0.00010 min. gold (Knoop hardness 130-200) over silver 3
- 4 0.00010 min. gold (Knoop hardness 130-200) over copper
- 0.00005 min. gold (Knoop hardness 130-200) over nickel 5
- 0.00005 min. gold (Knoop hardness 90 max.) over copper 0.00005 min. gold (Knoop hardness 130-200) over copper
- E F
- н 0.00010 min. gold (Knoop hardness 130-200) over copper

Coaxial Contacts for MIL-DTL-5015, Heavy Duty MIL-DTL-22992 Application Data





NOTE: All contacts of the same size and the same inner and outer contact diameters (G & H) will mate with each other.

	COAX CONTACTS For use in MS/Standard MIL-DTL-5015 Type and Heavy Duty MIL-DTL-22992 Type Connectors												
	(See L-650	art Number Termination		Finish			nsional awings			Crimp Ferrule Tools			
Cable	Instruction contacts lis	Sheet for all ted below)**	Size	on Mating		н	F	Lenç	L gth Ref.				Retainer Nut
	Pin	Socket		Parts (See Pg. 42)	G Dia.	Dia. ± 0.001	Across Flats ±0.004	Pin	Socket	MIL-T-22910/7-1 Tool Use with Die Part Number	MIL-T-22520/5-01 Tool Use with Die Part Number	MIL-T-229520/10-01 Tool Use with Die Part Number	Wrench
RG-58C/U, RG-141A/U, RG-303/U	21-033014-001 21-033034-002 21-033048-002 21-033016-005 21-033130-002()	21-033013-001 21-033033-002 21-033047-002 21-033015-005 21-033129-002()	8 8 8 8 8	5 1 †† 3 ***	0.0355 ± 0.0010	0.218	0.280	1.481	1.511	M22910/7-15 (B)	M22520/5-05 (B) M22520/5-41 (B)	M22520/10-07 (B)	11-8676-2
RG-59B/U, RG-62A/U, RG-62B/U, RG-210/U	21-033014-005 21-033016-002 21-033034-005 21-033130-005() 21-033064-021()	21-033013-005 21-033015-002 21-033033-005† 21-033129-005() 21-033063-021()	8 8 8 8	5 3 1 ****	0.0355 ±0.0010	0.218	0.280	1.481	1.511	M22910/7-18 (B)) M22520/5-45 (E		11-8676-3
	21-033060-010()	21-033059-010()	4	***	0.0400 ± 0.0010	0.344	0.375	1.669	1.605				11-8676-4
RG-161/U, RG-174A/U, RG-179B/U, RG-187A/U,	21-033014-003 21-033016-001 21-033034-003 21-033130-003()† 21-033064-020()†	21-033013-003 21-033015-001 21-033033-003 21-033129-003()† 21-033063-020()†	8 8 8 8 8	5 3 1 ***	0.0355 ±0.0010	0.218	0.280	1.481	1.511	M22910/7-12 (B)	M22520/5-03 (A) M22520/5-08 (A)	M22520/10-05 (A)	11-8676-2
RG-188A/U, RG-316/U	21-033014-021 21-033034-001 21-033048-001 21-033130-001()†	21-033013-021 21-033033-001 21-033047-001 21-033129-001()†	12 12 12 12	5 1 ****	0.0200 ±0.0005	0.128	0.172				M22520/5-35 (B)		11-8676-1
RG-178B/U, RG-196A/U	21-033014-022†	21-033013-022†	12	5	0.0200 ± 0.0005	0.128	0.172	1.481	1.511	M22910/7-11 (B)	M22520/5-03 (B) M22520/5-33 (B)	M22520/10-05 (B)	11-8676-1
RG-180B/U, RG-195A/U	21-033014-006 21-033034-006† 21-033048-003 21-033130-006()†	21-033013-006 21-033033-006† 21-033047-003 21-033129-006()	8 8 8 8	5 1 ****	0.355 ± 0.0010	0.218	0.280	1.481	1.511	M22910/7-15 (B)	M22520/5-05 (B) M22520/5-41 (B)	M22520/10-07 (B)	11-8676-2
RG-212/U	21-033060-011()	21-033059-011()	4	***	0.0625 ±0.0010	0.344	0.375	1.669	1.605	M22910/7-14 (A)	M22520/5-39 (A)		11-8676-4
RG-140/U, RG-302/U	21-033014-008 21-033034-008 21-033130-008()†	21-033013-008 21-033033-008 21-033129-008()†	8 8 8	5 1 ***	0.0355 ±0.0010	0.218	0.280	1.481	1.511	M22910/7-17 (B)	M22520/5-05 (A) M22520/5-19 (B)	M22520/10-07 (A)	11-8676-2
RG-55B/U, RG-142A/U, RG-142B/U,	21-033014-004 21-033034-004 21-033130-004()	21-033013-004 21-033033-004 21-033129-004()	8 8 8	5 1 ***	0.0355 ±0.0010	0.218	0.280	1.481	1.511	M22910/7-17 (B)	M22520/5-05 (A) M22520/5-19 (B)	M22520/10-07 (A)	11-8676-2
RG-223/U	21-033060-102()	21-033059-012()	4	***	0.0625 ±0.0010	0.344	0.375	1.669	1.605				11-8676-4


***See finish options for MS/Standard and Heavy Duty contacts listed on page 416. Replace the parenthesis of the contact part number with the finish suffix number. However, you should consult Amphenol Aerospace regarding the availability of all finish choices for each part number. † Consult Amphenol Aerospace for current availability of this contact. CRIMPING TOOLS: Italicized letters in parenthesis that follow positioner part numbers indicate applicable die closure. Commercial equivalents with the same die closure dimension may be used. †† 21-033047-X and 21-033048-X are supplied with E (soft gold) finish on mating socket parts, and F (hard gold) finish on mating pin parts.**Termination instruction sheet L-650 can be found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp


Insert Patterns - Standard MIL-DTL-5015, Heavy Duty MIL-DTL-22992


Incorporating Coax Contacts

Front face of pin inserts illustrated


Amphenol Aerospace










Insert Arrangement	16-10	18-10	18-16	20-4
Connector Series	MS/Standard, QWLD, QWL	MS/Standard, QWLD, QWL	MS/Standard, QWLD, QWL	MS/Standard, QWLD, QWL
Service Rating	А	A	С	D
Number of Contact	3	4	1	4
Contact Size	12	12	12	12










Insert Arrangement	28-6	28-11	1	32-	8
Connector Series	MS/Standard, QWLD, QWL	MS/Standard, Q	WLD, QWL	MS/Standard,	QWLD, QWL
Service Rating	D	А		А	
Number of Contact	3	4	18	6	24
Contact Size	4	12	16	12	16

The insert arrangements shown on this page represent the most readily available patterns within the MIL-DTL-5015 and MIL-DTL-22992 Series. If you require other arrangements than what are shown here, consult Amphenol for further availability. MS/Standard connectors have over 200 insert pattern arrangements available, and within these patterns any size 4, 8 or 12 contact cavities can be incorporated with coax contacts. However, you need to consult Amphenol, Sidney NY for availability and ordering information. All coax contacts in the Standard and Heavy Duty series come pre-installed in connectors.



Rectangular Rack & Panel Connectors

That Incorporate High Speed Contacts



Amphenol provides an impressive array of Rectangular Interconnection products to meet the needs of high density systems such as opto-electrical backplanes used in many applications that include: medical equipment, IC chip testers, telecommunications, military and commercial aviation, military ground vehicles, GPS systems, space and industrial applications.

- ARINC 600 and R27 Rack and Panel connectors can incorporate:
 - size 8 Coax contacts
 - Size 1 and size 5 Coax (consult Amphenol Canada)
 - Size 12 Twinax contacts
 - · Size 8 Quadrax contacts
 - · Size 8 Differential Twinax contacts

ARINC 600 Rack and Panel Rectangular Connectors See Amphenol Canada Publication SL-379, ARINC 600 Rack and Panel Connectors for complete information.

- The ARINC 600 is the successor to the ARINC 404 for many of the new avionics designs and offers lower mating force contacts, increased contact count and a front release, floating keying system
- ARINC 600 Connectors are a recognized standard rack and panel connector for aircraft applications with both environmental and non-environmental versions available
- · Designed to meet all relevant ARINC 600 connector specifications
- Front removable keying posts
- · Up to 800 size 22 contact positions in one connector
- Contact options: standard contacts are power/signal crimp rear release in sizes 12, 16, 20 and 22 in crimp or PCB; or shielded coax, concentric twinax, quadrax contacts; or fiber optics
- Waveguide connections


R27 Rack and Panel Rectangular Connectors

See Amphenol Canada Publication for R27 Series Connectors for complete information.


- The R27 Series is a robust rectangular connector designed to meet or surpass all the requirements of the MIL-DTL-83527 specification and EN 3682 European Standard.
- Well suited for harsh environments enhanced environmental sealing, robust and durable shells, EMI shielding spring
- Filtered or non-filtered
- Connectors, shells, inserts, termination modules and contacts are sold separately or fully assembled
- · Interchangeable insert patterns with ARINC 600 models
- Contact options: standard contacts are power/signal crimp rear release in sizes 12, 16, 20 and 22 in crimp or PCB; or shielded coax, concentric twinax, quadrax contacts; or fiber optics




Coax Contact, Size 8 for use in ARINC Rack and Panel Connectors



ARINC 600 Rack and Panel Connectors are high density connectors that can incorporate high speed shielded contacts



R27 Series Rack and Panel Connector can incorporate high speed shielded contacts



Quadrax Contact , Size 8 for use in ARINC Rack and Panel Connectors

ARINC 600 & R27 Rack and Panel Connectors

QUADRAX CONTACTS FOR USE IN ARINC 600 & R27 CONNECTORS						
.	Contact Part Number (Termination Instruction Sheet)**		Impedance	Contact	Crimping Tools	
Cable	Pin	Socket	(Ohms)	Size	Inner Contact	Outer Contact
Tensolite NF24Q100-01, 24443/9P025X-4(LD), S280W502-4, 24443/03130X-4(LD)	21-033382-021 (L-2119-AH)	21-033383-021 (L-2119-AH)	100		M22520/2-01 with Positioner Daniels K709	M22520/5-01 With Die Set M22520/5-45 (Location B)
Draka Fileca F-4703-3	21-033382-031 (L-2119-I)	21-033383-031 (L-2119-I)	100		(M22520/2-37)	
Draka Fileca F-4704-5, NF22Q100	21-033382-101 (L-2119-AS)†	21-033383-101 (L-2119-AS)†	100	8		
JSFY02-1	21-033382-071 †	21-033383-071 †	110			
Tensolite 26473/02006X-4(LD), Gore RCN8328	21-033382-061 (L-2119-L)	21-033383-061 (L-2119-L)	150		M22520/2-01 with Positioner Daniels K709 (M22520/2-37)	M22520/5-01 with Die Set M22520/5-45 (Location A)

DIFFERENTIAL TWINAX CONTACTS FOR USE IN ARINC 600 & R27 CONNECTORS						
Cable	Contact Part Number (Termination Instruction Sheet)**		Impedance	Contact	Crimping Tools	
	Pin	Socket	(Ohms)	Size	Inner Contact	Outer Contact
ABS0386WF24	21-033378-021 (L-2119-G)	21-033379-021 (L-2119-G)	100	- 8	M22520/2-01 with Positioner Daniels K709 (M22520/2-37)	M22520/5-01 with Die Set M22520/5-45 (Location A & B)
ASNE0272TK22	21-033378-031 (L-2119-G)	21-033379-031 (L-2119-G)	100			
ASNE0272TK24	21-033378-041 (L-2119-G)	21-033379-041 (L-2119-G)	100			
Tensolite 24463/9P025X-2(LD)	21-033378-051 †	21-033379-051 †	100			
GC875TM24H	21-033378-061 (L-2119-AU)	21-033379-061 (L-2119-AU)	77			
	21-033378-071 †	21-033379-071 †	110			

COAX CONTACTS FOR USE IN ARINC 600 & R27 CONNECTORS						
Cable	Contact Part Number (Termination Instruction Sheet)**		Contact	Crimping Tools		
Cubic	Pin	Socket	Size	Inner Contact	Outer Contact	
RG-179	21-033676-001 (L-2090-B)	21-033675-001 (L-2090-A)		M22520/2-01 with Positioner K1275	M22520/10-01 with Die Set M22520/10-05 (A)	
RG-179	21-033476-001	21-033475-001	8			
5M2869-001	21-033676-002 †	21-033675-002 †				

TWINAX CONTACTS FOR USE IN ARINC 600 & R27 CONNECTORS					
Cable	Contact Pa (Termination Inst		Contact Size	CrimpingTools	
Cubic	Pin	Socket		Inner Contact	Outer Contact
EPD 32263, 10612, GSC-12-2548-00	21-033631-004† (L-2092-U)†	21-033632-003 (L-2092-J)	12	MH992 with Positioner K1365	GS200-1 with Positioner GP959

PCB QUADRAX CONTACTS FOR USE IN ARINC 600 & R27 CONNECTORS					
PCB	Contact Part Number Impedance Contact				
Quadrax Contacts	Pin	Socket	Impedance (Ohms)	Size	
PCB (.346 Length)		21-033397-171	100	8	
PCB (.473 Length)	21-033398-261		100	5	

† Consult Amphenol Aerospace for current release of this contact or instruction sheet if applicable.

Daniels crimping tools are available from Daniels Mfg. Corp. 6103 Anno Ave., Orlando, FL 32809 **Termination instructions are packaged with each contact and can be

found on-line at: www.amphenol-aerospace.com/serviceinstructions.asp

Additional Contact Styles from Amphenol



Amphenol has today's broadest range of interconnection solutions for military, commercial and industrial applications. As a worldwide interconnection product leader, Amphenol can meet not only connector needs, but also contact needs of all types. In addition to the shielded and high frequency contacts shown in this publication, Amphenol offers many other contact styles:

PRINTED CIRCUIT BOARD SIGNAL AND POWER CONTACTS

See the Printed Circuit Board section of this catalog.

THERMOCOUPLE CONTACTS

Available for MIL-DTL-5015, MIL-DTL-22992, MIL-DTL-26482, MIL-DTL-26500, MIL-DTL-38999, MIL-DTL-83723 and other series connectors. Thermocouples are designed for temperature measuring applications, and are available in both pin and socket configurations in alumel, chromel, iron and constantan materials. Please refer to the mil series sections in this catalog.

FLEX TERMINATION ASSEMBLIES FOR PCB APPLICATION

Flex circuits are available for MIL-DTL-38999, MIL-DTL-5015 and MIL-DTL-26482, as well as for special products such as EMI/EMP filter connectors and rectangular LRM connectors. Please contact an Amphenol Sales Person for more information or visit www.amphenol-aerospace.com/support to find a sales person in your area.

FIBER OPTIC TERMINI

See the Fiber Optic section of this catalog

FILTER PITYPE TUBULAR AND PLANAR ARRAY CONTACT ASSEMBLIES

See the Printed Circuit Board section of this catalog.

RADSOK® HIGH POWER CONTACTS

Amphenol's RADSOK[®] contact design is a hyperbolic, stamped grid configuration within the socket cylinder. As the male pin is inserted, axial members in the female socket half deflect, imparting high current flow across the connection with minimal voltage loss. Another advantage of the RADSOK[®] contact is low insertion force. The RADSOK[®] contact has been incorporated into three of the large industrial families of connectors; the GT series, the P-Lok series and 5015 types. These connectors, known as Amphe-Power[®] connectors, can handle up to 150% higher amperages. Amphenol Industrial Operations division also provides a wide range of power to board interconnects utilizing the RADSOK[®] technology. These provide high amperage connection to busbars, wires and circuit boards.

RADSOK[®] contacts are being further introduced into military/aerospace products. High power RADSOK[®] is now developed into applications for engine connectors for Commercial Air, and are also being designed into LRM interconnects for high speed data transfer. See Amphenol Industrial Brochure, SL-391. (visit www. amphenol-industrial.com)

See more information on RADSOK® in options, other products section of this catalog pages.

RECTANGULAR CONNECTORS

Amphenol provides an impressive array of Rectangular Interconnection products to meet the needs of high density systems such as opto-electrical backplanes used in many applications that include: medical equipment, IC chip testers, tele-communications, military and commercial aviation, military ground vehicles, GPS systems, space and industrial applications.

Available in Low Mating Force with Brush contacts, Power Strip, LRM, ARINC 600 Rack and Panel, and R27 Rack and Panel Rectangular Connectors.

For more information please contact an Amphenol Sales Person on visit www. amphenol-aerospace.com/support for a sales person in your area.



PC Tails Signal and Power Contacts and Custom PC Tail Designs. Compliant Pin (Press Fit) Contacts for Solderless Mounting to PC Boards



Sculptured Flex Circuits



RADSOK® High Power Contacts and Connectors



LRM Connectors with Inserts of Staggered Brush Contacts and Inserts of Coax Contacts



Guide for Selecting High Frequency Contacts and Cables

		Date				
The following check list is provided to help y frequency contact and cable system, and it	will help our design	Amphenol Salesperson				
team to meet your requirements. You may co to Amphenol Aerospace 607-563-5157, atte Or call 607-563-5011 or 800-678-0141 for a	ention Contact Design.	CONNECTOR INFORMATION				
		Connector Far	nily: TV-R LJT-R JT-R			
CUSTOMER INFORMATION		Other				
Customer Company Name		_ Insert Arrange	ment Desired			
Engineer Name		,				
Program		_ Shell Plating_				
Forecast		CONTAC	T INFORMATION			
CABLE INFORMATION			ial 🗌 Concentric Twinax 🗌 Triax 🗌			
Cable Part Number*		Differe	ential Twinax* 🗌 Quadrax* 🗌			
Cable Manufacturer		Size*: 8 12 16				
Cable Type: Coaxial Twinax		Contact Impedance Matched? Yes No				
Triax 🗌 🛛 Quadrax 🗌		50Ω 75Ω 100Ω 150Ω Other				
Cable Impedance		_	d Differential Twinax currently available in			
* if not an RG-Number complete below informa	ation:	size 8 only.				
O.D. of Inner Wire	AWG of Inner Wires					
No. of Inner Wire Strands	Material of Inner Wires					
O.D. of Inner Insulation	Material of Inner Insulatio	n				
O.D. of First Braid	Braid Type(flat, rou	und. wrap)	Braid AWG			
O.D. of First Jacket	Jacket Material					
O.D. of Second Braid	Braid Type(flat, rou	und, wrap)	Braid AWG			
O.D. of Second Jacket						
It is essential that a 3 foot sample of the cable b	be supplied for performance	e and crimp tool de	velopment.			
PERFORMANCE INFORMATIO	N					
Electrical Protocol						
VSWR Requirement 1. to 1.	Cross Talk	db				
Operating Frequency	Attenuation		Insertion Loss			
Operating VoltageVA	AC (RMS)	DC				
Current Outer Contact Amp	Cı	<u>urrent Inner</u> O kumip ad	ots			
Application Temperature	Environmental Requirem	ent				

58 Contact Amphenol Aerospace for more information at 800-678-0141 • www.amphenol-aerospace.com

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Amphenol:

10-497623-04510-497623-08510-497623-15510-497643-01521-033101-02421-033102-02321-033321-00521-033470-00121-033875-00121-033321-00921-033837-04121-033908-2821-033123-54621-033384-03110-628485-258N21-033384-02121-033909-2321-033321-00721-033967-5521-033102-02121-033121-56321-033397-03121-033122-54621-033908-02821-033385-08110-497623-14510-497623-075