

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0432550083](#)  
**Status:** **Active**  
**Overview:** [MLX Power Connectors](#)  
**Description:** 6.35mm Pitch MLX Power Connector Header, 2.13mm Contact Diameter, Vertical, with Plastic Polarizing Peg, 6 Circuits, Polyester 94V-0, Tin (Sn) Plating, Natural

**Documents:**

<a href="#">Drawing (PDF)</a>	<a href="#">Packaging Specification PK-43255-001-001 (PDF)</a>
<a href="#">3D Model</a>	<a href="#">Packaging Specification PK-43255-003-001 (PDF)</a>
<a href="#">3D Model (PDF)</a>	<a href="#">Datasheet (PDF)</a>
<a href="#">Product Specification PSX-42002-0001-001 (PDF)</a>	<a href="#">RoHS Certificate of Compliance (PDF)</a>



*Series image - Reference only*

**Agency Certification**

CSA	LR19980
UL	E29179

**General**

Product Family	PCB Headers
Series	<a href="#">43255</a>
Application	Board-to-Board, Power, Wire-to-Board
Comments	High Vibration Application
Overview	<a href="#">MLX Power Connectors</a>
Product Name	MLX
UPC	800754855082

**Physical**

Breakaway	No
Circuits (Loaded)	6
Circuits (maximum)	6
Color - Resin	Natural
Durability (mating cycles max)	50
First Mate / Last Break	No
Flammability	94V-0
Glow-Wire Capable	No
Keying to Mating Part	Yes
Lock to Mating Part	Yes
Mated Height	10.16mm
Material - Metal	Phosphor Bronze
Material - Plating Mating	Tin
Material - Plating Termination	Tin
Material - Resin	Polyester
Net Weight	3.872/g
Number of Rows	2
Orientation	Vertical
PC Tail Length	4.30mm
PCB Locator	Yes
PCB Retention	Yes
PCB Thickness - Recommended	1.60mm
Packaging Type	Tray
Pitch - Mating Interface	6.35mm
Pitch - Termination Interface	6.35mm
Polarized to Mating Part	Yes
Polarized to PCB	Yes
Shrouded	Fully
Stackable	No
Surface Mount Compatible (SMC)	No
Temperature Range - Operating	-55° to +105°C

**EU ELV**

**Not Relevant**

**EU RoHS**

**Compliant**

**REACH SVHC**

Not Contained Per -  
D(2020)9139-DC (19  
January 20

**Halogen-Free**

**Status**

**Not Low-Halogen**

For more information, please visit [Contact US](#)

China ROHS

ELV

RoHS Phthalates

**China RoHS**

Green Image

Not Relevant

Not Contained

**Search Parts in this Series**

[43255](#) Series

**Mates With**

[42021](#) MLX Power Crimp Housing Plug,  
[42023](#) MLX Crimp Terminal, [42024](#) MLX  
Crimp Terminal

Termination Interface: Style Through Hole

**Electrical**

Current - Maximum per Contact 20.0A, 9.0A  
Voltage - Maximum 600V

**Solder Process Data**

Duration at Max. Process Temperature (seconds) 010  
Lead-free Process Capability WAVE  
Process Temperature max. C 260

**Material Info**

**Reference - Drawing Numbers**

Packaging Specification PK-43255-001-001, PK-43255-003-001  
Product Specification PSX-42002-0001-001  
Sales Drawing SDA-43255-00XX

This document was generated on 02/12/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[43255-0083](#)