


# **Dimensions: [mm]**












Scale - 6:1

### **Product Marking:**


Marking	XP

# **Recommended Land Pattern: [mm]**



Scale - 6:1

### **Schematic:**



## **Electrical Properties:**

Properties		Test conditions	Value	Unit	Tol.			
DC Operating Voltage	V <sub>DC</sub>		16	V	max.			
(Reverse) Breakdown Voltage	$V_{BR}$	1 mA	18.75	V	±5%			
Clamping Voltage	V <sub>Clamp</sub>	I <sub>PEAK</sub>	26	٧	max.			
(Reverse) Peak Pulse Current	I <sub>Peak</sub>	10/1000 μs	15.4	А	max.			
Leakage Current	I <sub>Leak</sub>	V <sub>DC</sub>	1	μΑ	max.			
Steady State Power Dissipation	P <sub>Diss</sub>	T <sub>A</sub> = 50 °C	3.3	W	max.			
Power Dissipation 1)	P <sub>Diss</sub>	10/1000 μs	400	W	max.			
Polarity	Bidirectional							

<sup>1)</sup> Mounted on 5.0 mm x 5.0 mm (0.03 mm thick) Copper Pads to each terminal

### **Certification:**

RoHS Approval	Compliant [2011/65/EU&2015/863]					
REACh Approval	Conform or declared [(EC)1907/2006]					
Halogen Free	Conform [JEDEC JS709B]					
Halogen Free	Conform [IEC 61249-2-21]					
UL Approval	UL497B: E478010, UL 1449: E332875					
Plastic Housing Flammability Rating	UL94 V-0					

### **General Information:**

CHECKED

RoD

REVISION

001.002

Operating Temperature	-65 up to +150 °C				
Storage Conditions (in original packaging)	< 40 °C; < 75 % RH				
Moisture Sensitivity Level (MSL)	1				
Test conditions of Electrical Properties: +20 °C, 33 % RH if not specified differently					

GENERAL TOLERANCE

DIN ISO 2768-1m

PROJECTION METHOD

Reach REACH REACH HALOGEN SWEET STATE OF THE STATE OF THE

eiSos@we-online.com


DESCRIPTION
WE-TVSP Power TVS Diode

TECHNICAL REFERENCE
SMAJ16CA
ORDER CODE
824501161


DATE (YYYY-MM-DD)


2023-04-12

## **Maximum Peak Pulse Power Rating:**




# **Peak Pulse Power and Current Derating:**







### **Steady State Power Dissipation Derating:**





# **Typical Junction Capacitance:**







# Packaging Specification - Tape and Reel: [mm]










CHECKED

SIZE/TYPE

DO-214AC

RoD



W1 close to center

W3

A (mm)	B (mm)	C D N (mm)					W3 W3 (mm)		Material			
± 2,0	min.	min.	min.	min.	+ 2,0	max.	min.	max.				
178,00	1,50	12,80	20,20	50,00	12,40	18,40	11,90	15,40	Polystyrene/ Polyurethane			

GENERAL TOLERANCE


BUSINESS UNIT

eiSos

DIN ISO 2768-1m

Packaging is referred to the international standard IEC 60286-3:2019

Таре Туре	A0 (mm)	B0 (mm)	W (mm)	T (mm)	T1 (mm)	T2 (mm)	KO (mm)	P0 (mm)	P1 (mm)	P2 (mm)	DO (mm)	D1 (mm)	E1 (mm)	E2 (mm)	F (mm)	Material	Qty. (pcs.)
	typ.	typ.	+0,3/ -0,1	ref.	max.	typ.	typ.	±0,1	±0,1	±0,05	+0,1/-0,0	min.	±0,1	min.	±0,05		
2a	2,79	5,33	12,00	0,25	0,10	2,55		4,00	4,00	2,00	1,50	1,50	1,75	10,25	5,50	Polystyrene	1000



 Pull-off force

 Tape width
 12 mm
 0,1 N - 1,3 N



WURTH ELEKTRONIK MORE THAN YOU EXPECT Würth Elektronik eiSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germany

Tel. +49 (0) 79 42 945 - 0 www.we-online.com eiSos@we-online.com WE-TVSP Power TVS Diode

REVISION

001.002

DATE (YYYY-MM-DD)

2023-04-12

TECHNICAL REFERENCE
SMAJ16CA

Valid

ORDER CODE

PROJECTION METHOD

**824501161**STATUS PAGE

4/7

This electronic component has been designed and developed for usage in general electronic equipment only. This product is not authorized for use in equipment only. This product is reasonably expected to cause severe personal injury or death, unless the parties have executed an agreement specifically governing such use. Moreover Würth Elektronik elSos GmbH & Co KG products are neither designed nor intended for use in areas such as military, aerospace, aviation, nuclear control, submarine, transportation, transportation, transportation retwork etc.. Würth Elektronik elSos GmbH & Co KG must be informed about the intent of such usage before the design-in stage. In addition, sufficient reliability evaluation checks for safety must be performed on every electronic component which is used in electrical circuits that require high safety and reliability functions or performance.

# **Classification Reflow Profile for SMT components:**



## **Classification Reflow Soldering Profile:**

Profile Feature		Value					
Preheat Temperature Min	T <sub>s min</sub>	150 °C					
Preheat Temperature Max	T <sub>s max</sub>	200 °C					
Preheat Time $t_s$ from $T_{s  min}$ to $T_{s  max}$	t <sub>s</sub>	60 - 120 seconds					
Ramp-up Rate (T <sub>L</sub> to T <sub>P</sub> )		3 °C/ second max.					
Liquidous Temperature	T <sub>L</sub>	17 °C					
Time t <sub>L</sub> maintained above T <sub>L</sub>	t <sub>L</sub>	0 - 150 seconds					
Peak package body temperature		$T_p \le T_c$ , see Table below					
Time within 5°C of actual peak temperature	t <sub>p</sub>	20 - 30 seconds					
Ramp-down Rate (T <sub>P</sub> to T <sub>L</sub> )		6 °C/ second max.					
Time 25°C to peak temperature		8 minutes max.					

refer to IPC/ JEDEC J-STD-020E

# Package Classification Reflow Temperature (T<sub>c</sub>):

Properties	Volume mm³ <350	Volume mm <sup>3</sup> 350-2000	Volume mm³ >2000		
PB-Free Assembly I Package Thickness < 1.6 mm	260 °C	260 °C	260 °C		
PB-Free Assembly   Package Thickness 1.6 mm - 2.5 mm	260 °C	250 °C	245 °C		
PB-Free Assembly   Package Thickness > 2.5 mm	250 °C	245 °C	245 °C		

refer to IPC/ JEDEC J-STD-020E

B O A				CHECKED			PROJECTION METHOD	<b>-</b>	
ROHS REACH HALLOGEN COMPLIANT COMPLIANT FREE		WE-TVSP Power TVS Diode					TECHNICAL REFERENCE SMAJ16CA		
WÜRTH ELEKTRONIK	Würth Elektronik elSos GmbH & Co. KG EMC & Inductive Solutions Max-Eyth-Str. 1 74638 Waldenburg Germann					0RDER CODE 824	501161		
MORE THAN YOU EXPECT	ORE THAN Tel. +49 (0) 79 42 945 - 0  OU EXPECT www.we-online.com elSos@we-orline.com				BUSINESS UNIT eiSos	status Valid		PAGE 5/7	

### **Cautions & Warnings:**

# The following conditions apply to all goods within the product series of WE-TVSP of Würth Elektronik eiSos GmbH & Co. KG:

#### General:

- This electronic component is designed and developed with the intention for use in general electronic equipment.
- Würth Elektronik must be asked for a written approval (following the certain PPAP procedure) before incorporating the components into
  any equipment in the field such as military, aerospace, aviation, nuclear control, submarine, transportation, (automotive control, train
  control, ship control), transportation signal, disaster prevention, medical, public information network etc. where higher safety and
  reliability are especially required and/or if there is the possibility of direct damage or human injury.
- Electronic components that will be used in safety-critical or high-reliability applications, should be pre-evaluated by the customer.
- The component is designed and manufactured to be used within the datasheets specified values. If the usage and operation conditions specified in the datasheet are not met, the wire insulation may be damaged or dissolved.
- Do not drop or impact the components, the component may be damaged
- Würth Elektronik products are qualified according to international standards, which are listed in each product reliability report. Würth
  Elektronik does not warrant any customer qualified product characteristics beyond Würth Elektroniks' specifications, for its validity and
  sustainability over time.
- The responsibility for the applicability of the customer specific products and use in a particular customer design is always within the
  authority of the customer. All technical specifications for standard products also apply to customer specific products.

### **Product specific:**

### Soldering:

- The solder profile must comply with the technical product specifications. All other profiles will void the warranty.
- · All other soldering methods are at the customer's own risk.

#### **Cleaning and Washing:**

 Washing agents used during the production to clean the customer application might damage or change the characteristics of the body, the marking or the plating. Washing agent may have a negative effect on the long term functionality of the product.

#### Pottina:

If the product is potted in the customer application, the potting material might shrink or expand during and after hardening. Shrinking
could lead to an incomplete seal, allowing contaminants into the component body, pins or termination. Expansion could damage the
components. We recommend a manual inspection after potting to avoid these effects.

### **Storage Conditions**

- A storage of Würth Elektronik products for longer than 12 months is not recommended. Within other effects, the terminals may suffer
  degradation, resulting in bad solderability. Therefore, all products shall be used within the period of 12 months based on the day of
  shipment.
- Do not expose the components to direct sunlight.
- The storage conditions in the original packaging are defined according to DIN EN 61760-2.
- The storage conditions stated in the original packaging apply to the storage time and not to the transportation time of the components.


#### **Packaging:**

 The packaging specifications apply only to purchase orders comprising whole packaging units. If the ordered quantity exceeds or is lower than the specified packaging unit, packaging in accordance with the packaging specifications cannot be ensured.

#### **Handling:**

- Violation of the technical product specifications such as exceeding the nominal rated current will void the warranty.
- The TVSP Diode is not designed for voltage stabilization with continuous power dissipation.
- The exposure of steam, saline spray, atmosphere with reduced oxygen content, corrosive gases, rain or condensation and direct sunlight shall be prohibited.
- Signals operated continuously with a high ratio of direct-current voltage might have an influence on the product life time.
- The temperature rise of the component must be taken into consideration. The operating temperature is comprised of ambient temperature and temperature rise of the component. The operating temperature of the component shall not exceed the maximum temperature specified.

These cautions and warnings comply with the state of the scientific and technical knowledge and are believed to be accurate and reliable. However, no responsibility is assumed for inaccuracies or incompleteness.



### **Important Notes**

# The following conditions apply to all goods within the product range of Würth Elektronik eiSos GmbH & Co. KG:

### 1. General Customer Responsibility

Some goods within the product range of Würth Elektronik eiSos GmbH & Co. KG contain statements regarding general suitability for certain application areas. These statements about suitability are based on our knowledge and experience of typical requirements concerning the areas, serve as general guidance and cannot be estimated as binding statements about the suitability for a customer application. The responsibility for the applicability and use in a particular customer design is always solely within the authority of the customer. Due to this fact it is up to the customer to evaluate, where appropriate to investigate and decide whether the device with the specific product characteristics described in the product specification is valid and suitable for the respective customer application or not.

### 2. Customer Responsibility related to Specific, in particular Safety-Relevant Applications

It has to be clearly pointed out that the possibility of a malfunction of electronic components or failure before the end of the usual lifetime cannot be completely eliminated in the current state of the art, even if the products are operated within the range of the specifications. In certain customer applications requiring a very high level of safety and especially in customer applications in which the malfunction or failure of an electronic component could endanger human life or health it must be ensured by most advanced technological aid of suitable design of the customer application that no injury or damage is caused to third parties in the event of malfunction or failure of an electronic component. Therefore, customer is cautioned to verify that data sheets are current before placing orders. The current data sheets can be downloaded at www.we-online.com.

#### 3. Best Care and Attention

Any product-specific notes, cautions and warnings must be strictly observed. Any disregard will result in the loss of warranty.

#### 4. Customer Support for Product Specifications

Some products within the product range may contain substances which are subject to restrictions in certain jurisdictions in order to serve specific technical requirements. Necessary information is available on request. In this case the field sales engineer or the internal sales person in charge should be contacted who will be happy to support in this matter.

#### 5. Product R&D

Due to constant product improvement product specifications may change from time to time. As a standard reporting procedure of the Product Change Notification (PCN) according to the JEDEC-Standard inform about minor and major changes. In case of further queries regarding the PCN, the field sales engineer or the internal sales person in charge should be contacted. The basic responsibility of the customer as per Section 1 and 2 remains unaffected.

### 6. Product Life Cycle

Due to technical progress and economical evaluation we also reserve the right to discontinue production and delivery of products. As a standard reporting procedure of the Product Termination Notification (PTN) according to the JEDEC-Standard we will inform at an early stage about inevitable product discontinuance. According to this we cannot guarantee that all products within our product range will always be available. Therefore it needs to be verified with the field sales engineer or the internal sales person in charge about the current product availability expectancy before or when the product for application design-in disposal is considered. The approach named above does not apply in the case of individual agreements deviating from the foregoing for customer-specific products.

### 7. Property Rights

All the rights for contractual products produced by Würth Elektronik eiSos GmbH & Co. KG on the basis of ideas, development contracts as well as models or templates that are subject to copyright, patent or commercial protection supplied to the customer will remain with Würth Elektronik eiSos GmbH & Co. KG does not warrant or represent that any license, either expressed or implied, is granted under any patent right, copyright, mask work right, or other intellectual property right relating to any combination, application, or process in which Würth Elektronik eiSos GmbH & Co. KG components or services are used.

#### 8. General Terms and Conditions

Unless otherwise agreed in individual contracts, all orders are subject to the current version of the "General Terms and Conditions of Würth Elektronik eiSos Group", last version available at www.we-online.com.

