



NOTES:

1. METALSHELLS: COPPER ALLOY; min. 315µin TIN over 40-80µin NICKEL
2. INSULATORS: PBT GF UL 94 V-0; GREEN
3. SIGNAL CONTACTS: COPPER ALLOY
PLATING: 30µin HARD GOLD over min. 50µin NICKEL
SOLDER CUP ACCEPTS CABLE AWG 20
4. NO CONTACTS ON POS. A1 and A2
5. UL APPROVED UNDER E228329
6. CONNECTOR IS PART MARKED: 3007W2PCM99A10X CONEC ABC

Directive 2002/95/EC RoHS compliant

THIS DRAWING MAY NOT BE COPIED OR REPRODUCED IN ANY WAY, AND MAY NOT BE PASSED ON TO A THIRD PARTY WITHOUT WRITTEN PERMISSION. OWNERSHIP AND COPYRIGHT OF CONEC GmbH DO NOT ALTER CAD DRAWING BY HAND				tolerance		scale: 2:1 (5:1)			
				date	name	material: SEE NOTES			
				drawn	08.05.02	Parei			
				appd.	08.05.02	E.Mickenbecker			
				norm					
				3 x c	Ä3935	15.03.2011	K.H.	d-old	title: D-SUB COMBINATION MALE 7W2P SOLDER CUP
			1 x b	Ä3231	19.12.2008	Lehmen	dwg no: Inventor 10		DIN-A3
			a	Origin			7K1A562		sh: 1
			rev.	description	date	name	part no: 3007W2PCM99A10X		

