

[illegible]

Technical drawing of the 120x120x80 mm cube, showing two views: a front view (left) and a side view (right).

Dimensions:

- Top View (Front View):**
 - Overall width: 120 mm
 - Overall height: 80 mm (Gesamthöhe / total height)
 - Inner width: 32 mm
 - Inner height: 10 mm ($\phi 10$)
 - Bottom flange width: 5 mm
 - Bottom flange height: 4 mm
- Side View:**
 - Overall width: 40 mm
 - Overall height: 113 mm (max. Einbauhöhe / max. assembly height)
 - Bottom flange width: 3 mm

Assembly Details:

- The front view shows a central hole with a diameter of $\phi 5$ mm.
- The side view shows a central hole with a diameter of $\phi 10$ mm.
- The bottom flange is secured with two screws (indicated by circles 5 and 6).

Zylinderschraube M6 x 45/10
ähnl. DIN EN ISO 7045/
cylinder screw M6 x 45/10
similar to DIN EN ISO 7045

ABS-Gehäuse können durch eine andere Schwindung ca. 0,1-0,25% größer sein als gezeichnete PC-Gehäuse/
Due to a different shrinkage rate of the plastic material, ABS enclosures can be about 0.1 - 0.25% bigger than the PC enclosures shown in the drawing.