

1N4460 - 1N4496 and 1N6485 - 1N6491

RoHS						
Available on						
commercial						
versions						

VOIDLESS HERMETICALLY SEALED 1.5 WATT GLASS ZENER DIODES Qualified per MIL-PRF-19500/406

DESCRIPTION

This Zener voltage regulator series is military qualified to MIL-PRF-19500/406 and is ideal for high-reliability applications where a failure cannot be tolerated. These industry-recognized 1.5 watt Zener voltage regulators are hermetically sealed with void-less glass construction using an internal metallurgical bond. It includes Zener selections from 3.3 to 200 volts in standard 5% tolerance. 1% and 2% tolerance versions are also available. Microsemi also offers numerous other Zener products to meet higher and lower power ratings in both thru-hole and surface mount packages.

Important: For the latest information, visit our website http://www.microsemi.com.

FEATURES

- Popular JEDEC registered series.
- Void-less hermetically sealed glass package.
- Triple-layer passivation.
- Extremely robust construction.
- Internal "Category 1" metallurgical bonds for 1N4462 thru 1N4496 and "Category III" for 1N6485 thru 1N6491 as well as 1N4460 and 1N4461.
- JAN, JANTX, JANTXV and JANS qualifications are available per MIL-PRF-19500/406.
- RoHS compliant versions available (commercial grade only).

APPLICATIONS / BENEFITS

- Regulates voltage over a broad operating current and temperature range.
- Extensive selection from 3.3 to 200 V.
- Standard voltage tolerances are plus/minus 5% with no suffix.
- Tighter tolerances available in plus or minus 2% or 1%.
- Flexible axial-lead mounting terminals.
- Non-sensitive to ESD per MIL-STD-750 method 1020.
- Inherently radiation hard as described in Microsemi MicroNote 050.

MAXIMUM RATINGS @ T_A= 25°C unless otherwise specified

Parameters/Test Conditions	Symbol	Value	Unit	
Junction and Storage Temperatur	T _J & T _{STG}	-65 to +175	°C	
Steady State Power Dissipation @ L = .375 inch (9.53 mm)	PD	1.5	W	
Thermal Resistance Junction-to-L (9.52 mm) from body	R _{ƏJL}	42	°C/W	
Thermal Impedance @ 10 ms	1N4462 – 1N4496 1N6485 – 1N6491 1N4460 – 1N4461	Z _{θJX}	Figure 3 Figure 4 Figure 4	°C/W
Forward Voltage	@ 200 mA @ 1.0 A	VF	1.0 1.5	V
Solder Temperature @ 10 s	T _{SP}	260	°C	

<u>Qualified Levels</u>: JAN, JANTX, JANTXV and JANS



DO-41 Package

Also available in:



MSC – Lawrence

6 Lake Street, Lawrence, MA 01841 Tel: 1-800-446-1158 or (978) 620-2600 Fax: (978) 689-0803

MSC – Ireland

Gort Road Business Park, Ennis, Co. Clare, Ireland Tel: +353 (0) 65 6840044 Fax: +353 (0) 65 6822298

Website:

www.microsemi.com




1N4460 - 1N4496 and 1N6485 - 1N6491

MECHANICAL and PACKAGING

- CASE: Hermetically sealed voidless hard glass with tungsten slugs.
- TERMINALS: Tin/lead (Sn/Pb) or RoHS compliant matte/tin (commercial grade only) over copper.
- MARKING: Body coated in blue with part number.
- POLARITY: Cathode indicated by band.
- TAPE & REEL option: Standard per EIA-296. Consult factory for quantities.
- WEIGHT: 340 milligrams.
- See <u>Package Dimensions</u> on last page.

PART NOMENCLATURE



SYMBOLS & DEFINITIONS								
Symbol	Definition							
Vz	Zener Voltage: The Zener voltage the device will exhibit at a specified current (I _Z) in its breakdown region.							
Ι _Ζ , Ι _{ΖΤ} , Ι _{ΖΚ}	Regulator Current: The dc regulator current (I_z), at a specified test point (I_{ZT}), near breakdown knee (I_{ZK}).							
Z_{ZT} or Z_{ZK}	Dynamic Impedance: The small signal impedance of the diode when biased to operate in its breakdown region at a specified rms current modulation (typically 10% of I_{ZT} or I_{ZK}) and superimposed on I_{ZT} or I_{ZK} respectively.							
VF	Maximum Forward Voltage: The maximum forward voltage the device will exhibit at a specified current.							
I _R	Maximum Reverse Current: The maximum reverse (leakage) current that will flow at the specified voltage and temperature.							
I _{ZM}	Maximum Regulator (Zener) Current: The maximum rated dc current for the specified power rating.							
I _{ZSM}	Maximum Zener Surge Current: The non-repetitive peak value of Zener surge current at a specified wave form.							



ELECTRICAL CHARACTERISTICS @ 25 °C Case temperature

ТҮРЕ	NOMINAL ZENER VOLTAGE Vz	TEST CURRENT I _{ZT}	MAXIMUM DYNAMIC IMPEDANCE Z _{ZT} @ I _{ZT}	MAXIMUM KNEE IMPEDANCE Z _{ZK} @ I _{ZK}		MAXIMUM REVERSE CURRENT I _R @ V _R		MAXIMUM CONTINUOUS CURRENT I _{ZM}	SURGE CURRENT @ 8.3 ms square wave
	Volts	mA	Ohms	Ohms	mA	μA Volts		(Note 1) mA	I _{ZSM} Amps
1N4460	6.2	40.0	4	200	1.0	10.0	3.72	230	2.3
1N4461	6.8	37.0	2.5	200	1.0	5.0	4.08	210	2.0
1N4462	7.5	34.0	2.5	400	.5	1.0	4.50	191	1.9
1N4463	8.2	31.0	3	400	.5	.50	4.92	174	1.7
1N4464	9.1	28.0	4	500	.5	.30	5.46	157	1.6
1N4465	10.0	25.0	5	500	.25	.30	8.00	143	1.4
1N4466	11.0	23.0	6	550	.25	.30	8.80	130	1.3
1N4467	12.0	21.0	7	550	.25	.20	9.60	119	1.2
1N4468	13.0	19.0	8	550	.25	.05	10.4	110	1.1
1N4469	15.0	17.0	9	600	.25	.05	12.0	95	.95
1N4470	16.0	15.5	10	600	.25	.05	12.8	90	.90
1N4471	18.0	14.0	11	650	.25	.05	14.4	79	.79
1N4472	20.0	12.5	12	650	.25	.05	16.0	71	.71
1N4473	22.0	11.5	14	650	.25	.05	17.6	65	.65
1N4474	24.0	10.5	16	700	.25	.05	19.2	60	.60
1N4475	27.0	9.5	18	700	.25	.05	21.6	53	.53
1N4476	30.0	8.5	20	750	.25	.05	24.0	48	.48
1N4477	33.0	7.5	25	800	.25	.05	26.4	43	.43
1N4478	36.0	7.0	27	850	.25	.05	28.8	40	.40
1N4479	39.0	6.5	30	900	.25	.05	31.2	37	.37
1N4480	43.0	6.0	40	950	.25	.05	34.4	33	.33
1N4481	47.0	5.5	50	1000	.25	.05	37.6	30	.30
1N4482	51.0	5.0	60	1100	.25	.05	40.8	28	.28
1N4483	56.0	4.5	70	1300	.25	.25	44.8	26	.26
1N4484	62.0	4.0	80	1500	.25	.25	49.6	23	.23
1N4485	68.0	3.7	100	1700	.25	.25	54.4	21	.21
1N4486	75.0	3.3	130	2000	.25	.25	60.0	19	.19
1N4487	82.0	3.0	160	2500	.25	.25	65.6	17	.17
1N4488	91.0	2.8	200	3000	.25	.25	72.8	16	.16
1N4489	100.0	2.5	250	3100	.25	.25	80.0	14	.14
1N4490	110.0	2.3	300	4000	.25	.25	88.0	13	.13
1N4491	120.0	2.0	400	4500	.25	.25	96.0	12	.12
1N4492	130.0	1.9	500	5000	.25	.25	104.0	11	.11
1N4493	150.0	1.7	700	6000	.25	.25	120.0	9.5	.095
1N4494	160.0	1.6	1000	6500	.25	.25	128.0	8.9	.089
1N4495	180.0	1.4	1300	7000	.25	.25	144.0	7.9	.079
1N4496	200.0	1.2	1500	8000	.25	.25	160.0	7.2	.072
1N6485	3.3	76.0	10	400	1.0	50	1.0	433	4.2
1N6486	3.6	69.0	10	400	1.0	50	1.0	397	3.9
1N6487	3.9	64.0	9	400	1.0	35	1.0	366	3.6
1N6488	4.3	58.0	9	400	1.0	5.0	1.0	332	3.3
1N6489	4.7	53.0	8	500	1.0	4.0	1.0	304	3.0
1N6490	5.1	49.0	7	500	1.0	1.0	1.0	280	2.7
1N6491	5.6	45.0	5	600	1.0	0.5	2.0	255	2.5

NOTE: 1. See "<u>Maximum Ratings</u>" for P_D temperature conditions for leaded package where I_{ZM} is applicable.



GRAPHS




FIGURE 2 Temperature-Power Derating Curve

Downloaded from Arrow.com.



GRAPHS (continued)




FIGURE 3 Thermal Impedance Curve for 1N4462 through 1N4496





FIGURE 4 Thermal Impedance Curve for 1N6485 through 1N6491 and 1N4460 through 1N4461

T4-LDS-0183, Rev. 3 (120901)



PACKAGE DIMENSIONS



NOTES:

- 1. Dimensions are in inches.
- 2. Millimeters are given for general information only.
- 3. Package contour optional with BD and length BL. Heat slugs, if any, shall be included within this cylinder length but shall not be subject to minimum limit of BD.
- 4. The specified lead diameters apply in the zone between .050 inch (1.27 mm) from the diode body and the end of the lead.
- 5. In accordance with ASME Y14.5M, diameters are equivalent to Φx symbology.

Ltr	IN	СН	MILLIM	Notes	
	Min	Max	Min	Max	
BD	.060	.085	1.52	2.16	3
BL	.106	.160	2.69	4.06	3
LD	.028	.032	0.71	0.81	
LL	.800	1.300	20.32	33.02	
LU		.050		1.27	4