



VOLTAGE RANGE: 50 - 1000V
CURRENT: 3.0 A

Features

- Diffused Junction
- Low Forward Voltage Drop
- High Current Capability
- High Reliability
- High Surge Current Capability

Mechanical Data

- Case: DO-201AD, Molded Plastic
- Terminals: Plated Leads Solderable per MIL-STD-202, Method 208
- Polarity: Cathode Band
- Weight: 1.2 grams (approx.)
- Mounting Position: Any
- Marking: Type Number



| DO-201AD | | |
|----------------------|-------|------|
| Dim | Min | Max |
| A | 25.40 | — |
| B | 8.50 | 9.53 |
| C | 0.96 | 1.06 |
| D | 4.80 | 5.21 |
| All Dimensions in mm | | |

Maximum Ratings and Electrical Characteristics T_A = 25°C unless otherwise specified

Single phase, half wave, 60Hz, resistive or inductive load. For capacitive load, derate current by 20%.

| Characteristic | Symbol | UF 5400 | UF 5401 | UF 5402 | UF 5403 | UF 5404 | UF 5406 | UF 5407 | UF 5408 | Unit |
|---|---------------------|-------------|---------|---------|---------|---------|---------|---------|---------|------|
| Peak Repetitive Reverse Voltage | V _{RRM} | 50 | 100 | 200 | 300 | 400 | 600 | 800 | 1000 | V |
| Working Peak Reverse Voltage | V _{RWM} | | | | | | | | | |
| DC Blocking Voltage | V _R | | | | | | | | | |
| RMS Reverse Voltage | V _{R(RMS)} | 35 | 70 | 140 | 210 | 280 | 420 | 560 | 700 | V |
| Average Rectified Output Current (Note 1) @T _A = 55°C | I _O | 3.0 | | | | | | | | A |
| Non-Repetitive Peak Forward Surge Current 8.3ms Single half sine-wave superimposed on rated load (JEDEC Method) | I _{FSM} | 150 | | | | | | | | A |
| Forward Voltage @I _F = 3.0A | V _{FM} | 1.0 | | | 1.3 | | 1.7 | | | V |
| Peak Reverse Current @T _A = 25°C At Rated DC Blocking Voltage @T _A = 100°C | I _{RM} | 10 100 | | | | | | | | μA |
| Reverse Recovery Time (Note 2) | t _{rr} | 50 | | | | 75 | | | | nS |
| Typical Junction Capacitance (Note 3) | C _j | 80 | | | | 50 | | | | pF |
| Operating Temperature Range | T _j | -65 to +125 | | | | | | | | °C |
| Storage Temperature Range | T _{STG} | -65 to +150 | | | | | | | | °C |

Note: 1. Leads maintained at ambient temperature at a distance of 9.5mm from the case
 2. Measured with I_F = 0.5A, I_R = 1.0A, I_{RR} = 0.25A. See figure 5.
 3. Measured at 1.0 MHz and applied reverse voltage of 4.0V D.C.




Fig. 1 Forward Current Derating Curve




Fig. 2 Typical Forward Characteristics




Fig. 3 Peak Forward Surge Current






Fig. 4 Typical Junction Capacitance



- Notes:
1. Rise Time = 7.0ns max. Input Impedance = 1.0MΩ, 22pF.
 2. Rise Time = 10ns max. Input Impedance = 50Ω.



Set time base for 5/10ns/cm

Fig. 5 Reverse Recovery Time Characteristic and Test Circuit