



Search within category GO

PN10-14R-2K



Ring Terminal, nylon insulated, metal sleeve, 12 – 10 AWG, 1/4" stud size.

BUY NOW

DESIGN / INSTALL

Specs Packaging Details Documents [★ Add to Favorites](#) [Add to BOM](#)

Stud Size	1/4"
Wire Range	12 AWG - 10 AWG
Wire Range (mm ²)	4.0 - 6.0
Barrel Configuration	Standard
Barrel Type	Insulation Grip Sleeve
Base Material	Copper
Insulation	Nylon
Panduit Color Code	Yellow
Plating Type	Tinned
Part Number Series	PN
Clearance	0.38
Clearance (mm)	9.7
Length (In.)	1.21
Length (mm)	30.7
Max. Insulation Diameter In. (mm)	0.225 (5.7)
Stock	0.04
Stock (mm)	1.0
Width (In.)	0.52
Width (mm)	13.2
Wire Strip Length (In.)	9/32" (.2812)
Wire Strip Length (mm)	7.1
Flammability Rating	UL 94V-2/HB
Max. Voltage Rating	600 V
Temperature Rating	221 Degrees Fahrenheit (105 Degrees Celsius)
CA-800/EZ Series Crimp Die	CD-800-3
CA9 Series Crimp Die	CD9-3B
Tool	CA9 Applicator, CA-800EZ Applicator
CSA Certified	C22.2 No. 65
Mil. Std. Part Number	MS25036-157 (Class 2)
UL Listed	UL 486A - UL 486B
Packaging Type	Reel
Key Features	• Continuously molded design provides reliable, consistent performance through the

applicator for a high quality termination every time • Ring tongue design assures a secure connection in high vibration applications • Metal insulation grip sleeve crimps to wire insulation, providing protection to the crimp joint during high vibration applications • Internal barrel serrations assure good wire contact and maximum tensile strength

Pieces Per Reel 2000

RoHS Compliancy Status Compliant

Min. Order Qty. 2,000

[LEGAL INFORMATION](#) | [PRIVACY POLICY](#) | [CONTACT US](#) | [SITE MAP](#) | [WHERE TO BUY](#) | [JOBS](#) | [UNSUBSCRIBE](#)