



## Surface Mount Glass Passivated Junction Fast Switching Rectifier

**SUPERECTIFIER®**



**DO-213AA (GL34)**

### FEATURES

- Superectifier structure for high reliability condition
- Ideal for automated placement
- Fast switching for high efficiency
- Meets MSL level 1, per J-STD-020, LF maximum peak of 260 °C
- AEC-Q101 qualified
- Material categorization: For definitions of compliance please see [www.vishay.com/doc?99912](http://www.vishay.com/doc?99912)



**RoHS**  
COMPLIANT

### TYPICAL APPLICATIONS

For use in fast switching rectification of power supply, inverters, converters, and freewheeling diodes for consumer, automotive, and telecommunication.

### MECHANICAL DATA

**Case:** DO-213AA, molded epoxy over glass body  
Molding compound meets UL 94 V-0 flammability rating  
Base P/N-E3 - RoHS- compliant, commercial grade  
Base P/NHE3 - RoHS-compliant, AEC-Q101 qualified

**Terminals:** Matte tin plated leads, solderable per J-STD-002 and JESD 22-B102

E3 suffix meets JESD 201 class 1A whisker test, HE3 suffix meets JESD 201 class 2 whisker test

**Polarity:** Two bands indicate cathode end - 1<sup>st</sup> band denotes device type and 2<sup>nd</sup> band denotes repetitive peak reverse voltage rating

PRIMARY CHARACTERISTICS	
$I_{F(AV)}$	0.5 A
$V_{RRM}$	50 V, 100 V, 200 V, 400 V, 600 V, 800 V
$I_{FSM}$	10 A
$t_{tr}$	150 ns, 250 ns
$V_F$	1.3 V
$T_J$ max.	175 °C
Package	DO-213AA (GL34)
Diode variation	Single die

MAXIMUM RATINGS ( $T_A = 25\text{ °C}$ unless otherwise noted)								
PARAMETER	SYMBOL	RGL34A	RGL34B	RGL34D	RGL34G	RGL34J	RGL34K	UNIT
<b>FAST SWITCHING DEVICE: 1<sup>st</sup> BAND IS RED</b>								
Polarity color bands (2 <sup>nd</sup> band)		Gray	Red	Orange	Yellow	Green	Blue	
Maximum repetitive peak reverse voltage	$V_{RRM}$	50	100	200	400	600	800	V
Maximum RMS voltage	$V_{RMS}$	35	70	140	280	420	560	V
Maximum DC blocking voltage	$V_{DC}$	50	100	200	400	600	800	V
Maximum average forward rectified current at $T_T = 55\text{ °C}$	$I_{F(AV)}$	0.5						A
Peak forward surge current 8.3 ms single half sine-wave superimposed on rated load	$I_{FSM}$	10						A
Maximum full load reverse current, full cycle average $T_A = 55\text{ °C}$	$I_{R(AV)}$	30						$\mu$ A
Operating junction and storage temperature range	$T_J, T_{STG}$	- 65 to + 175						°C



ELECTRICAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)									
PARAMETER	TEST CONDITIONS	SYMBOL	RGL34A	RGL34B	RGL34D	RGL34G	RGL34J	RGL34K	UNIT
Maximum instantaneous forward voltage	0.5 A	V <sub>F</sub>	1.3						V
Maximum DC reverse current at rated DC blocking voltage	T <sub>A</sub> = 25 °C	I <sub>R</sub>	5.0						μA
	T <sub>A</sub> = 125 °C		50						
Maximum reverse recovery time	I <sub>F</sub> = 0.5 A, I <sub>R</sub> = 1.0 A, I <sub>rr</sub> = 0.25 A	t <sub>rr</sub>	150				250		ns
Typical junction capacitance	4.0 V, 1 MHz	C <sub>J</sub>	4						pF

THERMAL CHARACTERISTICS (T <sub>A</sub> = 25 °C unless otherwise noted)									
PARAMETER	SYMBOL	RGL34A	RGL34B	RGL34D	RGL34G	RGL34J	RGL34K	UNIT	
Maximum thermal resistance	R <sub>θJA</sub> <sup>(1)</sup>	150						°C/W	
	R <sub>θJT</sub> <sup>(2)</sup>	70							

**Notes**

- (1) Thermal resistance from junction to ambient, 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal
- (2) Thermal resistance from junction to terminal, 0.2" x 0.2" (5.0 mm x 5.0 mm) copper pads to each terminal

ORDERING INFORMATION (Example)				
PREFERRED P/N	UNIT WEIGHT (g)	PREFERRED PACKAGE CODE	BASE QUANTITY	DELIVERY MODE
RGL34J-E3/98	0.036	98	2500	7" diameter plastic tape and reel
RGL34J-E3/83	0.036	83	9000	13" diameter plastic tape and reel
RGL34JHE3/98 <sup>(1)</sup>	0.036	98	2500	7" diameter plastic tape and reel
RGL34JHE3/83 <sup>(1)</sup>	0.036	83	9000	13" diameter plastic tape and reel

**Note**

- (1) AEC-Q101 qualified

**RATINGS AND CHARACTERISTICS CURVES (T<sub>A</sub> = 25 °C unless otherwise noted)**




Fig. 1 - Forward Current Derating Curve




Fig. 2 - Maximum Non-Repetitive Peak Forward Surge Current




Fig. 3 - Typical Instantaneous Forward Characteristics




Fig. 5 - Typical Junction Capacitance





Fig. 4 - Typical Reverse Characteristics


**PACKAGE OUTLINE DIMENSIONS** in inches (millimeters)

**DO-213AA (GL34)**



1<sup>st</sup> band denotes type and polarity  
2<sup>nd</sup> band denotes voltage type

**Mounting Pad Layout**





## **Disclaimer**

ALL PRODUCT, PRODUCT SPECIFICATIONS AND DATA ARE SUBJECT TO CHANGE WITHOUT NOTICE TO IMPROVE RELIABILITY, FUNCTION OR DESIGN OR OTHERWISE.

Vishay Intertechnology, Inc., its affiliates, agents, and employees, and all persons acting on its or their behalf (collectively, "Vishay"), disclaim any and all liability for any errors, inaccuracies or incompleteness contained in any datasheet or in any other disclosure relating to any product.

Vishay makes no warranty, representation or guarantee regarding the suitability of the products for any particular purpose or the continuing production of any product. To the maximum extent permitted by applicable law, Vishay disclaims (i) any and all liability arising out of the application or use of any product, (ii) any and all liability, including without limitation special, consequential or incidental damages, and (iii) any and all implied warranties, including warranties of fitness for particular purpose, non-infringement and merchantability.

Statements regarding the suitability of products for certain types of applications are based on Vishay's knowledge of typical requirements that are often placed on Vishay products in generic applications. Such statements are not binding statements about the suitability of products for a particular application. It is the customer's responsibility to validate that a particular product with the properties described in the product specification is suitable for use in a particular application. Parameters provided in datasheets and / or specifications may vary in different applications and performance may vary over time. All operating parameters, including typical parameters, must be validated for each customer application by the customer's technical experts. Product specifications do not expand or otherwise modify Vishay's terms and conditions of purchase, including but not limited to the warranty expressed therein.

Except as expressly indicated in writing, Vishay products are not designed for use in medical, life-saving, or life-sustaining applications or for any other application in which the failure of the Vishay product could result in personal injury or death. Customers using or selling Vishay products not expressly indicated for use in such applications do so at their own risk. Please contact authorized Vishay personnel to obtain written terms and conditions regarding products designed for such applications.

No license, express or implied, by estoppel or otherwise, to any intellectual property rights is granted by this document or by any conduct of Vishay. Product names and markings noted herein may be trademarks of their respective owners.

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Vishay:](#)

[RGL34A-E3/51](#) [RGL34A-E3/82](#) [RGL34A-E3/98](#) [RGL34AHE3/82](#) [RGL34AHE3/98](#) [RGL34B-E3/82](#) [RGL34B-E3/83](#)  
[RGL34B-E3/98](#) [RGL34BHE3/83](#) [RGL34BHE3/98](#) [RGL34D-E3/51](#) [RGL34D-E3/82](#) [RGL34D-E3/98](#) [RGL34DHE3/98](#)  
[RGL34G-E3/51](#) [RGL34G-E3/82](#) [RGL34G-E3/98](#) [RGL34GHE3/82](#) [RGL34GHE3/98](#) [RGL34J-E3/51](#) [RGL34J-E3/82](#)  
[RGL34J-E3/83](#) [RGL34J-E3/98](#) [RGL34JHE3/83](#) [RGL34JHE3/98](#) [RGL34K-E3/82](#) [RGL34K-E3/98](#) [RGL34KHE3/82](#)  
[RGL34KHE3/98](#) [RGL34K-E3/83](#) [RGL34D-E3/1](#) [RGL34D-E3/83](#)