Model 67

Cermet Trimming Potentiometer

Electronics

Features:

- 3/8" square
- Multiturn
- Sealed to be compatible with aqueous PCB cleaning process
- Highly reliable
- Long life



Applications:

- Any application requiring adjustability or calibration
- Medical

Consumer electronics

Electrical

Standard resistance range	10 Ohms to 2 Megohms
Standard resistance tolerance	±10% (<100 Ohms = ±20%)
Input voltage	200 Vdc max. or rms not to exceed power rating
Slider current	100 mA max. or within rated power, whichever is less
Power rating	0.5 Watts at 85°C derating to 0 at 125°C
End resistance	2 Ohms max
Actual electrical travel	20 turns nominal
Dielectric strength	900 Vrms
Insulation resistance	1,000 Megohms minimum
Resolution	Essentially infinite
Contact resistance variation	1% or 1 Ohm max., whichever is greater

Environmental

Seal	85°C Fluorinert® (No Leak	
Temperature coefficient	±100 ppm/°C (<100 Ohms = ±250 ppm/°C)	
Operating temperature range -55°C to		
Thermal shock	Five cycles –55°C to +125°C (1% ΔRT, 1% ΔVR)	
Moisture resistance	Ten 24 hour cycles (1% ΔRT, IR 1,000 Megohms min.)	
Shock	6 ms saw-tooth, 100 G's (1% ΔRT, 1% ΔVR)	
Vibration	20 G's, 10 to 2,000 Hz (1% ΔRT, 1% ΔVR)	
High temperature exposure	250 hours at 125°C (2% ΔRT, 2% ΔVR)	
Rotational life	200 cycles (3% ΔRT)	
Load life	1,000 hours at 70°C & 0.5 Watts (2% ΔRT)	
Resistance to solder heat	260°C for 10 sec. (1% ΔRT)	

General Note

TT Electronics reserves the right to make changes in product specification without notice or liability. All information is subject to TT Electronics' own data and is considered accurate at time of going to print.

TT Electronics | BI Technologies
413 Rood RD, Suite 7
Calexico, CA 92231
Ph: +1 (714) 447-2345
www.ttelectronics.com/bi-technologies
Issue C 04/2019 Page 1

Model 67

Cermet Trimming Potentiometer



Mechanical

Mechanical stops	Clutch action, both ends
Torque, starting	5 ozin. max. (0.035 N-m)
Weight	0.04 oz. nominal (1.1 grams)

Packaging

Standard (no code): Boxes. Capacity = 100 units for 67W. 50 units for all other pin styles.

Option (TR code, available for 67W & 67X only): Tape & Reel. All units oriented with #1 pin to the right of the direction of feed.


Tape	Width =	18 mm
	Sprocket =	Single hole, 0.050" spacing
	Capacity =	1,000 units
	Seat plane to centerline of sprocket hole =	0.71" (18 mm)
Reel	Diameter =	14" (363 mm)

Option (AP code, available for 67W &67X only): Ammo Pack. All units oriented with #1 pin to the right of the direction of feed.

Option (TB code): Tubes. All units oriented with #1 pin to same side. Tube capacity = 50 units.

	Pin Style	P	W,Y	X,Z
Dimensions	Width =	0.57"	0.28"	0.28"
	Height =	0.66"	0.93"	0.93"
	Length =	20.9"	20.6"	24.4"

Ordering Information




Model 67


Cermet Trimming Potentiometer



Circuit Diagram




Top Adjustment




Standard Resistance Values

10	200	5K	50K	500K
20	500	10K	100K	1Meg
50	1K	20K	200K	2Meg
100	2K	25K	250K	

Side Adjustment



Side Adjustment



Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

TT Electronics:

67PR200K 67PR20K 67WR100 67WR100K 67WR10K 67WR1K 67WR1MEG 67WR200 67WR200K 67WR20K 67WR20K 67WR25K 67WR25K 67WR25K 67WR500 67WR500K 67WR50K 67WR50K 67XR100 67XR100K 67XR100KLF 67XR100LF 67XR10K 67XR10KLF 67XR1K 67XR1KLF 67XR200 67XR20K 67XR25K 67XR25KLF 67XR2K 67XR25K 67XR500 67XR50K 67XR5K 67YR100 67YR100K 67YR10K 67YR1K 67YR200 67YR20K 67YR2K 67YR2M 67YR500 67YR500K 67YR5K 67ZR10K 67ZR5K 67WR10KLF 67PR10 67PR100 67PR100K 67PR10K 67PR1K 67PR20 67PR200 67PR250K 67PR25K 67PR25K 67PR25K 67PR25K 67PR25K 67PR500 67PR500K 67WR10 67WR20 67WR250K 67YR20K 67YR20K 67YR20K 67YR20K 67YR20K 67YR20K 67YR20KLFTB 67YR200KLFTB 67YR20KLFTB 67YR20KLFTB 67YR20KLFTB 67YR20KLFTB 67YR20KLFTB 67YR20KLFTB 67YR20KLFTB 67YR20KLFTB 67YR20KLF 67YR20KLF