

# SS32 - S310 Schottky Rectifier

#### **Features**

- Metal to Silicon Rectifiers, Majority Carrier Conduction
- · Low-Forward Voltage Drop
- · Easy Pick and Place
- High-Surge Current Capability

#### **Description**

The SS32-S310 series includes a high-efficiency, low power loss, general-propose Schottky rectifiers. The clipbonded leg structure provides high thermal performance and low electrical resistance. These rectifiers are suited for free wheeling, secondary rectification, and reverse polarity protection applications.





SMC/DO-214AB COLOR BAND DENOTES CATHODE

### **Ordering Information**

Part Number	Marking	Package	Packing Method
SS32	SS32		
SS33	SS33		
SS34	SS34		
SS35	SS35	DO-214AB	Tape and Reel
SS36	SS36	DO-214AB	Tape and Neel
SS38	SS38		
SS39	SS39		
S310	S310		

## **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only. Values are at  $T_A = 25^{\circ}\text{C}$  unless otherwise noted.

Symbol	Parameter	Value								Units
	i arameter		SS33	SS34	SS35	SS36	SS38	SS39	S310	Units
V <sub>RRM</sub>	Maximum Repetitive Reverse Voltage	20	30	40	50	60	80	90	100	V
I <sub>F(AV)</sub>	Maximum Average Forward Current at $T_A = 75$ °C	3.0							А	
I <sub>FSM</sub>	Non-Repetitive Peak Forward Surge Current: 8.3 ms Single Half-Sine Wave	rent: 8.3 ms Single Half-Sine 100					Α			
dV/dt	Maximum Voltage Rate of Change 10000					V/µS				
T <sub>STG</sub>	Storage Temperature Range -55 to +150				°C					
TJ	Operating Junction Temperature -55 to +150					°C				

1

## **Thermal Characteristics**

Symbol	Parameter	Value	Units
P <sub>D</sub>	Power Dissipation	2.27	W
$R_{\theta JA}$	Thermal Resistance, Junction to Ambient <sup>(1)</sup>	55	°C/W
$R_{\theta JL}$	Thermal Resistance, Junction to Lead	17	°C/W

#### Note:

1. Device mounted on FE-4 PCB 0.55 x 0.55 inch (14 x 14 mm).

#### **Electrical Characteristics**

Values are at  $T_A = 25$ °C unless otherwise noted.

Symbol	Parameter	Test	Value								l linita
		Conditions	SS32	SS33	SS34	SS35	SS36	SS38	SS39	S310	Units
V <sub>F</sub>	Forwarded Voltage	I <sub>F</sub> = 3.0 A	500			7	50	850			mV
Reverse Current		T <sub>A</sub> = 25°C	0.5					mA			
IR	at Rated V <sub>R</sub>	T <sub>A</sub> = 100°C		20		10				IIIA	

## **Typical Performance Characteristics**




Figure 1. Forward Current Derating Curve




Figure 3. Forward Voltage Characteristics




Figure 5. Total Capacitance




Figure 2. Non-Repetitive Surge Current





Figure 4. Reverse Current vs. Reverse Voltage



**Figure 6. Thermal Impedance Characteristics** 

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdf/Patent-Marking.pdf">www.onsemi.com/site/pdf/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hol

#### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Phone: 421 33 790 2910

Japan Customer Focus Center
Phone: 81–3–5817–1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## **ON Semiconductor:**

SS32 SS33 SS34 SS35 SS36 SS38 SS39 S310