



NOTES:

- ① HOUSING MATERIAL IS FLAME RETARDANT PER UL 94V-0 OR EQUIV.
- ② PRODUCT NUMBER 65474-810 TO BE MARKED "BERG" CAGE 22526, DESC XXXX-XX (NO. TO BE ASSIGNED), AND DATE ON PACKAGING LABEL.
- ③ ADD "LF" SUFFIX AT THE END OF PART NUMBER FOR LEAD FREE OPTION.
- ④ THESE PRODUCTS MEET EUROPEAN UNION DIRECTIVES AND OTHER COUNTRY REGULATIONS AS DESCRIBED IN GS-22-008.
- ⑤ THE PRODUCT IS NOT INTENDED TO BE EXPOSED TO A MANUFACTURING SOLDER PROCESS.
- ⑥ THIS PRODUCT HAS 100% TIN PLATING IN THE INTERFACE AND HAS NOT BEEN TESTED FOR WHISKERS GROWTH IN ALL INTERCONNECT ENVIRONMENTS.

mat'l. code		surface	tolerance	projection	product family
		ISO 1302	ISO 1106		JUMPER
P	V41246 SAR	11/4/94	line	XXX±.005/.13	angle
R	V50585 SAR	6/26/95	line	XXX±.005/.13	angle
S	V50969 SAR	8/3/95	0±Z	.000±.0020/.051	scale 6:1
T	M05-0205 ERE	09/29/05dir	S. ROYER	11/4/94	
U	M06-0238 MN	06/16/06engr	L. FYE	11/4/94	
V	M06-0389 AGS	10/4/06 chr	L. FYE	11/4/94	
W	EX-4-01064 JZ	2012-04-24	appd	11/4/94	
sheet		revision	W		
index	sheet	1	2		

PRODUCT NUMBER	HOUSING COLOR	TERMINAL BODY		TERMINAL SPRING		HOUSING MATERIAL
		MATERIAL	PLATING	MATERIAL	PLATING	
65474-001	BLUE	.010/.25 THICK 1/4 HD BRASS ALLOY UNS C26000	STRIPE, 40u"/1.02u Au or GXT at CONTACT over 50u"/1.27u Ni	.0048/.122 THICK BE-CU ALLOY UNS C17200 HEAT TREATED	P-Ni/M-050 P-Au/M-003	PLAIN POLYESTER NOTE 1
-002	BLUE	.010/.25 THICK 1/4 HD BRASS ALLOY UNS C26000	SN PLATED	.0048/.122 THICK BE-CU ALLOY UNS C17200 HEAT TREATED	TIN PLATED	PLAIN POLYESTER NOTE 1
-003	DISCONTINUED					
-004	BLUE	.010/.25 THICK 1/4 HD CuNi ALLOY UNS C72500	.001/.03 MIN THICK GOLD DOT	.0048/.122 THICK BE-CU ALLOY UNS C17200 HEAT TREATED	P-Ni/M-050 P-Au/M-003	PLAIN POLYESTER NOTE 1
-005	BLACK	.010/.25 THICK 1/4 HD CuNi ALLOY UNS C72500	.001/.03 MIN THICK GOLD DOT	.0048/.122 THICK BE-CU ALLOY UNS C17200 HEAT TREATED	P-Ni/M-050 P-Au/M-003	PLAIN NORYL NOTE 1
-006	BLACK	.010/.25 THICK 1/4 HD BRASS ALLOY UNS C26000	STRIPE, 40u"/1.02u Au or GXT at CONTACT over 50u"/1.27u Ni	.0048/.122 THICK BE-CU ALLOY UNS C17200 HEAT TREATED	P-Ni/M-050 P-Au/M-003	PLAIN NORYL NOTE 1
-007	SAME AS -004	EXCEPT PACKAGING-RESTRICTED				
-008	SAME AS -004	EXCEPT PACKAGING-RESTRICTED				
-009	BLUE	.010/.25 THICK 1/4 HD BRASS ALLOY UNS C26000	STRIPE, 40u"/1.02u Au or GXT at CONTACT over 50u"/1.27u Ni	.0048/.122 THICK BE-CU ALLOY UNS C17200 HEAT TREATED	30u"/.76u Au	PLAIN NORYL NOTE 1-RESTRICTED
-010	BLUE	.010/.25 THICK 1/4 HD BRASS ALLOY UNS C26000	STRIPE, 30u"/0.76u Au or GXT at CONTACT over 50u"/1.27u Ni	.0048/.122 THICK BE-CU ALLOY UNS C17200 HEAT TREATED	P-Ni/M-050 P-Au/M-003	PLAIN POLYESTER NOTE 1
65474-810	SAME AS -010	EXCEPT ADD SPECIAL MIL MARKING PER NOTE 2				

1	2	3	4	5
---	---	---	---	---

mat'l. code	surface	tolerance	projection	product family
W	ISO 1302	ISO 406 ISO 1101	1st angle	JUMPER
date	tolerances unless otherwise specified			title
	angles	.XX±.01/3		MINI-JUMP ASSEM
	line	.XXX±.005/13		.100/2.54cc
	0±.2	.XXX±.0020/.051	scale 6:1	dwg no
	dr	S. ROYER	11/4/94	sheet no
	engr	L. FYE	11/4/94	65474
	chr	L. FYE	11/4/94	Product Customer
	appd	L. FYE	11/4/94	
sheet revision				
index sheet				

4 PDS: Rev :W
 STATUS: Released
 Printed: Jun



Copyright FCI