


Snubberless™, logic level and standard 8 A Triacs



Features

- On-state rms current, I_{T(RMS)} 8 A
- Repetitive peak off-state voltage, V_{DRM} / V_{RRM} 600 V to 800 V
- Triggering gate current, I_{GT} 5 to 50 mA

Description

Available either in through-hole and surface-mount packages, these devices are suitable for general purpose AC switching. They can be used as an ON/OFF function in applications such as static relays, heating regulation, induction motor starting circuits or for phase control operation in light dimmers and motor speed controllers, etc.

The Snubberless versions (BTA, BTB08_xxxxW and T8 series) are specially recommended for use on inductive loads, thanks to their high commutation performance.

Logic level versions are designed to interface directly with low power drivers such as Microcontrollers.

By using an internal ceramic pad, the BTA series provide voltage insulated tab (rated at 2500 V_{RMS}) in compliance with UL standards (file ref.: E81734).

Product status link	
BTA08	
BTB08	
T810	
T835	
T850	



1 Characteristics

Table 1. Absolute maximum ratings (T_j = 25 °C unless otherwise stated)

Symbol	Paran	neter		Value	Unit		
I	DMC on state compant (full size compant)	IPAK, DPAK,TO-220AB, D2PAK	T _c = 110 °C				
I _T (RMS)	RMS on-state current (full sine wave)	TO-220AB Ins.	T _c = 100 °C	8	A		
	Non repetitive surge peak on-state current (full	f = 50 Hz	t = 20 ms	80	_		
ITSM	cycle, T _j initial = 25 °C)	f = 60 Hz	t _p = 16.7 ms	84	Α		
I ² t	I ² t value for fusing	I^2 t value for fusing $t_p = 10 \text{ ms}$					
dl/dt	Critical rate of rise of on-state current $I_G = 2 x$ I_{GT} , tr $\leq 100 \text{ ns}$	f = 120 Hz	T _j = 125 °C	50	A/µs		
I _{GM}	Peak gate current	t _p = 20 μs	T _j = 125 °C	4	Α		
P _{G(AV)}	Average gate power dissipation	T _j = 125 °C	1	W			
T _{stg}	Storage junction temperature range		-40 to +150	°C			
Tj	Operating junction temperature range			-40 to +125	°C		

Table 2. Electrical characteristics (T_j = 25 °C, unless otherwise specified) Snubberless and logic level (3 quadrants)

Symbol	Parameter	Quadrant			Т8			BTA08	/BTB0	8	Unit
Syllibol	Farameter	Quaurani		10	35	50	TW	sw	CW	BW	Ullit
I _{GT} ⁽¹⁾	V _D = 12 V, R _L = 30 Ω	1 - 11 - 111	Max.	10	35	50	5	10	35	50	mA
V _{GT}	ν _D = 12 ν, 1\(\(\frac{1}{2}\)	1 - 11 - 111	Max.				1.2				V
V_{GD}	$V_D = V_{DRM}, R_L = 3.3 \text{ k}\Omega, T_j = 125 \text{ °C}$	1 - 11 - 111	Min.				0.2				V
I _H (2)	I _T = 100 mA	1 - 11 - 111	Max.	15	35	75	10	15	35	50	mA
IL	I _G = 1.2 x I _{GT}	I - III	Max.	25	50	70	10	25	50	70	mA
'L	1.2 × 1G1	П	Max.	30	60	110	15	30	60	80	ША
dV/dt (2)	$V_D = 67\% V_{DRM}$, gate open, $T_j = 125 °C$		Max.	40	400	1000	20	40	400	1000	V/µs
	(dV/dt)c = 0.1 V/µs, T _j = 125 °C		Min.	5.4			3.5	5.4			
(dl/dt)c (2)	$(dV/dt)c = 10 V/\mu s, T_j = 125 °C$		Min.	2.8			1.5	2.98			A/ms
	Without snubber, T _j = 125 °C		Min.		4.5	7			4.5	7	

^{1.} Minimum I_{GT} is guaranteed at 5 % of I_{GT} max.

DS2114 - Rev 15 page 2/21

^{2.} For both polarities of A2 referenced to A1



Table 3. Standard (4 quadrants)

Symbol	Parameter	Quadrant		BTA08	ВТВ08	Unit	
Symbol	Faranietei	Quaurant		С	В	Unit	
I _{GT} ⁽¹⁾		1 - 11 - 111	Max.	25	50	mA	
IGT V	$V_D = 12 \text{ V}, R_L = 33 \Omega$	IV	IVIAX.	50	100	IIIA	
V _{GT}		All	Max.	1.	.3	V	
V_{GD}	$V_D = V_{DRM}$, $R_L = 33 \text{ k}\Omega$, $T_j = 125 \text{ °C}$	All	Min.	0	.2	V	
I _H ⁽²⁾	I _T = 500 mA	1 - 11 - 111	Max.	25	50	mA	
L	I _G = 1.2 I _{GT}	I - III - IV	Max.	40	50	mA	
IL.	IG - 1.2 IGT	II	IVIAX.	80	100	IIIA	
dV/dt (2)	V _D = 67 % V _{DRM} gate open, T _j = 125 °C		Min.	200	400	V/µs	
(dV/dt)c (2)	(dl/dt)c = 3.5 A/ms, T _j = 125 °C		Min.	5	10	V/µs	

- 1. Minimum I_{GT} is guaranteed at 5 % of I_{GT} max.
- 2. For both polarities of A2 referenced to A1

Table 4. Static electrical characteristics

Symbol	Test condition		Value	Unit	
V _{TM} ⁽¹⁾	I_{TM} = 11 A, t_p = 380 µs	T _j = 25 °C	Max.	1.55	V
V _{TO} ⁽¹⁾	threshold on-state voltage	T _j = 125 °C	Max.	0.85	V
R _D ⁽¹⁾	Dynamic resistance	T _j = 125 °C	Max.	50	mΩ
loon loon	$V_{DRM} = V_{RRM}$	T _j = 25 °C	Max.	5	μA
I _{DRM} I _{RRM}	VDRM - VRRM	T _j = 125 °C	Max.	1	mA

^{1.} For both polarities of A2 referenced to A1

Table 5. Thermal resistance

Symbol	Parameter					
D.,	Max. junction to case thermal resist	rango (AC)	IPAK / D2PAK / DPAK / TO-220AB	1.6	°C/W	
R _{th(j-c)}	wax. juriction to case thermal resist	ance (AC)	TO-220AB Insulated	2.5	C/VV	
	lumation to ambigut (tum.)	S = 2 cm ^{2 (1)}	D²PAK	45		
D	Junction to ambient (typ.)	S = 1 cm ²⁽¹⁾	DPAK	70	°C/W	
R _{th(j-a)}	lumation to ambigut (tum.)	'	TO-220AB / TO-220AB Insulated	60	C/VV	
	Junction to ambient (typ.)		IPAK	100		

1. S = Copper surface under tab.

DS2114 - Rev 15 page 3/21



1.1 Characteristics (curves)

Figure 1. Maximum power dissipation versus on-state RMS current (full cycle)




Figure 2. RMS on-state current versus temperature (full cycle)




Figure 3. RMS on-state current versus ambient temperature (full cycle)





Figure 4. Relative variation of thermal impedance versus pulse duration



DS2114 - Rev 15 page 4/21



Figure 5. On-state characteristics (maximum values)




Figure 6. Surge peak on-state current versus number of cycles




Figure 7. Non repetitive surge peak on-state current for a sinusoidal pulse ($t_p < 10 \text{ ms}$)




Figure 8. Relative variation of gate trigger current




Figure 9. Relative variation of critical rate of decrease of main current versus (dV/dt)c (typical values)





Figure 10. Relative variation of critical rate of decrease of main current versus (dV/dt)c (typical values)



DS2114 - Rev 15 page 5/21



Figure 11. Relative variation of critical rate of decrease of main current versus junction temperature





Figure 12. DPAK and D2PAK thermal resistance junction to ambient versus copper surface under tab





2 Package information

In order to meet environmental requirements, ST offers these devices in different grades of ECOPACK® packages, depending on their level of environmental compliance. ECOPACK® specifications, grade definitions and product status are available at: www.st.com. ECOPACK® is an ST trademark.


DS2114 - Rev 15 page 7/21





2.1 DPAK package information


- Epoxy meets UL94, V0
- Lead-free package
- Recommended torque: 0.4 to 0.6 N·m


Figure 13. DPAK package outline











DS2114 - Rev 15 page 8/21

0.0402

+8°



Dimensions Millimeters Ref. Inches⁽¹⁾ Min. Max. Min. Тур. Max. Тур. 2.18 Α 2.40 0.0858 0.0945 Α1 0.90 1.10 0.0354 0.0433 0.03 0.0012 0.0091 A2 0.23 0.64 0.90 0.0252 0.354 b b4 4.95 5.46 0.1949 0.2150 С 0.46 0.61 0.0181 0.0240 c2 0.46 0.60 0.0181 0.0236 D 5.97 6.22 0.2350 0.2449 5.10 0.2008 D1 Ε 6.35 6.73 0.2500 0.2650 E1 4.32 0.1701 2.29 0.0900 4.57 0.1800 e1 Н 9.35 10.40 0.3681 0.4094 0.0701 L 1.00 1.78 0.0394 L2 1.27 0.0500

Table 6. DPAK package mechanical data

0.60

0°

L4

V2

This package drawing may slightly differ from the physical package. However, all the specified dimensions are Note: guaranteed.

1.02

+8°




Figure 14. DPAK recommended footprint (dimensions are in mm)

0.0236

0°

The device must be positioned within \$\oplus 0.05 \ AB\$

Downloaded from Arrow.com.

^{1.} Dimensions in inches are given for reference only



2.2 IPAK package information

 $\begin{bmatrix} E \\ b4 \\ \end{bmatrix}$ $\begin{bmatrix} D \\ \end{bmatrix}$

Figure 15. IPAK package outline

Note: This package drawing may slightly differ from the physical package. However, all the specified dimensions are guaranteed.

DS2114 - Rev 15 page 10/21



Table 7. IPAK package mechanical data

				Dimensions		
Ref.		Millimeters			Inches ⁽¹⁾	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	2.20		2.40	0.0866		0.0945
A1	0.90		1.10	0.0354		0.0433
b	0.64		0.90	0.0252		0.0354
b2			0.95			0.0374
b4	5.20		5.43	0.2047		0.2138
B5		0.30			0.0118	
С	0.45		0.60	0.0177		0.0236
c2	0.46		0.60	0.0181		0.0236
D	6.00		6.20	0.2362		0.2441
E	6.40		6.65	0.2520		0.2618
е		2.28			0.0898	
e1	4.40		4.60	0.1732		0.1811
Н		16.10			0.6339	
L	9.00		9.60	0.3545		0.3780
L1	0.80		1.20	0.0315		0.0472
L2		0.80	1.25		0.0315	0.0492
V1		10°			10°	

^{1.} Inch dimensions are for reference only.

DS2114 - Rev 15 page 11/21



2.3 TO-220AB insulated package information

C В b2 Resin gate 0.5 mm max. protusion⁽¹⁾ ↓ L F Α 14 13 c2 **a**1 12 a2 Μ c1 Resin gate 0.5 mm b1 max. protusion⁽¹⁾

Figure 16. TO-220AB insulated package outline

(1)Resin gate position accepted in one of the two positions or in the symmetrical opposites.

DS2114 - Rev 15 page 12/21



Table 8. TO-220AB insulated package mechanical data

			Di	mensions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	15.20		15.90	0.5984		0.6260
a1		3.75			0.1476	
a2	13.00		14.00	0.5118		0.5512
В	10.00		10.40	0.3937		0.4094
b1	0.61		0.88	0.0240		0.0346
b2	1.23		1.32	0.0484		0.0520
С	4.40		4.60	0.1732		0.1811
c1	0.49		0.70	0.0193		0.0276
c2	2.40		2.72	0.0945		0.1071
е	2.40		2.70	0.0945		0.1063
F	6.20		6.60	0.2441		0.2598
I	3.73		3.88	0.1469		0.1528
L	2.65		2.95	0.1043		0.1161
12	1.14		1.70	0.0449		0.0669
13	1.14		1.70	0.0449		0.0669
14	15.80	16.40	16.80	0.6220	0.6457	0.6614
М		2.6			0.1024	


^{1.} Inch dimensions are for reference only.

DS2114 - Rev 15 page 13/21



2.4 D²PAK package information

Figure 17. D²PAK package outline



(1) Resin gate position accepted in one of the two positions or in the symmetrical opposites

DS2114 - Rev 15 page 14/21



Table 9. D²PAK package mechanical data


				Dimensions		
Ref.		Millimeters			Inches	
	Min.	Тур.	Max.	Min.	Тур.	Max.
Α	4.30		4.60	0.1693		0.1811
A1	2.49		2.69	0.0980		0.1059
A2	0.03		0.23	0.0012		0.0091
A3		0.25			0.0098	
b	0.70		0.93	0.0276		0.0366
b2	1.25		1.7	0.0492		0.0669
С	0.45		0.60	0.0177		0.0236
c2	1.21		1.36	0.0476		0.0535
D	8.95		9.35	0.3524		0.3681
D1	7.50		8.00	0.2953		0.3150
D2	1.30		1.70	0.0512		0.0669
е	2.54			0.1		
E	10.00		10.28	0.3937		0.4047
E1	8.30		8.70	0.3268		0.3425
E2	6.85		7.25	0.2697		0.2854
G	4.88		5.28	0.1921		0.2079
Н	15		15.85	0.5906		0.6240
L	1.78		2.28	0.0701		0.0898
L2	1.27		1.40	0.0500		0.0551
L3	1.40		1.75	0.0551		0.0689
R		0.40			0.0157	
V2	0°		8°	0°		8°

^{1.} Dimensions in inches are given for reference only

DS2114 - Rev 15 page 15/21



Figure 18. D²PAK recommended footprint (dimensions are in mm)



DS2114 - Rev 15 page 16/21



Ordering information

Figure 19. Ordering information scheme (BTA08 and BTB08 series)





Figure 20. Ordering information scheme (T8 series)



DS2114 - Rev 15 page 17/21



Table 10. Product selector

5 (1)	Voltag	je (xxx)	2	_	
Part Number	600	800	- Sensitivity	Туре	Package
T810-xxxB	Х	Х	10 mA	Logic Level	DPAK
T835-xxxH	Х		35 mA	Snubberless™	IPAK
T810-xxxG	Х		10 mA	Logic Level	D ² PAK
T835-xxxG	Х	Х	35 mA	Snubberless™	D ² PAK
T850-xxxG	Х	Х	50 mA	Snubberless™	D ² PAK
BTA08-xxxS	Х		10 mA	Logic Level	TO-220AB Ins.
BTA08-xxxC	Х	Х	35 mA	Standard	TO-220AB Ins.
BTA08-xxxB	Х		50 mA	Standard	TO-220AB Ins.
BTA08-xxxTW	Х		5 mA	Logic Level	TO-220AB Ins.
BTA08-xxxSW	Х		10 mA	Logic Level	TO-220AB Ins.
BTA08-xxxCW	Х		35 mA	Snubberless™	TO-220AB Ins.
BTA08-xxxBW	Х	Х	50 mA	Snubberless™	TO-220AB Ins.
BTB08-xxxS	Х		10 mA	Logic Level	TO-220AB
BTB08-xxxC	Х		35 mA	Standard	TO-220AB
BTB08-xxxB	Х		50 mA	Standard	TO-220AB
BTB08-xxxTW	Х	Х	5 mA	Logic Level	TO-220AB
BTB08-xxxSW	Х		10 mA	Logic Level	TO-220AB
BTB08-xxxCW	Х	Х	35 mA	Snubberless™	TO-220AB
BTB08-xxxBW	Х		50 mA	Snubberless™	TO-220AB



Table 11. Ordering information

Order code	Marking	Package	Weight	Base qty.	Delivery mode
T810-600B	T8 1060				
T835-600B	T8 3560	_		75	Tube
T835-800B	T8 3580	-			
T810-600B-TR	T8 1060	DPAK	0.30		
T810-800B-TR	T8 1080	_		2500	Ton 2 9 Dool 42"
T835-600B-TR	T8 3560			2500	Tape&Reel 13"
T835-800B-TR	T8 3580				
T835-600H	T8 3560	IPAK	0.40	75	Tube
T835-600G	T835-600G				
T835-8G	T835-8G			5 0	Tuba
T850-6G	T850-6G			50	Tube
T850-8G	T850-8G				
T810-600G-TR	T810-600G	D ² PAK	1.50		
T835-600G-TR	T835-600G			1000	
T835-8G-TR	T835-8G				Tape&Reel 13"
T850-6G-TR	T850-6G				
T850-8G-TR	T850-8G				
BTA08-600SRG	BTA08-600S				
BTA08-600BRG	BTA08-600B				
BTA08-600CRG	BTA08-600C				
BTA08-800CRG	BTA08-800C	-			
BTA08-600BWRG	BTA08-600BW	TO-220AB Ins.			
BTA08-600CWRG	BTA08-600CW	_			
BTA08-600SWRG	BTA08-600SW	-			
BTA08-600TWRG	BTA08-600TW				
BTA08-800BWRG	BTA08-800BW		2.20	E 0	Tuba
BTB08-600BRG	BTB08-600B		2.30	50	Tube
BTB08-600CRG	BTB08-600C				
BTB08-600SRG	BTB08-600S				
BTB08-600BWRG	BTB08-600BW				
BTB08-600CWRG	BTB08-600CW	TO-220AB			
BTB08-600SWRG	BTB08-600SW				
BTB08-600TWRG	BTB08-600TW				
BTB08-800CWRG	BTB08-800CW				
BTB08-800TWRG	BTB08-800TW				



Table 12. Document revision history

Date	Revision	Changes
Apr-2002	5A	Last update.
13-Feb-2006	6	TO-220AB delivery mode changed from bulk to tube. ECOPACK statement added.
10-Mar-2010	7	Updated ECOPACK statement and Figure 26
02-Jun-2014	8	Updated DPAK and IPAK package information and reformatted to current standard.
07-Nov-2016	9	Updated Table 1 and reformatted to current standard.
06-Jan-2017	10	Updated Figure 20: "Ordering information scheme (T8 series)", Table 10: "Product selector" and Table 11: "Ordering information".
09-Feb-2017	11	Added T850 package information.
24-Apr-2017	12	Updated Figure 6 Minor text changes to improve readability.
14-Mar-2018	13	Updated Table 2. Electrical characteristics ($T_j = 25$ °C, unless otherwise specified) Snubberless and logic level (3 quadrants), cover image, Figure 9. Relative variation of critical rate of decrease of main current versus (dV/dt)c (typical values) and Figure 20. Ordering information scheme (T8 series).
14-May-2018	14	Updated product status links.
09-Aug-2018	15	Updated Table 3. Standard (4 quadrants).

DS2114 - Rev 15 page 20/21



IMPORTANT NOTICE - PLEASE READ CAREFULLY

STMicroelectronics NV and its subsidiaries ("ST") reserve the right to make changes, corrections, enhancements, modifications, and improvements to ST products and/or to this document at any time without notice. Purchasers should obtain the latest relevant information on ST products before placing orders. ST products are sold pursuant to ST's terms and conditions of sale in place at the time of order acknowledgement.

Purchasers are solely responsible for the choice, selection, and use of ST products and ST assumes no liability for application assistance or the design of Purchasers' products.

No license, express or implied, to any intellectual property right is granted by ST herein.

Resale of ST products with provisions different from the information set forth herein shall void any warranty granted by ST for such product.

ST and the ST logo are trademarks of ST. All other product or service names are the property of their respective owners.

Information in this document supersedes and replaces information previously supplied in any prior versions of this document.

© 2018 STMicroelectronics - All rights reserved

DS2114 - Rev 15 page 21/21