

**PLEASE CHECK WWW.MOLEX.COM FOR LATEST PART INFORMATION**

**Part Number:** [0638199200](#)  
**Status:** **Active**  
**Overview:** [Application Tooling](#)  
**Description:** Hand Crimp Tool for Cable Seal Crimp Terminals

**Documents:**

[RoHS Certificate of Compliance \(PDF\)](#)

**General**

|                                |   |
|--------------------------------|---|
| Product Family                 | Application Tooling   |
| Series                         | <a href="#">207129</a>  |
| Comments                       | See Tooling Specification (PDF) Above. Type: 4D   |
| Function                       | Crimp   |
| Geographic Area                | Global  |
| Level of Automation            | Manual  |
| More Detailed Tech Information | <a href="mailto:applicationtooling@molex.com">applicationtooling@molex.com</a>  |
| Overview                       | <a href="#">Application Tooling</a>   |
| Product Name                   | PremiumGrade  |
| Tool Type                      | Hand Crimp Tool   |
| UPC                            | 883906603977  |
| Warranty Disclaimer            | CAUTION: Molex tooling crimp specifications are valid only when used with Molex terminals and tooling manufactured by Molex and sold by Molex or authorized distributors ("Molex Tooling"). When using tooling other than Molex Tooling with Molex specific connector systems listed in our ATS documents, the Molex tooling qualification does not apply and the responsibility for full qualification of the connector system is that of the customer. Molex accepts no liability for connector performance or tooling support where tooling other than Molex Tooling is used or where Molex Tooling is modified. |

**Material Info**

**Reference - Drawing Numbers**

Application Tooling Documents

ATS-638199200-001, TM-638000029-001, TM-638000029CN-001, TM-638000029DE-001, TM-638000029FR-001, TM-638000029IT-001, TM-638000029JP-001, TM-638000029KR-001, TM-638000029MY-001, TM-638000029PL-001, TM-638000029RU-001, TM-638000029SK-001, TM-638000029SP-001, TM-638000029TH-001, TM-638000029TW-001, TM-638000029VN-001



**EU ELV**

**Not Relevant**

**EU RoHS**

**Not Reviewed**

**REACH SVHC**

Not Contained Per - ED/61/2018 (27 June 2018)

**Halogen-Free**

**Status**

**Not Relevant**

For more information, please visit [Contact US](#)

China ROHS

Not Relevant

ELV

Not Relevant

RoHS Phthalates

Not Contained

**Search Parts in this Series**

[207129](#) Series

**Use With**

MX150 Cable Seal Blade and Receptacle Crimp Terminals [34080](#) , [34081](#) , [34083](#)

**Application Tooling**

**Description**

**FAQ**

**Product #**

MX150 Cable Seal Male Terminal, Tin Plating, 18 and 20 AWG, Right Reel Payoff [340800002](#)

MX150 Cable Seal Male Terminal, Gold Plating, 18 and 20 AWG, Right Reel Payoff [340800104](#)

MX150 Cable Seal Male Terminal, Silver Plating, 18 and 20 AWG, Right Reel Payoff [340800204](#)

MX150 Cable Seal 340801002  
Male Terminal, Tin  
Plating, 18 and 20  
AWG, Left Reel  
Payoff

MX150 Cable Seal 340801104  
Male Terminal, Gold  
Plating, 18 and 20  
AWG, Left Reel  
Payoff

MX150 Cable Seal 340801204  
Male Terminal, Silver  
Plating, 18 and 20  
AWG, Left Reel  
Payoff

MX150 Cable Seal 340812004  
Female Terminal,  
Gold Plating, 18 and  
20 AWG, Right Reel  
Payoff

MX150 Cable Seal 340813004  
Female Terminal,  
Gold Plating, 18 and  
20 AWG, Left Reel  
Payoff

MX150 Cable Seal 340814002  
Female Terminal,  
Silver Plating, 18 and  
20 AWG, Right Reel  
Payoff

MX150 Cable Seal 340815002  
Female Terminal,  
Silver Plating, 18 and  
20 AWG, Left Reel  
Payoff

MX150 Cable Seal 340832002  
Female Terminal,  
Tin Plating, 18 and  
20 AWG, Right Reel  
Payoff

MX150 Cable Seal 340833002  
Female Terminal,  
Tin Plating, 18 and  
20 AWG, Left Reel  
Payoff

This document was generated on 11/02/2021

**PLEASE CHECK [WWW.MOLEX.COM](http://WWW.MOLEX.COM) FOR LATEST PART INFORMATION**

# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Molex:](#)

[63819-9200](#)