

# MEMS CLOCK OSCILLATOR

ASDMB



Life Size   
 2.5 x 2.0 x 0.85 mm

ASDMB

Moisture Sensitivity Level – MSL 1



RoHS/RoHS II Compliant

## FEATURES:

- Low Power Consumption <10mA
- Exceptional Stability +/- 10ppm Over Temp. at -40 to +105°C
- Compact QFN Plastic Packaging

## APPLICATIONS:

- CCD Clock for VTR Camera
- Equipment Connected to PCs
- Low Profile Equipment
- Computers and Peripherals
- Lower Cost Crystal Oscillator Replacement
- Portable Electronics (MP3 Players, Games)
- Consumer Electronics such as TV's, DVR's, etc.
- Vibrant, Shock-Prone & Humid Environments for Industrial Equipment
- Demanding Military & Automotive Electronics

## STANDARD SPECIFICATIONS:

Parameters	Minimum	Typical	Maximum	Units	Notes
Frequency Range:	1.0		150	MHz	
Operating Temperature:	0		+70	°C	See options
Storage Temperature:	-55		+150	°C	
Overall Frequency Stability*:	-50		+50	ppm	See options
Supply Voltage (V <sub>dd</sub> ):	+1.8 ~ +3.3			V	
Output Load:	10		15, 25, or 40	pF kΩ	See options
Symmetry:	45		55	%	@1/2V <sub>dd</sub>
Startup Time:		1.5	3.0	ms	
Disable Time:		20	100	ns	
Disable Stand-by Current:			15	uA	
Tri-state Function (Stand-by) :	"1" (VIH≥0.75*V <sub>dd</sub> ) or Open: Oscillation "0" (VIL<0.25*V <sub>dd</sub> ) : Hi Z			V	
Aging:	-5.0		+5.0	ppm	First year

## Key Electrical Specifications – V<sub>dd</sub>= 1.8V

Parameters	Minimum	Typical	Maximum	Units	Notes
Supply Current (no load):	1.0 to 39.9999MHz	5	15	mA	CL=0p
	40.0 to 79.9999MHz	6	15	mA	RL=∞
	80.0 to 124.9999MHz	7	15	mA	T=25°C
	125.0 to 150MHz	8	15	mA	(Standard CL: 15pF)
	1.0 to 39.9999MHz	6	15	mA	CL=0p
	40.0 to 79.9999MHz	7	15	mA	RL=∞
	80.0 to 124.9999MHz	8	15	mA	T=25°C
	125.0 to 150MHz	9	15	mA	(CL option: 25pF)
	1.0 to 39.9999MHz	7	15	mA	CL=0p
	40.0 to 79.9999MHz	8	15	mA	RL=∞
	80.0 to 124.9999MHz	9	15	mA	T=25°C
	125.0 to 150MHz	10	15	mA	(CL option: 40pF)
Output Voltage:	V <sub>OH</sub>	0.8*V <sub>dd</sub>		V	
	V <sub>OL</sub>		0.2*V <sub>dd</sub>	V	CL=15, 25, 40pF
Rise Time: Fall Time:	Tr	1.8	3.0	ns	CL=15pF; T=25°C
	Tf	1.0	3.0	ns	20%/80%*VDD
	Tr	1.5	3.0	ns	CL=25pF; T=25°C
	Tf	1.2	3.0	ns	20%/80%*VDD
	Tr	1.4	3.0	ns	CL=40pF; T=25°C
	Tf	1.1	3.0	ns	20%/80%*VDD
Cycle to Cycle Jitter:		60		ps	F=100MHz
Period Jitter RMS:		10		ps	F=100MHz

REVISED: 12.10.2018



5101 Hidden Creek Ln Spicewood TX 78669  
 Phone: 512-371-6159 | Fax: 512-351-8858  
 For terms and conditions of sales, please visit: [www.abracon.com](http://www.abracon.com)

ABRACON IS  
 ISO9001-2015  
 CERTIFIED

Key Electrical Specifications –  $V_{dd} = 2.5V$ 

Parameters		Minimum	Typical	Maximum	Units	Notes
Supply Current (no load):	1.0 to 39.9999MHz		6	15	mA	CL=0pF
	40.0 to 79.9999MHz		7	15	mA	RL=∞
	80.0 to 124.9999MHz		8	15	mA	T=25°C
	125.0 to 150MHz		9	15	mA	(Standard CL: 15pF)
	1.0 to 39.9999MHz		7	15	mA	CL=0pF
	40.0 to 79.9999MHz		8	15	mA	RL=∞
	80.0 to 124.9999MHz		9	15	mA	T=25°C
	125.0 to 150MHz		10	15	mA	(CL option: 25pF)
	1.0 to 39.9999MHz		8	16	mA	CL=0pF
	40.0 to 79.9999MHz		9	16	mA	RL=∞
	80.0 to 124.9999MHz		10	16	mA	T=25°C
	125.0 to 150MHz		11	16	mA	(CL option: 40pF)
Output Voltage:	$V_{OH}$	$0.8 * V_{dd}$			V	
	$V_{OL}$			$0.2 * V_{dd}$	V	CL=15, 25pF
	$V_{OH}$	$0.9 * V_{dd}$			V	
	$V_{OL}$			$0.1 * V_{dd}$	V	CL=40pF
Rise Time: Fall Time:	$T_r$		1.0	2.0	ns	CL=15pF; T=25°C
	$T_f$		0.9	2.0	ns	20%/80%*VDD
	$T_r$		1.1	2.0	ns	CL=25pF; T=25°C
	$T_f$		0.9	2.0	ns	20%/80%*VDD
	$T_r$		1.0	2.0	ns	CL=40pF; T=25°C
	$T_f$		0.9	2.0	ns	20%/80%*VDD
Cycle to Cycle Jitter:			50		ps	F=100MHz
Period Jitter RMS:			5		ps	F=100MHz



## Key Electrical Specifications – $V_{dd} = 3.3V$

Parameters		Minimum	Typical	Maximum	Units	Notes
Supply Current (no load):	1.0 to 39.9999MHz		7	15	mA	CL=0p RL=∞ T=25°C (Standard CL: 15pF)
	40.0 to 79.9999MHz		8	15	mA	
	80.0 to 124.9999MHz		9	15	mA	
	125.0 to 150MHz		10	15	mA	
	1.0 to 39.9999MHz		8	16	mA	CL=0p RL=∞ T=25°C (CL option: 25pF)
	40.0 to 79.9999MHz		9	16	mA	
	80.0 to 124.9999MHz		10	16	mA	
	125.0 to 150MHz		11	16	mA	
	1.0 to 39.9999MHz		8	16	mA	CL=0p RL=∞ T=25°C (CL option: 40pF)
	40.0 to 79.9999MHz		9	16	mA	
	80.0 to 124.9999MHz		10	16	mA	
	125.0 to 150MHz		11	16	mA	
Output Voltage:	$V_{OH}$	$0.8 * V_{dd}$			V	CL=15pF
	$V_{OL}$			$0.2 * V_{dd}$	V	
	$V_{OH}$	$0.9 * V_{dd}$			V	
	$V_{OL}$			$0.1 * V_{dd}$	V	
Rise Time: Fall Time:	Tr		1.0	2.0	ns	CL=15pF; T=25°C 20%/80%*VDD
	Tf		0.9	2.0	ns	
	Tr		1.0	2.0	ns	CL=25pF; T=25°C 20%/80%*VDD
	Tf		0.9	2.0	ns	
	Tr		0.8	2.0	ns	CL=40pF; T=25°C 20%/80%*VDD
	Tf		0.8	2.0	ns	
Cycle to Cycle Jitter:			50		ps	F=100MHz
Period Jitter RMS:			5		ps	F=100MHz



## Absolute Maximum Ratings

Item	Minimum	Maximum	Unit	Condition
Supply Voltage	-0.3	+4.0	V	
Input Voltage	-0.3	V <sub>dd</sub> +0.3	V	
Junction Temp.	-----	+150	°C	
Storage Temp.	-55	+150	°C	
Soldering Temp.	-----	+260	°C	40sec max
ESD			V	
HBM		4,000		
MM		200		
CDM		1,500		

## OPTIONS AND PART IDENTIFICATION: (Left Blank if Standard)

### Programmed Orders (Quantity > 1,000pcs)

ASDMB -  MHz -   -  -

Frequency in MHz
e.g. 14.3181 MHz (Maximum 4 digits after decimal)

Operating Temp.
Blank: 0°C ~ +70°C
E: -20°C ~ +70°C
L: -40°C ~ +85°C
X: -40°C ~ +105°C

Overall Freq. Stability
C: ±50ppm (STD)
Y: ±10ppm
R: ±25 ppm

Output Load
Blank: 15pF
25: 25pF
40: 40pF

Packaging
Blank*: 140pcs / Tube
T: 1,000pcs / reel
T3: 3,000pcs / reel
T5: 5,000pcs / reel
T10: 10,000pcs / reel

\* For Quick turn-around programmable orders < 1000pcs: Due to the immediate availability of stock and the qty of the order, the parts may be delivered as BULK: Cut Tape, Loose parts in Antistatic Bag or in Tube(s). The MOQ per the series will still apply for Tube packaging.

### Un-Programmed Orders

Blank un-programmed oscillators are available for quick turn engineering requirements. Please call ABRACON for more information.

ASDMB - BLANK -   -  -

Operating Temp.
Blank: 0°C ~ +70°C
E: -20°C ~ +70°C
L: -40°C ~ +85°C
X: -40°C ~ +105°C

Overall Freq. Stability
C: ±50ppm (STD)
Y: ±10ppm
R: ±25 ppm

Output Load
Blank: 15pF
25: 25pF
40: 40pF

Packaging
Blank: 140pcs / Tube
T: 1,000pcs / reel
T3: 3,000pcs / reel
T5: 5,000pcs / reel
T10: 10,000pcs / reel



# Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

## ABRACON:

[ASDMB-BLANK-XY](#) [ASDMB-BLANK-LY](#) [ASDMB-BLANK-EY](#) [ASDMB-BLANK-XR](#) [ASDMB-BLANK-LR](#) [ASDMB-BLANK-ER](#) [ASDMB-BLANK-E](#) [ASDMB-BLANK-L](#) [ASDMB-BLANK-X](#) [ASDMB-1.544MHZ-LY-T](#) [ASDMB-1.544MHZ-XY-T](#) [ASDMB-1.8432MHZ-LY-T](#) [ASDMB-1.8432MHZ-XY-T](#) [ASDMB-10.000MHZ-LY-T](#) [ASDMB-10.000MHZ-XY-T](#) [ASDMB-100.000MHZ-LY-T](#) [ASDMB-100.000MHZ-XY-T](#) [ASDMB-106.250MHZ-LY-T](#) [ASDMB-106.250MHZ-XY-T](#) [ASDMB-11.0592MHZ-LY-T](#) [ASDMB-11.0592MHZ-XY-T](#) [ASDMB-12.000MHZ-LY-T](#) [ASDMB-12.000MHZ-XY-T](#) [ASDMB-125.000MHZ-LY-T](#) [ASDMB-125.000MHZ-XY-T](#) [ASDMB-133.333MHZ-LY-T](#) [ASDMB-133.333MHZ-XY-T](#) [ASDMB-14.31818MHZ-LY-T](#) [ASDMB-14.31818MHZ-XY-T](#) [ASDMB-14.7456MHZ-LY-T](#) [ASDMB-14.7456MHZ-XY-T](#) [ASDMB-150.000MHZ-LY-T](#) [ASDMB-150.000MHZ-XY-T](#) [ASDMB-18.432MHZ-LY-T](#) [ASDMB-18.432MHZ-XY-T](#) [ASDMB-19.200MHZ-LY-T](#) [ASDMB-19.200MHZ-XY-T](#) [ASDMB-20.000MHZ-LY-T](#) [ASDMB-20.000MHZ-XY-T](#) [ASDMB-24.000MHZ-LY-T](#) [ASDMB-24.000MHZ-XY-T](#) [ASDMB-24.576MHZ-LY-T](#) [ASDMB-24.576MHZ-XY-T](#) [ASDMB-25.000MHZ-LY-T](#) [ASDMB-25.000MHZ-XY-T](#) [ASDMB-26.000MHZ-LY-T](#) [ASDMB-26.000MHZ-XY-T](#) [ASDMB-27.000MHZ-LY-T](#) [ASDMB-27.000MHZ-XY-T](#) [ASDMB-29.4912MHZ-LY-T](#) [ASDMB-29.4912MHZ-XY-T](#) [ASDMB-3.6864MHZ-LY-T](#) [ASDMB-3.6864MHZ-XY-T](#) [ASDMB-30.000MHZ-LY-T](#) [ASDMB-30.000MHZ-XY-T](#) [ASDMB-32.000MHZ-LY-T](#) [ASDMB-32.000MHZ-XY-T](#) [ASDMB-33.000MHZ-LY-T](#) [ASDMB-33.000MHZ-XY-T](#) [ASDMB-33.333MHZ-LY-T](#) [ASDMB-33.333MHZ-XY-T](#) [ASDMB-4.000MHZ-LY-T](#) [ASDMB-4.000MHZ-XY-T](#) [ASDMB-44.000MHZ-LY-T](#) [ASDMB-44.000MHZ-XY-T](#) [ASDMB-48.000MHZ-LY-T](#) [ASDMB-48.000MHZ-XY-T](#) [ASDMB-50.000MHZ-LY-T](#) [ASDMB-50.000MHZ-XY-T](#) [ASDMB-60.000MHZ-LY-T](#) [ASDMB-60.000MHZ-XY-T](#) [ASDMB-7.3728MHZ-LY-T](#) [ASDMB-7.3728MHZ-XY-T](#) [ASDMB-75.000MHZ-LY-T](#) [ASDMB-75.000MHZ-XY-T](#) [ASDMB-8.000MHZ-LY-T](#) [ASDMB-8.000MHZ-XY-T](#) [ASDMB-80.000MHZ-LY-T](#) [ASDMB-80.000MHZ-XY-T](#) [ASDMB- ADAPTER-KIT](#) [ASDMB-16.000MHZ-LY-T](#) [ASDMB-16.000MHZ-XY-T](#) [ASDMB-1.544MHZ-LC-T](#) [ASDMB-1.8432MHZ-LC-T](#) [ASDMB-10.000MHZ-LC-T](#) [ASDMB-11.0592MHZ-LC-T](#) [ASDMB-12.000MHZ-LC-T](#) [ASDMB-14.31818MHZ-LC-T](#) [ASDMB-14.7456MHZ-LC-T](#) [ASDMB-16.000MHZ-LC-T](#) [ASDMB-18.432MHZ-LC-T](#) [ASDMB-19.200MHZ-LC-T](#) [ASDMB-20.000MHZ-LC-T](#) [ASDMB-24.000MHZ-LC-T](#) [ASDMB-24.576MHZ-LC-T](#) [ASDMB-25.000MHZ-LC-T](#) [ASDMB-26.000MHZ-LC-T](#) [ASDMB-27.000MHZ-LC-T](#) [ASDMB-29.4912MHZ-LC-T](#) [ASDMB-3.6864MHZ-LC-T](#)