


MMBT4403-HF (PNP)

RoHS Device

Halogen Free





Features

- Power dissipation of 300mW.
- High stability and high reliability.

Mechanical data

- Case: SOT-23, molded plastic.
- Epoxy UL: 94V-0.
- Mounting position: Any.

Circuit Diagram



Maximum Ratings (at TA=25°C unless otherwise noted)

Parameter	Symbol	Value	Unit
Collector-base voltage	V _{CB0}	-40	V
Collector-emitter voltage	V _{CE0}	-40	V
Emitter-base voltage	V _{EB0}	-5	V
Collector current-continuous	I _c	-600	mA
Collector power dissipation	P _c	300	mW
Junction temperature	T _J	150	°C
Storage temperature range	T _{STG}	-55 to +150	°C
Thermal resistance from junction to ambient	R _{θJA}	417	°C/W

Electrical Characteristics (at TA=25°C unless otherwise noted)

Parameter	Symbol	Conditions	Min.	Typ.	Max.	Unit
Collector-base breakdown voltage	$V_{(BR)CBO}$	$I_C = -100\mu A, I_E = 0$	-40			V
Collector-emitter breakdown voltage	$V_{(BR)CEO}$	$I_C = -1mA, I_B = 0$	-40			V
Emitter-base breakdown voltage	$V_{(BR)EBO}$	$I_E = -100\mu A, I_C = 0$	-5			V
Collector cut-off current	I_{CBO}	$V_{CB} = -35V, I_E = 0$			-100	nA
Collector cut-off current	I_{CEX}	$V_{CE} = -35V, V_{EB(off)} = -0.4V$			-100	nA
Emitter cut-off current	I_{EBO}	$V_{EB} = -4V, I_C = 0$			-100	nA
DC current gain	h_{FE1}	$V_{CE} = -1V, I_C = -0.1mA$	30			
	h_{FE2}	$V_{CE} = -1V, I_C = -1mA$	60			
	h_{FE3}	$V_{CE} = -1V, I_C = -10mA$	100			
	h_{FE4}	$V_{CE} = -2V, I_C = -150mA$	100		300	
	h_{FE5}	$V_{CE} = -2V, I_C = -500mA$	20			
Collector-emitter saturation voltage	$V_{CE(sat)}$	$I_C = -150mA, I_B = -15mA$			-0.40	V
		$I_C = -500mA, I_B = -50mA$			-0.75	V
Base-emitter saturation voltage	$V_{BE(sat)}$	$I_C = -150mA, I_B = -15mA$			-0.95	V
		$I_C = -500mA, I_B = -50mA$			-1.30	V
Transition frequency	f_T	$V_{CE} = -10V, I_C = -20mA, f = 100MHz$	200			MHz
Delay time	t_d	$V_{CC} = -30V, V_{BE(off)} = -0.5V, I_C = -150mA, I_{B1} = -15mA$			15	ns
Rise time	t_r				20	ns
Storage time	t_s	$V_{CC} = -30V, I_C = -150mA, I_{B1} = I_{B2} = -15mA$			225	ns
Fall time	t_f				60	ns

Rating and Characteristic Curves (MMBT4403-HF)

Fig.1 - Static Characteristic





Fig.2 - $h_{FE} - I_C$



Company reserves the right to improve product design, functions and reliability without notice.

REV:A

Rating and Characteristic Curves (MMBT4403-HF)

Fig.3 - $V_{CEsat} - I_c$




Fig.4 - $V_{BEsat} - I_c$




Fig.5 - $I_c - V_{BE}$




Fig.6 - $C_{ob}/C_{ib} - V_{CB}/V_{EB}$




Fig.7 - $f_T - I_c$









Fig.8 - $P_C - T_a$



Reel Taping Specification



SOT-23	SYMBOL	A	B	C	d	D	D1	D2
	(mm)	3.15 ± 0.10	2.77 ± 0.10	1.22 ± 0.10	1.50 ± 0.10	178.00 ± 2.00	54.40 ± 1.00	13.00 ± 1.00
	(inch)	0.124 ± 0.004	0.109 ± 0.004	0.048 ± 0.004	0.059 ± 0.004	7.008 ± 0.079	2.142 ± 0.039	0.512 ± 0.039


SOT-23	SYMBOL	E	F	P	P0	P1	W	W1
	(mm)	1.75 ± 0.10	3.50 ± 0.10	4.00 ± 0.10	4.00 ± 0.10	2.00 ± 0.10	8.00 ± 0.10	12.30 ± 1.00
	(inch)	0.069 ± 0.004	0.138 ± 0.004	0.157 ± 0.004	0.157 ± 0.004	0.079 ± 0.004	0.315 ± 0.004	0.484 ± 0.039

Company reserves the right to improve product design , functions and reliability without notice.

REV:A


Marking Code

Part Number	Marking Code
MMBT4403-HF	2T



Suggested PAD Layout

SIZE	SOT-23	
	(mm)	(inch)
A	0.90	0.035
B	0.80	0.031
C	0.95	0.037
D	2.00	0.079
E	2.90	0.114



Note: 1. The pad layout is for reference purposes only.

Standard Packaging

Case Type	REEL PACK	
	REEL (pcs)	Reel Size (inch)
SOT-23	3,000	7

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

[Comchip Technology:](#)

[MMBT4403-HF](#)