		PRODUCT	SPECIFICATION				
TITLE		UNIVERSA	L SERIAL BUS				
		MICRO – USI	B CONNECTORS				
		TABLE OF CON	ITENTS				
	1.0	SCOPE					
	2.0	PRODUCT DESCRIPT	ION				
2.1 DESIGN AND CONSTRUCTION							
	2.2 MATERIAL AND PLATING						
3.0 APPLICABLE DOCUMENTS							
	3.1 RATING						
	3	.2 PERFORMANCE AI	ND TEST DESCRIPTION				
	3.3 TEST REQUIREMENTS AND PROCEDURES						
	4.0	TEST SEQUENCE					
	5.0	REFLOW CONDITION					
	6.0	PACKAGING					
REVISION: ECR/E	CN INFORMATION:	TITLE:		SHEET No.			
	<u>»:</u> SH2015-0018	MICRO	-USB CONNECTORS	1 of 7			
DATE	<u>:</u> 2014/07/10 BER:	CREATED / REVISED BY	CHECKED BY: AF	PROVED BY:			
PS-476	42-001	XQZHANG	XQZHANG	AYIN			



1.0 SCOPE

This product specification defines the mechanical, electrical and environmental performance requirements and test methods for Micro-USB connector series products.

2.0 PRODUCT DESCRIPTION

2.1 Design and Construction

Construction and physical dimensions shall be specified on the applicable sales drawing. Connector consists of a metal shell, a plastic housing, and 5 terminals.

Solder components shall meet Lead-Free soldering requirements and the connectors shall be RoHS Compliant.

2.2 Materials and Plating

Refer to respective Molex sales drawings for information on materials, plating and marking.

3.0 APPLICABLE DOCUMENTS

In the event of conflict between the requirements of this specification and the sales drawing, the sales drawing shall take precedence. In the event of conflict between the requirements of the specification and the referenced documents, this specification shall take precedence.

EIA-STANDARD-364: ELECTRICAL CONNECTOR/SOCKET TEST PROCEDURES INCLUDING ENVIRONMENTAL CLASSIFICATIONS

3.1 Rating

Item	Standard
Rated Voltage (Max.)	30V AC (rms)
Rated Current (Max.)	Signal (Pins 2,3,4): 1.0A* ¹
	Power (Pins 1,5): 1.8 A
Operating Temperature Range	-30°C ~ +85°C (Including Terminal Temperature Rise)
Shipping and Storage Temperature Range	-40°C ~ +85°C
Ambient Temperature (Ta):	25°C ± 2°C

*1: Test with power pins, the rated current of signal pins should be 0.5A.

3.2 Performance and Test Description

The connectors shall be designed to meet the electrical, mechanical and environmental performance requirements specified in Para. 3.3

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.
G	<u>EC No:</u> SH2015-0018	MICRO-	2 of 7		
G	<u>DATE:</u> 2014/07/10				
DOCUMENT NUMBER:		CREATED / REVISED BY:	EVISED BY: CHECKED BY: APPRO		OVED BY:
PS-47642-001		XQZHANG XQZHANG AYIN		YIN	
TEMPLATE FILENAME: PRODUCT SPECISIZE A41(V/1) DOC					



3.3 Test Requirements and Procedures

3.3.1 Electrical Performances

ltem	Requirement	Test Condition
Low Level Contact Resistance (initial)	30mΩ Max.	Mated plugs, measure by dry circuit, 20mV DC maximum, open circuit 100mA maximum. Except wire conductor resistance. EIA-364-23
Insulation Resistance (initial)	1000MΩ Min.	Mated plugs, apply 100V DC for 1 minute between adjacent terminal or ground. EIA-364-21
Dielectric Withstanding Voltage	No Breakdown	Mated plugs, apply 100V AC (rms) at 60Hz for 1 minute between adjacent terminal or ground. EIA-364-20
Temperature Rise	30°C Max.	Mated plugs and measure the temperature rise of contact when the maximum DC rated current is passed EIA-364-70
Contact Capacitance	2pF Max.	Measured between adjacent circuits of un- mated connectors at 1kHz. EIA-364-30

3.3.2 Mechanical Performances

Item	Requi	irement	Test Condition
Mating / un- mating force (initial)	Mating force	35N (3.57kgf) Max.	Mating / un-mating at a rate of 12.5mm
	Un-mating force	8N (0.82kgf) Min. 25N (2.58kgf) Max.	per minute. EIA-364-13
Durability	Contact Resistance	ΔR = 10mΩ Max.	Materia (up materia up to 10,000 publics
	Mating force	35N (3.57kgf) Max.	repeatedly at maximum rate of 500
	Un-mating force	8N (0.82kgf) Min. 25N (2.58kgf) Max.	operated, mating speed should be below 200 cycles per hour.)
	Appearance	No breakdown	EIA-304-09

REVISION:	ECR/ECN INFORMATION:	TITLE:			SHEET No.
C	EC No: SH2015-0018			DC	2 7
G	<u>DATE:</u> 2014/07/10	WICKU-	3 Of 1		
DOCUMEN	T NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPRO	OVED BY:
PS-47642-001		XQZHANG XQZHANG AYIN			YIN
TEMPLATE FILENAME: PRODUCT_SPECISIZE_A41(V_1).DOC					



3.3.3 Environmental Performances

	Requir	rement	Test Condition		
	Appearance	No Damage	Mate plugs and subject to the following vibration conditions:		
Vibration	Contact $\Delta R = 10m\Omega$ ResistanceMax.		Random Vibration 3 mutually perpendicularly. 10~2000Hz, 0.02G2/Hz		
	Discontinuity	1 microsecond Max.	20 minutes per plane EIA-364-28		
Mechanical Shock	Appearance	No damage	Mate plugs and subject to the following shock conditions, 3 shocks shall be applied along 3		
	Contact Resistance	ΔR =10mΩ Max.	mutually perpendicular axes, passing DC 100mA current during the test. (Total of 18 shocks) Test Pulse - Half Sine		
	Discontinuity	1 Microsecond Max.	Peak Value: 30G Duration: 11 ms EIA-364-27		
Temperature Life	Appearance	No damage	Mate plugs and expose to 105±2°		
	Contact Resistance	ΔR =10mΩ Max.	the exposure period, the test specimens shall be conditioned at		
Resistance)	Insulation Resistance	100 MΩ Min.	ambient room conditions for 1 to 2 hours, after which the specified		
	Dielectric Strength	No Breakdown	EIA-364-17B		
	Appearance	There shall be no remarkable corrosion	Mate connectors and expose to humidity in 7 cycles 7 clause. Upo		
Cyclic Humidity	Contact Resistance	ΔR =10mΩ Max.	completion of the exposure period the test specimens shall be conditioned at ambient room		
o y en e : y	Dielectric Strength	No breakdown	conditions for 1 to 2 hours, after which the specified measurement shall be performed.		

<u>REVISION:</u>	<u>ECR/ECN INFORMATION:</u> <u>EC No:</u> SH2015-0018 DATE: 2014/07/10	MICRO-	<u>SHEET No.</u> 4 of 7		
DOCUMEN	T NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPRO	OVED BY:
PS-47642-001		XQZHANG XQZHANG		А	YIN
			TEMPLATE FILENAM	: PRODUCT_SPE	C[SIZE_A4](V.1).DOC



PRODUCT SPECIFICATION

ltem	Requir	rement	Test Condition		
	Appearance	No Damage	Mate plugs and subject to the flowing conditions for 10 cycles, Upon completion of the exposure		
Thermal shock	Contact resistance	ΔR =10mΩ Max.	conditioned at ambient room conditions for 1 to 2 hours, after		
(Temperature cycling)	Dielectric Strength	No breakdown	which the specified measurements shall be performed. 1 cycle		
	Insulation Resistance	100 MΩ Min.	a) -55 ± 3°C 30 minutes. b) +85 ± 2°C 30 minutes. EIA-364-32C		
Salt spray	Appearance	By visual inspection without noticeable rust.	Mate plugs and expose to the following salt mist conditions. Upon completion of the exposure period salt deposits shall be removed by gentle wash or dip in running wate after which the specified		
	Contact Resistance	ΔR =10mΩ Max.	measurements shall be performe NaCl solution Concentration: 5 ± 1% Spray time: 48 ± 4 hours Ambient Temperature: 35 ± 2°C EIA-364-26		
Solder-ability (not for black nickel plating)	Solder Wetting	95% of immersed area must show no voids or pin holes	Dip solder-tails in flux then immerse in solder bath at 245 \pm 5°C up to 0.5mm from the bottom of the housing for 4 ~ 5 seconds (EIA-364-52 Category 2)		
Without any deformation of case or excessive looseness of the terminals (pins). Electrical characteristics shall be satisfied.		For procedures other than specific below, refer to IEC PUB. 68-2-20. Test Tb Method 1A or 2 Solder bath method Solder temperature: 255 +5/-0°C Immersion time: 10 ± 1 second Thickness of PCB: 0.8 mm Solder iron method Solder temperature: 350 ± 10°C			
	No any damage after reflow		Immersion time: 3 ± 1 second However, excessive pressure shall not be applied to the terminal Reference reflow condition at Para 5.0		

G	<u>EC No:</u> SH2015-0018 <u>DATE:</u> 2014/07/10	MICRO-USB CONNECTORS 5					
DOCUMENT NUMBER:		CREATED / REVISED BY:	CHECKED BY:	APPROVED BY:			
PS-47642-001		XQZHANG	XQZHANG	AYIN			
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A4](V.1).DOC							



4.0 TEST SEQUENCE

All samples have to be soldered on PCB and reflow twice before measuring and testing.

	ltem	А	В	С	D	E	F	G	Н
1	Contact Resistance	1, 4	2, 5	1, 7	1, 3	1, 3			
2	Insulation Resistance			3, 8					
3	Dielectric Strength			4, 9					
4	Contact capacitance			2					
5	Durability		3						
6	Vibration	3							
7	Mechanical Shock	2							
8	Temperature Life					2			
9	Humidity			6					
10	Thermal shock			5					
11	Salt spray				2				
12	Temperature Rise						1		
13	Mating / un- mating force		1, 4						
14	Solder-ability							1	
15	Resistance to soldering heat								1
	Number of sample	5	5	5	5	5	5	5	5

REVISION:	ECR/ECN INFORMATION:	<u>TITLE:</u>			SHEET No.
G	EC No: SH2015-0018	MICRO-	6 of 7		
U	<u>DATE:</u> 2014/07/10				
DOCUMEN	T NUMBER:	CREATED / REVISED BY:	CHECKED BY:	APPRO	OVED BY:
PS-47642-001		XQZHANG XQZHANG AY		YIN	
TEMPLATE FILENAME: PRODUCT_SPEC[SIZE_A4](V.1).DOC					

