

Item no.: 280-683
Product description: 3-conductor disconnect terminal block with disconnect tab



Produkt kann von Bild abweichen / product may differ

Packing unit 50 pieces

RoHS compliant

Product group	1 (Rail Mounted Terminal Blocks)
Cross section [mm ²]	0.08 - 2.5 mm ²
Cross section [AWG]	28 - 12 AWG
Connection method	CAGE CLAMP®CONNECTION
Measured voltage EN	400 V
Measured shock voltage	6 kV
Pollution degree	3
Current intensity EN	10 A
Weight	8.212 g
Color	grey
Wiring type	Front-entry
No. of connection Points	3
No. of potentials	2
Height	52.5 mm
Height	2.07 in
Width	5 mm
Width	0.197 in
Depth	64 mm
Depth	2.52 in

Strip length from	8 mm
Strip length to	9 mm
Strip length	0.33 in
Mounting	TS 35



Item number	Admission office	Approval no.	Voltage [V]	Current [A]	Cross section [mm ²]
280-683	ABS	05-HG476175/3-PDA	400	16	2,5
280-683	BV	07436/C0			0,08-2,5
280-683	CCA	NL5855	400	10	2,5
280-683	CSA	154112-1536071	600	15	28-12
280-683	DNV	E-10423	800	20	2,5
280-683	GL	17295-00HH	400	16	2,5
280-683	KEMA	2082859.07	400	10	2,5
280-683	LR	91/20112(E6)	400	16	2,5
280-683	PRS	TE/1718/880590/08	400	10	2,5
280-683	RMR	11130002	400	16	2,5
280-683	UR	E45172	300	15	28-12

Sorting criteria: admission office - approval number

© WAGO Kontakttechnik GmbH & Co. KG

Specifications are subject to changes and errors may be expected