



REPRESENTATIVE IMAGE

Product: [8451](#)

Audio & Instrumentation, 1 Pair 22 AWG, TC, O/A Foil, CM

Product Description

1 Pair 22 AWG stranded (7x30) TC conductors, polypropylene insulation, paper wrap, twisted pair, overall Beldfoil® shield (100% coverage), 22 AWG stranded TC drain wire, PVC jacket.

Technical Specifications

Product Overview

Suitable Applications:	for use with automatic stripping equipments; low voltage analog signals (4-20ma, 0-10v, ...); low voltage digital control (24v, ...); line level audio; computer communication; panel wiring
------------------------	--

Construction Details

Conductor

Element	Number of Element	AWG	Stranding	Material
Pair(s)	1	22	7x30	TC - Tinned Copper

Insulation

Element	Material	Thickness	Color Code
Pair(s)	PP - Polypropylene	0.009 in	Black & Red

Outer Shield Material

Shield Type	Material	Coverage	Drainwire Type
Tape	Bi-Laminate (Alum+Poly)	100%	22 AWG (7x30) TC

Outer Jacket Material

Material	Thickness	Nom. Diameter
PVC - Polyvinyl Chloride	0.020 in	0.138 in

Cable Diameter (Nominal): 0.138 in

Electrical Characteristics

Electricals

Element	Nom. Conductor DCR	Nom. Capacitance Cond-to-Cond	Nom. Capacitance Cond-to-Other (Conds + Shield)	Characteristic Impedance	Nom. Velocity of Prop.	Max. Current
Pair(s)	14.5 Ohm/1000ft	34 pF/ft	67 pF/ft	45 Ohm	66%	2.9 Amps per Conductor at 25°C
Nom Outer Shield DCR:	14.1 Ohm/1000ft					

Voltage

UL Voltage Rating
300 V RMS

Mechanical Characteristics

Temperature

Operating
-20°C To +75°C

Bend Radius

Stationary Min.	Installation Min.
1.5 in	1.4 in

Max. Pull Tension:	27 lbs
Bulk Cable Weight:	13 lbs/1000ft

Standards and Compliance

Environmental Suitability:	Indoor - Riser, Indoor
Flammability / Fire Resistance:	UL1666 Vertical Shaft, FT4, IEC 60332-1-2
NEC / UL Compliance:	Article 800, CMR
CEC / C(UL) Compliance:	CMG
CPR Euroclass:	Eca
European Directive Compliance:	EU CE Mark, EU Directive 2015/863/EU, EU Directive 2011/65/EU (ROHS II), EU Directive 2012/19/EU (WEEE)
APAC Compliance:	China RoHS II (GB/T 26572-2011)

Product Notes

Notes:	Unique paper separator facilitates jacket stripping.
--------	--

History

Update and Revision:	Revision Number: 0.344 Revision Date: 09-30-2020
----------------------	--

© 2021 Belden, Inc

All Rights Reserved.

Although Belden makes every reasonable effort to ensure their accuracy at the time of this publication, information and specifications described here in are subject to error or omission and to change without notice, and the listing of such information and specifications does not ensure product availability.

Belden provides the information and specifications herein on an "ASIS" basis, with no representations or warranties, whether express, statutory or implied. In no event will Belden be liable for any damages (including consequential, indirect, incidental, special, punitive, or exemplary damages) whatsoever, even if Belden has been advised of the possibility of such damages, whether in an action under contract, negligence or any other theory, arising out of or in connection with the use, or inability to use, the information or specifications described herein.

All sales of Belden products are subject to Belden's standard terms and conditions of sale.

Belden believes this product to be in compliance with all applicable environmental programs as listed in the data sheet. The information provided is correct to the best of Belden's knowledge, information and belief at the date of its publication. This information is designed only as a general guide for the safe handling, storage, and any other operation of the product itself or the one that it becomes a part of. The Product Disclosure is not to be considered a warranty or quality specification. Regulatory information is for guidance purposes only. Product users are responsible for determining the applicability of legislation and regulations based on their individual usage of the product.

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

Belden Wire & Cable:

[8451 010500](#) [8451 010100](#) [8451 0101000](#) [8451 010U1000](#) [8451 008U1000](#) [8451 008U500](#) [8451 0081000](#) [8451 008500](#) [8451 0105000](#) [8451 010U500](#) [8451 01015000](#) [8451 01010000](#)