

Is Now Part of



ON Semiconductor®

To learn more about ON Semiconductor, please visit our website at <u>www.onsemi.com</u>

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (_), the underscore (_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at www.onsemi.com. Please email any questions regarding the system integration to Fairchild_questions@onsemi.com.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or unavteries, and distributors harmless against all claims, costs, damages, and expenses, and reasonable attorney fees arising out or i, directly or indirectly, any claim of personal injury or death associated with such unintended or unauthorized use, even if such claim alleges that ON Semiconductor was negligent regarding the design or manufacture of the part. ON Semiconductor and is officers, employees, uniotificated use, even if such claim any manner.



December 2007

74VHC125 Quad Buffer with 3-STATE Outputs

Features

- High Speed: t_{PD} = 3.8ns (Typ.) at V_{CC} = 5V
- Lower power dissipation: $I_{CC} = 4 \ \mu A$ (Max.) at $T_A = 25^{\circ}C$
- High noise immunity: $V_{NIH} = V_{NIL} = 28\% V_{CC}$ (Min.)
- Power down protection is provided on all inputs
- Low noise: V_{OLP} = 0.8V (Max.)
- Pin and function compatible with 74HC125

General Description

The VHC125 contains four independent non-inverting buffers with 3-STATE outputs. It is an advanced highspeed CMOS device fabricated with silicon gate CMOS technology and achieves the high-speed operation similar to equivalent Bipolar Schottky TTL while maintaining the CMOS low power dissipation.

An input protection circuit insures that 0V to 7V can be applied to the input pins without regard to the supply voltage. This device can be used to interface 5V to 3V systems and two supply systems such as battery backup. This circuit prevents device destruction due to mismatched supply and input voltages.


Ordering Information

Order Number	Package Number	Package Description
74VHC125M	M14A	14-Lead Small Outline Integrated Circuit (SOIC), JEDEC MS-012, 0.150" Narrow
74VHC125SJ	M14D	14-Lead Small Outline Package (SOP), EIAJ TYPE II, 5.3mm Wide
74VHC125MTC	MTC14	14-Lead Thin Shrink Small Outline Package (TSSOP), JEDEC MO-153, 4.4mm Wide

Device also available in Tape and Reel. Specify by appending suffix letter "X" to the ordering number.

All packages are lead free per JEDEC: J-STD-020B standard.


Connection Diagram



Pin Description

Pin Names	Description					
Ā _n , B _n	Inputs					
O _n	Outputs					

Logic Symbol



Function Table

Inp	outs	Output			
Ān	B _n	On			
L	L	L			
L	Н	Н			
Н	Х	Z			

H = HIGH Voltage Level

L = LOW Voltage Level

Z = HIGH Impedance

X = Immaterial

©1993 Fairchild Semiconductor Corporation 74VHC125 Rev. 1.4.0

Absolute Maximum Ratings

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Rating
V _{CC}	Supply Voltage	-0.5V to +7.0V
V _{IN}	DC Input Voltage	-0.5V to +7.0V
V _{OUT}	DC Output Voltage	-0.5V to V _{CC} + 0.5V
I _{IK}	Input Diode Current	–20mA
I _{OK}	Output Diode Current	±20mA
I _{OUT}	DC Output Current	±25mA
I _{CC}	DC V _{CC} / GND Current	±50mA
T _{STG}	Storage Temperature	–65°C to +150°C
TL	Lead Temperature (Soldering, 10 seconds)	260°C

Recommended Operating Conditions⁽¹⁾

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

Symbol	Parameter	Rating
V _{CC}	Supply Voltage	2.0V to +5.5V
V _{IN}	Input Voltage	0V to +5.5V
V _{OUT}	Output Voltage	0V to V _{CC}
T _{OPR}	Operating Temperature	-40°C to +85°C
t _r , t _f	Input Rise and Fall Time,	
	$V_{CC} = 3.3V \pm 0.3V$	0ns/V ~ 100ns/V
	$V_{CC} = 5.0V \pm 0.5V$	0ns/V ~ 20ns/V

Note:

1. Unused inputs must be held HIGH or LOW. They may not float.

					T _A =						
			25°C		25°C	°C –40°C		o +85°C	1		
Symbol	Parameter	V _{CC} (V)	Conditions		Min.	Тур.	Max.	Min.	Max.	Units	
V _{IH}	HIGH Level Input	2.0			1.50			1.50		V	
	Voltage	3.0–5.5	1		$0.7 \times V_{CC}$			0.7 x V _{CC}			
V _{IL}	LOW Level Input	2.0					0.50		0.50	V	
	Voltage	3.0–5.5					0.3 x V _{CC}		$0.3 \times V_{CC}$		
V _{OH}	HIGH Level Output Voltage	2.0	$V_{IN} = V_{IH}$	I _{OH} = -50μA	1.9	2.0		1.9		V	
		3.0	or V _{IL}		2.9	3.0		2.9			
		4.5			4.4	4.5		4.4			
		3.0		$I_{OH} = -4mA$	2.58			2.48			
		4.5		I _{OH} = -8mA	3.94			3.80			
V _{OL}	LOW Level Output Voltage	2.0	$V_{IN} = V_{IH}$	I _{OL} = 50μA		0.0	0.1		0.1	V	
		3.0	or V _{IL}			0.0	0.1		0.1		
		4.5				0.0	0.1		0.1		
		3.0		$I_{OL} = 4mA$			0.36		0.44		
		4.5		I _{OL} = 8mA			0.36		0.44		
I _{OZ}	3-STATE Output Off-State Current	5.5	$V_{IN} = V_{IH} c$ $V_{OUT} = V_{C}$				±0.25		±2.5	μA	
I _{IN}	Input Leakage Current	0–5.5	V _{IN} = 5.5V	or GND			±0.1		±1.0	μΑ	
I _{CC}	Quiescent Supply Current	5.5	$V_{IN} = V_{CC}$	or GND			4.0		40.0	μA	

Noise Characteristics

				T _A =		
Symbol	Parameter	V _{CC} (V)	Conditions	Тур.	Limits	Units
V _{OLP} ⁽²⁾	Quiet Output Maximum Dynamic V _{OL}	5.0	$C_L = 50 pF$	0.5	0.8	V
V _{OLV} ⁽²⁾	Quiet Output Minimum Dynamic V _{OL}	5.0	$C_L = 50 pF$	-0.5	-0.8	V
V _{IHD} ⁽²⁾	Minimum HIGH Level Dynamic Input Voltage	5.0	$C_L = 50 pF$		3.5	V
V _{ILD} ⁽²⁾	Maximum HIGH Level Dynamic Input Voltage	5.0	$C_L = 50 pF$		1.5	V

Note:

2. Parameter guaranteed by design.

AC Electrical Characteristics

					т	_A = 25°	С	T _A = - to +	–40°C 85°C	
Symbol	Parameter	$V_{CC}(V)$	Conditions		Min.	Тур.	Max.	Min.	Max.	Units
t _{PLH} , t _{PHL}	Propagation Delay	3.3 ± 0.3		$C_L = 15 pF$		5.6	8.0	1.0	9.5	ns
	Time			$C_L = 50 pF$		8.1	11.5	1.0	13.0	
		5.0 ± 0.5		$C_L = 15 pF$		3.8	5.5	1.0	6.5	ns
				$C_L = 50 pF$		5.3	7.5	1.0	8.5	
t _{PZL} , t _{PZH}	3-STATE Output	3.3 ± 0.3	$R_L = 1k\Omega$	$C_L = 15 pF$		5.4	8.0	1.0	9.5	ns
	Enable Time			$C_L = 50 pF$		7.9	11.5	1.0	13.0	
		5.0 ± 0.5		$C_L = 15 pF$		3.6	5.1	1.0	6.0	ns
				$C_L = 50 pF$		5.1	7.1	1.0	8.0	
t _{PLZ} , t _{PHZ}	3-STATE Output	3.3 ± 0.3	$R_L = 1k\Omega$	$C_L = 50 pF$		9.5	13.2	1.0	15.0	ns
	Disable Time	5.0 ± 0.5]	$C_L = 50 pF$		6.1	8.8	1.0	10.0	
t _{OSLH} , t _{OSHL}	Output to Output	3.3 ± 0.3	(3)	$C_L = 50 pF$			1.5		1.5	ns
	Skew	5.0 ± 0.5]	$C_L = 50 pF$			1.0		1.0	
C _{IN}	Input Capacitance		V _{CC} = Ope	en		4	10		10	pF
C _{OUT}	Output Capacitance	V _{CC} = 5.0V		V		6				pF
C _{PD}	Power Dissipation Capacitance		(4)			14				pF

Notes:

3. Parameter guaranteed by design. $t_{OSLH} = |t_{PLHmax} - t_{PLHmin}|; t_{OSHL} = |t_{PHLmax} - t_{PHLmin}|.$

4. C_{PD} is defined as the value of the internal equivalent capacitance which is calculated from the operating current consumption without load. Average operating current can be obtained by the equation: I_{CC} (Opr.) = $C_{PD} \cdot V_{CC} \cdot f_{IN} + I_{CC} / 4$ (per bit).





ON Semiconductor and are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <u>www.onsemi.com/site/pdf/Patent-Marking.pdf</u>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor haves against all claims, costs, damages, and expenses, and reasonable attorney fees arising out of, directly or indirectly, any claim of personal injury or death a

PUBLICATION ORDERING INFORMATION

LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800–282–9855 Toll Free USA/Canada Europe, Middle East and Africa Technical Support: Phone: 421 33 790 2910

Japan Customer Focus Center Phone: 81-3-5817-1050 ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

© Semiconductor Components Industries, LLC

Mouser Electronics

Authorized Distributor

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi:

74VHC125M 74VHC125MX 74VHC125MTC 74VHC125MTCX 74VHC125SJX 74VHC125SJ