

### Is Now Part of



## ON Semiconductor®

# To learn more about ON Semiconductor, please visit our website at www.onsemi.com

Please note: As part of the Fairchild Semiconductor integration, some of the Fairchild orderable part numbers will need to change in order to meet ON Semiconductor's system requirements. Since the ON Semiconductor product management systems do not have the ability to manage part nomenclature that utilizes an underscore (\_), the underscore (\_) in the Fairchild part numbers will be changed to a dash (-). This document may contain device numbers with an underscore (\_). Please check the ON Semiconductor website to verify the updated device numbers. The most current and up-to-date ordering information can be found at <a href="www.onsemi.com">www.onsemi.com</a>. Please email any questions regarding the system integration to Fairchild <a href="guestions@onsemi.com">guestions@onsemi.com</a>.

ON Semiconductor and the ON Semiconductor logo are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at www.onsemi.com/site/pdf/Patent-Marking.pdf. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor makes no warranty, representation or guarantee regarding the suitability of its products for any particular purpose, nor does ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any EDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officer



February 2008

## FSA5157 0.4Ω Low-Voltage SPDT Analog Switch

### **Features**

- Typical 0.4Ω On Resistance (R<sub>ON</sub>) for +2.7V Supply
- FSA5157 Features Less than 12µA I<sub>CCT</sub> Current When S Input is Lower than V<sub>CC</sub>
- 0.25Ω Maximum R<sub>ON</sub> Flatness for +2.7V Supply
- 1.0 x 1.45mm 6-Lead MicroPak™ Package
- Broad V<sub>CC</sub> Operating Range: 1.65V to 4.3V
- Low THD (0.02% Typical for 32Ω Load)
- High-Current Handling Capability (350mA Continuous Current Under 3.3V Supply)
- Control Logic is 1.8V CMOS Logic Compatible

### **Applications**

- Cellular Phone
- PDA
- Portable Media Player

### **General Description**

The FSA5157 is a low on resistance, low-power, Single Pole Double Throw (SPDT) analog switch. This product has been designed for switching audio signals in applications such as cell phones and portable media players. The ultra-low  $0.4\Omega$  impedance, sub- $\mu$ A current consumption, and 1.65V to 4.3V operating voltage range makes this product ideal for battery-powered applications. The FSA5157 also features bi-directional operation and break-before-make functionality. This device is fully specified for operation at 1.8V, 2.5V, and 3.3V.

A growing number of applications require the voltage applied to the select input to be lower than the  $V_{CC}$  applied. Under this condition, most switches would typically consume over  $100\mu A$  of current. This would be an unacceptable level for battery-powered applications. The FSA5157 is designed to minimize current consumption under this condition. The  $I_{CCT}$  is specified for <12 $\mu A$  under a worst-case condition of  $V_{CC}=4.3V$  and  $V_{IN}=1.8V$ .

## **Ordering Information**

Order Number	Top Mark	Package Description	Packing Method
FSA5157P6X	C57	6-Lead SC70, EIAJ SC88, 1.25mm Wide	3000 Units on Tape and Reel
FSA5157L6X	FT	6-Lead MicroPak, 1.0mm Wide	5000 Units on Tape and Reel



All packages are lead free per JEDEC: J-STD-020B standard.

## **Application Diagram**




Figure 1. Application Diagram

MicroPak™ is a trademark of Fairchild Semiconductor Corporation.

## **Pin Assignments**




Figure 2. 6-Lead SC70




Figure 3. 6-Lead MicroPak™

## **Truth Tables**

Control Input(s)	Function
LOW Logic Level	B <sub>0</sub> Connected to A
HIGH Logic Level	B <sub>1</sub> Connected to A

## **Pin Descriptions**

Pin Names	Function
A, B <sub>0</sub> , B <sub>1</sub>	Data Ports
S	Control Input

### **Absolute Maximum Ratings**

Stresses exceeding the absolute maximum ratings may damage the device. The device may not function or be operable above the recommended operating conditions and stressing the parts to these levels is not recommended. In addition, extended exposure to stresses above the recommended operating conditions may affect device reliability. The absolute maximum ratings are stress ratings only.

Symbol	Parameter	Min.	Max	Units
V <sub>CC</sub>	Supply Voltage	-0.5	5.5	V
V <sub>S</sub>	Switch Voltage <sup>(1)</sup>	-0.5	V <sub>CC</sub> + 0.3V	V
V <sub>IN</sub>	Input Voltage <sup>(1)</sup>	-0.5	V <sub>CC</sub>	V
I <sub>IK</sub>	Input Diode Current		-50	mA
I <sub>SW</sub>	Switch Current		350	mA
I <sub>SWPEAK</sub>	Peak Switch Current (Pulsed at 1ms duration, <10% Duty Cycle)		500	mA
P <sub>D</sub>	SC70 6L Package		180	mW
' D	MicroPak 6L Package		180	mW
T <sub>STG</sub>	Storage Temperature Range	-65	+150	°C
$T_J$	Maximum Junction Temperature		+150	°C
$T_L$	Lead Temperature Soldering, 10 seconds		+260	°C
ESD	Human Body Model		8000	V

#### Note:

 The input and output negative voltage ratings may be exceeded if the input and output diode current ratings are observed.

## **Recommended Operating Conditions**

The Recommended Operating Conditions table defines the conditions for actual device operation. Recommended operating conditions are specified to ensure optimal performance to the datasheet specifications. Fairchild does not recommend exceeding them or designing to absolute maximum ratings.

Symbol	Parameter	Min.	Max.	Rating
$V_{CC}$	Supply Voltage	1.65	4.30	V
$V_{IN}$	Control Input Voltage <sup>(2)</sup>	0	V <sub>CC</sub>	V
V <sub>IN</sub>	Switch Input Voltage	0	V <sub>CC</sub>	V
T <sub>A</sub>	Operating Temperature	-40	+85	°C

### Note:

2. Unused inputs must be held HIGH or LOW. They may not float.

### **DC Electrical Characteristics**

All typical values are at 25°C unless otherwise specified.

Symbol	Parameter	Conditions	V <sub>CC</sub> (V)	T <sub>A</sub> =+25°C			T <sub>A</sub> = -40°C to +85°C		Units
-				Min.	Тур.	Max.	Min.	Max.	
			3.6 to 4.3				1.4		
			2.7 to 3.6				1.3		
$V_{IH}$	Input Voltage High		2.3 to 2.7				1.1		V
			1.65 to 1.95				0.9		
			3.6 to 4.3					0.7	
			2.7 to 3.6					0.5	
$V_{IL}$	Input Voltage Low		2.3 to 2.7					0.4	V
			1.65 to 1.95					0.4	
I <sub>IN</sub>	Control Input Leakage	V <sub>IN</sub> = 0V to V <sub>CC</sub>	1.65 to 4.3				-0.5	0.5	μΑ
I <sub>NO(OFF)</sub> , I <sub>NC(OFF)</sub>	Off-Leakage Current of Port B <sub>0</sub> and B <sub>1</sub>	$A = 0.3V, V_{CC} - 0.3V,$ $B_0 \text{ or } B_1 = 0.3V,$ $V_{CC} - 0.3V \text{ or Floating}$	1.95 to 4.3	-10		10	-50	50	nA
I <sub>A(ON)</sub>	On Leakage Current of Port A	$A = 0.3V, V_{CC} - 0.3V,$ $B_0 \text{ or } B_1 = 0.3V,$ $V_{CC} - 0.3V \text{ or Floating}$	1.95 to 4.3	-20		20	-100	100	nA
		I <sub>OUT</sub> = 100mA, B <sub>0</sub> or B <sub>1</sub> = 0V, 0.7V, 3.6V, 4.3V	4.3		0.36			0.60	Ω
R <sub>ON</sub>	Switch On Resistance <sup>(3)</sup>	I <sub>OUT</sub> = 100mA, B <sub>0</sub> or B <sub>1</sub> = 0V, 0.7V, 2.0V, 2.7V	2.7		0.4			0.7	
TON	Owner on resistance	I <sub>OUT</sub> = 100mA, B <sub>0</sub> or B <sub>1</sub> = 0V, 0.7V, 2.0V, 2.3V	2.3		0.55			0.80	
		$I_{OUT} = 100 \text{mA}, B_0 \text{ or} $ $B_1 = 0.7 \text{V}$	1.65		1.5	2.5		3.0	
			4.3		0.04			0.75	
ΔR <sub>ON</sub>	On Resistance Matching	I <sub>OUT</sub> = 100mA,	2.7		0.06			0.13	Ω
ZIVON	Between Channels <sup>(4)</sup>	$B_0 \text{ or } B_1 = 0.7V$	2.3		0.12			0.20	32
			1.65		1.0	A			
			4.3					0.25	
R <sub>FLAT(ON)</sub>	On Resitance	I <sub>OUT</sub> = 100mA,	2.7					0.25	Ω
	Flatness <sup>(5)</sup>	$B_0$ or $B_1 = 0V$ to $V_{CC}$	2.3					0.3	
			1.65		0.3				
I <sub>CC</sub>	Quiescent Supply Current	$V_{IN} = 0V \text{ or } V_{CC}, I_{OUT} = 0$	4.3	-100	30	100	-500	500	nA
la	Increase in I <sub>CC</sub> per	V <sub>IN</sub> = 1.8V	4.3		7.0	12.0		15.0	μΑ
I <sub>CCT</sub>	Control Input	V <sub>IN</sub> = 2.6V	4.3		3.0	6.0		7.0	

- 3. On resistance is determined by the voltage drop between A and B pins at the indicated current through the switch.
- 4.  $\Delta R_{ON} = R_{ONmax} R_{ONmin}$  measured at identical  $V_{CC}$ , temperature, and voltage. 5. Flatness is defined as the difference between the maximum and minimum value of on resistance over the specified range of conditions.

## **AC Electrical Characteristics**


All typical values are at 25°C unless otherwise specified.

Symbol	Parameter	Conditions	V <sub>CC</sub> (V)	T	<sub>A</sub> = +25>	«С		10×C to	Units	Figure
				Min.	Тур.	Max.	Min.	Max.		
			3.6 to 4.3			55		60		
	Turn On Time	$B_0 \text{ or } B_1 = 1.5V,$	2.7 to 3.6			60		65	-	Figure 7
t <sub>ON</sub>	Turn-On Time	$R_L = 50\Omega$ , $C_L = 35pF$	2.3 to 2.7			65		70	ns	Figure 7
			1.65 to 1.95		70			90		
		$B_0$ or $B_1 = 1.5V$ ,	3.6 to 4.3			30		35		
	Turn Off Times		2.7 to 3.6			35		40		Figure 7
t <sub>OFF</sub>	Turn-Off Time	$R_L = 50\Omega$ , $C_L = 35pF$	2.3 to 2.7			40		45	ns	Figure 7
			1.65 to 1.95		40			55		
	/		3.6 to 4.3				5			
	Break-Before-	$B_0$ or $B_1 = 1.5V$ ,	2.7 to 3.6				5		ns	Figure 8
t <sub>BBM</sub>	Make Time	$R_L = 50\Omega, C_L = 35pF$	2.3 to 2.7				5			
			1.65 to 1.95				5			
		rge Injection $C_L = 1.0 \text{ nF}, V_{GEN} = 0V,$ $R_{GEN} = 0\Omega$	3.6 to 4.3		6				pC	Figure 11
	Charge Injection		2.7 to 3.6		6					
Q			2.3 to 2.7		6					
			1.65 to 1.95							
			3.6 to 4.3		-75					
0.00	0"	$f = 100kHz, R_L = 50\Omega,$	2.7 to 3.6		-75				- dB	Figure 9
OIRR	Off-Isolation	C <sub>L</sub> = 5pF (Stray)	2.3 to 2.7		-75					
			1.65 to 1.95		-75					
			3.6 to 4.3		-75					
V/. II		$f = 100kHz, R_L = 50\Omega,$	2.7 to 3.6		-75				1	
Xtalk	Crosstalk	$C_L = 5pF (Stray)$	2.3 to 2.7		-75				dB	Figure 10
			1.65 to 1.95		-70		/			
BW	-3db Bandwidth	$R_L = 50\Omega$	1.65 to 4.3		80				MHz	Figure 13
			3.6 to 4.3							/
	Total Harmonic Distortion	$R_L = 32\Omega$ , $V_{IN} = 2V_{PP}$ , $f = 20$ Hz to $20$ kHz	2.7 to 3.6		0.02					
THD		Distortion $R_L = 32\Omega, V_{IN} = 1.$	$R_L = 32\Omega, V_{IN} = 1.5V_{PP},$ f = 20Hz to 20kHz	2.3 to 2.7		0.036				%
		$R_L = 32\Omega, V_{IN} = 1.2V_{PP},$ f = 20Hz to 20kHz	1.65 to 1.95		0.01					

## Capacitance

Symbol	Parameter	Conditions	V <sub>CC</sub> (V)	Т	<sub>A</sub> =+25	°C		0°C to 5°C	Units	Figure
				Min.	Тур.	Max.	Min.	Max.		
C <sub>IN</sub>	Control Pin Input Capacitance	f = 1MHz	0.0		1.5				pF	Figure 12
C <sub>OFF</sub>	B Port OFF Capacitance	f = 1MHz	4.5		21.0				pF	Figure 12
C <sub>ON</sub>	A Port ON Capacitance	f = 1MHz	4.5		90.0				pF	Figure 12

## **Typical Characteristics**






Figure 4.  $R_{ON}$  Switch On Resistance,  $I_{ON}$  = 100mA,  $V_{CC}$  = 2.3V B0

Figure 5.  $R_{ON}$  Switch On Resistance,  $I_{ON}$  = 100mA,  $V_{CC}$  = 2.7V B0






Figure 6.  $R_{ON}$  Switch On Resistance,  $I_{ON}$  = 100mA,  $V_{CC}$  = 4.3V B0

## **AC Loading and Waveforms**



### Notes:

- 6.  $R_L$ ,  $R_S$ , and  $C_L$  are functions of the application environment (see AC Electrical table for specific values). 7.  $C_L$  includes test fixture and stray capacitance.
  - Figure 7. Turn-Off Timing



\*C<sub>L</sub> includes fixture and stray capacitance

Figure 8. Break-Before-Make Timing




Figure 9. Off Isolation

## AC Loading and Waveforms (continued)




Figure 10. Non-Adjacent Channel-to-Channel Crosstalk




Figure 11. Charge Injection Test




Figure 12. On/Off Capacitance Measurement Setup

## AC Loading and Waveforms (continued)




Figure 13. Bandwidth




Figure 14. Harmonic Distortion

## **Physical Dimensions**





Figure 15. 6-Lead SC70, EIAJ SC88, 1.25mm Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: <a href="http://www.fairchildsemi.com/packaging/">http://www.fairchildsemi.com/packaging/</a>

## **Physical Dimensions**



- 1. CONFORMS TO JEDEC STANDARD M0-252 VARIATION UAAD
- 2. DIMENSIONS ARE IN MILLIMETERS
- 3. DRAWING CONFORMS TO ASME Y14.5M-1994

MAC06AREVC

Figure 16. 6-Lead MicroPak™, 1.0mm Wide

Package drawings are provided as a service to customers considering Fairchild components. Drawings may change in any manner without notice. Please note the revision and/or date on the drawing and contact a Fairchild Semiconductor representative to verify or obtain the most recent revision. Package specifications do not expand the terms of Fairchild's worldwide terms and conditions, specifically the warranty therein, which covers Fairchild products.

Always visit Fairchild Semiconductor's online packaging area for the most recent package drawings: <a href="http://www.fairchildsemi.com/packaging/">http://www.fairchildsemi.com/packaging/</a>

For MicroPak tape and reel specifications, please visit Fairchild Semiconductor's online packaging area: http://www.fairchildsemi.com/products/logic/pdf/micropak\_tr.pdf





SupreMOS™

SyncFET™

p wer

TinyBoost™

TinyBuck™

TinyLogic<sup>®</sup>

TINYOPTO™

TinyPower™

TinyPWM™

TinyWire™

μSerDes™

UniFET™

Ultra FRFET™

UHC®

VСX™

SYSTEM ®

The Power Franchise®

### **TRADEMARKS**

The following includes registered and unregistered trademarks and service marks, owned by Fairchild Semiconductor and/or its global subsidiaries, and is not intended to be an exhaustive list of all such trademarks.

ACEx<sup>®</sup> FPS™ PDP-SPM™ FRFET® Power220® Build it Now™ POWEREDGE® CorePLUS™ Global Power Resources Power-SPM™ Green FPS™ CROSSVOLT™ PowerTrench® CTL TM Green FPS™e-Series™ Current Transfer Logic™ EcoSPARK<sup>®</sup> Programmable Active Droop™ GTO™ QFET® i-Lo™ EZSWITCH™ \* QS™ IntelliMAX™ QT Optoelectronics™ ISOPLANAR™ Quiet Series™ MegaBuck™ RapidConfigure™ MICROCOUPLER™ SMART START™ SPM<sup>®</sup> MicroFET™ Fairchild<sup>®</sup> MicroPak™ Fairchild Semiconductor® STEALTH™ MillerDrive™ FACT\_Quiet Series™ FACT® Motion-SPM™ SuperFET™ FAST® OPTOLOGIC® SuperSOT™-3

OPTOPLANAR®

SuperSOT™-6

SuperSOT™8

#### DISCLAIMER

FastvCore™

FlashWriter®

FAIRCHILD SEMICONDUCTOR RESERVES THE RIGHT TO MAKE CHANGES WITHOUT FURTHER NOTICE TO ANY PRODUCTS HEREIN TO IMPROVE RELIABILITY, FUNCTION, OR DESIGN. FAIRCHILD DOES NOT ASSUME ANY LIABILITY ARISING OUT OF THE APPLICATION OR USE OF ANY PRODUCT OR CIRCUIT DESCRIBED HEREIN; NEITHER DOES IT CONVEY ANY LICENSE UNDER ITS PATENT RIGHTS, NOR THE RIGHTS OF OTHERS. THESE SPECIFICATIONS DO NOT EXPAND THE TERMS OF FAIRCHILD'S WORLDWIDE TERMS AND CONDITIONS, SPECIFICALLY THE WARRANTY THEREIN, WHICH COVERS THESE PRODUCTS.

### LIFE SUPPORT POLICY

FAIRCHILD'S PRODUCTS ARE NOT AUTHORIZED FOR USE AS CRITICAL COMPONENTS IN LIFE SUPPORT DEVICES OR SYSTEMS WITHOUT THE EXPRESS WRITTEN APPROVAL OF FAIRCHILD SEMICONDUCTOR CORPORATION.

### As used herein:

- 1. Life support devices or systems are devices or systems 2. A critical component in any component of a life support, which, (a) are intended for surgical implant into the body or (b) support or sustain life, and (c) whose failure to perform when properly used in accordance with instructions for use provided in the labeling, can be reasonably expected to result in a significant injury of the user.
- device, or system whose failure to perform can be reasonably expected to cause the failure of the life support device or system, or to affect its safety or effectiveness.

### PRODUCT STATUS DEFINITIONS

### **Definition of Terms**

Datasheet Identification	Product Status	Definition
Advance Information	Formative or In Design	This datasheet contains the design specifications for product development. Specifications may change in any manner without notice.
Preliminary	First Production	This datasheet contains preliminary data; supplementary data will be published at a later date. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve design.
No Identification Needed	Full Production	This datasheet contains final specifications. Fairchild Semiconductor reserves the right to make changes at any time without notice to improve the design.
Obsolete	Not In Production	This datasheet contains specifications on a product that has been discontinued by Fairchild Semiconductor. The datasheet is printed for reference information only.

Rev. 133

<sup>\*</sup> EZSWITCH™ and FlashWriter® are trademarks of System General Corporation, used under license by Fairchild Semiconductor.

ON Semiconductor and in are trademarks of Semiconductor Components Industries, LLC dba ON Semiconductor or its subsidiaries in the United States and/or other countries. ON Semiconductor owns the rights to a number of patents, trademarks, copyrights, trade secrets, and other intellectual property. A listing of ON Semiconductor's product/patent coverage may be accessed at <a href="www.onsemi.com/site/pdt/Patent-Marking.pdf">www.onsemi.com/site/pdt/Patent-Marking.pdf</a>. ON Semiconductor reserves the right to make changes without further notice to any products herein. ON Semiconductor assume any liability arising out of the application or use of any product or circuit, and specifically disclaims any and all liability, including without limitation special, consequential or incidental damages. Buyer is responsible for its products and applications using ON Semiconductor products, including compliance with all laws, regulations and safety requirements or standards, regardless of any support or applications information provided by ON Semiconductor. "Typical" parameters which may be provided in ON Semiconductor data sheets and/or specifications can and do vary in different applications and actual performance may vary over time. All operating parameters, including "Typicals" must be validated for each customer application by customer's technical experts. ON Semiconductor does not convey any license under its patent rights nor the rights of others. ON Semiconductor products are not designed, intended, or authorized for use as a critical component in life support systems or any FDA Class 3 medical devices or medical devices with a same or similar classification in a foreign jurisdiction or any devices intended for implantation in the human body. Should Buyer purchase or use ON Semiconductor products for any such unintended or unauthorized application, Buyer shall indemnify and hold ON Semiconductor and its officers, employees, subsidiaries, affiliates, and distributors harmless against all claims, costs, damages, and exp

### **PUBLICATION ORDERING INFORMATION**

#### LITERATURE FULFILLMENT:

Literature Distribution Center for ON Semiconductor 19521 E. 32nd Pkwy, Aurora, Colorado 80011 USA Phone: 303-675-2175 or 800-344-3860 Toll Free USA/Canada Fax: 303-675-2176 or 800-344-3867 Toll Free USA/Canada Email: orderlit@onsemi.com N. American Technical Support: 800-282-9855 Toll Free USA/Canada
Europe, Middle East and Africa Technical Support:
Phone: 421 33 790 2910
Japan Customer Focus Center
Phone: 81-3-5817-1050

ON Semiconductor Website: www.onsemi.com

Order Literature: http://www.onsemi.com/orderlit

For additional information, please contact your local Sales Representative

## **Mouser Electronics**

**Authorized Distributor** 

Click to View Pricing, Inventory, Delivery & Lifecycle Information:

onsemi

FSA5157P6X FSA5157L6X